

ALFAAA14670

## Carbitol

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

<b>产品说明:</b> <b>Product Description:</b>	<b>二乙二醇单乙醚</b> <b>Carbitol</b>
<b>Cat No. :</b>	<b>A14670</b>
<b>Synonyms</b>	Diethylene glycol monoethyl ether; Carbitol®4
<b>CAS No</b>	111-90-0
<b>Molecular Formula</b>	C6 H14 O3
<b>Supplier</b>	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
<b>Emergency Telephone Number</b>	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
<b>E-mail address</b>	begel.sdsdesk@thermofisher.com
<b>Recommended Use</b>	Laboratory chemicals.
<b>Uses advised against</b>	No Information available

### SECTION 2. HAZARD IDENTIFICATION

<b>Physical State</b> Liquid	<b>Appearance</b> Colorless	<b>Odor</b> sweet
<b>Emergency Overview</b> Hygroscopic.		

#### Classification of the substance or mixture

Based on available data, the classification criteria are not met

#### Label Elements

None required

#### **Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling  
P280 - Wear eye protection/ face protection

#### **Response**

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P337 + P313 - If eye irritation persists: Get medical advice/attention

#### **Storage**

## Carbitol

P403 - Store in a well-ventilated place

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Hygroscopic.

**Health Hazards**

The product contains no substances which at their given concentration are considered to be hazardous to health.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. . Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Diethylene glycol monoethyl ether	111-90-0	98

**SECTION 4. FIRST AID MEASURES****Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Get medical attention if symptoms occur.

**Inhalation**

Remove to fresh air. Get medical attention if symptoms occur. If not breathing, give artificial respiration.

**Ingestion**

Do NOT induce vomiting. Get medical attention if symptoms occur.

**Most important symptoms and effects**

Difficulty in breathing. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

**Self-Protection of the First Aider**

No special precautions required.

**Notes to Physician**

Treat symptomatically. Symptoms may be delayed.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors. Containers may explode when heated. Keep product and empty container away from heat and sources of ignition.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## Carbitol

## SECTION 6. ACCIDENTAL RELEASE MEASURES

**Personal Precautions**

Use personal protective equipment as required. Ensure adequate ventilation. Avoid contact with skin, eyes or clothing.

**Environmental Precautions**

Avoid release to the environment. See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

## SECTION 7. HANDLING AND STORAGE

**Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid contact with skin, eyes or clothing. Avoid ingestion and inhalation.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep under nitrogen.

**Specific Use(s)**

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Control Parameters****Exposure Controls****Engineering Measures**

None under normal use conditions.

**Personal protective equipment**

**Eye Protection** Wear safety glasses with side shields (or goggles) (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Viton (R)	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** No protective equipment is needed under normal use conditions.

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits

## Carbitol

are exceeded or if irritation or other symptoms are experienced

**Recommended Filter type:** Particle filter

**Small scale/Laboratory use**

Maintain adequate ventilation

**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141

**Hygiene Measures**

Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls**

No information available.

### SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Colorless	
<b>Physical State</b>	Liquid	
<b>Odor</b>	sweet	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	-80 °C / -112 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	197 °C / 386.6 °F	@ 760 mmHg
<b>Flash Point</b>	94 °C / 201.2 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	<b>Lower</b> 1.2 vol % <b>Upper</b> 8.5 vol %	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	No data available	(Air = 1.0)
<b>Specific Gravity / Density</b>	0.990	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	Miscible	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
Diethylene glycol monoethyl ether	-0.8	
<b>Autoignition Temperature</b>	204 °C / 399.2 °F	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	No data available	
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C6 H14 O3	
<b>Molecular Weight</b>	134.17	

### SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions. Hygroscopic.
<b>Hazardous Reactions</b>	No information available.
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid</b>	Incompatible products. Excess heat. Exposure to moisture.
<b>Materials to avoid</b>	Strong oxidizing agents. Strong acids. Acid anhydrides. Acid chlorides.
<b>Hazardous Decomposition Products</b>	Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ). peroxides.

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

## (a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Diethylene glycol monoethyl ether	6031 mg/kg ( Rat )	9143 mg/kg (Rabbit) 4200 µL/kg ( Rabbit ) 6 mL/kg ( Rat )	LC50 > 5240 mg/m <sup>3</sup> ( Rat ) 4 h

(b) skin corrosion/irritation; Based on available data, the classification criteria are not met

(c) serious eye damage/irritation; Based on available data, the classification criteria are not met

## (d) respiratory or skin sensitization;

Respiratory  
Skin

Based on available data, the classification criteria are not met

Based on available data, the classification criteria are not met

(e) germ cell mutagenicity; Based on available data, the classification criteria are not met

(f) carcinogenicity; Based on available data, the classification criteria are not met

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; Based on available data, the classification criteria are not met

(h) STOT-single exposure; Based on available data, the classification criteria are not met

(i) STOT-repeated exposure; Based on available data, the classification criteria are not met

Target Organs

None known.

(j) aspiration hazard; Based on available data, the classification criteria are not met

Other Adverse Effects The toxicological properties have not been fully investigated.

Symptoms / effects, both acute and delayed Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

## SECTION 12. ECOLOGICAL INFORMATION

## Ecotoxicity effects

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Diethylene glycol monoethyl ether	LC50: 11600 - 16700 mg/L, 96h flow-through (Pimephales promelas) LC50: 11400 - 15700 mg/L, 96h flow-through (Oncorhynchus mykiss) LC50: 19100 - 23900 mg/L, 96h flow-through (Lepomis macrochirus) LC50: = 10000 mg/L, 96h static (Lepomis	EC50: 3940 - 4670 mg/L, 48h (Daphnia magna)		

## Carbitol

	macrochirus)			
--	--------------	--	--	--

**Persistence and Degradability****Persistence**

Persistence is unlikely.

**Bioaccumulative Potential**

Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Diethylene glycol monoethyl ether	-0.8	No data available

**Mobility in soil**

The product is water soluble, and may spread in water systems. Will likely be mobile in the environment due to its water solubility. Highly mobile in soils.

**Endocrine Disruptor Information**

This product does not contain any known or suspected endocrine disruptors.

**Persistent Organic Pollutant**

This product does not contain any known or suspected substance.

**Ozone Depletion Potential**

This product does not contain any known or suspected substance.

**SECTION 13. DISPOSAL CONSIDERATIONS****Waste from Residues/Unused Products**

Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

**Contaminated Packaging**

Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.

**Other Information**

Waste codes should be assigned by the user based on the application for which the product was used.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

Not Regulated

**IMDG/IMO**

Not regulated

**IATA**

Not regulated

**Special Precautions for User**

No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Diethylene glycol monoethyl ether	-	-	X	X	203-919-7	X	X	X	X	X	X	KE-10467

## Carbitol

## National Regulations

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 02-Jul-2014  
**Revision Date** 26-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Legend

<b>CAS</b> - Chemical Abstracts Service	<b>TSCA</b> - United States Toxic Substances Control Act Section 8(b) Inventory
<b>EINECS/ELINCS</b> - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances	<b>DSL/NDSL</b> - Canadian Domestic Substances List/Non-Domestic Substances List
<b>PICCS</b> - Philippines Inventory of Chemicals and Chemical Substances	<b>ENCS</b> - Japanese Existing and New Chemical Substances
<b>IECSC</b> - Chinese Inventory of Existing Chemical Substances	<b>AICS</b> - Australian Inventory of Chemical Substances
<b>KECL</b> - Korean Existing and Evaluated Chemical Substances	<b>NZIoC</b> - New Zealand Inventory of Chemicals
<b>WEL</b> - Workplace Exposure Limit	<b>TWA</b> - Time Weighted Average
<b>ACGIH</b> - American Conference of Governmental Industrial Hygienists	<b>IARC</b> - International Agency for Research on Cancer
<b>DNEL</b> - Derived No Effect Level	<b>PNEC</b> - Predicted No Effect Concentration
<b>RPE</b> - Respiratory Protective Equipment	<b>LD50</b> - Lethal Dose 50%
<b>LC50</b> - Lethal Concentration 50%	<b>EC50</b> - Effective Concentration 50%
<b>NOEC</b> - No Observed Effect Concentration	<b>POW</b> - Partition coefficient Octanol:Water
<b>PBT</b> - Persistent, Bioaccumulative, Toxic	<b>vPvB</b> - very Persistent, very Bioaccumulative
<b>ICAO/IATA</b> - International Civil Aviation Organization/International Air Transport Association	<b>IMO/IMDG</b> - International Maritime Organization/International Maritime Dangerous Goods Code
<b>ADR</b> - European Agreement Concerning the International Carriage of Dangerous Goods by Road	<b>MARPOL</b> - International Convention for the Prevention of Pollution from Ships
<b>OECD</b> - Organisation for Economic Co-operation and Development	<b>ATE</b> - Acute Toxicity Estimate
<b>BCF</b> - Bioconcentration factor	<b>VOC</b> - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>  
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**