

ALFAAA15350

## N,N-Dimethylformamide dimethyl acetal

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

**产品说明:** N,N-二甲基甲酰胺二甲基缩醛  
**Product Description:** N,N-Dimethylformamide dimethyl acetal

**Cat No. :** A15350  
**CAS No** 4637-24-5  
**Molecular Formula** (C H<sub>3</sub>)<sub>2</sub> N C H (O C H<sub>3</sub>)<sub>2</sub>

**Supplier** Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

**Emergency Telephone Number** For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

**E-mail address** begel.sdsdesk@thermofisher.com

**Recommended Use** Laboratory chemicals.  
**Uses advised against** No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Liquid

**Appearance**  
No information available

**Odor**  
No information available

#### Emergency Overview

Moisture sensitive. Highly flammable liquid and vapor. May cause an allergic skin reaction. Causes serious eye damage. Harmful if inhaled. May damage fertility or the unborn child.

#### Classification of the substance or mixture

Flammable liquids.	Category 2
Acute Inhalation Toxicity - Vapors	Category 4
Serious Eye Damage/Eye Irritation	Category 1
Skin Sensitization	Category 1
Reproductive Toxicity	Category 1B

#### Label Elements



**Signal Word****Danger****Hazard Statements**

H225 - Highly flammable liquid and vapor  
 H317 - May cause an allergic skin reaction  
 H318 - Causes serious eye damage  
 H332 - Harmful if inhaled  
 H360 - May damage fertility or the unborn child

**Precautionary Statements****Prevention**

P201 - Obtain special instructions before use  
 P202 - Do not handle until all safety precautions have been read and understood  
 P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
 P233 - Keep container tightly closed  
 P240 - Ground and bond container and receiving equipment  
 P242 - Use non-sparking tools  
 P243 - Take action to prevent static discharges  
 P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
 P271 - Use only outdoors or in a well-ventilated area  
 P272 - Contaminated work clothing should not be allowed out of the workplace  
 P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower  
 P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
 P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
 P310 - Immediately call a POISON CENTER or doctor  
 P363 - Wash contaminated clothing before reuse  
 P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish

**Storage**

P403 + P235 - Store in a well-ventilated place. Keep cool

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Highly flammable. Vapors may cause flash fire or explosion.

**Health Hazards**

May cause an allergic skin reaction. Harmful if inhaled. May damage fertility or the unborn child.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Other Hazards**

This product does not contain any known or suspected endocrine disruptors. Toxic to terrestrial vertebrates.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Methanamine, 1,1-dimethoxy-N,N-dimethyl-	4637-24-5	99.8
Dimethylformamide	68-12-2	0.2

**SECTION 4. FIRST AID MEASURES**
**General Advice**

If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water.

**Most important symptoms and effects**

None reasonably foreseeable. Causes severe eye damage. May cause allergic skin reaction. Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Flammable. Containers may explode when heated. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Remove all sources of ignition. Take precautionary measures against static discharges.

**Environmental Precautions**

Should not be released into the environment.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

# SAFETY DATA SHEET

## N,N-Dimethylformamide dimethyl acetal

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Take precautionary measures against static discharges.

### Storage

Keep under nitrogen. Keep container tightly closed in a dry and well-ventilated place. Keep away from heat, sparks and flame.

### Specific Use(s)

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control Parameters

Component	China	Taiwan	Thailand	Hong Kong
Dimethylformamide	TWA: 20 mg/m <sup>3</sup> Skin	TWA: 10 ppm TWA: 30 mg/m <sup>3</sup>	TWA: 10 ppm	TWA: 10 ppm TWA: 30 mg/m <sup>3</sup>

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Dimethylformamide	TWA: 5 ppm Skin	(Vacated) TWA: 10 ppm (Vacated) TWA: 30 mg/m <sup>3</sup> Skin TWA: 10 ppm TWA: 30 mg/m <sup>3</sup>	IDLH: 500 ppm REL = 10 ppm (TWA) REL = 30 mg/m <sup>3</sup> (TWA)	STEL: 10 ppm 15 min STEL: 30 mg/m <sup>3</sup> 15 min TWA: 5 ppm 8 hr TWA: 15 mg/m <sup>3</sup> 8 hr Skin	TWA: 15 mg/m <sup>3</sup> (8h) TWA: 5 ppm (8h) Skin STEL: 10 ppm (15min) STEL: 30 mg/m <sup>3</sup> (15min) STEL: 30 mg/m <sup>3</sup> (8h) STEL: 10 ppm (8h)

### Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

### Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

### Exposure Controls

### Engineering Measures

Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Use explosion-proof electrical/ventilating/lighting equipment. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

### Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Neoprene				
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

# SAFETY DATA SHEET

## N,N-Dimethylformamide dimethyl acetal

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

<b>Skin and body protection</b>	Long sleeved clothing
<b>Respiratory Protection</b>	When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly
<b>Large scale/emergency use</b>	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced <b>Recommended Filter type:</b> Organic gases and vapours filter Type A Brown conforming to EN14387
<b>Small scale/Laboratory use</b>	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. <b>Recommended half mask:-</b> Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141 When RPE is used a face piece Fit Test should be conducted
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.
<b>Environmental exposure controls</b>	No information available.

### SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>		
<b>Physical State</b>	Liquid	
<b>Odor</b>	No information available	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	Not applicable	
<b>Melting Point/Range</b>	-85 °C / -121 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	102 - 104 °C / 215.6 - 219.2 °F	
<b>Flash Point</b>	7 °C / 44.6 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	No data available	(Air = 1.0)
<b>Specific Gravity / Density</b>	0.897	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	No information available	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
Dimethylformamide	-1.028	
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	No data available	
<b>Explosive Properties</b>		Vapors may form explosive mixtures with air
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	(C H <sub>3</sub> ) <sub>2</sub> N C H (O C H <sub>3</sub> ) <sub>2</sub>	
<b>Molecular Weight</b>	119.16	

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Moisture sensitive.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	Keep away from open flames, hot surfaces and sources of ignition.
<b>Materials to avoid</b>	No information available.

**Hazardous Decomposition Products** Carbon oxides. Nitrogen oxides (NOx).

## SECTION 11. TOXICOLOGICAL INFORMATION

### Product Information

**(a) acute toxicity;**

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Methanamine, 1,1-dimethoxy-N,N-dimethyl-			LC50 = 12.16 mg/L ( Rat ) 4 h
Dimethylformamide	3040 mg/kg ( Rat ) OECD 401	LD50 = 1100 mg/kg ( Rat )	>5.58 mg/L/4h (Rat) OECD 403

**(b) skin corrosion/irritation;** Based on available data, the classification criteria are not met

**(c) serious eye damage/irritation;** Category 1 Based on available data, the classification criteria are not met

**(d) respiratory or skin sensitization;**

**Respiratory**  
**Skin**

Based on available data, the classification criteria are not met  
Category 1  
Based on available data, the classification criteria are not met

Component	Test method	Test species	Study result
Dimethylformamide 68-12-2 ( 0.2 )	Guinea Pig Maximisation Test (GPMT)	guinea pig	- non-sensitising

May cause sensitization by skin contact

**(e) germ cell mutagenicity;** Based on available data, the classification criteria are not met

**(f) carcinogenicity;** Based on available data, the classification criteria are not met

The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	EU	UK	Germany	IARC
Dimethylformamide				Group 2A

**(g) reproductive toxicity;** Based on available data, the classification criteria are not met

**(h) STOT-single exposure;** Based on available data, the classification criteria are not met

**(i) STOT-repeated exposure;** Based on available data, the classification criteria are not met

# SAFETY DATA SHEET

## N,N-Dimethylformamide dimethyl acetal

**Target Organs** None known.

**(j) aspiration hazard;** Based on available data, the classification criteria are not met

**Symptoms / effects, both acute and delayed** Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

### SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects** .

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Dimethylformamide	LC50 = 7100 mg/l (96h) Lepomis macrochirus	EC50 = 7500 mg/L/48h	EC50 > 1000 mg/L/72h Desmodesmus subspicatus	EC50 = 2000 mg/L 5 min EC50 = 570 mg/L 240 h

**Persistence and Degradability** No information available

Component	Degradability
Dimethylformamide 68-12-2 ( 0.2 )	100 % (OECD 301E (21d))

**Bioaccumulative Potential** No information available

Component	log Pow	Bioconcentration factor (BCF)
Methanamine, 1,1-dimethoxy-N,N-dimethyl-		0.3 - 1.2 L/kg
Dimethylformamide	-1.028	0.3 - 1.2 L/kg

**Mobility in soil** No information available

**Endocrine Disruptor Information**

Component	EU - Endocrine Disruptors Candidate List	EU - Endocrine Disruptors - Evaluated Substances	Japan - Endocrine Disruptor Information
Dimethylformamide	Group III Chemical		

**Persistent Organic Pollutant** This product does not contain any known or suspected substance

**Ozone Depletion Potential** This product does not contain any known or suspected substance

### SECTION 13. DISPOSAL CONSIDERATIONS

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

**Other Information** Waste codes should be assigned by the user based on the application for which the product was used. Do not flush to sewer. Can be landfilled or incinerated, when in compliance with local regulations. Do not empty into drains.

### SECTION 14. TRANSPORT INFORMATION

**Road and Rail Transport**

**UN-No** UN1993  
**Proper Shipping Name** FLAMMABLE LIQUID, N.O.S.

# SAFETY DATA SHEET

## N,N-Dimethylformamide dimethyl acetal

**Technical Shipping Name** N,N-Dimethylformamide dimethyl acetal  
**Hazard Class** 3  
**Packing Group** II

### IMDG/IMO

**UN-No** UN1993  
**Proper Shipping Name** FLAMMABLE LIQUID, N.O.S.  
**Technical Shipping Name** N,N-Dimethylformamide dimethyl acetal  
**Hazard Class** 3  
**Packing Group** II

### IATA

**UN-No** UN1993  
**Proper Shipping Name** FLAMMABLE LIQUID, N.O.S.  
**Technical Shipping Name** N,N-Dimethylformamide dimethyl acetal  
**Hazard Class** 3  
**Packing Group** II

**Special Precautions for User** No special precautions required

## SECTION 15. REGULATORY INFORMATION

### International Inventories

China, X = listed, Australia, U.S.A. (TSCA), Canada (DSL/NDSL), Europe (EINECS/ELINCS/NLP), Australia (AICS), Korea (KECL), China (IECSC), Japan (ENCS), Philippines (PICCS), Taiwan (TCSI), Japan (ISHL), New Zealand (NZIoC), Japan (ISHL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Methanamine, 1,1-dimethoxy-N,N-dimethyl-	-	-	X	X	225-063-3	X	X	X	X	X	X	KE-11054
Dimethylformamide	X	X	X	X	200-679-5	X	X	X	X	X	X	KE-11411

### National Regulations

Component	Toxic Chemical Substances Control Act
Dimethylformamide 68-12-2 ( 0.2 )	Class II (30 wt%) TRQ = 50 kg

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 19-Dec-2024  
**Revision Date** 01-Nov-2025  
**Revision Summary** Initial Release.

### Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit

# SAFETY DATA SHEET

## N,N-Dimethylformamide dimethyl acetal

and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

### Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

### **Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

### **Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**