

Classified as hazardous in accordance with the criteria of EPA New Zealand

## Section 1 - Identification

### Product Identifier

<b>Product Name</b>	<u>Phenolphthalein</u>
<b>CAS No</b>	77-09-8
<b>Synonyms</b>	3,3-Bis(4-Hydroxyphenyl)-1(3H)-Isobenzofuranone; 3,3-Bis(p-Hydroxyphenyl)Phthalide
<b>Molecular Formula</b>	C20 H14 O4
<b>Molecular Weight</b>	318.32
<b>Recommended Use</b>	Laboratory chemicals.
<b>Uses advised against</b>	No Information available

<b>Product Code</b>	<b>A17135</b>
<b>Address</b>	Thermo Fisher Scientific New Zealand Ltd 244 Bush Road, Albany, Auckland, New Zealand
<b>Emergency Tel.</b>	<b>CHEMTREC®</b> <b>09 980 6780 or +64 9 980 6780</b>
<b>Telephone / Fax Numbers</b>	Tel: 09 980 6700 Fax: 09 980 6788
<b>E-mail address</b>	<a href="mailto:ANZinfo@thermofisher.com">ANZinfo@thermofisher.com</a>

## Section 2 - Hazard(s) Identification

### Classification under Work Safe New Zealand

Classified as hazardous in accordance with the criteria of EPA New Zealand

**HSNO Approval Number**      **HSR002512**

### GHS Classification

#### Physical hazards

Based on available data, the classification criteria are not met

#### Health hazards

Germ Cell Mutagenicity	Category 2
Carcinogenicity	Category 1B
Reproductive Toxicity	Category 2

#### Environmental hazards

Based on available data, the classification criteria are not met

### Label Elements



**Signal Word****Danger****Hazard Statements**

H341 - Suspected of causing genetic defects if inhaled

H350 - May cause cancer

H361 - Suspected of damaging fertility or the unborn child

**Precautionary Statements****Prevention**

P201 - Obtain special instructions before use

P202 - Do not handle until all safety precautions have been read and understood

P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P308 + P313 - IF exposed or concerned: Get medical advice/attention

**Storage**

P403 - Store in a well-ventilated place

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Other hazards which do not result in classification**

No information available

## Section 3 - Composition and Information on Ingredients

Component	CAS No	Weight %
Phenolphthalein	77-09-8	<=100

## Section 4 - First Aid Measures

**Description of first aid measures****General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**New Zealand Emergency Tel.**CHEMTREC®  
09 980 6780 or +64 9 980 6780**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

**Ingestion**

Do NOT induce vomiting. Call a physician or poison control center immediately.



<b>Self-Protection of the First Aider</b>	Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.
<b>First Aid Facilities</b>	Eyewash, safety shower and washroom.
<b>Most important symptoms and effects</b>	None reasonably foreseeable.
<b>Notes to Physician</b>	Treat symptomatically.

## **Section 5 - Fire Fighting Measures**

### **Suitable Extinguishing Media**

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam.

### **Extinguishing media which must not be used for safety reasons**

No information available.

### **Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

### **Hazardous Combustion Products**

Carbon monoxide (CO), Carbon dioxide (CO<sub>2</sub>).

### **Special protective equipment and precautions for fire fighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

## **Section 6 - Accidental Release Measures**

### **Personal Precautions, Protective Equipment and Emergency Procedures**

#### **Emergency procedures**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas.

#### **Environmental Precautions**

Should not be released into the environment.

#### **Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

#### **Precautions to prevent secondary hazards**

Clean contaminated objects and areas thoroughly observing environmental regulations

#### **Reference to Other Sections**

Refer to protective measures listed in Sections 8 and 13.

## **Section 7 - Handling and Storage**

### **Precautions for Safe Handling**

#### **Advice on safe handling**

Wear personal protective equipment/face protection. Avoid dust formation. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe (dust, vapor, mist, gas). Do not ingest. If swallowed then seek immediate medical assistance.

#### **Hygiene Measures**

Handle in accordance with good industrial hygiene and safety practice. Keep away from food, drink and animal feeding stuffs. Do



not eat, drink or smoke when using this product. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Wash hands before breaks and after work.

#### **Conditions for Safe Storage, Including any Incompatibilities**

##### **Storage Conditions**

Keep containers tightly closed in a dry, cool and well-ventilated place.

##### **Incompatible Materials**

Oxidizing agent.

AS/NZS 2243.10:2004, Safety in laboratories - Storage of chemicals

## **Section 8 - Exposure Controls and Personal Protection**

#### **Control parameters**

##### **Exposure limits**

The product does not contain any hazardous materials with occupational exposure limits established.

##### **Biological limit values**

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

#### **Appropriate engineering controls**

##### **Engineering Measures**

Use only under a chemical fume hood. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source

#### **Individual protection measures, such as personal protective equipment**

##### **Eye Protection**

Wear safety glasses with side shields (or goggles) (Australian/New Zealand Standard AS/NZS 1337 - Eye protectors for Industrial applications)

##### **Hand Protection**

Protective gloves

<b>Glove material</b>	<b>Breakthrough time</b>	<b>Glove thickness</b>	<b>AUS/NZ Standard</b>	<b>Glove comments</b>
Nitrile rubber, Neoprene, Natural rubber, PVC.	See manufacturers recommendations	-	AS/NZS 2161	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

##### **Skin and body protection**

Wear appropriate protective gloves and clothing to prevent skin exposure

##### **Respiratory Protection**

Use an AS/NZS 1716 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained in line with AS/NZS 1715 on the use and maintenance of respiratory protective devices

##### **Recommended Filter type: Recommended half mask:-**

Particulates filter conforming to EN 143 (or AUS/NZ equivalent)  
Particle filtering: EN149:2001 (or AUS/NZ equivalent)  
When RPE is used a face piece Fit Test should be conducted

##### **Hygiene Measures**

Handle in accordance with good industrial hygiene and safety practice.



**Environmental exposure controls** No information available.

## Section 9 - Physical and Chemical Properties

### Information on basic physical and chemical properties

<b>Physical State</b>	Solid	
<b>Appearance</b>	Off-white	
<b>Odor</b>	Odorless	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	260 - 263 °C / 500 - 505.4 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	450 °C / 842 °F	
<b>Flammability (liquid)</b>	Not applicable	Solid
<b>Flammability (solid,gas)</b>	No information available	
<b>Explosion Limits</b>	No data available	
<b>Flash Point</b>	No information available	<b>Method -</b> No information available
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	Not applicable	Solid
<b>Water Solubility</b>	3.36mg/L	practically insoluble
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
Phenolphthalein	2.41	
<b>Vapor Pressure</b>	negligible	
<b>Density / Specific Gravity</b>	No data available	
<b>Bulk Density</b>	No data available	
<b>Vapor Density</b>	Not applicable	Solid
<b>Particle characteristics</b>	No data available	

### Other information

<b>Molecular Formula</b>	C20 H14 O4
<b>Molecular Weight</b>	318.32
<b>Evaporation Rate</b>	Not applicable - Solid

## Section 10 - Stability and Reactivity

<b>Reactivity</b>	None known, based on information available
<b>Stability</b>	No information available.
<b>Sensitivity to Mechanical Impact</b>	No information available
<b>Sensitivity to Static Discharge</b>	No information available
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Conditions to Avoid</b>	Incompatible products, Excess heat, Avoid dust formation.
<b>Incompatible Materials</b>	Oxidizing agent.
<b>Hazardous Decomposition Products</b>	Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ).



## Section 11 - Toxicological Information

### Acute Effects

#### Information on likely routes of exposure

<b>Product Information</b>	See actual entry in RTECS for complete information.
<b>Inhalation</b>	Not an expected route of exposure.
<b>Eyes</b>	Avoid contact with eyes.
<b>Skin</b>	Avoid contact with skin.
<b>Ingestion</b>	May be harmful if swallowed.

#### Numerical measures of toxicity

<b>(a) acute toxicity;</b>	
<b>Oral</b>	Based on available data, the classification criteria are not met
<b>Dermal</b>	Based on available data, the classification criteria are not met
<b>Inhalation</b>	Based on available data, the classification criteria are not met

<b>(b) skin corrosion/irritation;</b>	Based on available data, the classification criteria are not met
---------------------------------------	--

<b>(c) serious eye damage/irritation;</b>	Based on available data, the classification criteria are not met
---	--

<b>(d) respiratory or skin sensitization;</b>	
<b>Respiratory</b>	Based on available data, the classification criteria are not met
<b>Skin</b>	Based on available data, the classification criteria are not met

<b>(e) germ cell mutagenicity;</b>	Category 2
	Mutagenic effects have occurred in humans

<b>(f) carcinogenicity;</b>	Category 1B
	The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	New Zealand	Australia	New South Wales	Western Australia	IARC	EU	UK	Germany
Phenolphthalein					Group 2B	Carc Cat. 1B		

<b>(g) reproductive toxicity;</b>	Category 2
<b>Reproductive Effects</b>	Experiments have shown reproductive toxicity effects on laboratory animals
<b>Developmental Effects</b>	Possible risk of harm to the unborn child

<b>(h) STOT-single exposure;</b>	Based on available data, the classification criteria are not met
----------------------------------	--

<b>(i) STOT-repeated exposure;</b>	Based on available data, the classification criteria are not met
<b>Target Organs</b>	None known.

<b>(j) aspiration hazard;</b>	Not applicable
	Solid

Symptoms / effects, both acute and delayed



No information available.

## Section 12 - Ecological Information

### Ecotoxicity

**Aquatic ecotoxicity** Do not empty into drains.

**Terrestrial ecotoxicity** There is no data for this product

### Persistence and Degradability

**Persistence** Persistence is unlikely.

**Bioaccumulative Potential** Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Phenolphthalein	2.41	No data available

**Mobility** Spillage unlikely to penetrate soil. Is not likely mobile in the environment due its low water solubility.

### Other adverse effects

### Endocrine Disruptor Information

Component	EU - Endocrine Disruptors Candidate List	EU - Endocrine Disruptors - Evaluated Substances	Japan - Endocrine Disruptor Information
Phenolphthalein	Group III Chemical		

**Persistent Organic Pollutant** This product does not contain any known or suspected substance

**Ozone Depletion Potential** This product does not contain any known or suspected substance

## Section 13 - Disposal Considerations

### Waste treatment methods

**Waste from Residues/Unused Products** Do not allow into drains or watercourses or dispose of where ground or surface waters may be affected. Wastes, including emptied containers, are controlled wastes and should be disposed of in accordance with all federal, E.P.A., state and local regulations. Assure conformity with all applicable regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point.

**Other Information** Disposal agencies or waste contractors must comply with the New Zealand Hazardous Substances (Disposal) Regulations . Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

## Section 14 - Transport Information

**NZS 5433:2020** Not regulated

**IATA** Not regulated



<b>IMDG/IMO</b>	Not regulated
<b>Environmental hazards</b>	No hazards identified
<b>Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code</b>	Not applicable, packaged goods
<b>Special Precautions</b>	No special precautions required. Please refer to the applicable dangerous goods regulations for additional information.
<b>Additional information</b>	None known

## Section 15 - Regulatory Information

### Safety, health and environmental regulations/legislation specific for the substance or mixture

<b>HSNO Approval Number</b>	HSR002512
-----------------------------	-----------

#### **National Regulations**

There are no applicable tolerable exposure limits or environmental exposure limits according to the EPA Controls for Hazardous Substances

#### **Certified handlers, tracking and controlled substance license requirements**

Certified handlers are required for some substances. This includes substances requiring a controlled substance license, and most explosives, vertebrates toxic agents, and certain fumigants. Acutely toxic substances which are a Category 1 or 2, such as pesticides also require Certified handlers. Please check the Health and Safety at Work Act 2015 for further information. Tracking is required for some highly hazardous substances. These substances need to be under the control of an appropriately trained person or appropriately secured. Please check the Health and Safety at Work Act 2015 for further information.

#### **Prohibition or notification/licensing requirements**

Shown below are details of specific prohibition/notifications or licencing requirements when they apply.

### International Regulations

**Ozone Depletion Potential** This product does not contain any known or suspected substance

**Persistent Organic Pollutant** This product does not contain any known or suspected substance

**Rotterdam Convention (PIC)** Not applicable

#### **Authorisation/Restrictions according to EU REACH**

Component	REACH (1907/2006) - Annex XIV - Substances Subject to Authorization	REACH (1907/2006) - Annex XVII - Restrictions on Certain Dangerous Substances	REACH Regulation (EC 1907/2006) article 59 - Candidate List of Substances of Very High Concern (SVHC)
Phenolphthalein	-	Use restricted. See item 28. (see link for restriction details) Use restricted. See item 75. (see link for restriction details)	SVHC Candidate list - Carcinogenic (Article 57a)

After the sunset date the use of this substance requires either an authorization or can only be used for exempted uses, e.g. use in scientific research and development which includes routine analytics or use as intermediate.

<https://echa.europa.eu/authorisation-list>

<https://echa.europa.eu/substances-restricted-under-reach>

<https://echa.europa.eu/candidate-list-table>



**International Inventories**

New Zealand (NZIoC), Australia (AICS), Europe (EINECS/ELINCS/NLP), Korea (KECL), China (IECSC), Taiwan (TCSI), Japan (ENCS), Japan (ISHL), Canada (DSL/NDSL), Philippines (PICCS). US EPA (TSCA) - Toxic Substances Control Act, (40 CFR Part 710)

Component	CAS No	NZIoC	AICS	EINECS	ELINCS	NLP	KECL	IECSC	TCSI
Phenolphthalein	77-09-8	X	X	-	-	-	KE-03234	X	X

Component	CAS No	TSCA	TSCA Inventory notification - Active-Inactive	DSL	NDSL	PICCS	ISHL	ENCS
Phenolphthalein	77-09-8	X	ACTIVE	X	-	X	X	X

**Legend:** X - Listed '-' - Not Listed

**KECL** - NIER number or KE number (<http://ncis.nier.go.kr/en/main.do>)

**Section 16 - Other Information**

**This safety data sheet complies with the requirements of the EPA Hazardous Substances (Hazard Classification) Notice 2020 and WorkSafe New Zealand Regulations**

**Legend**

**NZIoC** - New Zealand Inventory of Chemicals

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**IECSC** - Chinese Inventory of Existing Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**NZS 5433:2020** - Transport of Dangerous Goods on Land

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**WEL** - Workplace Exposure Limit

**DNEL** - Derived No Effect Level

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**VOC** - (Volatile Organic Compound)

**AICS** - Australian Inventory of Chemical Substances

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**ENCS** - Japanese Existing and New Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**CAS** - Chemical Abstracts Service

**ACGIH** - American Conference of Governmental Industrial Hygienists

**PNEC** - Predicted No Effect Concentration

**OECD** - Organisation for Economic Co-operation and Development

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**ADG** - Australian Code for the Transport of Dangerous Goods by Road and Rail

**LC50** - Lethal Concentration 50%

**ATE** - Acute Toxicity Estimate

**RPE** - Respiratory Protective Equipment

**NOEC** - No Observed Effect Concentration

**BCF** - Bioconcentration factor

**PBT** - Persistent, Bioaccumulative, Toxic

**Key literature references and sources for data**

HSNO classifications provided in the New Zealand Chemical Classification Information Database (CCID).

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

EPA Guide to classifying hazardous substances in New Zealand

EPA - Assigning a product to an existing HSNO approval guide

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

**Revision Date**

16-Mar-2023

**Revision Summary**

SDS sections updated

**Disclaimer**



---

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**