

Creation Date 23-Sep-2009

Revision Date 29-Jan-2021

Revision Number 3

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product Description:	Oleic acid
Cat No. :	A16663
Synonyms	cis-9-Octadecenoic acid
CAS-No	112-80-1
EC-No.	204-007-1
Molecular Formula	C18 H34 O2
Reach Registration Number	-

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

1.3. Details of the supplier of the safety data sheet

Company	Alfa Aesar Avocado Research Chemicals, Ltd. Shore Road Port of Heysham Industrial Park Heysham, Lancashire LA3 2XY United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
E-mail address	uktech@alfa.com www.alfa.com Product Safety Department

1.4. Emergency telephone number

Call Carechem 24 at
+44 (0) 1865 407333 (English only);
+44 (0) 1235 239670 (Multi-language)

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

CLP Classification - Regulation (EC) No 1272/2008

Not hazardous

Physical hazards

Based on available data, the classification criteria are not met

SAFETY DATA SHEET

Oleic acid

Revision Date 29-Jan-2021

Health hazards

Based on available data, the classification criteria are not met

Environmental hazards

Based on available data, the classification criteria are not met

Full text of Hazard Statements: see section 16

2.2. Label elements

None required

2.3. Other hazards

No information available

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1. Substances

Component	CAS-No	EC-No.	Weight %	CLP Classification - Regulation (EC) No 1272/2008
Oleic acid	112-80-1	EEC No. 204-007-1	>95	-

Reach Registration Number

-

Full text of Hazard Statements: see section 16

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

General Advice	If symptoms persist, call a physician.
Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Skin Contact	Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.
Ingestion	Clean mouth with water and drink afterwards plenty of water.
Inhalation	Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.
Self-Protection of the First Aider	No special precautions required.

4.2. Most important symptoms and effects, both acute and delayed

ALFAAA16663

SAFETY DATA SHEET

Oleic acid

Revision Date 29-Jan-2021

None reasonably foreseeable.

4.3. Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Suitable Extinguishing Media

Water spray, carbon dioxide (CO₂), dry chemical, alcohol-resistant foam.

Extinguishing media which must not be used for safety reasons

No information available.

5.2. Special hazards arising from the substance or mixture

Thermal decomposition can lead to release of irritating gases and vapors. Keep product and empty container away from heat and sources of ignition.

Hazardous Combustion Products

Carbon monoxide (CO), Carbon dioxide (CO₂).

5.3. Advice for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Use personal protective equipment as required. Ensure adequate ventilation.

6.2. Environmental precautions

Should not be released into the environment.

6.3. Methods and material for containment and cleaning up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal.

6.4. Reference to other sections

Refer to protective measures listed in Sections 8 and 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid ingestion and inhalation. Do not get in eyes, on skin, or on clothing.

Hygiene Measures

ALFAAA16663

SAFETY DATA SHEET

Oleic acid

Revision Date 29-Jan-2021

Handle in accordance with good industrial hygiene and safety practice. Keep away from food, drink and animal feeding stuffs. Do not eat, drink or smoke when using this product. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Wash hands before breaks and after work.

7.2. Conditions for safe storage, including any incompatibilities

Keep container tightly closed in a dry and well-ventilated place. Store under an inert atmosphere. To maintain product quality: Store in freezer.

Technical Rules for Hazardous Substances (TRGS) 510 Storage Class (LGK)
(Germany)

Class 10

7.3. Specific end use(s)

Use in laboratories

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Exposure limits

List source(s):

Biological limit values

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents.

Derived No Effect Level (DNEL) No information available

<u>Route of exposure</u>	<u>Acute effects (local)</u>	<u>Acute effects (systemic)</u>	<u>Chronic effects (local)</u>	<u>Chronic effects (systemic)</u>
Oral Dermal Inhalation				

Predicted No Effect Concentration (PNEC) No information available.

8.2. Exposure controls

Engineering Measures

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location.

Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source

Personal protective equipment

Eye Protection

Goggles (European standard - EN 166)

Hand Protection

Protective gloves

SAFETY DATA SHEET

Oleic acid

Revision Date 29-Jan-2021

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Butyl rubber	See manufacturers	-	EN 374	(minimum requirement)
Natural rubber	recommendations			
Nitrile rubber				
Neoprene				
PVC				

Skin and body protection

Long sleeved clothing

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Respiratory Protection

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Recommended Filter type: Particulates filter conforming to EN 143 or Acid gases filter Type E Yellow conforming to EN14387

Small scale/Laboratory use

Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141

When RPE is used a face piece Fit Test should be conducted

Environmental exposure controls

No information available.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical State	Liquid	
Appearance	Colorless	
Odor	fatty odor	
Odor Threshold	No data available	
Melting Point/Range	13 °C / 55.4 °F	
Softening Point	No data available	
Boiling Point/Range	360 °C / 680 °F	@ 760 mmHg
Flammability (liquid)	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Flash Point	189 °C / 372.2 °F	Method - No information available
Autoignition Temperature	363 °C / 685.4 °F	
Decomposition Temperature	> 80°C	
pH	No information available	
Viscosity	39.1 mPa.s at 20 °C	
Water Solubility	Insoluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
Oleic acid	7.73	

SAFETY DATA SHEET

Oleic acid

Revision Date 29-Jan-2021

Vapor Pressure	1 mmHg @ 176 °C	
Density / Specific Gravity	0.890	
Bulk Density	Not applicable	Liquid
Vapor Density	9.7	(Air = 1.0)
Particle characteristics	(liquid) Not applicable	

9.2. Other information

Molecular Formula	C18 H34 O2
Molecular Weight	282.46

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

None known, based on information available

10.2. Chemical stability

Air sensitive.

10.3. Possibility of hazardous reactions

Hazardous Polymerization	Hazardous polymerization does not occur.
Hazardous Reactions	None under normal processing.

10.4. Conditions to avoid

Incompatible products. Excess heat. Exposure to light. Exposure to air.

10.5. Incompatible materials

Strong oxidizing agents.

10.6. Hazardous decomposition products

Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Product Information

(a) acute toxicity;

Oral	Based on available data, the classification criteria are not met
Dermal	No data available
Inhalation	No data available

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Oleic acid	LD50 = 25 g/kg (Rat)	-	-

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;

Respiratory	No data available
-------------	-------------------

SAFETY DATA SHEET

Oleic acid

Revision Date 29-Jan-2021

Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available The table below indicates whether each agency has listed any ingredient as a carcinogen
(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	No data available
Other Adverse Effects	The toxicological properties have not been fully investigated.
Symptoms / effects, both acute and delayed	No information available.

11.2. Information on other hazards

Endocrine Disrupting Properties Assess endocrine disrupting properties for human health. This product does not contain any known or suspected endocrine disruptors.

SECTION 12: ECOLOGICAL INFORMATION

12.1. Toxicity Ecotoxicity effects

Component	Freshwater Fish	Water Flea	Freshwater Algae
Oleic acid	LC50: = 205 mg/L, 96h static (Pimephales promelas)		

12.2. Persistence and degradability

Persistence May persist.

12.3. Bioaccumulative potential Product has a high potential to bioconcentrate

Component	log Pow	Bioconcentration factor (BCF)
Oleic acid	7.73	44000

12.4. Mobility in soil

Hydrolyses Spillage unlikely to penetrate soil The product is insoluble and floats on water . Is not likely mobile in the environment due its low water solubility. Is not likely mobile in the environment due its low water solubility and propensity to bind to soil particles

SAFETY DATA SHEET

Oleic acid

Revision Date 29-Jan-2021

12.5. Results of PBT and vPvB assessment

No data available for assessment.

12.6. Endocrine disrupting properties

Endocrine Disruptor Information

This product does not contain any known or suspected endocrine disruptors

12.7. Other adverse effects

Persistent Organic Pollutant

This product does not contain any known or suspected substance

Ozone Depletion Potential

This product does not contain any known or suspected substance

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Waste from Residues/Unused Products

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging

Dispose of this container to hazardous or special waste collection point.

European Waste Catalogue (EWC)

According to the European Waste Catalog, Waste Codes are not product specific, but application specific.

Other Information

Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

SECTION 14: TRANSPORT INFORMATION

IMDG/IMO

Not regulated

14.1. UN number

14.2. UN proper shipping name

14.3. Transport hazard class(es)

14.4. Packing group

ADR

Not regulated

14.1. UN number

14.2. UN proper shipping name

14.3. Transport hazard class(es)

14.4. Packing group

IATA

Not regulated

14.1. UN number

14.2. UN proper shipping name

14.3. Transport hazard class(es)

14.4. Packing group

14.5. Environmental hazards

No hazards identified

14.6. Special precautions for user

No special precautions required

14.7. Maritime transport in bulk according to IMO instruments

Not applicable, packaged goods

SECTION 15: REGULATORY INFORMATION

SAFETY DATA SHEET

Oleic acid

Revision Date 29-Jan-2021

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

International Inventories

X = listed, Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), China (IECSC), Japan (ENCS), Australia (AICS), Korea (ECL).

Component	EINECS	ELINCS	NLP	TSCA	DSL	NDSL	PICCS	ENCS	IECSC	AICS	KECL
Oleic acid	204-007-1	-		X	X	-	X	X	X	X	KE-2645 0

Regulation (EC) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of dangerous chemicals

Not applicable

National Regulations

WGK Classification See table for values

Component	Germany - Water Classification (VwVwS)	Germany - TA-Luft Class
Oleic acid	WGK1	

UK - Take note of Control of Substances Hazardous to Health Regulations (COSHH) 2002 and 2005 Amendment

15.2. Chemical safety assessment

A Chemical Safety Assessment/Report (CSA/CSR) has not been conducted

SECTION 16: OTHER INFORMATION

Full text of H-Statements referred to under sections 2 and 3

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer
Predicted No Effect Concentration (PNEC)

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC (volatile organic compound)

SAFETY DATA SHEET

Oleic acid

Revision Date 29-Jan-2021

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Chemical incident response training.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Prepared By

Health, Safety and Environmental Department

Creation Date

23-Sep-2009

Revision Date

29-Jan-2021

Revision Summary

SDS authoring systems update, replaces ChemGes SDS No. 112-80-1/2.

**This safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006
COMMISSION REGULATION (EU) 2020/878 amending Annex II to Regulation (EC) No
1907/2006**

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet