

ALFAAA17629

Sodium thiosulphate, anhydrous

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: Product Description:	无水硫代硫酸钠 Sodium thiosulphate, anhydrous
Cat No. :	A17629
Synonyms	Thiosulfuric Acid Disodium Salt; Sodium Oxide Sulfide; Sodium Hyposulfite
CAS No	7772-98-7
Molecular Formula	Na ₂ O ₃ S ₂
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information US call: 001-800-227-6701 / Europe call: +32 14 57 52 11 Emergency Number US :001-201-796-7100 / Europe : +32 14 57 52 99 CHEMTREC Tel. No. US :001-800-424-9300 / Europe :001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State Solid	Appearance White	Odor Odorless
Emergency Overview Hygroscopic.		

Classification of the substance or mixture

Based on available data, the classification criteria are not met

Label Elements

None required

Storage

P403 - Store in a well-ventilated place

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Hygroscopic.

Health Hazards

Sodium thiosulphate, anhydrous

The product contains no substances which at their given concentration are considered to be hazardous to health.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. . Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Sodium thiosulfate	7772-98-7	<=100

SECTION 4. FIRST AID MEASURES**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Get medical attention immediately if symptoms occur.

Inhalation

Remove to fresh air. Get medical attention immediately if symptoms occur. If not breathing, give artificial respiration.

Ingestion

Do NOT induce vomiting. Get medical attention.

Most important symptoms and effects

No information available.

Self-Protection of the First Aider

No special precautions required.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE

Handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid contact with skin, eyes or clothing. Avoid ingestion and inhalation. Avoid dust formation.

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls

Engineering Measures

None under normal use conditions.

Personal protective equipment

Eye Protection Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection No protective equipment is needed under normal use conditions.

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits

Sodium thiosulphate, anhydrous

are exceeded or if irritation or other symptoms are experienced

Recommended Filter type: Particle filter

Small scale/Laboratory use Maintain adequate ventilation

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	White	
Physical State	Solid	
Odor	Odorless	
Odor Threshold	No data available	
pH	6.0-8.5	5% aq. sol. 20°C
Melting Point/Range	> 100 °C	
Softening Point	No data available	
Boiling Point/Range	No data available	
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	negligible	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	700 g/L @ 20°C	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
Sodium thiosulfate	-4.35	
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	Na ₂ O ₃ S ₂	
Molecular Weight	158.1	

SECTION 10. STABILITY AND REACTIVITY

Stability	Hygroscopic.
Hazardous Reactions	No information available.
Hazardous Polymerization	No information available.
Conditions to Avoid	Exposure to moist air or water. Incompatible products.
Materials to avoid	Strong oxidizing agents. Acids.
Hazardous Decomposition Products	Sulfur oxides. Sodium oxides.

SECTION 11. TOXICOLOGICAL INFORMATION

SAFETY DATA SHEET

Sodium thiosulphate, anhydrous

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Sodium thiosulfate	>8000 mg/kg (Rat)		

(b) skin corrosion/irritation; Based on available data, the classification criteria are not met

(c) serious eye damage/irritation; Based on available data, the classification criteria are not met

(d) respiratory or skin sensitization;

Respiratory
Skin

Based on available data, the classification criteria are not met

Based on available data, the classification criteria are not met

(e) germ cell mutagenicity; Based on available data, the classification criteria are not met

(f) carcinogenicity; Based on available data, the classification criteria are not met
There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; Based on available data, the classification criteria are not met

(h) STOT-single exposure; Based on available data, the classification criteria are not met

(i) STOT-repeated exposure; Based on available data, the classification criteria are not met

Target Organs

None known.

(j) aspiration hazard; Not applicable
Solid

Symptoms / effects, both acute and delayed No information available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Do not empty into drains. .

Persistence and Degradability

Persistence
Degradability

Soluble in water, Persistence is unlikely, based on information available.

Not relevant for inorganic substances.

Bioaccumulative Potential

Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Sodium thiosulfate	-4.35	No data available

Mobility in soil The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

Sodium thiosulphate, anhydrous

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

Contaminated Packaging Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.

Other Information Waste codes should be assigned by the user based on the application for which the product was used.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport Not Regulated

IMDG/IMO Not regulated

IATA Not regulated

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Sodium thiosulfate	-	X	X	X	231-867-5	X	X	X	X	X	X	KE-31633

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Creation Date 15-Oct-2009
Revision Date 06-Sep-2025
Revision Summary Not applicable.

Training Advice

SAFETY DATA SHEET

Sodium thiosulphate, anhydrous

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet