

Section 1 - Identification

Product Name	<u>D-(+)-Glucose, anhydrous</u>
CAS No	50-99-7
Synonyms	Dextrose

Product Code	A16828
Address	ThermoFisher Scientific Australia Pty Ltd 5 Caribbean Drive, Scoresby VICTORIA 3179, Australia
Emergency Tel.	CHEMTREC® 03 9757 4559 or +613 9757 4559
Telephone / Fax Numbers	Tel: 1300 735 292 Fax: 1800 067 639
E-mail address	ANZinfo@thermofisher.com

Recommended Use Laboratory chemicals.

Uses advised against This product does not contain any substance(s) on the Illicit Drug Precursors/Reagents list. This product does not contain any substance(s) subject to Prohibition, Authorization or Restriction. This product does not contain any substance(s) listed on the voluntary National Code of Practice for Chemicals of Security Concern.

Section 2 - Hazard(s) Identification

Classification under Safe Work Australia

Classified as not hazardous according to criteria of Safe Work Australia.

Physical hazards
No hazards identified

Health hazards
No hazards identified

Environmental hazards
No hazards identified

Label Elements None required

Other information
No information available

Section 3 - Composition and Information on Ingredients

Component	CAS No	Weight %
Glucose	50-99-7	>95

Section 4 - First Aid Measures

Inhalation	Remove to fresh air. Get medical attention immediately if symptoms occur.
Ingestion	Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.
Skin Contact	Wash off immediately with plenty of water for at least 15 minutes. Get medical attention immediately if symptoms occur.
Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If symptoms persist, call a physician.
Self-Protection of the First Aider	No special precautions required.
First Aid Facilities	Eyewash, safety shower and washroom.
Most important symptoms and effects	None reasonably foreseeable.
Notes to Physician	Treat symptomatically.

Section 5 - Fire Fighting Measures

Suitable Extinguishing Media

Water spray, carbon dioxide (CO₂), dry chemical, alcohol-resistant foam.

Extinguishing media which must not be used for safety reasons

No information available.

Hazardous Decomposition Products

Carbon monoxide (CO), Carbon dioxide (CO₂).

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Special protective equipment and precautions for fire fighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Section 6 - Accidental Release Measures

Emergency procedures

Ensure adequate ventilation. Avoid dust formation.

Environmental Precautions

No special environmental precautions required. See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Clean-up methods - small spillage

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

Clean-up methods - large spillage

Not applicable, packaged goods.

Reference to Other Sections

Refer to protective measures listed in Sections 8 and 13.

Section 7 - Handling and Storage

Precautions for Safe Handling

Ensure adequate ventilation. Avoid contact with skin, eyes or clothing. Avoid ingestion and inhalation. Avoid dust formation.

Conditions for Safe Storage, Including any Incompatibilities

Keep containers tightly closed in a dry, cool and well-ventilated place.

AS/NZS 2243.10:2004, Safety in laboratories - Storage of chemicals

Section 8 - Exposure Controls and Personal Protection

Exposure limits

The product does not contain any hazardous materials with occupational exposure limits established.

Biological limit values

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

Exposure Controls**Engineering Measures**

None under normal use conditions.

Personal protective equipment**Eye Protection**

Wear safety glasses with side shields (or goggles) (Australian/New Zealand Standard AS/NZS 1337 - Eye protectors for Industrial applications)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	AUS/NZ Standard	Glove comments
Natural rubber	See manufacturers	-	AS/NZS 2161	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection

Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection

Use an AS/NZS 1716 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained in line with AS/NZS 1715 on the use and maintenance of respiratory protective devices

Recommended Filter type: Particle filter (or AUS/NZ equivalent)

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

Section 9 - Physical and Chemical Properties

Information on basic physical and chemical properties

Appearance	White	
Physical State	Solid	
Odor	Odorless	
Odor Threshold	No data available	
pH	6-7	10% aq. sol
Melting Point/Range	146 °C / 294.8 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	negligible	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	1.5400	
Bulk Density	No data available	
Water Solubility	Soluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Other information		
Molecular Formula	C6 H12 O6	
Molecular Weight	180.16	

Section 10 - Stability and Reactivity

Reactivity	None known, based on information available
Stability	Stable under normal conditions.
Conditions to Avoid	Incompatible products, Excess heat, Avoid dust formation.
Incompatible Materials	Strong oxidizing agents.
Hazardous Decomposition Products	Carbon monoxide (CO). Carbon dioxide (CO ₂).
Hazardous Polymerization	Hazardous polymerization does not occur.

Section 11 - Toxicological Information

Information on Toxicological Effects

Product Information

(a) acute toxicity;

Oral

Based on available data, the classification criteria are not met

Dermal

No data available

Inhalation

No data available

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Glucose	25.8 g/kg (Rat)		

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;

Respiratory

No data available

Skin

No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available

Target Organs

No information available.

(j) aspiration hazard; Not applicable
Solid

Symptoms / effects, both acute and delayed No information available

Section 12 - Ecological Information

Ecotoxicity effects

Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.

Persistence and Degradability

Persistence

Soluble in water, Persistence is unlikely, based on information available.

Bioaccumulative Potential

Bioaccumulation is unlikely

Mobility

The product is water soluble, and may spread in water systems. Will likely be mobile in the environment due to its water solubility Highly mobile in soils

Endocrine Disruptor Information

This product does not contain any known or suspected endocrine disruptors

Persistent Organic Pollutant

This product does not contain any known or suspected substance

Ozone Depletion Potential

This product does not contain any known or suspected substance

Section 13 - Disposal Considerations

Waste from Residues/Unused Products

Do not allow into drains or watercourses or dispose of where ground or surface waters may be affected. Wastes, including emptied containers, are controlled wastes and should be disposed of in accordance with all federal, E.P.A., state and local regulations. Assure conformity with all applicable regulations.

Contaminated Packaging

Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.

Other Information

Chemical wastes should be disposed through a licensed commercial waste collection service.

Section 14 - Transport Information

IMDG/IMO

Not regulated

ADG

Not regulated

IATA

Not regulated

Environmental hazards

No hazards identified

Special Precautions

No special precautions required

Additional information

None known

Section 15 - Regulatory Information

Safety, health and environmental regulations/legislation specific for the substance or mixture**National Regulations**

Australia

See section 8 for national exposure control parameters.

Standard for the Uniform Scheduling of Medicines and Poisons

No poison schedule number allocated.

Australian Industrial Chemicals Introduction Scheme (AICIS)

Component	Australian Industrial Chemicals Introduction Scheme (AICIS)	Additional information
Glucose - 50-99-7	Present	-

Australian - Illicit Drug Precursors/Reagents Substance List

This product does not contain any substance(s) on the Illicit Drug Precursors/Reagents list.

Chemicals of Security Concern

This product does not contain any substance(s) listed on the voluntary National Code of Practice for Chemicals of Security Concern

National pollutant inventory Not applicable

Prohibition or notification/licensing requirements

Shown below are details of specific prohibition/notifications or licensing requirements when they apply.

This product does not contain any substance(s) subject to Prohibition, Authorization or Restriction.

International Inventories

Component	AICS	NZIoC	EINECS	ELINCS	TSCA	DSL	NDSL	PICCS	ENCS	ISHL	IECSC	KECL
Glucose	X	X	200-075-1	-	X	X	-	X	X	X	X	KE-17727

Legend: X - Listed. '-' - Not Listed. KECL - NIER number or KE number (<http://ncis.nier.go.kr/en/main.do>)

International Regulations

Ozone Depletion Potential This product does not contain any known or suspected substance

Persistent Organic Pollutant This product does not contain any known or suspected substance

Rotterdam Convention (PIC) Not applicable

Basel convention on the control of transboundary movements of hazardous wastes and their disposal

Not applicable.

Component	CAS No	OECD HPV	Restriction of Hazardous Substances (RoHS)	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Major Accident Notification	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Safety Report Requirements
Glucose	50-99-7	Listed	Not applicable	Not applicable	Not applicable

Authorisation/Restrictions according to EU REACH Not applicable

Section 16 - Other Information

Legend

AICS - Australian Inventory of Chemical Substances
TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
IECSC - Chinese Inventory of Existing Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
TWA - Time Weighted Average
IARC - International Agency for Research on Cancer
ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

NZIoC - New Zealand Inventory of Chemicals
EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances
ENCS - Japanese Existing and New Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
CAS - Chemical Abstracts Service
ACGIH - American Conference of Governmental Industrial Hygienists
Predicted No Effect Concentration (PNEC)
IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships
NZS 5433:2012 - Transport of Dangerous Goods on Land
LD50 - Lethal Dose 50%
EC50 - Effective Concentration 50%
WEL - Workplace Exposure Limit
DNEL - Derived No Effect Level
POW - Partition coefficient Octanol:Water
vPvB - very Persistent, very Bioaccumulative
VOC - (Volatile Organic Compound)

ADG Australian Code for the Transport of Dangerous Goods by Road and Rail
OECD - Organisation for Economic Co-operation and Development
LC50 - Lethal Concentration 50%
ATE - Acute Toxicity Estimate
RPE - Respiratory Protective Equipment
NOEC - No Observed Effect Concentration
BCF - Bioconcentration factor
PBT - Persistent, Bioaccumulative, Toxic

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Revision Date 18-Nov-2022
Revision Summary Not applicable.

This Safety Data Sheet (SDS) is prepared in accordance to and complies with the requirements of Safe Work Australia - Work Health and Safety Regulations (WHS Regulations).

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet