

ALFAAA18796

## (-)-Cinchonidine

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

<b>产品说明:</b> <b>Product Description:</b>	<b>辛可尼丁</b> <b>(-)-Cinchonidine</b>
<b>Cat No. :</b>	<b>A18796</b>
<b>Synonyms</b>	alpha-Quinidine; (8alpha,9R)-Cinchonan-9-ol
<b>CAS No</b>	485-71-2
<b>Molecular Formula</b>	C <sub>19</sub> H <sub>22</sub> N <sub>2</sub> O
<b>Supplier</b>	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
<b>Emergency Telephone Number</b>	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
<b>E-mail address</b>	begel.sdsdesk@thermofisher.com
<b>Recommended Use</b>	Laboratory chemicals.
<b>Uses advised against</b>	No Information available

### SECTION 2. HAZARD IDENTIFICATION

<b>Physical State</b> Powder Solid	<b>Appearance</b> Light cream	<b>Odor</b> Odorless
<b>Emergency Overview</b> Harmful if swallowed. May cause an allergic skin reaction. Sensitivity to light.		

#### Classification of the substance or mixture

Acute Oral Toxicity	Category 4
Skin Sensitization	Category 1

#### Label Elements



**Signal Word**

**Warning**

**Hazard Statements**

# SAFETY DATA SHEET

## (-)-Cinchonidine

H302 - Harmful if swallowed  
H317 - May cause an allergic skin reaction

### Precautionary Statements

#### Prevention

P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product  
P272 - Contaminated work clothing should not be allowed out of the workplace  
P280 - Wear protective gloves

#### Response

P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell  
P302 + P352 - IF ON SKIN: Wash with plenty of soap and water  
P330 - Rinse mouth  
P333 + P313 - If skin irritation or rash occurs: Get medical advice/attention  
P362 + P364 - Take off contaminated clothing and wash it before reuse

#### Storage

P403 - Store in a well-ventilated place

#### Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

### Physical and Chemical Hazards

None identified.

### Health Hazards

Harmful if swallowed. May cause an allergic skin reaction.

### Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil.

This product does not contain any known or suspected endocrine disruptors.

## SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Cinchonan-9-ol, (8.alpha.,9R)-	485-71-2	>95

## SECTION 4. FIRST AID MEASURES

### Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

### Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention.

### Inhalation

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Get medical attention.

### Ingestion

Clean mouth with water. Get medical attention.

### Most important symptoms and effects

May cause allergic skin reaction. Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

### Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

### Notes to Physician

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray. Carbon dioxide (CO<sub>2</sub>). Dry chemical. Chemical foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation.

**Environmental Precautions**

See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Avoid dust formation. Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Avoid contact with skin and eyes. Do not breathe dust.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Protect from direct sunlight.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

**Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of

## (-)-Cinchonidine

properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Neoprene				
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particulates filter conforming to EN 143

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Particle filtering: EN149:2001  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Light cream	
<b>Physical State</b>	Powder Solid	
<b>Odor</b>	Odorless	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	200 - 203.00 °C / 392 - 397.4 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	No information available	
<b>Flash Point</b>	No information available	
<b>Evaporation Rate</b>	Not applicable	<b>Method -</b> No information available
<b>Flammability (solid,gas)</b>	No information available	Solid
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	Not applicable	Solid
<b>Specific Gravity / Density</b>	No data available	
<b>Bulk Density</b>	No data available	
<b>Water Solubility</b>	Insoluble	

# SAFETY DATA SHEET

## (-)-Cinchonidine

<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
Cinchonan-9-ol, (8.alpha.,9R)-	2.82	
<b>Autoignition Temperature</b>	400 °C / 752 °F	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	Not applicable	Solid
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C19 H22 N2 O	
<b>Molecular Weight</b>	294.39	

### SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Light sensitive.
<b>Hazardous Reactions</b>	No information available.
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid</b>	Exposure to light. Incompatible products.
<b>Materials to avoid</b>	Strong oxidizing agents. Strong bases. Strong reducing agents.
<b>Hazardous Decomposition Products</b>	Nitrogen oxides (NO <sub>x</sub> ). Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ). Sulfur oxides.

### SECTION 11. TOXICOLOGICAL INFORMATION

#### Product Information

##### (a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Cinchonan-9-ol, (8.alpha.,9R)-	305.82 mg/kg (Rat)		

<b>(b) skin corrosion/irritation;</b>	Based on available data, the classification criteria are not met
<b>(c) serious eye damage/irritation;</b>	Based on available data, the classification criteria are not met
<b>(d) respiratory or skin sensitization;</b>	
<b>Respiratory</b>	Based on available data, the classification criteria are not met
<b>Skin</b>	Category 1  May cause sensitization by skin contact
<b>(e) germ cell mutagenicity;</b>	Based on available data, the classification criteria are not met
<b>(f) carcinogenicity;</b>	Based on available data, the classification criteria are not met  There are no known carcinogenic chemicals in this product
<b>(g) reproductive toxicity;</b>	Based on available data, the classification criteria are not met
<b>(h) STOT-single exposure;</b>	Based on available data, the classification criteria are not met

**(i) STOT-repeated exposure;** Based on available data, the classification criteria are not met

**Target Organs** None known.

**(j) aspiration hazard;** Not applicable  
Solid

**Other Adverse Effects** The toxicological properties have not been fully investigated.

**Symptoms / effects, both acute and delayed** Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

## SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects** Do not empty into drains.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Cinchonan-9-ol, (8.alpha.,9R)-		EC50: 68.09 mg/L/48h		

**Persistence and Degradability Persistence** Readily biodegradable  
Persistence is unlikely.

**Bioaccumulative Potential** Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Cinchonan-9-ol, (8.alpha.,9R)-	2.82	No data available

**Mobility in soil** Spillage unlikely to penetrate soil Is not likely mobile in the environment due its low water solubility

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors

**Persistent Organic Pollutant** This product does not contain any known or suspected substance

**Ozone Depletion Potential** This product does not contain any known or suspected substance

## SECTION 13. DISPOSAL CONSIDERATIONS

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point.

**Other Information** Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

## SECTION 14. TRANSPORT INFORMATION

**Road and Rail Transport** Not Regulated

**IMDG/IMO** Not regulated

**IATA** Not regulated

## (-)-Cinchonidine

**Special Precautions for User** No special precautions required

### SECTION 15. REGULATORY INFORMATION

#### International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Cinchonan-9-ol, (8.alpha.,9R)-	-	-	X	-	207-622-3	X	-	X	X	X	-	-

#### National Regulations

### SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 06-Jan-2012  
**Revision Date** 23-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

#### Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

#### Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

# SAFETY DATA SHEET

(-)-Cinchonidine

---

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**