

ALFAAB21902

## Digoxin

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

 产品说明:  
 Product Description:

 地高辛  
 Digoxin

 Cat No. :  
 Synonyms  
 CAS No  
 Molecular Formula

 B21902  
 Lanoxin  
 20830-75-5  
 C41 H64 O14

Supplier

 Avocado Research Chemicals Ltd.  
 (Part of Thermo Fisher Scientific)  
 Shore Road, Heysham  
 Lancashire, LA3 2XY,  
 United Kingdom  
 Office Tel: +44 (0) 1524 850506  
 Office Fax: +44 (0) 1524 850608

Emergency Telephone Number

 For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
 Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address

begel.sdsdesk@thermofisher.com

 Recommended Use  
 Uses advised against

 Laboratory chemicals.  
 No Information available

### SECTION 2. HAZARD IDENTIFICATION

 Physical State  
 Solid

 Appearance  
 Off-white

 Odor  
 Odorless

#### Emergency Overview

Fatal if swallowed. Causes serious eye irritation. Fatal if inhaled. Causes damage to organs through prolonged or repeated exposure. Very toxic to aquatic life.

#### Classification of the substance or mixture

|                                                      |            |
|------------------------------------------------------|------------|
| Acute Oral Toxicity                                  | Category 2 |
| Acute Inhalation Toxicity - Dusts and Mists          | Category 2 |
| Serious Eye Damage/Eye Irritation                    | Category 2 |
| Specific target organ toxicity - (repeated exposure) | Category 1 |
| Acute aquatic toxicity                               | Category 1 |

#### Label Elements



**Signal Word****Danger****Hazard Statements**

H319 - Causes serious eye irritation  
H372 - Causes damage to organs through prolonged or repeated exposure  
H400 - Very toxic to aquatic life  
H300 + H330 - Fatal if swallowed or if inhaled

**Precautionary Statements****Prevention**

P201 - Obtain special instructions before use  
P202 - Do not handle until all safety precautions have been read and understood  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product  
P271 - Use only outdoors or in a well-ventilated area  
P280 - Wear protective gloves/protective clothing/eye protection/face protection  
P284 - Wear respiratory protection

**Response**

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P310 - Immediately call a POISON CENTER or doctor  
P330 - Rinse mouth

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed  
P405 - Store locked up

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Very toxic if swallowed. Causes serious eye irritation. Fatal if inhaled. Causes damage to organs through prolonged or repeated exposure.

**Environmental hazards**

Very toxic to aquatic life. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil. The product is insoluble and floats on water.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

| Component | CAS No     | Weight % |
|-----------|------------|----------|
| Digoxin   | 20830-75-5 | >95      |

**SECTION 4. FIRST AID MEASURES****General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**Eye Contact**

In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the

## Digoxin

substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

**Ingestion**

Do NOT induce vomiting. Call a physician or poison control center immediately.

**Most important symptoms and effects**

None reasonably foreseeable.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Do not allow run-off from fire-fighting to enter drains or water courses.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas.

**Environmental Precautions**

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Avoid dust formation. Use only under a chemical fume hood. Do not breathe (dust, vapor, mist, gas). Do not ingest. If swallowed then seek immediate medical assistance.

**Storage**

Keep containers tightly closed in a dry, cool and well-ventilated place. To maintain product quality. Keep refrigerated.

**Specific Use(s)**

## Digoxin

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

## Control Parameters

## Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

## Exposure Controls

## Engineering Measures

Use only under a chemical fume hood. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

## Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

| Glove material | Breakthrough time | Glove thickness | EU standard | Glove comments        |
|----------------|-------------------|-----------------|-------------|-----------------------|
| Natural rubber | See manufacturers | -               | EN 374      | (minimum requirement) |
| Nitrile rubber | recommendations   |                 |             |                       |
| Neoprene       |                   |                 |             |                       |
| PVC            |                   |                 |             |                       |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particulates filter conforming to EN 143

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Particle filtering: EN149:2001  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

|                                                |                               |                                          |
|------------------------------------------------|-------------------------------|------------------------------------------|
| <b>Appearance</b>                              | Off-white                     |                                          |
| <b>Physical State</b>                          | Solid                         |                                          |
| <b>Odor</b>                                    | Odorless                      |                                          |
| <b>Odor Threshold</b>                          | No data available             |                                          |
| <b>pH</b>                                      | Not applicable                |                                          |
| <b>Melting Point/Range</b>                     | 248 - 250 °C / 478.4 - 482 °F |                                          |
| <b>Softening Point</b>                         | No data available             |                                          |
| <b>Boiling Point/Range</b>                     | No information available      |                                          |
| <b>Flash Point</b>                             | No information available      | <b>Method -</b> No information available |
| <b>Evaporation Rate</b>                        | Not applicable                | Solid                                    |
| <b>Flammability (solid,gas)</b>                | No information available      |                                          |
| <b>Explosion Limits</b>                        | No data available             |                                          |
| <b>Vapor Pressure</b>                          | No data available             |                                          |
| <b>Vapor Density</b>                           | Not applicable                | Solid                                    |
| <b>Specific Gravity / Density</b>              | 1.36 g/cm3 @ 20 C             |                                          |
| <b>Bulk Density</b>                            | No data available             |                                          |
| <b>Water Solubility</b>                        | Insoluble                     |                                          |
| <b>Solubility in other solvents</b>            | No information available      |                                          |
| <b>Partition Coefficient (n-octanol/water)</b> |                               |                                          |
| <b>Component</b>                               | <b>log Pow</b>                |                                          |
| Digoxin                                        | 1.26                          |                                          |
| <b>Autoignition Temperature</b>                | No data available             |                                          |
| <b>Decomposition Temperature</b>               | No data available             |                                          |
| <b>Viscosity</b>                               | Not applicable                | Solid                                    |
| <b>Explosive Properties</b>                    | No information available      |                                          |
| <b>Oxidizing Properties</b>                    | No information available      |                                          |
| <b>Molecular Formula</b>                       | C41 H64 O14                   |                                          |
| <b>Molecular Weight</b>                        | 780.94                        |                                          |

## SECTION 10. STABILITY AND REACTIVITY

|                                 |                                          |
|---------------------------------|------------------------------------------|
| <b>Stability</b>                | Stable under normal conditions.          |
| <b>Hazardous Reactions</b>      | None under normal processing.            |
| <b>Hazardous Polymerization</b> | Hazardous polymerization does not occur. |
| <b>Conditions to Avoid</b>      | Incompatible products. Excess heat.      |
| <b>Materials to avoid</b>       | Strong oxidizing agents. Strong acids.   |

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

## SECTION 11. TOXICOLOGICAL INFORMATION

### Product Information

(a) acute toxicity;  
Toxicology data for the components

| Component | LD50 Oral                | LD50 Dermal | LC50 Inhalation |
|-----------|--------------------------|-------------|-----------------|
| Digoxin   | LD50 = 28.27 mg/kg (Rat) |             |                 |

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; Category 2

(d) respiratory or skin sensitization;

Respiratory No data available

Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

The table below indicates whether each agency has listed any ingredient as a carcinogen

| Component | EU | UK | Germany | IARC     |
|-----------|----|----|---------|----------|
| Digoxin   |    |    |         | Group 2B |

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; Category 1

Target Organs None known.

(j) aspiration hazard; Not applicable  
Solid

Other Adverse Effects The toxicological properties have not been fully investigated.

Symptoms / effects, both acute and delayed No information available

## SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Very toxic to aquatic organisms. The product contains following substances which are hazardous for the environment.

| Component | Freshwater Fish | Water Flea                                | Freshwater Algae | Microtox |
|-----------|-----------------|-------------------------------------------|------------------|----------|
| Digoxin   |                 | EC50 = 24.21 mg/L, 24h<br>(Daphnia magna) |                  |          |

## Persistence and Degradability

Persistence Persistence is unlikely.

Degradation in sewage treatment plant Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential Bioaccumulation is unlikely

| Component | log Pow | Bioconcentration factor (BCF) |
|-----------|---------|-------------------------------|
| Digoxin   | 1.26    | No data available             |

Mobility in soil Spillage unlikely to penetrate soil The product is insoluble and floats on water Is not likely mobile in the environment due its low water solubility

**Endocrine Disruptor Information**  
**Persistent Organic Pollutant**  
**Ozone Depletion Potential**

This product does not contain any known or suspected endocrine disruptors  
 This product does not contain any known or suspected substance  
 This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS****Waste from Residues/Unused Products**

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations. Should not be released into the environment.

**Contaminated Packaging**

Dispose of this container to hazardous or special waste collection point.

**Other Information**

Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not let this chemical enter the environment.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport****UN-No**

UN3462

**Proper Shipping Name**

Toxins, extracted from living sources, solid, n.o.s.

**Technical Shipping Name**

Digoxin

**Hazard Class**

6.1

**Packing Group**

II

**IMDG/IMO****UN-No**

UN3462

**Proper Shipping Name**

Toxins extracted from living sources, solid, n.o.s.

**Technical Shipping Name**

Digoxin

**Hazard Class**

6.1

**Packing Group**

II

**IATA****UN-No**

UN3462

**Proper Shipping Name**

Toxins, extracted from living sources, solid, n.o.s.

**Technical Shipping Name**

Digoxin

**Hazard Class**

6.1

**Packing Group**

II

**Special Precautions for User**

No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, U.S.A. (TSCA), Canada (DSL/NDL), Europe (EINECS/ELINCS/NLP), Australia (AICS), Korea (KECL), China (IECSC), Japan (ENCS), Philippines (PICCS), Taiwan (TCSI), Japan (ISHL), New Zealand (NZIoC), Japan (ISHL).

| Component | The Inventory of Hazardous Chemicals (2015 Edition) | List of dangerous goods GB 12268 - 2012 | TCSI | IECSC | EINECS    | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL |
|-----------|-----------------------------------------------------|-----------------------------------------|------|-------|-----------|------|-----|-------|------|------|------|------|
| Digoxin   | X                                                   | -                                       | X    | -     | 244-068-1 | X    | X   | X     | -    |      | -    | -    |

## National Regulations

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 11-Sep-2009  
**Revision Date** 09-Sep-2025  
**Revision Summary** SDS sections updated.

**Training Advice**  
Chemical incident response training.

Legend

|                                                                                                                              |                                                                                                   |
|------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|
| <b>CAS</b> - Chemical Abstracts Service                                                                                      | <b>TSCA</b> - United States Toxic Substances Control Act Section 8(b) Inventory                   |
| <b>EINECS/ELINCS</b> - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances | <b>DSL/NDSL</b> - Canadian Domestic Substances List/Non-Domestic Substances List                  |
| <b>PICCS</b> - Philippines Inventory of Chemicals and Chemical Substances                                                    | <b>ENCS</b> - Japanese Existing and New Chemical Substances                                       |
| <b>IECSC</b> - Chinese Inventory of Existing Chemical Substances                                                             | <b>AICS</b> - Australian Inventory of Chemical Substances                                         |
| <b>KECL</b> - Korean Existing and Evaluated Chemical Substances                                                              | <b>NZIoC</b> - New Zealand Inventory of Chemicals                                                 |
| <b>WEL</b> - Workplace Exposure Limit                                                                                        | <b>TWA</b> - Time Weighted Average                                                                |
| <b>ACGIH</b> - American Conference of Governmental Industrial Hygienists                                                     | <b>IARC</b> - International Agency for Research on Cancer                                         |
| <b>DNEL</b> - Derived No Effect Level                                                                                        | <b>PNEC</b> - Predicted No Effect Concentration                                                   |
| <b>RPE</b> - Respiratory Protective Equipment                                                                                | <b>LD50</b> - Lethal Dose 50%                                                                     |
| <b>LC50</b> - Lethal Concentration 50%                                                                                       | <b>EC50</b> - Effective Concentration 50%                                                         |
| <b>NOEC</b> - No Observed Effect Concentration                                                                               | <b>POW</b> - Partition coefficient Octanol:Water                                                  |
| <b>PBT</b> - Persistent, Bioaccumulative, Toxic                                                                              | <b>vPvB</b> - very Persistent, very Bioaccumulative                                               |
| <b>ICAO/IATA</b> - International Civil Aviation Organization/International Air Transport Association                         | <b>IMO/IMDG</b> - International Maritime Organization/International Maritime Dangerous Goods Code |
| <b>ADR</b> - European Agreement Concerning the International Carriage of Dangerous Goods by Road                             | <b>MARPOL</b> - International Convention for the Prevention of Pollution from Ships               |
| <b>OECD</b> - Organisation for Economic Co-operation and Development                                                         | <b>ATE</b> - Acute Toxicity Estimate                                                              |
| <b>BCF</b> - Bioconcentration factor                                                                                         | <b>VOC</b> - (Volatile Organic Compound)                                                          |

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>  
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

|                              |                       |
|------------------------------|-----------------------|
| <b>Physical hazards</b>      | On basis of test data |
| <b>Health Hazards</b>        | Calculation method    |
| <b>Environmental hazards</b> | Calculation method    |

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**