

SAFETY DATA SHEET

Creation Date 12-December-1997

Revision Date 14-February-2020

Revision Number 3

1. Identification**Product Name** Manganese(II) sulfate tetrahydrate**Cat No. :** B22081**CAS-No** 10101-68-5**Synonyms** Sulfuric acid, manganese(2+) salt (1:1), tetrahydrate.**Recommended Use** Laboratory chemicals.**Uses advised against** Food, drug, pesticide or biocidal product use.**Details of the supplier of the safety data sheet****Company****Importer/Distributor**Fisher Scientific
112 Colonnade Road,
Ottawa, ON K2E 7L6,
Canada
Tel: 1-800-234-7437**Manufacturer**Alfa Aesar
Thermo Fisher Scientific Chemicals, Inc.
30 Bond Street, Ward Hill, MA 01835-8099
Tel: 800-343-0660 **Fax:** 800-322-4757
Email: tech@alfa.com
www.alfa.com**Emergency Telephone Number**During normal business hours (Monday-Friday, 8am-7pm EST), call (800) 343-0660.
After normal business hours, call Carechem 24 at (800) 579-7421.**2. Hazard(s) identification****Classification****WHMIS 2015 Classification** Not classified under the Hazardous Products Regulations (SOR/2015-17)Based on available data, the classification criteria are not met
Target Organs - Brain.**Label Elements**

None required

3. Composition/Information on Ingredients

Component	CAS-No	Weight %
Manganese(II) sulfate tetrahydrate	10101-68-5	>95
Manganese(II) sulfate	7785-87-7	-

4. First-aid measures

General Advice	If symptoms persist, call a physician.
Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Skin Contact	Wash off immediately with plenty of water for at least 15 minutes. Get medical attention.
Inhalation	Remove to fresh air. Get medical attention. If not breathing, give artificial respiration.
Ingestion	Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.
Most important symptoms/effects Notes to Physician	Causes eye burns. Causes severe eye damage. Treat symptomatically

5. Fire-fighting measures

Unsuitable Extinguishing Media	No information available
Flash Point	No information available
Method -	No information available
Autoignition Temperature	
Explosion Limits	
Upper	No data available
Lower	No data available
Sensitivity to Mechanical Impact	No information available
Sensitivity to Static Discharge	No information available

Specific Hazards Arising from the Chemical

Keep product and empty container away from heat and sources of ignition.

Hazardous Combustion Products

Sulfur oxides.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

NFPA

Health	Flammability	Instability	Physical hazards
1	0	0	N/A

6. Accidental release measures

Personal Precautions	Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.
Environmental Precautions	Do not flush into surface water or sanitary sewer system.
Methods for Containment and Clean Up	Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal.

7. Handling and storage

Handling	Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Avoid dust formation. Ensure adequate ventilation.
-----------------	---

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place.

8. Exposure controls / personal protection

Exposure Guidelines

This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

Component	Alberta	British Columbia	Ontario TWAEV	Quebec	ACGIH TLV	OSHA PEL	NIOSH IDLH
Manganese(II) sulfate tetrahydrate	TWA: 0.2 mg/m ³	TWA: 0.2 mg/m ³ TWA: 0.02 mg/m ³	TWA: 0.02 mg/m ³ TWA: 0.1 mg/m ³	TWA: 0.2 mg/m ³	TWA: 0.02 mg/m ³ TWA: 0.1 mg/m ³	(Vacated) Ceiling: 5 mg/m ³ Ceiling: 5 mg/m ³	IDLH: 500 mg/m ³ TWA: 1 mg/m ³ STEL: 3 mg/m ³
Manganese(II) sulfate	TWA: 0.2 mg/m ³	TWA: 0.2 mg/m ³ TWA: 0.02 mg/m ³	TWA: 0.02 mg/m ³ TWA: 0.1 mg/m ³	TWA: 0.2 mg/m ³	TWA: 0.02 mg/m ³ TWA: 0.1 mg/m ³	(Vacated) Ceiling: 5 mg/m ³ Ceiling: 5 mg/m ³	IDLH: 500 mg/m ³ TWA: 1 mg/m ³ STEL: 3 mg/m ³

Engineering Measures

Use only under a chemical fume hood. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source

Personal protective equipment

Eye Protection
Hand Protection

Goggles
Wear appropriate protective gloves and clothing to prevent skin exposure.

Glove material	Breakthrough time	Glove thickness	Glove comments
Natural rubber Nitrile rubber Neoprene PVC	See manufacturers recommendations	-	Splash protection only

Inspect gloves before use. observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information) gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion. gloves with care avoiding skin contamination.

Respiratory Protection

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN 149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Recommended Filter type: Particulates filter conforming to EN 143

When RPE is used a face piece Fit Test should be conducted

Environmental exposure controls

Prevent product from entering drains. Do not allow material to contaminate ground water system.

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice.

9. Physical and chemical properties

Physical State	Solid
Appearance	Light red
Odor	Odorless
Odor Threshold	No information available

pH	4.5-6.0 50g/L (20°C)
Melting Point/Range	26 - 27 °C
Boiling Point/Range	No information available
Flash Point	No information available
Evaporation Rate	Not applicable
Flammability (solid,gas)	No information available
Flammability or explosive limits	
Upper	No data available
Lower	No data available
Vapor Pressure	No information available
Vapor Density	Not applicable
Specific Gravity	No information available
Solubility	Soluble in water
Partition coefficient; n-octanol/water	No data available
Autoignition Temperature	
Decomposition Temperature	No information available
Viscosity	Not applicable
Molecular Formula	MnSO ₄ ·4H ₂ O
Molecular Weight	223.05

10. Stability and reactivity

Reactive Hazard	None known, based on information available
Stability	Stable under normal conditions.
Conditions to Avoid	Incompatible products. Excess heat. Avoid dust formation.
Incompatible Materials	No information available
Hazardous Decomposition Products	Sulfur oxides
Hazardous Polymerization	Hazardous polymerization does not occur.
Hazardous Reactions	None under normal processing.

11. Toxicological information

Acute Toxicity

Product Information See actual entry in RTECS for complete information.

Component Information

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Manganese(II) sulfate tetrahydrate	2150 mg/kg (Rat)	Not listed	Not listed
Manganese(II) sulfate	LD50 = 782 mg/kg (Rat)	Not listed	Not listed

Toxicologically Synergistic Products No information available

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Irritation No information available

Sensitization No information available

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen.

Component	CAS-No	IARC	NTP	ACGIH	OSHA	Mexico
Manganese(II) sulfate tetrahydrate	10101-68-5	Not listed	Not listed	Not listed	Not listed	Not listed
Manganese(II) sulfate	7785-87-7	Not listed	Not listed	Not listed	Not listed	Not listed

Mutagenic Effects No information available

Reproductive Effects	No information available.
Developmental Effects	No information available.
Teratogenicity	No information available.
STOT - single exposure	None known
STOT - repeated exposure	Brain
Aspiration hazard	No information available
Symptoms / effects, both acute and delayed	No information available
Endocrine Disruptor Information	No information available
Other Adverse Effects	The toxicological properties have not been fully investigated.

12. Ecological information

Ecotoxicity

The product contains following substances which are hazardous for the environment. Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Component	Freshwater Algae	Freshwater Fish	Microtox	Water Flea
Manganese(II) sulfate tetrahydrate	Not listed	30.6 mg/l LC50 96h	Not listed	8.3 mg/l EC50 48h

Persistence and Degradability Soluble in water Persistence is unlikely based on information available.

Bioaccumulation/ Accumulation No information available.

Mobility Will likely be mobile in the environment due to its water solubility.

13. Disposal considerations

Waste Disposal Methods Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

14. Transport information

DOT

UN-No UN3077
 Proper Shipping Name consumer commodity Environmentally hazardous substances, solid, n.o.s.
 Technical Name Manganese(II) sulfate tetrahydrate
 Hazard Class 9
 Packing Group III

TDG

UN-No UN3077
 Proper Shipping Name Environmentally hazardous substances, solid, n.o.s.
 Hazard Class 9
 Packing Group III

IATA

UN-No UN3077
 Proper Shipping Name Environmentally hazardous substances, solid, n.o.s.
 Hazard Class 9
 Packing Group III

IMDG/IMO

UN-No UN3077
 Proper Shipping Name Environmentally hazardous substances, solid, n.o.s.
 Hazard Class 9

Packing Group

III

15. Regulatory information

International Inventories

Component	DSL	NDSL	TSCA	EINECS	ELINCS	PICCS	ENCS	AICS	KECL	IECSC
Manganese(II) sulfate tetrahydrate	-	-	-	-	-	-	-	X	-	X
Manganese(II) sulfate	X	-	X	232-089-9	-	X	X	X	KE-23032	X

Legend

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

Canada

SDS in compliance with provisions of information as set out in Canadian Standard - Part 4, Schedule 1 and 2 of the Hazardous Products Regulations (HPR) and meets the requirements of the HPR (Paragraph 13(1)(a) of the Hazardous Products Act (HPA)).

Component	Canada - National Pollutant Release Inventory (NPRI)	Canadian Environmental Protection Agency (CEPA) - List of Toxic Substances	Canada's Chemicals Management Plan (CEPA)
Manganese(II) sulfate tetrahydrate	Part 1, Group A Substance		
Manganese(II) sulfate	Part 1, Group A Substance		

16. Other information

Prepared By

Product Safety Department
Email: tech@alfa.com
www.alfa.com

Creation Date

12-December-1997

Revision Date

14-February-2020

Print Date

14-February-2020

Revision Summary

Mise à jour des systèmes de création SDS, remplace ChemGes SDS No. 10101-68-5.

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS