

ALFAAH50105

## Benzo[b]thiophene-3-carboxylic acid

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
Product Description: 苯并[b]噻吩-3-羧酸  
Benzo[b]thiophene-3-carboxylic acid

Cat No. : H50105  
CAS No 5381-25-9  
Molecular Formula C9 H6 O2 S

Supplier Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Solid

**Appearance**  
Off-white - Brown

**Odor**  
No information available

**Emergency Overview**  
Causes skin irritation. Causes serious eye irritation.

#### Classification of the substance or mixture

|                                   |            |
|-----------------------------------|------------|
| Skin Corrosion/Irritation         | Category 2 |
| Serious Eye Damage/Eye Irritation | Category 2 |

#### Label Elements



Signal Word

Warning

Hazard Statements  
H315 - Causes skin irritation

H319 - Causes serious eye irritation

**Precautionary Statements****Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling

P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P337 + P313 - If eye irritation persists: Get medical advice/attention

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P332 + P313 - If skin irritation occurs: Get medical advice/attention

P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 - Store in a well-ventilated place

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Causes skin irritation. Causes serious eye irritation.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Other Hazards**

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

| Component                          | CAS No    | Weight % |
|------------------------------------|-----------|----------|
| 1-Benzothiophene-3-carboxylic acid | 5381-25-9 | 97       |

**SECTION 4. FIRST AID MEASURES****General Advice**

If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

**Most important symptoms and effects**

None reasonably foreseeable.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

## SECTION 5. FIRE-FIGHTING MEASURES

### Suitable Extinguishing Media

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam.

### Extinguishing media which must not be used for safety reasons

No information available.

### Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors. Keep product and empty container away from heat and sources of ignition.

### Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## SECTION 6. ACCIDENTAL RELEASE MEASURES

### Personal Precautions

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

### Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information.

### Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

## SECTION 7. HANDLING AND STORAGE

### Handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Avoid dust formation.

### Storage

Keep containers tightly closed in a dry, cool and well-ventilated place.

### Specific Use(s)

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control Parameters

### Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

### Exposure Controls

### Engineering Measures

# SAFETY DATA SHEET

## Benzo[b]thiophene-3-carboxylic acid

Use only under a chemical fume hood. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

### Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

| Glove material | Breakthrough time | Glove thickness | EU standard | Glove comments        |
|----------------|-------------------|-----------------|-------------|-----------------------|
| Natural rubber | See manufacturers | -               | EN 374      | (minimum requirement) |
| Nitrile rubber | recommendations   |                 |             |                       |
| Neoprene       |                   |                 |             |                       |
| PVC            |                   |                 |             |                       |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

**Small scale/Laboratory use** Maintain adequate ventilation

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

|                                     |                                 |  |
|-------------------------------------|---------------------------------|--|
| <b>Appearance</b>                   | Off-white - Brown               |  |
| <b>Physical State</b>               | Solid                           |  |
| <b>Odor</b>                         | No information available        |  |
| <b>Odor Threshold</b>               | No data available               |  |
| <b>pH</b>                           | No information available        |  |
| <b>Melting Point/Range</b>          | 174 - 176 °C / 345.2 - 348.8 °F |  |
| <b>Softening Point</b>              | No data available               |  |
| <b>Boiling Point/Range</b>          | No information available        |  |
| <b>Flash Point</b>                  | No information available        | <b>Method -</b> No information available |
| <b>Evaporation Rate</b>             | Not applicable                  | Solid                                    |
| <b>Flammability (solid,gas)</b>     | No information available        |  |
| <b>Explosion Limits</b>             | No information available        |  |
| <b>Vapor Pressure</b>               | No information available        |  |
| <b>Vapor Density</b>                | Not applicable                  | Solid                                    |
| <b>Specific Gravity / Density</b>   | No data available               |  |
| <b>Bulk Density</b>                 | No data available               |  |
| <b>Water Solubility</b>             | No information available        |  |
| <b>Solubility in other solvents</b> | No information available        |  |

# SAFETY DATA SHEET

## Benzo[b]thiophene-3-carboxylic acid

|  |                          |       |
|--|--------------------------|-------|
| <b>Partition Coefficient (n-octanol/water)</b> |                          |       |
| <b>Autoignition Temperature</b>                | No data available        |       |
| <b>Decomposition Temperature</b>               | No information available |       |
| <b>Viscosity</b>                               | Not applicable           | Solid |
| <b>Explosive Properties</b>                    | No information available |       |
| <b>Oxidizing Properties</b>                    | No information available |       |
| <br>   |                          |       |
| <b>Molecular Formula</b>                       | C9 H6 O2 S               |       |
| <b>Molecular Weight</b>                        | 178.21                   |       |

### SECTION 10. STABILITY AND REACTIVITY

|   |   |
|---|---|
| <b>Stability</b>                        | Stable under normal conditions.   |
| <b>Hazardous Reactions</b>              | None under normal processing.   |
| <b>Hazardous Polymerization</b>         | Hazardous polymerization does not occur.                                |
| <b>Conditions to Avoid</b>              | Incompatible products. Excess heat. Avoid dust formation.               |
| <b>Materials to avoid</b>               | Strong oxidizing agents. Bases.   |
| <br>                                    |   |
| <b>Hazardous Decomposition Products</b> | Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ). Sulfur oxides. |

### SECTION 11. TOXICOLOGICAL INFORMATION

|   |   |
|---|---|
| <b>Product Information</b>                    | No acute toxicity information is available for this product |
| <b>(a) acute toxicity;</b>                    |   |
| <b>(b) skin corrosion/irritation;</b>         | Category 2  |
| <b>(c) serious eye damage/irritation;</b>     | Category 2  |
| <b>(d) respiratory or skin sensitization;</b> |   |
| <b>Respiratory</b>                            | No data available   |
| <b>Skin</b>                                   | No data available   |
| <b>(e) germ cell mutagenicity;</b>            | No data available   |
| <b>(f) carcinogenicity;</b>                   | No data available   |
|   | There are no known carcinogenic chemicals in this product   |
| <b>(g) reproductive toxicity;</b>             | No data available   |
| <b>(h) STOT-single exposure;</b>              | No data available   |
| <b>(i) STOT-repeated exposure;</b>            | No data available   |
| <b>Target Organs</b>                          | No information available.                                   |
| <b>(j) aspiration hazard;</b>                 | Not applicable  |

# SAFETY DATA SHEET

## Benzo[b]thiophene-3-carboxylic acid

Solid

**Symptoms / effects, both acute and delayed** No information available

### SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects** Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.

**Persistence and Degradability** No information available

**Bioaccumulative Potential** No information available

**Mobility in soil** No information available

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

### SECTION 13. DISPOSAL CONSIDERATIONS

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point.

**Other Information** Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

### SECTION 14. TRANSPORT INFORMATION

**Road and Rail Transport** Not Regulated

**IMDG/IMO** Not regulated

**IATA** Not regulated

**Special Precautions for User** No special precautions required

### SECTION 15. REGULATORY INFORMATION

#### International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

| Component | The Inventory of Hazardous Chemicals | List of dangerous goods GB 12268 - | TCSI | IECSC | EINECS | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL |
|-----------|--------------------------------------|------------------------------------|------|-------|--------|------|-----|-------|------|------|------|------|
|           |                                      |                                    |      |       |        |      |     |       |      |      |      |      |

# SAFETY DATA SHEET

## Benzo[b]thiophene-3-carboxylic acid

|                                    | (2015 Edition) | 2012 |   |   |   |   |   |   |   |   |   |   |
|------------------------------------|----------------|------|---|---|---|---|---|---|---|---|---|---|
| 1-Benzothiophene-3-carboxylic acid | -              | -    | X | - | - | - | - | - | - | - | - | - |

### National Regulations

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 23-Feb-2009  
**Revision Date** 27-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

### Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

### Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

### Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

### Disclaimer

**The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text**

**SAFETY DATA SHEET**  
**Benzo[b]thiophene-3-carboxylic acid**

**End of Safety Data Sheet**