

ALFAAL04703

n-Butyl phenyl ether

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: Product Description:	正丁基苯基醚 n-Butyl phenyl ether
Cat No. :	L04703
Synonyms	n-Butoxybenzene
CAS No	1126-79-0
Molecular Formula	C10 H14 O
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information US call: 001-800-227-6701 / Europe call: +32 14 57 52 11 Emergency Number US :001-201-796-7100 / Europe : +32 14 57 52 99 CHEMTREC Tel. No. US :001-800-424-9300 / Europe :001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State Liquid	Appearance Colorless	Odor No information available
Emergency Overview Combustible liquid.		

Classification of the substance or mixture

Flammable liquids.	Category 4
--------------------	------------

Label Elements

None required

Signal Word **Warning**

Hazard Statements
H227 - Combustible liquid

Precautionary Statements
Prevention

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray

n-Butyl phenyl ether

P264 - Wash face, hands and any exposed skin thoroughly after handling
P271 - Use only outdoors or in a well-ventilated area
P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P312 - Call a POISON CENTER or doctor if you feel unwell
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Disposal of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Combustible material.

Health Hazards

The product contains no substances which at their given concentration are considered to be hazardous to health.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Butyl phenyl ether	1126-79-0	99

SECTION 4. FIRST AID MEASURES**Eye Contact**

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention. Take off contaminated clothing and shoes immediately.

Inhalation

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Immediate medical attention is required.

Ingestion

Never give anything by mouth to an unconscious person. Drink plenty of water. Call a physician immediately. If possible drink milk afterwards.

Most important symptoms and effects

Difficulty in breathing. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

Self-Protection of the First Aider

No special precautions required.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

n-Butyl phenyl ether

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Combustible material. Containers may explode when heated.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions

Do not flush into surface water or sanitary sewer system.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Remove all sources of ignition.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Avoid contact with skin and eyes. Avoid contact with skin and clothing. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Avoid breathing vapors or mists. Do not ingest. If swallowed then seek immediate medical assistance. Wash thoroughly after handling. Keep away from open flames, hot surfaces and sources of ignition.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat, sparks and flame.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours

Exposure Controls**Engineering Measures**

None under normal use conditions. Ensure adequate ventilation, especially in confined areas. .

Personal protective equipment

n-Butyl phenyl ether

Eye Protection	Wear safety glasses with side shields (or goggles) (European standard - EN 166)
Hand Protection	Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection No protective equipment is needed under normal use conditions.

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Particle filter

Small scale/Laboratory use Maintain adequate ventilation
Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls Prevent product from entering drains. Do not allow material to contaminate ground water system.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Colorless	
Physical State	Liquid	
Odor	No information available	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	-19 - 0.00 °C / -2.2 - 32 °F	
Softening Point	No data available	
Boiling Point/Range	210.2 °C / 410.4 °F	@ 760 mmHg
Flash Point	82 °C / 179.6 °F	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	5.18	(Air = 1.0)
Specific Gravity / Density	0.930	
Bulk Density	Not applicable	Liquid
Water Solubility	No information available	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
Butyl phenyl ether	4.26	

n-Butyl phenyl ether

Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	No data available	
Explosive Properties		explosive air/vapour mixtures possible
Oxidizing Properties	No information available	
Molecular Formula	C10 H14 O	
Molecular Weight	150.22	

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions.
Hazardous Reactions	No information available.
Hazardous Polymerization	No information available.
Conditions to Avoid	Keep away from open flames, hot surfaces and sources of ignition.
Materials to avoid	Oxidizing agent.

Hazardous Decomposition Products Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information	No acute toxicity information is available for this product
(a) acute toxicity;	
(b) skin corrosion/irritation;	No data available
(c) serious eye damage/irritation;	No data available
(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available
	There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	No data available

n-Butyl phenyl ether

Symptoms / effects, both acute and delayed Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting delayed

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Butyl phenyl ether	LC50: 5.2 - 6.41 mg/L, 96h flow-through (Pimephales promelas)			

Persistence and Degradability
Degradation in sewage treatment plant

No information available
Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential

No information available

Component	log Pow	Bioconcentration factor (BCF)
Butyl phenyl ether	4.26	No data available

Mobility in soil

No information available

Endocrine Disruptor Information
Persistent Organic Pollutant
Ozone Depletion Potential

This product does not contain any known or suspected endocrine disruptors
This product does not contain any known or suspected substance
This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products

Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

Contaminated Packaging

Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.

Other Information

Do not flush to sewer.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

Not Regulated

IMDG/IMO

Not regulated

IATA

Not regulated

Special Precautions for User

No special precautions required

SECTION 15. REGULATORY INFORMATION

n-Butyl phenyl ether

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Butyl phenyl ether	-	-	X	X	214-426-1	X	-	X	-		X	-

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Revision Date 22-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

SAFETY DATA SHEET

n-Butyl phenyl ether

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet