

Revision Date 07-Jan-2021

Revision Number 2

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product Description:	4-Nitrobenzenediazonium tetrafluoroborate
Cat No. :	H55315
Synonyms	Fast Red GG; p-Nitrophenyldiazonium fluoborate.
CAS-No	456-27-9
EC-No.	207-261-1
Molecular Formula	C ₆ H ₄ BF ₄ N ₃ O ₂
Reach Registration Number	-

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

1.3. Details of the supplier of the safety data sheet

Company	Alfa Aesar Avocado Research Chemicals, Ltd. Shore Road Port of Heysham Industrial Park Heysham, Lancashire LA3 2XY United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
E-mail address	uktech@alfa.com www.alfa.com Product Safety Department

1.4. Emergency telephone number

Call Carechem 24 at
+44 (0) 1865 407333 (English only);
+44 (0) 1235 239670 (Multi-language)

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

CLP Classification - Regulation (EC) No 1272/2008

Physical hazards

Based on available data, the classification criteria are not met

SAFETY DATA SHEET

4-Nitrobenzenediazonium tetrafluoroborate

Revision Date 07-Jan-2021

Health hazards

Acute oral toxicity
Acute dermal toxicity
Acute Inhalation Toxicity - Dusts and Mists
Skin Corrosion/Irritation
Serious Eye Damage/Eye Irritation

Category 4 (H302)
Category 4 (H312)
Category 4 (H332)
Category 1 B (H314)
Category 1 (H318)

Environmental hazards

Based on available data, the classification criteria are not met

Full text of Hazard Statements: see section 16

2.2. Label elements



Signal Word

Danger

Hazard Statements

H314 - Causes severe skin burns and eye damage
H302 + H312 + H332 - Harmful if swallowed, in contact with skin or if inhaled

Precautionary Statements

P304 + P340 - IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
P280 - Wear protective gloves/protective clothing/eye protection/face protection
P301 + P330 + P331 - IF SWALLOWED: Rinse mouth. Do NOT induce vomiting
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P310 - Immediately call a POISON CENTER or doctor/physician
P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower

2.3. Other hazards

No information available

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1. Substances

Component	CAS-No	EC-No.	Weight %	CLP Classification - Regulation (EC) No 1272/2008
Benzenediazonium, 4-nitro-, tetrafluoroborate(1-)	456-27-9	EEC No. 207-261-1	95 - 97	Acute Tox. 4 (H302) Acute Tox. 4 (H312) Acute Tox. 4 (H332) Skin Corr. 1B (H314) Eye Dam. 1 (H318)

SAFETY DATA SHEET

4-Nitrobenzenediazonium tetrafluoroborate

Revision Date 07-Jan-2021

Reach Registration Number

-

Full text of Hazard Statements: see section 16

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

General Advice	Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.
Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required. Keep eye wide open while rinsing.
Skin Contact	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Call a physician immediately.
Ingestion	Immediate medical attention is required. Do NOT induce vomiting. Drink plenty of water. Never give anything by mouth to an unconscious person.
Inhalation	Remove to fresh air. If not breathing, give artificial respiration. Call a physician or poison control center immediately. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device.
Self-Protection of the First Aider	Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

4.2. Most important symptoms and effects, both acute and delayed

Causes burns by all exposure routes. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

4.3. Indication of any immediate medical attention and special treatment needed

Notes to Physician Treat symptomatically.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Suitable Extinguishing Media

CO₂, dry chemical, dry sand, alcohol-resistant foam.

Extinguishing media which must not be used for safety reasons

No information available.

5.2. Special hazards arising from the substance or mixture

The product causes burns of eyes, skin and mucous membranes.

Hazardous Combustion Products

Carbon monoxide (CO), Carbon dioxide (CO₂), Nitrogen oxides (NO_x), Oxides of boron, Hydrogen fluoride.

5.3. Advice for firefighters

SAFETY DATA SHEET

4-Nitrobenzenediazonium tetrafluoroborate

Revision Date 07-Jan-2021

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Use personal protective equipment as required. Evacuate personnel to safe areas. Avoid contact with skin, eyes or clothing.

6.2. Environmental precautions

Should not be released into the environment. Do not allow material to contaminate ground water system.

6.3. Methods and material for containment and cleaning up

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

6.4. Reference to other sections

Refer to protective measures listed in Sections 8 and 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe dust. Do not ingest. If swallowed then seek immediate medical assistance.

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice. Keep away from food, drink and animal feeding stuffs. Do not eat, drink or smoke when using this product. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Wash hands before breaks and after work.

7.2. Conditions for safe storage, including any incompatibilities

Corrosives area. Keep containers tightly closed in a dry, cool and well-ventilated place.

Technical Rules for Hazardous Substances (TRGS) 510 Storage Class (LGK)
(Germany)

Class 8A

7.3. Specific end use(s)

Use in laboratories

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Exposure limits

This product, as supplied, does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies

Biological limit values

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

SAFETY DATA SHEET

4-Nitrobenzenediazonium tetrafluoroborate

Revision Date 07-Jan-2021

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents.

MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Derived No Effect Level (DNEL) No information available

<u>Route of exposure</u>	Acute effects (local)	Acute effects (systemic)	Chronic effects (local)	Chronic effects (systemic)
Oral Dermal Inhalation				

Predicted No Effect Concentration (PNEC) No information available.

8.2. Exposure controls

Engineering Measures

Ensure that eyewash stations and safety showers are close to the workstation location.

Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber Neoprene Natural rubber PVC	See manufacturers recommendations	-	EN 374	(minimum requirement)

Skin and body protection Long sleeved clothing

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Particulates filter conforming to EN 143

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Particle filtering: EN149:2001
When RPE is used a face piece Fit Test should be conducted

SAFETY DATA SHEET

4-Nitrobenzenediazonium tetrafluoroborate

Revision Date 07-Jan-2021

Environmental exposure controls No information available.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical State	Solid	
Appearance	Beige	
Odor	No information available	
Odor Threshold	No data available	
Melting Point/Range	144 °C / 291.2 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flammability (liquid)	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Flash Point	No information available	Method - No information available
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
pH	No information available	
Viscosity	Not applicable	Solid
Water Solubility	No information available	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Vapor Pressure	No information available	
Density / Specific Gravity	No data available	
Bulk Density	No data available	
Vapor Density	Not applicable	Solid
Particle characteristics	No data available	

9.2. Other information

Molecular Formula	C6H4BF4N3O2
Molecular Weight	236.92
Evaporation Rate	Not applicable - Solid

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity
None known, based on information available

10.2. Chemical stability
Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous Polymerization No information available.
Hazardous Reactions None under normal processing.

10.4. Conditions to avoid
Incompatible products. Excess heat.

10.5. Incompatible materials
Oxidizing agent.

SAFETY DATA SHEET

4-Nitrobenzenediazonium tetrafluoroborate

Revision Date 07-Jan-2021

10.6. Hazardous decomposition products

Carbon monoxide (CO). Carbon dioxide (CO₂). Nitrogen oxides (NO_x). Oxides of boron.
Hydrogen fluoride.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Product Information

(a) acute toxicity;

Oral	Category 4
Dermal	Category 4
Inhalation	Category 4

(b) skin corrosion/irritation; Category 1 B

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Respiratory	No data available
Skin	No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available

Target Organs No information available.

(j) aspiration hazard; Not applicable
Solid

Symptoms / effects, both acute and delayed

Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated. Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation.

11.2. Information on other hazards

Endocrine Disrupting Properties

Assess endocrine disrupting properties for human health. This product does not contain any known or suspected endocrine disruptors.

SECTION 12: ECOLOGICAL INFORMATION

ALFAAH55315

SAFETY DATA SHEET

4-Nitrobenzenediazonium tetrafluoroborate

Revision Date 07-Jan-2021

12.1. Toxicity

Ecotoxicity effects

Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.

12.2. Persistence and degradability No information available

12.3. Bioaccumulative potential No information available

12.4. Mobility in soil No information available

12.5. Results of PBT and vPvB assessment No data available for assessment.

12.6. Endocrine disrupting properties

Endocrine Disruptor Information

This product does not contain any known or suspected endocrine disruptors

12.7. Other adverse effects

Persistent Organic Pollutant

This product does not contain any known or suspected substance

Ozone Depletion Potential

This product does not contain any known or suspected substance

SECTION 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Waste from Residues/Unused Products

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging

Dispose of this container to hazardous or special waste collection point.

European Waste Catalogue (EWC)

According to the European Waste Catalog, Waste Codes are not product specific, but application specific.

Other Information

Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms.

SECTION 14: TRANSPORT INFORMATION

IMDG/IMO

14.1. UN number

UN2923

14.2. UN proper shipping name

Corrosive solid, toxic, n.o.s

Technical Shipping Name

4-Nitrobenzenediazonium tetrafluoroborate

14.3. Transport hazard class(es)

8

Subsidiary Hazard Class

6.1

14.4. Packing group

II

ADR

14.1. UN number

UN2923

ALFAAH55315

SAFETY DATA SHEET

4-Nitrobenzenediazonium tetrafluoroborate

Revision Date 07-Jan-2021

14.2. UN proper shipping name	Corrosive solid, toxic, n.o.s
Technical Shipping Name	4-Nitrobenzenediazonium tetrafluoroborate
14.3. Transport hazard class(es)	8
Subsidiary Hazard Class	6.1
14.4. Packing group	II

IATA

14.1. UN number	UN2923
14.2. UN proper shipping name	Corrosive solid, toxic, n.o.s
Technical Shipping Name	4-Nitrobenzenediazonium tetrafluoroborate
14.3. Transport hazard class(es)	8
Subsidiary Hazard Class	6.1
14.4. Packing group	II

14.5. Environmental hazards	No hazards identified
14.6. Special precautions for user	No special precautions required
14.7. Maritime transport in bulk according to IMO instruments	Not applicable, packaged goods

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

International Inventories

X = listed, Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), China (IECSC), Japan (ENCS), Australia (AICS), Korea (ECL).

Component	EINECS	ELINCS	NLP	TSCA	DSL	NDSL	PICCS	ENCS	IECSC	AICS	KECL
Benzenediazonium, 4-nitro-, tetrafluoroborate(1-)	207-261-1	-		X	X	-	X	-	-	X	2014-3-5 936

Regulation (EC) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of dangerous chemicals
Not applicable

National Regulations

WGK Classification Water endangering class = 3 (self classification)

UK - Take note of Control of Substances Hazardous to Health Regulations (COSHH) 2002 and 2005 Amendment

15.2. Chemical safety assessment

A Chemical Safety Assessment/Report (CSA/CSR) has not been conducted

SECTION 16: OTHER INFORMATION

Full text of H-Statements referred to under sections 2 and 3

H302 - Harmful if swallowed

H312 - Harmful in contact with skin

SAFETY DATA SHEET

4-Nitrobenzenediazonium tetrafluoroborate

Revision Date 07-Jan-2021

H332 - Harmful if inhaled
H314 - Causes severe skin burns and eye damage
H318 - Causes serious eye damage

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer
Predicted No Effect Concentration (PNEC)

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC (volatile organic compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Prepared By

Health, Safety and Environmental Department

Revision Date

07-Jan-2021

Revision Summary

SDS authoring systems update, replaces ChemGes SDS No. 456-27-9.

**This safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006
COMMISSION REGULATION (EU) 2020/878 amending Annex II to Regulation (EC) No
1907/2006**

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet