

ALFAAL13200

Chloroform, stabilized

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: 氯仿
Product Description: Chloroform, stabilized

Cat No. : L13200
Synonyms Methane trichloride; Methenyl trichloride; Formyl trichloride
CAS No 67-66-3
Molecular Formula C H Cl₃

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against

SECTION 2. HAZARD IDENTIFICATION

Physical State
Liquid

Appearance
Colorless

Odor
aromatic sweet

Emergency Overview

Toxic if inhaled. Causes skin irritation. Causes serious eye irritation. Suspected of causing cancer. Suspected of damaging fertility or the unborn child. Causes damage to organs through prolonged or repeated exposure. Harmful if swallowed. May cause drowsiness and dizziness.

Classification of the substance or mixture

Acute Oral Toxicity	Category 4
Acute Inhalation Toxicity - Vapors	Category 3
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Carcinogenicity	Category 2
Reproductive Toxicity	Category 2
Specific target organ toxicity - (single exposure)	Category 3
Specific target organ toxicity - (repeated exposure)	Category 1

Label Elements

Chloroform, stabilized

**Signal Word****Danger****Hazard Statements**

H331 - Toxic if inhaled
H315 - Causes skin irritation
H319 - Causes serious eye irritation
H351 - Suspected of causing cancer
H372 - Causes damage to organs through prolonged or repeated exposure
H302 - Harmful if swallowed
H336 - May cause drowsiness or dizziness
H361 - Suspected of damaging fertility or the unborn child

Precautionary Statements**Prevention**

P201 - Obtain special instructions before use
P202 - Do not handle until all safety precautions have been read and understood
P260 - Do not breathe dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling
P270 - Do not eat, drink or smoke when using this product
P271 - Use only outdoors or in a well-ventilated area
P280 - Wear eye protection/ face protection

Response

P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell
P302 + P352 - IF ON SKIN: Wash with plenty of soap and water
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P308 + P313 - IF exposed or concerned: Get medical advice/attention
P330 - Rinse mouth
P332 + P313 - If skin irritation occurs: Get medical advice/attention
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed
P405 - Store locked up

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

Toxic if inhaled. Harmful if inhaled. Causes skin irritation. Causes serious eye irritation. Suspected of causing cancer. Suspected of damaging fertility or the unborn child. Causes damage to organs through prolonged or repeated exposure. Harmful if swallowed. May cause drowsiness or dizziness.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its volatility. The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

Other Hazards

Cardiac and respiratory depression Overexposure may cause decreased heart rate, decreased blood pressure, heart block, and cardiac failure

Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chloroform, stabilized

Component	CAS No	Weight %
Chloroform	67-66-3	>99

Note Amylene is used as a stabilizer, but there is evidence that it may not prevent phosgene generation. Chloroform stabilized with amylene should be tested for phosgene content.

SECTION 4. FIRST AID MEASURES**General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

Ingestion

Do NOT induce vomiting. Call a physician or poison control center immediately.

Most important symptoms and effects

. Symptoms of overexposure are dizziness, headache, tiredness, nausea, unconsciousness, cessation of breathing: Causes central nervous system depression

Self-Protection of the First Aider

Use personal protective equipment as required.

Notes to Physician

Treat symptomatically. Signs of overdose include stupor and respiratory depression. Symptoms may be delayed.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Substance is nonflammable; use agent most appropriate to extinguish surrounding fire.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Non-combustible, substance itself does not burn but may decompose upon heating to produce corrosive and/or toxic fumes.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Use personal protective equipment as required. Ensure adequate ventilation. Keep people away from and upwind of spill/leak.

Chloroform, stabilized

Evacuate personnel to safe areas.

Environmental Precautions

Should not be released into the environment.

Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE

Handling

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance.

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place. Protect from direct sunlight. Store under an inert atmosphere. Protect from moisture.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

Component	China	Taiwan	Thailand	Hong Kong
Chloroform	TWA: 20 mg/m ³ STEL: 40 mg/m ³	-	Ceiling: 50 ppm	TWA: 10 ppm TWA: 49 mg/m ³

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Chloroform	TWA: 10 ppm	(Vacated) TWA: 2 ppm (Vacated) TWA: 9.78 mg/m ³ Ceiling: 50 ppm Ceiling: 240 mg/m ³	IDLH: 500 ppm STEL: 2 ppm STEL: 9.78 mg/m ³	TWA: 2 ppm TWA: 9.9 mg/m ³ STEL: 6 ppm STEL: 29.7 mg/m ³	TWA: 2 ppm 8 hr TWA: 10 mg/m ³ 8 hr Possibility of significant uptake through the skin

Legend

NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

Exposure Controls**Engineering Measures**

Use only under a chemical fume hood. Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Chloroform, stabilized

Eye Protection Goggles (European standard - EN 166)**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Viton (R)	> 480 minutes	-	Level 6 EN 374	As tested under EN374-3 Determination of Resistance to Permeation by Chemicals
Neoprene	< 25 minutes	0.45 mm		
Butyl rubber	< 15 minutes	0.35 mm		

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: low boiling organic solvent Type AX Brown conforming to EN371**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
When RPE is used a face piece Fit Test should be conducted**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.**Environmental exposure controls** Prevent product from entering drains.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Colorless	
Physical State	Liquid	
Odor	aromatic sweet	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	-63 °C / -81.4 °F	
Softening Point	No data available	
Boiling Point/Range	61 °C / 141.8 °F	
Flash Point	No information available	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	213 mbar @ 20 °C	
Vapor Density	No data available	(Air = 1.0)
Specific Gravity / Density	1.480	
Bulk Density	Not applicable	Liquid
Water Solubility	8 g/L (20°C)	
Solubility in other solvents	No information available	

Partition Coefficient (n-octanol/water)

Component	log Pow
Chloroform	2
Autoignition Temperature	No data available
Decomposition Temperature	No data available
Viscosity	0.56 mPa s at 20 °C
Explosive Properties	No information available
Oxidizing Properties	No information available

Molecular Formula	C H Cl ₃
Molecular Weight	119.38
VOC Content(%)	100

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions. UNSTABLE (REACTIVE) UPON DEPLETION OF INHIBITOR. Light sensitive.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	Hazardous polymerization does not occur.
Conditions to Avoid	Incompatible products. Heat, flames and sparks. Excess heat. Exposure to light. Protect from moisture.
Materials to avoid	Strong oxidizing agents. Alkali metals. Aluminium. Acetone.
Hazardous Decomposition Products	Carbon monoxide (CO). Carbon dioxide (CO ₂). Phosgene. Hydrogen chloride gas.

SECTION 11. TOXICOLOGICAL INFORMATION**Product Information****(a) acute toxicity;**

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Chloroform	LD50 = 908 mg/kg (rat) LD50 = 695 mg/kg (Rat) LD50 = 450 mg/kg (Rat)	LD50 > 20 g/kg (Rabbit)	LC50 = 10.5 mg/L (Rat) 4 h

(b) skin corrosion/irritation; Category 2**(c) serious eye damage/irritation;** Category 2**(d) respiratory or skin sensitization;**

Respiratory	Based on available data, the classification criteria are not met
Skin	Based on available data, the classification criteria are not met

(e) germ cell mutagenicity; Based on available data, the classification criteria are not met**(f) carcinogenicity;** Category 2

The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	EU	UK	Germany	IARC
Chloroform				Group 2B

Chloroform, stabilized

(g) reproductive toxicity; Reproductive Effects Developmental Effects Teratogenicity	Category 2 Experiments have shown reproductive toxicity effects on laboratory animals. Developmental effects have occurred in experimental animals. Study result . negative.
(h) STOT-single exposure; Results / Target organs	Category 3 Central nervous system (CNS)
(i) STOT-repeated exposure; Study result Route of exposure Target Organs	Category 1 LOAEL = 15 mg/kg bw/day NOAEC = 25 mg/m ³ Inhalation Liver, Kidney.
(j) aspiration hazard; Other Adverse Effects	Based on available data, the classification criteria are not met Tumorigenic effects have been reported in experimental animals.
Symptoms / effects,both acute and delayed	Symptoms of overexposure are dizziness, headache, tiredness, nausea, unconsciousness, cessation of breathing: Causes central nervous system depression

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Do not empty into drains. The product contains following substances which are hazardous for the environment. Contains a substance which is:. Harmful to aquatic organisms.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Chloroform	LC50: = 300 mg/L, 96h static (Poecilia reticulata) LC50: = 18 mg/L, 96h flow-through (Lepomis macrochirus) LC50: = 18 mg/L, 96h flow-through (Oncorhynchus mykiss) LC50: = 71 mg/L, 96h flow-through (Pimephales promelas)	EC50 = 28.9 mg/L/48h	EC50 = 560 mg/L/48h	Photobacterium phosphoreum: EC50 = 520 mg/L/5 min Photobacterium phosphoreum: EC50 = 670 mg/L/15 min Photobacterium phosphoreum: EC50 = 670 mg/L/30min

Persistence and Degradability Product is biodegradable
Persistence Persistence is unlikely, based on information available.
Degradation in sewage treatment plant Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Chloroform	2	1.4 - 13 dimensionless

Mobility in soil The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces Will likely be mobile in the environment due to its volatility Disperses rapidly in air

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance

Chloroform, stabilized

Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point.

Other Information Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No UN1888
Proper Shipping Name Chloroform
Hazard Class 6.1
Packing Group III

IMDG/IMO

UN-No UN1888
Proper Shipping Name Chloroform
Hazard Class 6.1
Packing Group III

IATA

UN-No UN1888
Proper Shipping Name Chloroform
Hazard Class 6.1
Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Chloroform	X	X	X	X	200-663-8	X	X	X	X	X	X	X

Note Amylene is used as a stabilizer, but there is evidence that it may not prevent phosgene generation. Chloroform stabilized with amylene should be tested for phosgene content.

National Regulations

Chloroform, stabilized

Component	Toxic Chemical Substances Control Act
Chloroform 67-66-3 (>99)	Class I (50 wt%) TRQ = 50 kg

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Creation Date 20-Oct-2009
Revision Date 23-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical incident response training.

Fire prevention and fighting, identifying hazards and risks, static electricity, explosive atmospheres posed by vapours and dusts.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet