

ALFAAL14619

## Isoprene

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

<b>产品说明:</b> Product Description:	<b>异戊二烯</b> Isoprene
<b>Cat No. :</b> <b>Synonyms</b>	<b>L14619</b> 2-Methyl-1,3-butadiene; 1,3-Butadiene, 2-Methyl-; 2-Methylbutadiene; 3-Methyl-1,3-Butadiene, Methylbivinyll; Beta-Methylbivinyll; Hemiterpene
<b>CAS No</b> <b>Molecular Formula</b>	78-79-5 C5 H8
<b>Supplier</b>	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
<b>Emergency Telephone Number</b>	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
<b>E-mail address</b>	begel.sdsdesk@thermofisher.com
<b>Recommended Use</b> <b>Uses advised against</b>	Laboratory chemicals. No Information available

### SECTION 2. HAZARD IDENTIFICATION

<b>Physical State</b> Liquid	<b>Appearance</b> Light yellow	<b>Odor</b> mild aromatic
<b>Emergency Overview</b>		
Extremely flammable liquid and vapor. Suspected of causing genetic defects. Toxic to aquatic life with long lasting effects. May cause cancer. Sensitivity to light. Air sensitive.		

#### Classification of the substance or mixture

Flammable liquids.	Category 1
Germ Cell Mutagenicity	Category 2
Carcinogenicity	Category 1B
Acute aquatic toxicity	Category 2
Chronic aquatic toxicity	Category 2

#### Label Elements

## Isoprene



## Signal Word

## Danger

## Hazard Statements

H224 - Extremely flammable liquid and vapor  
 H341 - Suspected of causing genetic defects  
 H350 - May cause cancer  
 H401 - Toxic to aquatic life  
 H411 - Toxic to aquatic life with long lasting effects

## Precautionary Statements

## Prevention

P201 - Obtain special instructions before use  
 P202 - Do not handle until all safety precautions have been read and understood  
 P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
 P240 - Ground and bond container and receiving equipment  
 P241 - Use explosion-proof electrical/ ventilating/ lighting equipment  
 P233 - Keep container tightly closed  
 P242 - Use non-sparking tools  
 P243 - Take action to prevent static discharges  
 P280 - Wear protective gloves/protective clothing/eye protection/face protection

## Response

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower  
 P308 + P313 - IF exposed or concerned: Get medical advice/attention  
 P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish

## Storage

P403 + P235 - Store in a well-ventilated place. Keep cool

## Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

## Physical and Chemical Hazards

Extremely flammable. Vapors may cause flash fire or explosion.

## Health Hazards

Suspected of causing genetic defects. May cause cancer.

## Environmental hazards

Toxic to aquatic life with long lasting effects. Will likely be mobile in the environment due to its volatility. The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

## Other Hazards

Contains a known or suspected endocrine disruptor. Contains a substance on the National Authorities Endocrine Disruptor Lists.

## SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Isoprene	78-79-5	>95
4-tert-Butyl catechol	98-29-3	0.01

## SECTION 4. FIRST AID MEASURES

## General Advice

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

## Isoprene

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

**Ingestion**

Do NOT induce vomiting. Call a physician or poison control center immediately.

**Most important symptoms and effects**

Difficulty in breathing. Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Extremely flammable. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back. Containers may explode when heated. Vapors may form explosive mixtures with air.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas. Remove all sources of ignition. Take precautionary measures against static discharges.

**Environmental Precautions**

Do not flush into surface water or sanitary sewer system.

**Methods for Containment and Clean Up**

Keep in suitable, closed containers for disposal. Soak up with inert absorbent material. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

## Isoprene

## SECTION 7. HANDLING AND STORAGE

**Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition. Use spark-proof tools and explosion-proof equipment. Use only non-sparking tools. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Take precautionary measures against static discharges.

**Storage**

Refrigerator/flammables. Store under an inert atmosphere. Keep container tightly closed. Protect from direct sunlight. Keep away from heat, sparks and flame.

**Specific Use(s)**

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

**Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Use explosion-proof electrical/ventilating/lighting equipment. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Nitrile rubber				
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

## Isoprene

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Organic gases and vapours filter Type A Brown conforming to EN14387

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141  
 When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** Prevent product from entering drains. Do not allow material to contaminate ground water system.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Light yellow	
<b>Physical State</b>	Liquid	
<b>Odor</b>	mild aromatic	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	-146 °C / -230.8 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	34 °C / 93.2 °F	@ 760 mmHg
<b>Flash Point</b>	-48 °C / -54.4 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	<b>Lower</b> 1 <b>Upper</b> 9.7	
<b>Vapor Pressure</b>	532 hPa @ 20 °C	
<b>Vapor Density</b>	2.35	(Air = 1.0)
<b>Specific Gravity / Density</b>	0.680	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	0.7 mg/L (25°C)	practically insoluble
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
Isoprene	2.42	
4-tert-Butyl catechol	1.98	
<b>Autoignition Temperature</b>	220 °C / 428 °F	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	0.225 cP at 15 °C	
<b>Explosive Properties</b>		Vapors may form explosive mixtures with air
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C5 H8	
<b>Molecular Weight</b>	68.11	

## SECTION 10. STABILITY AND REACTIVITY

**Stability** Sensitivity to light. Air sensitive.

**Hazardous Reactions** No information available.

**Hazardous Polymerization** Hazardous polymerization may occur upon depletion of inhibitor.

## Isoprene

**Conditions to Avoid** Keep away from open flames, hot surfaces and sources of ignition. Excess heat. Incompatible products. Exposure to light. Exposure to air.

**Materials to avoid** Strong bases. Acids. Alcohols. Ammonia. Halogens. oxygen. Acid chlorides. Metals. Strong oxidizing agents. Reducing Agent.

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

**(a) acute toxicity;**  
**Toxicology data for the components**

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Isoprene	2043-2210 mg/kg ( Rat )	>1 mL/kg ( Rat )	LC50 = 180 mg/L ( Rat ) 4 h
4-tert-Butyl catechol	815 mg/kg ( Rat )	1331 mg/kg ( Rat )	

**(b) skin corrosion/irritation;** No data available

**(c) serious eye damage/irritation;** No data available

**(d) respiratory or skin sensitization;**  
Respiratory No data available  
Skin No data available

**(e) germ cell mutagenicity;** Category 2  
Animal experiments showed mutagenic and teratogenic effects

**(f) carcinogenicity;** Category 1B  
Limited evidence of a carcinogenic effect The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	EU	UK	Germany	IARC
Isoprene	Carc Cat. 1B			Group 2B

**(g) reproductive toxicity;** No data available

**(h) STOT-single exposure;** No data available

**(i) STOT-repeated exposure;** No data available  
**Target Organs** No information available.

**(j) aspiration hazard;** No data available

**Symptoms / effects, both acute and delayed** Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

## SECTION 12. ECOLOGICAL INFORMATION

## Isoprene

**Ecotoxicity effects**

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Isoprene	LC50: 32.5 - 50.15 mg/L, 96h static (Lepomis macrochirus) LC50: 188.77 - 305.14 mg/L, 96h static (Poecilia reticulata) LC50: 58.75 - 95.32 mg/L, 96h static (Pimephales promelas)	EC50: = 140 mg/L, 48h (Daphnia magna)	EC50: > 1000 mg/L, 96h (Scenedesmus quadricauda)	
4-tert-Butyl catechol	LC50 = 0.12 mg/L 96h	EC50=0.48 mg/L 48h		

**Persistence and Degradability****Persistence****Degradation in sewage treatment plant**

Not readily biodegradable

Persistence is unlikely, based on information available.

Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Bioaccumulative Potential**

Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Isoprene	2.42	No data available
4-tert-Butyl catechol	1.98	No data available

**Mobility in soil**

The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces. Will likely be mobile in the environment due to its volatility. Disperses rapidly in air.

**Endocrine Disruptor Information**

This product does not contain any known or suspected endocrine disruptors

**Persistent Organic Pollutant**

This product does not contain any known or suspected substance

**Ozone Depletion Potential**

This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS****Waste from Residues/Unused Products**

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging**

Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

**Other Information**

Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Can be landfilled or incinerated, when in compliance with local regulations. Do not let this chemical enter the environment. Do not empty into drains.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

UN-No	UN1218
Proper Shipping Name	ISOPRENE, STABILIZED
Hazard Class	3
Packing Group	I

## Isoprene

**IMDG/IMO**

UN-No UN1218  
 Proper Shipping Name ISOPRENE, STABILIZED  
 Hazard Class 3  
 Packing Group I

**IATA**

UN-No UN1218  
 Proper Shipping Name ISOPRENE, STABILIZED  
 Hazard Class 3  
 Packing Group I

**Special Precautions for User** Inhibitors have been added to stabilize this product Inhibitor levels should be maintained  
 Hazardous polymerization may occur upon depletion of inhibitor

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Isoprene	X	X	X	X	201-143-3	X	X	X	X	X	X	KE-23526
4-tert-Butyl catechol	-	-	X	X	202-653-9	X	X	X	X	X	X	KE-11368

**National Regulations****SECTION 16. OTHER INFORMATION**

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 09-Feb-2012  
**Revision Date** 16-May-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical incident response training.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration



**Isoprene**

**RPE** - Respiratory Protective Equipment  
**LC50** - Lethal Concentration 50%  
**NOEC** - No Observed Effect Concentration  
**PBT** - Persistent, Bioaccumulative, Toxic

**LD50** - Lethal Dose 50%  
**EC50** - Effective Concentration 50%  
**POW** - Partition coefficient Octanol:Water  
**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association  
**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road  
**OECD** - Organisation for Economic Co-operation and Development  
**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code  
**MARPOL** - International Convention for the Prevention of Pollution from Ships  
**ATE** - Acute Toxicity Estimate  
**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>  
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

<b>Physical hazards</b>	On basis of test data
<b>Health Hazards</b>	Calculation method
<b>Environmental hazards</b>	Calculation method

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**