

ALFAAL17891

Tetra-n-butylammonium dihydrogen trifluoride, 50-55% w/w solution in 1,2-dichloroethane

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: 四正丁基二氢三氟化铵
Product Description: Tetra-n-butylammonium dihydrogen trifluoride, 50-55% w/w solution in 1,2-dichloroethane

Cat No. : L17891
Molecular Formula C16 H38 F3 N

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Liquid

Appearance
Dark yellow

Odor
Odorless

Emergency Overview

Highly flammable liquid and vapor. May cause respiratory irritation. Harmful if swallowed. Harmful in contact with skin. Causes severe skin burns and eye damage. Harmful if inhaled. May cause cancer. Moisture sensitive.

Classification of the substance or mixture

Flammable liquids.	Category 2
Acute Oral Toxicity	Category 4
Acute Dermal Toxicity	Category 4
Acute Inhalation Toxicity - Vapors	Category 4
Skin Corrosion/Irritation	Category 1 C
Serious Eye Damage/Eye Irritation	Category 1
Carcinogenicity	Category 1B
Specific target organ toxicity - (single exposure)	Category 3

Label Elements

Tetra-n-butylammonium dihydrogenotrifluoride, 50-55% w/w solution in 1,2-dichloroethane

**Signal Word****Danger****Hazard Statements**

H225 - Highly flammable liquid and vapor
 H335 - May cause respiratory irritation
 H314 - Causes severe skin burns and eye damage
 H350 - May cause cancer
 H302 + H312 + H332 - Harmful if swallowed, in contact with skin or if inhaled

Precautionary Statements**Prevention**

P201 - Obtain special instructions before use
 P202 - Do not handle until all safety precautions have been read and understood
 P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
 P240 - Ground and bond container and receiving equipment
 P242 - Use non-sparking tools
 P243 - Take action to prevent static discharges
 P260 - Do not breathe dust/fume/gas/mist/vapors/spray
 P264 - Wash face, hands and any exposed skin thoroughly after handling
 P270 - Do not eat, drink or smoke when using this product
 P271 - Use only outdoors or in a well-ventilated area
 P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
 P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
 P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 P310 - Immediately call a POISON CENTER or doctor
 P330 - Rinse mouth
 P331 - Do NOT induce vomiting
 P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
 P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Vapors may cause flash fire or explosion. Highly flammable.

Health Hazards

May cause respiratory irritation. Harmful if swallowed. Harmful in contact with skin. Corrosive. Causes skin and eye burns. Harmful if inhaled. May cause cancer.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. .

Other Hazards

Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Ethylene dichloride	107-06-2	45-50
1-Butanaminium, N,N,N-tributyl-, (dihydrogen trifluoride)	99337-56-1	50-55

Tetra-n-butylammonium dihydrogenotrifluoride, 50-55% w/w solution in 1,2-dichloroethane

SECTION 4. FIRST AID MEASURES**Eye Contact**

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

Inhalation

Remove to fresh air. Immediate medical attention is required. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. If not breathing, give artificial respiration.

Ingestion

Do NOT induce vomiting. Call a physician or poison control center immediately.

Most important symptoms and effects

Difficulty in breathing. Causes burns by all exposure routes. Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Carbon dioxide (CO₂). Dry chemical. Chemical foam. Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Flammable. Vapors may travel to source of ignition and flash back. Containers may explode when heated. Vapors may form explosive mixtures with air.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid contact with skin, eyes or clothing. Remove all sources of ignition. Take precautionary measures against static discharges. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas.

Environmental Precautions

See Section 12 for additional Ecological Information.

Tetra-n-butylammonium dihydrogenotrifluoride, 50-55% w/w solution in 1,2-dichloroethane

Methods for Containment and Clean Up

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Ensure adequate ventilation. Wear personal protective equipment/face protection. Do not breathe mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Handle product only in closed system or provide appropriate exhaust ventilation. Use spark-proof tools and explosion-proof equipment. Use only non-sparking tools. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep away from open flames, hot surfaces and sources of ignition. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Take precautionary measures against static discharges.

Storage

Refrigerator/flammables. Corrosives area. Keep in a dry place. Keep container tightly closed. Keep away from heat, sparks and flame. Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
Ethylene dichloride	TWA: 7 mg/m ³ STEL: 15 mg/m ³	TWA: 10 ppm TWA: 40 mg/m ³	Ceiling: 100 ppm STEL: 200 ppm TWA: 50 ppm	TWA: 10 ppm TWA: 40 mg/m ³

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Ethylene dichloride	TWA: 10 ppm	(Vacated) TWA: 1 ppm (Vacated) TWA: 4 mg/m ³ Ceiling: 100 ppm (Vacated) STEL: 2 ppm (Vacated) STEL: 8 mg/m ³ TWA: 50 ppm	IDLH: 50 ppm TWA: 1 ppm TWA: 4 mg/m ³ STEL: 2 ppm STEL: 8 mg/m ³	STEL: 15 ppm 15 min STEL: 63 mg/m ³ 15 min TWA: 5 ppm 8 hr TWA: 21 mg/m ³ 8 hr Carc. Skin	TWA: 8.2 mg/m ³ (8h) TWA: 2 ppm (8h) Skin

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

Exposure Controls**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Use explosion-proof electrical/ventilating/lighting equipment. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Tetra-n-butylammonium dihydrogenotrifluoride, 50-55% w/w solution in 1,2-dichloroethane

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Viton (R)	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: low boiling organic solvent Type AX Brown conforming to EN371 or Organic gases and vapours filter Type A Brown conforming to EN14387**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
When RPE is used a face piece Fit Test should be conducted**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.**Environmental exposure controls** No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Dark yellow	
Physical State	Liquid	
Odor	Odorless	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	13 °C / 55.4 °F	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	10.4	(Air = 1.0)
Specific Gravity / Density	No data available	
Bulk Density	Not applicable	Liquid
Water Solubility	No information available	
Solubility in other solvents	No information available	

Tetra-n-butylammonium dihydrogenotrifluoride, 50-55% w/w solution in 1,2-dichloroethane

Partition Coefficient (n-octanol/water)

Component	log Pow	
Ethylene dichloride	1.45	
Autoignition Temperature	415 °C / 779 °F	
Decomposition Temperature	No data available	
Viscosity	No data available	
Explosive Properties		Vapors may form explosive mixtures with air
Oxidizing Properties	No information available	

Molecular Formula	C16 H38 F3 N
Molecular Weight	301.47

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions. Moisture sensitive.
Hazardous Reactions	No information available.
Hazardous Polymerization	No information available.
Conditions to Avoid	Incompatible products. Exposure to moist air or water. Keep away from open flames, hot surfaces and sources of ignition.
Materials to avoid	Strong oxidizing agents.
Hazardous Decomposition Products	Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO ₂). Gaseous hydrogen fluoride (HF).

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;
Toxicology data for the components

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Ethylene dichloride	LD50 = 680 mg/kg (Rat)	LD50 = 4890 mg/kg (Rabbit)	LC50 = 4 mg/L (Rat) 6 h

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;
Respiratory No data available
Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

Limited evidence of a carcinogenic effect The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	EU	UK	Germany	IARC
Ethylene dichloride	Carc Cat. 1B		Cat. 2	Group 2B

Tetra-n-butylammonium dihydrogentrifluoride, 50-55% w/w solution in 1,2-dichloroethane

(g) reproductive toxicity; No data available**(h) STOT-single exposure;** No data available**Results / Target organs** Respiratory system**(i) STOT-repeated exposure;** No data available**Target Organs** No information available.**(j) aspiration hazard;** No data available**Other Adverse Effects** The toxicological properties have not been fully investigated.**Symptoms / effects,both acute and delayed** Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation**SECTION 12. ECOLOGICAL INFORMATION****Ecotoxicity effects** Do not empty into drains. .

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Ethylene dichloride	Oncorhynchus mykiss: LC50 = 225 mg/L 96h	EC50 = 137 mg/L 48h	EC50 = >433 mg/L 96h	EC50 = 1100 mg/L 15 min EC50 = 158 mg/L 5 min EC50 = 696 mg/L 5 min EC50 = 918 mg/L 30 min

Persistence and Degradability No information available**Bioaccumulative Potential** No information available

Component	log Pow	Bioconcentration factor (BCF)
Ethylene dichloride	1.45	2 dimensionless

Mobility in soil No information available**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance**SECTION 13. DISPOSAL CONSIDERATIONS****Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point.**Other Information** Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms.

Tetra-n-butylammonium dihydrogenotrifluoride, 50-55% w/w solution in 1,2-dichloroethane

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No UN2924
Proper Shipping Name Flammable liquid, corrosive, n.o.s.
Technical Shipping Name Tetrabutylammonium dihydrogenotrifluoride, 1,2-Dichloroethane
Hazard Class 3
Subsidiary Hazard Class 8
Packing Group II

IMDG/IMO

UN-No UN2924
Proper Shipping Name Flammable liquid, corrosive, n.o.s.
Technical Shipping Name Tetrabutylammonium dihydrogenotrifluoride, 1,2-Dichloroethane
Hazard Class 3
Subsidiary Hazard Class 8
Packing Group II

IATA

UN-No UN2924
Proper Shipping Name Flammable liquid, corrosive, n.o.s.
Technical Shipping Name Tetrabutylammonium dihydrogenotrifluoride, 1,2-Dichloroethane
Hazard Class 3
Subsidiary Hazard Class 8
Packing Group II

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Ethylene dichloride	X	X	X	X	203-458-1	X	X	X	X	X	X	KE-10121
1-Butanaminium, N,N,N-tributyl-, (dihydrogen trifluoride)	-	-	X	-	-	-	-	-	-	-	-	-

National Regulations

Component	Toxic Chemical Substances Control Act
Ethylene dichloride 107-06-2 (45-50)	Class IV (15 wt%)

SECTION 16. OTHER INFORMATION

Tetra-n-butylammonium dihydrogenotrifluoride, 50-55% w/w solution in 1,2-dichloroethane

Prepared By	Health, Safety and Environmental Department
Creation Date	21-Mar-2011
Revision Date	08-May-2024
Revision Summary	New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical incident response training.

Fire prevention and fighting, identifying hazards and risks, static electricity, explosive atmospheres posed by vapours and dusts.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Physical hazards	On basis of test data
Health Hazards	Calculation method
Environmental hazards	Calculation method

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet