

## SAFETY DATA SHEET

Revision Date 04-Mar-2024

Revision Number 5

### 1. Identification

**Product Name** 1-Methylindole

**Cat No. :** AC186300000; AC186300050; AC186300250; AC186301000

**CAS No** 603-76-9

**Synonyms** 1H-Indole, 1-methyl-

**Recommended Use** Laboratory chemicals.

**Uses advised against** Food, drug, pesticide or biocidal product use.

#### Details of the supplier of the safety data sheet

##### Company

Fisher Scientific Company  
One Reagent Lane  
Fair Lawn, NJ 07410  
Tel: (201) 796-7100

Acros Organics  
One Reagent Lane  
Fair Lawn, NJ 07410

##### **Emergency Telephone Number**

For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

### 2. Hazard(s) identification

#### **Classification**

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Specific target organ toxicity (single exposure)	Category 3
Target Organs - Respiratory system.	

#### Label Elements

##### **Signal Word**

Warning

##### **Hazard Statements**

Causes skin irritation  
Causes serious eye irritation

May cause respiratory irritation



### Precautionary Statements

#### Prevention

Wash face, hands and any exposed skin thoroughly after handling  
 Wear protective gloves/protective clothing/eye protection/face protection  
 Avoid breathing dust/fume/gas/mist/vapors/spray  
 Use only outdoors or in a well-ventilated area

#### Inhalation

IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing  
 Call a POISON CENTER or doctor/physician if you feel unwell

#### Skin

IF ON SKIN: Wash with plenty of soap and water  
 If skin irritation occurs: Get medical advice/attention  
 Take off contaminated clothing and wash before reuse

#### Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
 If eye irritation persists: Get medical advice/attention

#### Storage

Store in a well-ventilated place. Keep container tightly closed  
 Store locked up

#### Disposal

Dispose of contents/container to an approved waste disposal plant

#### Hazards not otherwise classified (HNOC)

None identified

#### Other hazards

Stench.

## 3. Composition/Information on Ingredients

Component	CAS No	Weight %
1H-Indole, 1-methyl-	603-76-9	> 98

## 4. First-aid measures

<b>Eye Contact</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>Skin Contact</b>	Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention.
<b>Inhalation</b>	Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Get medical attention.
<b>Ingestion</b>	Clean mouth with water. Get medical attention.
<b>Most important symptoms and effects</b>	No information available.
<b>Notes to Physician</b>	Treat symptomatically

## 5. Fire-fighting measures

**Suitable Extinguishing Media** Water spray. Carbon dioxide (CO<sub>2</sub>). Dry chemical. Chemical foam.

**Unsuitable Extinguishing Media** No information available

**Flash Point** > 112 °C / > 233.6 °F

**Method -** No information available

**Autoignition Temperature** No information available

**Explosion Limits**

**Upper** No data available

**Lower** No data available

**Sensitivity to Mechanical Impact** No information available

**Sensitivity to Static Discharge** No information available

**Specific Hazards Arising from the Chemical**

Keep product and empty container away from heat and sources of ignition.

**Hazardous Combustion Products**

Nitrogen oxides (NO<sub>x</sub>). Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**NFPA**

**Health**  
2

**Flammability**  
1

**Instability**  
0

**Physical hazards**  
N/A

## 6. Accidental release measures

**Personal Precautions** Ensure adequate ventilation. Use personal protective equipment as required.

**Environmental Precautions** See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up** Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal. Do not let this chemical enter the environment.

## 7. Handling and storage

**Handling** Avoid contact with skin and eyes. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance. Handle product only in closed system or provide appropriate exhaust ventilation.

**Storage.** Keep in a dry place. Keep container tightly closed. Keep refrigerated. Incompatible Materials. Strong oxidizing agents.

## 8. Exposure controls / personal protection

**Exposure Guidelines** This product does not contain any hazardous materials with occupational exposure limits established by the region specific regulatory bodies.

**Engineering Measures** Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location.

**Personal Protective Equipment**

<b>Eye/face Protection</b>	Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166.
<b>Skin and body protection</b>	Wear appropriate protective gloves and clothing to prevent skin exposure.
<b>Respiratory Protection</b>	No protective equipment is needed under normal use conditions.
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.

## 9. Physical and chemical properties

<b>Physical State</b>	Liquid
<b>Appearance</b>	Yellow
<b>Odor</b>	Stench
<b>Odor Threshold</b>	No information available
<b>pH</b>	No information available
<b>Melting Point/Range</b>	No data available
<b>Boiling Point/Range</b>	236 - 239 °C / 456.8 - 462.2 °F @ 760 mmHg
<b>Flash Point</b>	> 112 °C / > 233.6 °F
<b>Evaporation Rate</b>	No information available
<b>Flammability (solid,gas)</b>	Not applicable
<b>Flammability or explosive limits</b>	
<b>Upper</b>	No data available
<b>Lower</b>	No data available
<b>Vapor Pressure</b>	No information available
<b>Vapor Density</b>	No information available
<b>Specific Gravity</b>	1.020
<b>Solubility</b>	No information available
<b>Partition coefficient; n-octanol/water</b>	No data available
<b>Autoignition Temperature</b>	No information available
<b>Decomposition Temperature</b>	No information available
<b>Viscosity</b>	No information available
<b>Molecular Formula</b>	C9 H9 N
<b>Molecular Weight</b>	131.18

## 10. Stability and reactivity

<b>Reactive Hazard</b>	None known, based on information available
<b>Stability</b>	Light sensitive.
<b>Conditions to Avoid</b>	Exposure to light. Incompatible products.
<b>Incompatible Materials</b>	Strong oxidizing agents
<b>Hazardous Decomposition Products</b>	Nitrogen oxides (NO <sub>x</sub> ), Carbon monoxide (CO), Carbon dioxide (CO <sub>2</sub> )
<b>Hazardous Polymerization</b>	No information available.
<b>Hazardous Reactions</b>	None under normal processing.

## 11. Toxicological information

### Acute Toxicity

<b>Product Information</b>	No acute toxicity information is available for this product
<b>Component Information</b>	
<b>Toxicologically Synergistic Products</b>	No information available

**Delayed and immediate effects as well as chronic effects from short and long-term exposure**

<b>Irritation</b>	No information available
<b>Sensitization</b>	No information available
<b>Carcinogenicity</b>	The table below indicates whether each agency has listed any ingredient as a carcinogen.

Component	CAS No	IARC	NTP	ACGIH	OSHA	Mexico
1H-Indole, 1-methyl-	603-76-9	Not listed	Not listed	Not listed	Not listed	Not listed

<b>Mutagenic Effects</b>	No information available
<b>Reproductive Effects</b>	No information available.
<b>Developmental Effects</b>	No information available.
<b>Teratogenicity</b>	No information available.
<b>STOT - single exposure</b>	Respiratory system
<b>STOT - repeated exposure</b>	None known
<b>Aspiration hazard</b>	No information available
<b>Symptoms / effects, both acute and delayed</b>	No information available
<b>Endocrine Disruptor Information</b>	No information available
<b>Other Adverse Effects</b>	The toxicological properties have not been fully investigated.

**12. Ecological information****Ecotoxicity**

Do not empty into drains.

<b>Persistence and Degradability</b>	Insoluble in water May persist based on information available.
<b>Bioaccumulation/ Accumulation</b>	No information available.
<b>Mobility</b>	Is not likely mobile in the environment due its low water solubility.

**13. Disposal considerations**

<b>Waste Disposal Methods</b>	Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Chemical waste generators must also consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.
-------------------------------	---

**14. Transport information**

<b>DOT</b>	Not regulated
<b>TDG</b>	Not regulated
<b>IATA</b>	
<b>UN-No</b>	UN3334
<b>Proper Shipping Name</b>	AVIATION REGULATED LIQUID, N.O.S.*
<b>Hazard Class</b>	9
<b>Packing Group</b>	III
<b>IMDG/IMO</b>	Not regulated

**15. Regulatory information****United States of America Inventory**

Component	CAS No	TSCA	TSCA Inventory notification - Active-Inactive	TSCA - EPA Regulatory Flags
1H-Indole, 1-methyl-	603-76-9	X	INACTIVE	-

**Legend:**

TSCA US EPA (TSCA) - Toxic Substances Control Act, (40 CFR Part 710)

X - Listed

-' - Not Listed

**TSCA - Per 40 CFR 751, Regulation of Certain Chemical Substances & Mixtures, Under TSCA Section 6(h) (PBT)** Not applicable

**TSCA 12(b)** - Notices of Export Not applicable

**International Inventories**

Canada (DSL/NDL), Europe (EINECS/ELINCS/NLP), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), China (IECSC), Korea (KECL).

Component	CAS No	DSL	NDL	EINECS	PICCS	ENCS	ISHL	AICS	IECSC	KECL
1H-Indole, 1-methyl-	603-76-9	-	X	210-057-5	-	-		-	-	KE-24307

KECL - NIER number or KE number (<http://ncis.nier.go.kr/en/main.do>)

**U.S. Federal Regulations****SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

**SARA 311/312 Hazard Categories**

Should this product meet EPCRA 311/312 Tier reporting criteria at 40 CFR 370, refer to Section 2 of this SDS for appropriate classifications.

**CWA (Clean Water Act)** Not applicable

**Clean Air Act** Not applicable

**OSHA - Occupational Safety and Health Administration** Not applicable

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

**California Proposition 65** This product does not contain any Proposition 65 chemicals.

**U.S. State Right-to-Know Regulations** Not applicable

**U.S. Department of Transportation**

Reportable Quantity (RQ): N

DOT Marine Pollutant N

DOT Severe Marine Pollutant N

**U.S. Department of Homeland** This product does not contain any DHS chemicals.

**Security****Other International Regulations****Mexico - Grade** No information available**Authorisation/Restrictions according to EU REACH** Not applicable

Component	CAS No	REACH (1907/2006) - Annex XIV - Substances Subject to Authorization	REACH (1907/2006) - Annex XVII - Restrictions on Certain Dangerous Substances	REACH Regulation (EC 1907/2006) article 59 - Candidate List of Substances of Very High Concern (SVHC)
1H-Indole, 1-methyl-	603-76-9	-	-	-

**Safety, health and environmental regulations/legislation specific for the substance or mixture**

Component	CAS No	OECD HPV	Persistent Organic Pollutant	Ozone Depletion Potential	Restriction of Hazardous Substances (RoHS)
1H-Indole, 1-methyl-	603-76-9	Not applicable	Not applicable	Not applicable	Not applicable

**Contains component(s) that meet a 'definition' of per & poly fluoroalkyl substance (PFAS)?**

Not applicable

**Other International Regulations**

Component	CAS No	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Major Accident Notification	Seveso III Directive (2012/18/EC) - Qualifying Quantities for Safety Report Requirements	Rotterdam Convention (PIC)	Basel Convention (Hazardous Waste)
1H-Indole, 1-methyl-	603-76-9	Not applicable	Not applicable	Not applicable	Not applicable

## 16. Other information

**Prepared By** Regulatory Affairs  
Thermo Fisher Scientific  
Email: EMSDS.RA@thermofisher.com

**Revision Date** 04-Mar-2024**Print Date** 04-Mar-2024

**Revision Summary** This document has been updated to comply with the US OSHA HazCom 2012 Standard replacing the current legislation under 29 CFR 1910.1200 to align with the Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

## End of SDS