

ALFAAL10332

## 1,3-Dichloropropene, cis + trans

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

<b>产品说明:</b> <b>Product Description:</b>	<b>1,3-二氯丙烯</b> <b>1,3-Dichloropropene, cis + trans</b>
<b>Cat No. :</b>	<b>L10332</b>
<b>CAS No</b>	542-75-6
<b>Molecular Formula</b>	CICH <sub>2</sub> CH=CHCl
<b>Supplier</b>	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
<b>Emergency Telephone Number</b>	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
<b>E-mail address</b>	begel.sdsdesk@thermofisher.com
<b>Recommended Use</b>	Laboratory chemicals.
<b>Uses advised against</b>	No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Liquid

**Appearance**  
Colorless

**Odor**  
Chloroform-like

#### Emergency Overview

Highly flammable liquid and vapor. Toxic if swallowed. May be fatal if swallowed and enters airways. Toxic in contact with skin. Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation. May cause respiratory irritation. Harmful to aquatic life. Very toxic to aquatic life with long lasting effects. Toxic if inhaled. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Suspected of causing genetic defects. May cause cancer.

#### Classification of the substance or mixture

Flammable liquids.	Category 2
Aspiration Toxicity	Category 1
Acute Oral Toxicity	Category 3
Acute Dermal Toxicity	Category 3
Acute Inhalation Toxicity - Vapors	Category 3
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Respiratory Sensitization	Category 1
Skin Sensitization	Category 1
Germ Cell Mutagenicity	Category 2
Carcinogenicity	Category 1B
Specific target organ toxicity - (single exposure)	Category 3
Acute aquatic toxicity	Category 1 Category 3

**1,3-Dichloropropene, cis + trans**

Chronic aquatic toxicity

Category 1

**Label Elements****Signal Word****Danger****Hazard Statements**

H225 - Highly flammable liquid and vapor  
 H304 - May be fatal if swallowed and enters airways  
 H315 - Causes skin irritation  
 H317 - May cause an allergic skin reaction  
 H319 - Causes serious eye irritation  
 H335 - May cause respiratory irritation  
 H410 - Very toxic to aquatic life with long lasting effects  
 H334 - May cause allergy or asthma symptoms or breathing difficulties if inhaled  
 H341 - Suspected of causing genetic defects  
 H350 - May cause cancer  
 H301 + H311 + H331 - Toxic if swallowed, in contact with skin or if inhaled

**Precautionary Statements****Prevention**

P201 - Obtain special instructions before use  
 P202 - Do not handle until all safety precautions have been read and understood  
 P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
 P240 - Ground and bond container and receiving equipment  
 P242 - Use non-sparking tools  
 P243 - Take action to prevent static discharges  
 P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
 P264 - Wash face, hands and any exposed skin thoroughly after handling  
 P270 - Do not eat, drink or smoke when using this product  
 P271 - Use only outdoors or in a well-ventilated area  
 P280 - Wear eye protection/ face protection  
 P284 - In case of inadequate ventilation wear respiratory protection

**Response**

P301 + P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor  
 P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower  
 P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
 P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
 P311 - Call a POISON CENTER or doctor  
 P330 - Rinse mouth  
 P331 - Do NOT induce vomiting  
 P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish  
 P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P405 - Store locked up  
 P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Vapors may cause flash fire or explosion. Highly flammable.

**Health Hazards**

Toxic if swallowed. Aspiration hazard if swallowed - can enter lungs and cause damage. Toxic in contact with skin. Causes skin

## 1,3-Dichloropropene, cis + trans

irritation. May cause an allergic skin reaction. Causes serious eye irritation. May cause respiratory irritation. Toxic if inhaled. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Suspected of causing genetic defects. May cause cancer.

**Environmental hazards**

Harmful to aquatic life. Very toxic to aquatic life with long lasting effects.

Toxic to terrestrial invertebrates. Toxicity to Soil Dwelling Organisms. Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
1,3-Dichloropropene	542-75-6	<=100

**SECTION 4. FIRST AID MEASURES****General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required. Risk of serious damage to the lungs (by aspiration).

**Ingestion**

Do NOT induce vomiting. Call a physician or poison control center immediately. If vomiting occurs naturally, have victim lean forward.

**Most important symptoms and effects**

Difficulty in breathing. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Carbon dioxide (CO<sub>2</sub>). Powder. Water spray. In case of major fire and large quantities: Evacuate area. Fight fire remotely due to the risk of explosion. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Flammable. Containers may explode when heated. Vapors may form explosive mixtures with air. Vapors may travel to source of

## 1,3-Dichloropropene, cis + trans

ignition and flash back. Do not allow run-off from fire-fighting to enter drains or water courses.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas. Remove all sources of ignition. Take precautionary measures against static discharges.

**Environmental Precautions**

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Take precautionary measures against static discharges.

**Storage**

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat, sparks and flame.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
1,3-Dichloropropene	TWA: 4 mg/m <sup>3</sup> Skin	TWA: 1 ppm TWA: 4.5 mg/m <sup>3</sup>		-

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
1,3-Dichloropropene	TWA: 1 ppm Skin	(Vacated) TWA: 1 ppm (Vacated) TWA: 5 mg/m <sup>3</sup> Skin	TWA: 1 ppm TWA: 5 mg/m <sup>3</sup>	-	

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

**Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88

## 1,3-Dichloropropene, cis + trans

Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

**Exposure Controls****Engineering Measures**

Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Use explosion-proof electrical/ventilating/lighting equipment. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Viton (R)	480 minutes	0.7 mm	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** In case of insufficient ventilation, wear suitable respiratory equipment  
**Recommended Filter type:** Multi-purpose/ABEK conforming to EN14387

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

<b>Appearance</b>	Colorless	
<b>Physical State</b>	Liquid	
<b>Odor</b>	Chloroform-like	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	~ -84 - 84 °C / -119.2 - 183.2 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	105 - 106 °C / 221 - 222.8 °F	
<b>Flash Point</b>	21 °C / 69.8 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	<b>Lower</b> 5.3 Vol %	

## 1,3-Dichloropropene, cis + trans

<b>Vapor Pressure</b>	Upper 14.5 Vol % No data available	
<b>Vapor Density</b>	No data available	(Air = 1.0)
<b>Specific Gravity / Density</b>	1.181 g/cm <sup>3</sup>	@ 20 °C
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	No information available	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
1,3-Dichloropropene	2.3	
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	No data available	
<b>Explosive Properties</b>		Vapors may form explosive mixtures with air
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C1CH2 CH=CHCl	
<b>Molecular Weight</b>	110.97	

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	Keep away from open flames, hot surfaces and sources of ignition.
<b>Materials to avoid</b>	Oxidizing agent.
<b>Hazardous Decomposition Products</b>	Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ). Hydrogen chloride.

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

## (a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
1,3-Dichloropropene	LD50 = 224 mg/kg ( Rat )	LD50 = 333 mg/kg ( Rabbit )	LC50 = 904 ppm ( Rat ) 4 h

(b) skin corrosion/irritation; Category 2

(c) serious eye damage/irritation; Category 2

## (d) respiratory or skin sensitization;

Respiratory	Category 1
Skin	No data available

(e) germ cell mutagenicity; Category 2

(f) carcinogenicity; Category 1B

The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	EU	UK	Germany	IARC
1,3-Dichloropropene			Cat. 2	Group 2B

## 1,3-Dichloropropene, cis + trans

(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	Category 3
Results / Target organs	Respiratory system
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	Category 1

**Symptoms / effects, both acute and delayed** Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

## SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects** The product contains following substances which are hazardous for the environment. Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
1,3-Dichloropropene	LC50: 5.1 - 6.8 mg/L, 96h static (Lepomis macrochirus) LC50: = 2 mg/L, 96h (Oncorhynchus mykiss) LC50: = 4.5 mg/L, 96h semi-static (Oncorhynchus mykiss) LC50: 3.1 - 4.9 mg/L, 96h static (Oncorhynchus mykiss) LC50: 0.211 - 0.271 mg/L, 96h flow-through (Pimephales promelas) LC50: 1.52 - 2.68 mg/L, 96h static (Pimephales promelas)	EC50: = 0.09 mg/L, 48h (Daphnia magna) EC50: 0.063 - 0.129 mg/L, 48h Static (Daphnia magna)	EC50: 3.12 - 10.5 mg/L, 72h (Pseudokirchneriella subcapitata) EC50: 2.45 - 6.45 mg/L, 96h (Pseudokirchneriella subcapitata)	EC50 = 112 mg/L 5 min EC50 = 71.6 mg/L 30 min

**Persistence and Degradability** No information available  
**Persistence** Persistence is unlikely.  
**Degradation in sewage treatment plant** Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Bioaccumulative Potential** Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
1,3-Dichloropropene	2.3	No data available

**Mobility in soil** No information available

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance

**1,3-Dichloropropene, cis + trans**

**Ozone Depletion Potential** This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS**

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

**Other Information** Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Can be landfilled or incinerated, when in compliance with local regulations. Do not let this chemical enter the environment. Do not empty into drains.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

**UN-No** UN2047  
**Proper Shipping Name** DICHLOROPROPENES  
**Hazard Class** 3  
**Packing Group** II

**IMDG/IMO**

**UN-No** UN2047  
**Proper Shipping Name** DICHLOROPROPENES  
**Hazard Class** 3  
**Packing Group** II

**IATA**

**UN-No** UN2047  
**Proper Shipping Name** DICHLOROPROPENES  
**Hazard Class** 3  
**Packing Group** II

**Special Precautions for User** No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
1,3-Dichloropropene	X	-	X	X	208-826-5	X	-	X	X	X	X	KE-05-0466

**National Regulations**

## 1,3-Dichloropropene, cis + trans

Component	Toxic Chemical Substances Control Act
1,3-Dichloropropene 542-75-6 ( <=100 )	Class IV (50 wt%)

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 03-May-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**  
 Chemical incident response training.

Legend

**CAS** - Chemical Abstracts Service  
**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances  
**PICCS** - Philippines Inventory of Chemicals and Chemical Substances  
**IECSC** - Chinese Inventory of Existing Chemical Substances  
**KECL** - Korean Existing and Evaluated Chemical Substances

**WEL** - Workplace Exposure Limit  
**ACGIH** - American Conference of Governmental Industrial Hygienists  
**DNEL** - Derived No Effect Level  
**RPE** - Respiratory Protective Equipment  
**LC50** - Lethal Concentration 50%  
**NOEC** - No Observed Effect Concentration  
**PBT** - Persistent, Bioaccumulative, Toxic

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association  
**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road  
**OECD** - Organisation for Economic Co-operation and Development  
**BCF** - Bioconcentration factor

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory  
**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List  
**ENCS** - Japanese Existing and New Chemical Substances  
**AICS** - Australian Inventory of Chemical Substances  
**NZIoC** - New Zealand Inventory of Chemicals

**TWA** - Time Weighted Average  
**IARC** - International Agency for Research on Cancer  
**PNEC** - Predicted No Effect Concentration  
**LD50** - Lethal Dose 50%  
**EC50** - Effective Concentration 50%  
**POW** - Partition coefficient Octanol:Water  
**vPvB** - very Persistent, very Bioaccumulative

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code  
**MARPOL** - International Convention for the Prevention of Pollution from Ships  
**ATE** - Acute Toxicity Estimate  
**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**  
<https://echa.europa.eu/information-on-chemicals>  
 Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**