

ALFAA24139

Dibenzenechromium

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: Product Description:	二苯铬 Dibenzenechromium
Cat No. :	24139
CAS No	1271-54-1
Molecular Formula	C ₁₂ H ₁₂ Cr
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information US call: 001-800-227-6701 / Europe call: +32 14 57 52 11 Emergency Number US :001-201-796-7100 / Europe : +32 14 57 52 99 CHEMTREC Tel. No. US :001-800-424-9300 / Europe :001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State Solid	Appearance No information available	Odor No information available
Emergency Overview Moisture sensitive. Air sensitive. Flammable solid.		

Classification of the substance or mixture

Flammable solids.	Category 2
-------------------	------------

Label Elements



Signal Word

Warning

Hazard Statements

H228 - Flammable solid

Precautionary Statements**Prevention**

P240 - Ground and bond container and receiving equipment

P280 - Wear protective gloves/protective clothing/eye protection/face protection

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking

Response

P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish

Storage

P403 - Store in a well-ventilated place

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Combustible material.

Health Hazards

The product contains no substances which at their given concentration are considered to be hazardous to health.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Bis(.eta.6-benzene)chromium	1271-54-1	97

SECTION 4. FIRST AID MEASURES**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention.

Inhalation

Remove from exposure, lie down. Remove to fresh air.

Ingestion

Clean mouth with water. Get medical attention.

Most important symptoms and effects

No information available.

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**Water spray. Carbon dioxide (CO₂). Dry chemical. Chemical foam. Water mist may be used to cool closed containers.**Extinguishing media which must not be used for safety reasons**

No information available.

Specific Hazards Arising from the Chemical

Combustible material. Combustible material. Containers may explode when heated.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions

See Section 12 for additional Ecological Information. Should not be released into the environment. Do not allow material to contaminate ground water system. Do not flush into surface water or sanitary sewer system.

Methods for Containment and Clean Up

Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment. Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Avoid contact with skin and eyes. Do not breathe dust. Use spark-proof tools and explosion-proof equipment. Use only non-sparking tools. Handle under argon. Keep away from open flames, hot surfaces and sources of ignition.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep away from heat, sparks and flame. Flammables area. Keep under nitrogen. Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust MDHS70 General methods for sampling airborne gases and vapours MDHS12/2 Chromium and inorganic compounds of chromium in air Laboratory method using flame atomic absorption spectrometry

Exposure Controls**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment**Eye Protection**

Goggles (European standard - EN 166)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection

Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Recommended Filter type: Particulates filter conforming to EN 143**Small scale/Laboratory use**

Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

Recommended half mask:- Particle filtering: EN149:2001

When RPE is used a face piece Fit Test should be conducted

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls

No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**Appearance****Physical State**

Solid

Odor

No information available

Odor Threshold

No data available

pH

No information available

Melting Point/Range

260 - 265 °C / 500 - 509 °F

Softening Point

No data available

Boiling Point/Range

No information available

Flash Point

82 °C / 179.6 °F

Method - No information available**Evaporation Rate**

Not applicable

Solid

Flammability (solid,gas)

No information available

Explosion Limits

No data available

Vapor Pressure

No data available

Vapor Density

Not applicable

Solid

Specific Gravity / Density

No data available

Bulk Density

No data available

Water Solubility

No information available

Solubility in other solvents

No information available

Partition Coefficient (n-octanol/water)**Autoignition Temperature**

No data available

Decomposition Temperature

No data available

Dibenzenechromium

Viscosity	Not applicable	Solid
Explosive Properties		explosive air/vapour mixtures possible
Oxidizing Properties	No information available	
Molecular Formula	C12H12Cr	
Molecular Weight	208.08	

SECTION 10. STABILITY AND REACTIVITY

Stability	Moisture sensitive. Air sensitive.
Hazardous Reactions	No information available.
Hazardous Polymerization	Hazardous polymerization does not occur.
Conditions to Avoid	Keep away from open flames, hot surfaces and sources of ignition. Exposure to air. Incompatible products. Exposure to moist air or water.
Materials to avoid	Strong oxidizing agents.

Hazardous Decomposition Products Carbon monoxide (CO). Carbon dioxide (CO₂). Chromium oxide.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information	No acute toxicity information is available for this product
(a) acute toxicity;	
(b) skin corrosion/irritation;	No data available
(c) serious eye damage/irritation;	No data available
(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available
	There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	Not applicable
	Solid

Dibenzenechromium

Other Adverse Effects The toxicological properties have not been fully investigated.

Symptoms / effects, both acute and delayed No information available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects May cause long-term adverse effects in the environment. Do not allow material to contaminate ground water system.

Persistence and Degradability Product contains heavy metals. Discharge into the environment must be avoided. Special pre-treatment is necessary
Persistence May persist.
Degradation in sewage treatment plant Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential Product has a high potential to bioconcentrate

Mobility in soil No information available

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

Other Information Waste codes should be assigned by the user based on the application for which the product was used. Do not flush to sewer. Can be landfilled or incinerated, when in compliance with local regulations.

SECTION 14. TRANSPORT INFORMATION**Road and Rail Transport**

UN-No UN1325
Proper Shipping Name Flammable solid, organic, n.o.s.
Technical Shipping Name Bis(.eta.6-benzene)chromium
Hazard Class 4.1
Packing Group III

IMDG/IMO

UN-No UN1325
Proper Shipping Name Flammable solid, organic, n.o.s.
Technical Shipping Name Bis(.eta.6-benzene)chromium
Hazard Class 4.1
Packing Group III

IATA

UN-No UN1325
Proper Shipping Name Flammable solid, organic, n.o.s.
Technical Shipping Name Bis(.eta.6-benzene)chromium
Hazard Class 4.1
Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Bis(.eta.6-benzene)chromium	-	-	X	-	215-042-7	-	-	-	-		-	-

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Revision Date 22-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet