

ALFAA13069

## Manganese(III) fluoride

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

<b>产品说明:</b> <b>Product Description:</b>	<b>氟化锰(III)</b> <b>Manganese(III) fluoride</b>
<b>Cat No. :</b>	<b>13069</b>
<b>Synonyms</b>	Manganese trifluoride; Manganic fluoride.
<b>CAS No</b>	7783-53-1
<b>Molecular Formula</b>	F3 Mn
<b>Supplier</b>	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
<b>Emergency Telephone Number</b>	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
<b>E-mail address</b>	begel.sdsdesk@thermofisher.com
<b>Recommended Use</b> <b>Uses advised against</b>	Laboratory chemicals. No Information available

### SECTION 2. HAZARD IDENTIFICATION

<b>Physical State</b> Powder Solid	<b>Appearance</b> Grey	<b>Odor</b> No information available
<b>Emergency Overview</b> May intensify fire; oxidizer. Harmful if swallowed. Causes skin irritation. Causes serious eye damage. Harmful if inhaled. May cause respiratory irritation. Moisture sensitive. Hygroscopic.		

#### Classification of the substance or mixture

Oxidizing solids	Category 2
Acute Oral Toxicity	Category 4
Acute Inhalation Toxicity - Dusts and Mists	Category 4
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 1
Specific target organ toxicity - (single exposure)	Category 3

#### Label Elements

**Signal Word****Danger****Hazard Statements**

H272 - May intensify fire; oxidizer  
H315 - Causes skin irritation  
H318 - Causes serious eye damage  
H335 - May cause respiratory irritation  
H302 + H332 - Harmful if swallowed or if inhaled

**Precautionary Statements****Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P220 - Keep away from clothing and other combustible materials  
P221 - Take any precaution to avoid mixing with combustibles  
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product  
P271 - Use only outdoors or in a well-ventilated area  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water  
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P310 - Immediately call a POISON CENTER or doctor  
P330 - Rinse mouth  
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish  
P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Oxidizing. Contact with combustible material may cause fire. Hygroscopic.

**Health Hazards**

Harmful if swallowed. Causes skin irritation. Harmful if inhaled. May cause respiratory irritation.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Manganese fluoride (MnF <sub>3</sub> )	7783-53-1	99

**SECTION 4. FIRST AID MEASURES****Eye Contact**

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

**Skin Contact**

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention.

**Inhalation**

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Get medical attention.

**Ingestion**

Clean mouth with water. Get medical attention.

**Most important symptoms and effects**

Causes eye burns. Causes severe eye damage.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Carbon dioxide (CO<sub>2</sub>). Dry chemical. Chemical foam. Do not use a solid water stream as it may scatter and spread fire.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Oxidizer: Contact with combustible/organic material may cause fire. May ignite combustibles (wood, paper, oil, clothing, etc.).

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation.

**Environmental Precautions**

See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal. Do not expose spill to water. Do not let this chemical enter the environment. Keep combustibles (wood, paper, oil, etc) away from spilled material. Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Avoid contact with skin and eyes. Do not breathe dust. Handle product only in closed system or provide appropriate exhaust ventilation. Keep away from clothing and other combustible materials. Do not allow contact with water.

**Storage**

## Manganese(III) fluoride

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Do not store near combustible materials. Keep containers tightly closed in a dry, cool and well-ventilated place.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
Manganese fluoride (MnF <sub>3</sub> )	-	TWA: 2.5 mg/m <sup>3</sup>	TWA: 2.5 mg/m <sup>3</sup>	-

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Manganese fluoride (MnF <sub>3</sub> )	TWA: 2.5 mg/m <sup>3</sup> 0.02 mg/m <sup>3</sup> TWA: 0.1 mg/m <sup>3</sup>	(Vacated) TWA: 2.5 mg/m <sup>3</sup> (Vacated) Ceiling: 5 mg/m <sup>3</sup> Ceiling: 5 mg/m <sup>3</sup>	IDLH: 500 mg/m <sup>3</sup> IDLH: 250 mg/m <sup>3</sup> TWA: 1 mg/m <sup>3</sup> STEL: 3 mg/m <sup>3</sup>	STEL: 0.6 mg/m <sup>3</sup> 15 min STEL: 0.15 mg/m <sup>3</sup> 15 min TWA: 0.2 mg/m <sup>3</sup> 8 hr TWA: 0.05 mg/m <sup>3</sup> 8 hr	TWA: 0.05 mg/m <sup>3</sup> (8h)

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

**Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

**Exposure Controls****Engineering Measures**

Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.  
To protect the wearer, respiratory protective equipment must be the correct fit and be used

	and maintained properly
<b>Large scale/emergency use</b>	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced <b>Recommended Filter type:</b> Particulates filter conforming to EN 143
<b>Small scale/Laboratory use</b>	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. <b>Recommended half mask:-</b> Particle filtering: EN149:2001 When RPE is used a face piece Fit Test should be conducted
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.
<b>Environmental exposure controls</b>	No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Grey	
<b>Physical State</b>	Powder Solid	
<b>Odor</b>	No information available	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	No data available	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	No information available	
<b>Flash Point</b>	No information available	<b>Method -</b> No information available
<b>Evaporation Rate</b>	Not applicable	Solid
<b>Flammability (solid,gas)</b>	No information available	
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No information available	
<b>Vapor Density</b>	Not applicable	Solid
<b>Specific Gravity / Density</b>	3.540	
<b>Bulk Density</b>	No data available	
<b>Water Solubility</b>	decomposes	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	> 600°C	
<b>Viscosity</b>	Not applicable	Solid
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	Oxidizer	
<b>Molecular Formula</b>	F3 Mn	
<b>Molecular Weight</b>	111.93	

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions. Hygroscopic. Moisture sensitive. Oxidizer: Contact with combustible/organic material may cause fire.
<b>Hazardous Reactions</b>	No information available.
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid</b>	Incompatible products. Exposure to moist air or water. Excess heat. Combustible material.
<b>Materials to avoid</b>	Strong oxidizing agents. Strong acids. Strong reducing agents. Combustible material.

**Hazardous Decomposition Products** Gaseous hydrogen fluoride (HF). Fluorine.

**SECTION 11. TOXICOLOGICAL INFORMATION****Product Information**

(a) acute toxicity;

(b) skin corrosion/irritation; Category 2

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Respiratory No data available  
Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available  
There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; Category 3

Results / Target organs Respiratory system

(i) STOT-repeated exposure; No data available

Target Organs No information available.

(j) aspiration hazard; Not applicable  
Solid

**Other Adverse Effects** The toxicological properties have not been fully investigated.

**Symptoms / effects, both acute and delayed** No information available

**SECTION 12. ECOLOGICAL INFORMATION**

**Ecotoxicity effects** Do not empty into drains.

**Persistence and Degradability**

Persistence Soluble in water, Persistence is unlikely, based on information available.  
Degradability Not relevant for inorganic substances.

**Bioaccumulative Potential** Bioaccumulation is unlikely

**Mobility in soil** The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

### SECTION 13. DISPOSAL CONSIDERATIONS

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point.

**Other Information** Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer.

### SECTION 14. TRANSPORT INFORMATION

#### Road and Rail Transport

**UN-No** UN3087  
**Proper Shipping Name** Oxidizing solid, toxic, n.o.s.  
**Hazard Class** 5.1  
**Subsidiary Hazard Class** 6.1  
**Packing Group** II

#### IMDG/IMO

**UN-No** UN3087  
**Proper Shipping Name** Oxidizing solid, toxic, n.o.s.  
**Hazard Class** 5.1  
**Subsidiary Hazard Class** 6.1  
**Packing Group** II

#### IATA

**UN-No** UN3087  
**Proper Shipping Name** OXIDIZING SOLID, TOXIC, N.O.S.\*  
**Hazard Class** 5.1  
**Subsidiary Hazard Class** 6.1  
**Packing Group** II

**Special Precautions for User** No special precautions required

### SECTION 15. REGULATORY INFORMATION

#### International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Manganese fluoride (MnF <sub>3</sub> )	-	-		-	232-006-6	X	-	-	X	X	-	KE-23051

## National Regulations

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 27-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadviser - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**