

ALFAA13096

## Selenium (IV) chloride

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

|   |  |
|---|--|
| <b>产品说明:</b><br><b>Product Description:</b>           | <b>四氯化硒(IV)</b><br><b>Selenium (IV) chloride</b>   |
| <b>Cat No. :</b>                                      | <b>13096</b>   |
| <b>Synonyms</b>                                       | Selenium tetrachloride   |
| <b>CAS No</b>   | 10026-03-6   |
| <b>Molecular Formula</b>                              | Cl <sub>4</sub> Se   |
| <b>Supplier</b>                                       | Avocado Research Chemicals Ltd.<br>(Part of Thermo Fisher Scientific)<br>Shore Road, Heysham<br>Lancashire, LA3 2XY,<br>United Kingdom<br>Office Tel: +44 (0) 1524 850506<br>Office Fax: +44 (0) 1524 850608   |
| <b>Emergency Telephone Number</b>                     | For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11<br>Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99<br><b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887 |
| <b>E-mail address</b>                                 | begel.sdsdesk@thermofisher.com   |
| <b>Recommended Use</b><br><b>Uses advised against</b> | Laboratory chemicals.<br>No Information available  |

### SECTION 2. HAZARD IDENTIFICATION

|  |                             |   |
|--|-----------------------------|---|
| <b>Physical State</b><br>Powder Solid  | <b>Appearance</b><br>Yellow | <b>Odor</b><br>No information available |
| <b>Emergency Overview</b><br>Toxic if swallowed. Toxic if inhaled. Harmful to aquatic life. Very toxic to aquatic life with long lasting effects. May cause damage to organs through prolonged or repeated exposure. Moisture sensitive. |                             |   |

#### Classification of the substance or mixture

|  |                       |
|--|-----------------------|
| Acute Oral Toxicity                                  | Category 3            |
| Acute Inhalation Toxicity - Dusts and Mists          | Category 3            |
| Specific target organ toxicity - (repeated exposure) | Category 2            |
| Acute aquatic toxicity                               | Category 1 Category 3 |
| Chronic aquatic toxicity                             | Category 1            |

#### Label Elements



**Signal Word****Danger****Hazard Statements**

H410 - Very toxic to aquatic life with long lasting effects

H373 - May cause damage to organs through prolonged or repeated exposure

H301 + H331 - Toxic if swallowed or if inhaled

**Precautionary Statements****Prevention**

P260 - Do not breathe dust/fume/gas/mist/vapors/spray

P264 - Wash face, hands and any exposed skin thoroughly after handling

P270 - Do not eat, drink or smoke when using this product

P271 - Use only outdoors or in a well-ventilated area

**Response**

P301 + P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P311 - Call a POISON CENTER or doctor

P330 - Rinse mouth

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

P405 - Store locked up

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Toxic if swallowed. Toxic if inhaled. Harmful if inhaled. May cause damage to organs through prolonged or repeated exposure.

**Environmental hazards**

Harmful to aquatic life. Very toxic to aquatic life with long lasting effects. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

| Component                                      | CAS No     | Weight % |
|--|------------|----------|
| Selenium chloride (SeCl <sub>4</sub> ), (T-4)- | 10026-03-6 | 95       |

**SECTION 4. FIRST AID MEASURES****Eye Contact**

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

**Skin Contact**

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Immediate medical attention is required.

**Inhalation**

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Immediate medical attention is required.

**Ingestion**

Call a physician immediately. Clean mouth with water.

**Most important symptoms and effects**

No information available.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Do not allow run-off from fire-fighting to enter drains or water courses.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation.

**Environmental Precautions**

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Do not breathe dust. Do not get in eyes, on skin, or on clothing. Handle product only in closed system or provide appropriate exhaust ventilation.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters**

| Component                                      | China | Taiwan                     | Thailand                   | Hong Kong |
|--|-------|----------------------------|----------------------------|-----------|
| Selenium chloride (SeCl <sub>4</sub> ), (T-4)- | -     | TWA: 0.2 mg/m <sup>3</sup> | TWA: 0.2 mg/m <sup>3</sup> | -         |

| Component | ACGIH TLV | OSHA PEL | NIOSH | The United Kingdom | European Union |
|-----------|-----------|----------|-------|--------------------|----------------|
|-----------|-----------|----------|-------|--------------------|----------------|

## Selenium (IV) chloride

|  |                            |                                      |   |   |  |
|--|----------------------------|--------------------------------------|---|---|--|
| Selenium chloride (SeCl <sub>4</sub> ), (T-4)- | TWA: 0.2 mg/m <sup>3</sup> | (Vacated) TWA: 0.2 mg/m <sup>3</sup> | IDLH: 1 mg/m <sup>3</sup><br>TWA: 0.2 mg/m <sup>3</sup> | STEL: 0.3 mg/m <sup>3</sup> 15 min<br>TWA: 0.1 mg/m <sup>3</sup> 8 hr |  |
|--|----------------------------|--------------------------------------|---|---|--|

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

**Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

**Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

| Glove material | Breakthrough time | Glove thickness | EU standard | Glove comments        |
|----------------|-------------------|-----------------|-------------|-----------------------|
| Natural rubber | See manufacturers | -               | EN 374      | (minimum requirement) |
| Nitrile rubber | recommendations   |                 |             |                       |
| Neoprene       |                   |                 |             |                       |
| PVC            |                   |                 |             |                       |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.  
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particulates filter conforming to EN 143

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Particle filtering: EN149:2001  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

|  |                             |  |
|--|-----------------------------|--|
| <b>Appearance</b>                              | Yellow                      |  |
| <b>Physical State</b>                          | Powder Solid                |  |
| <b>Odor</b>                                    | No information available    |  |
| <b>Odor Threshold</b>                          | No data available           |  |
| <b>pH</b>                                      | No information available    |  |
| <b>Melting Point/Range</b>                     | 200 - 210 °C / 392 - 410 °F |  |
| <b>Softening Point</b>                         | No data available           |  |
| <b>Boiling Point/Range</b>                     | No information available    |  |
| <b>Flash Point</b>                             | No information available    | <b>Method -</b> No information available |
| <b>Evaporation Rate</b>                        | Not applicable              | Solid                                    |
| <b>Flammability (solid,gas)</b>                | No information available    |  |
| <b>Explosion Limits</b>                        | No data available           |  |
| <b>Vapor Pressure</b>                          | No data available           |  |
| <b>Vapor Density</b>                           | Not applicable              | Solid                                    |
| <b>Specific Gravity / Density</b>              | No data available           |  |
| <b>Bulk Density</b>                            | No data available           |  |
| <b>Water Solubility</b>                        | decomposes                  |  |
| <b>Solubility in other solvents</b>            | No information available    |  |
| <b>Partition Coefficient (n-octanol/water)</b> |                             |  |
| <b>Autoignition Temperature</b>                | No data available           |  |
| <b>Decomposition Temperature</b>               | No data available           |  |
| <b>Viscosity</b>                               | Not applicable              | Solid                                    |
| <b>Explosive Properties</b>                    | No information available    |  |
| <b>Oxidizing Properties</b>                    | No information available    |  |
| <b>Molecular Formula</b>                       | Cl4 Se                      |  |
| <b>Molecular Weight</b>                        | 220.77                      |  |

**SECTION 10. STABILITY AND REACTIVITY**

|                                 |  |
|---------------------------------|--|
| <b>Stability</b>                | Moisture sensitive.                                    |
| <b>Hazardous Reactions</b>      | No information available.                              |
| <b>Hazardous Polymerization</b> | No information available.                              |
| <b>Conditions to Avoid</b>      | Incompatible products. Exposure to moist air or water. |
| <b>Materials to avoid</b>       | Strong oxidizing agents. Strong acids.                 |

**Hazardous Decomposition Products** Hydrogen chloride gas.

**SECTION 11. TOXICOLOGICAL INFORMATION****Product Information**

|   |                   |
|---|-------------------|
| <b>(a) acute toxicity;</b>                    |                   |
| <b>(b) skin corrosion/irritation;</b>         | No data available |
| <b>(c) serious eye damage/irritation;</b>     | No data available |
| <b>(d) respiratory or skin sensitization;</b> |                   |
| <b>Respiratory</b>                            | No data available |

|  |  |
|--|--|
| <b>Skin</b>                                      | No data available  |
| <b>(e) germ cell mutagenicity;</b>               | No data available  |
| <b>(f) carcinogenicity;</b>                      | No data available<br>There are no known carcinogenic chemicals in this product |
| <b>(g) reproductive toxicity;</b>                | No data available  |
| <b>(h) STOT-single exposure;</b>                 | No data available  |
| <b>(i) STOT-repeated exposure;</b>               | Category 2   |
| <b>Target Organs</b>                             | Liver.   |
| <b>(j) aspiration hazard;</b>                    | Not applicable<br>Solid  |
| <b>Symptoms / effects,both acute and delayed</b> | No information available   |

**SECTION 12. ECOLOGICAL INFORMATION**

|  |   |
|--|---|
| <b>Ecotoxicity effects</b>                   | Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment. |
| <b>Persistence and Degradability</b>         |   |
| <b>Persistence</b>                           | Soluble in water, Persistence is unlikely, based on information available.  |
| <b>Degradability</b>                         | Not relevant for inorganic substances.  |
| <b>Degradation in sewage treatment plant</b> | Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.   |
| <b>Bioaccumulative Potential</b>             | Bioaccumulation is unlikely   |
| <b>Mobility in soil</b>                      | The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils                           |
| <b>Endocrine Disruptor Information</b>       | This product does not contain any known or suspected endocrine disruptors   |
| <b>Persistent Organic Pollutant</b>          | This product does not contain any known or suspected substance  |
| <b>Ozone Depletion Potential</b>             | This product does not contain any known or suspected substance  |

**SECTION 13. DISPOSAL CONSIDERATIONS**

|  |   |
|--|---|
| <b>Waste from Residues/Unused Products</b> | Should not be released into the environment. Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations. |
| <b>Contaminated Packaging</b>              | Dispose of this container to hazardous or special waste collection point.   |

## Selenium (IV) chloride

## Other Information

Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not let this chemical enter the environment.

## SECTION 14. TRANSPORT INFORMATION

## Road and Rail Transport

UN-No UN3283  
Proper Shipping Name SELENIUM COMPOUND, SOLID, N.O.S.  
Technical Shipping Name Selenium chloride (SeCl<sub>4</sub>), (T-4)-  
Hazard Class 6.1  
Packing Group III

## IMDG/IMO

UN-No UN3283  
Proper Shipping Name SELENIUM COMPOUND, SOLID, N.O.S.  
Technical Shipping Name Selenium chloride (SeCl<sub>4</sub>), (T-4)-  
Hazard Class 6.1  
Packing Group III

## IATA

UN-No UN3283  
Proper Shipping Name SELENIUM COMPOUND, SOLID, N.O.S.  
Technical Shipping Name Selenium chloride (SeCl<sub>4</sub>), (T-4)-  
Hazard Class 6.1  
Packing Group III

Special Precautions for User No special precautions required

## SECTION 15. REGULATORY INFORMATION

## International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

| Component                                      | The Inventory of Hazardous Chemicals (2015 Edition) | List of dangerous goods GB 12268 - 2012 | TCSI | IECSC | EINECS    | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL     |
|--|---|---|------|-------|-----------|------|-----|-------|------|------|------|----------|
| Selenium chloride (SeCl <sub>4</sub> ), (T-4)- | X   | X                                       | X    | X     | 233-053-5 | X    | -   | -     | -    | X    | X    | KE-30930 |

## National Regulations

## SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department  
Revision Date 07-Mar-2024  
Revision Summary New emergency telephone response service provider.

## Selenium (IV) chloride

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical incident response training.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**