

ALFAA36574

Lithium tantalum tert-butoxide, 10% w/v in tert-butanol

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 叔丁氧基钽锂
Lithium tantalum tert-butoxide, 10% w/v in tert-butanol

Cat No. : 36574

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Liquid

Appearance
Light yellow

Odor
No information available

Emergency Overview

Highly flammable liquid and vapor. May cause respiratory irritation. May be harmful if swallowed. Causes skin irritation. Causes serious eye damage. Harmful if inhaled. May cause drowsiness and dizziness. Moisture sensitive.

Classification of the substance or mixture

Flammable liquids.	Category 2
Acute Oral Toxicity	Category 5
Acute Inhalation Toxicity - Vapors	Category 4
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 1
Specific target organ toxicity - (single exposure)	Category 3

Label Elements



Lithium tantalum tert-butoxide, 10% w/v in tert-butanol

Signal Word

Danger

Hazard Statements

H225 - Highly flammable liquid and vapor
H335 - May cause respiratory irritation
H303 - May be harmful if swallowed
H315 - Causes skin irritation
H318 - Causes serious eye damage
H332 - Harmful if inhaled
H336 - May cause drowsiness or dizziness

Precautionary Statements

Prevention

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
P240 - Ground and bond container and receiving equipment
P242 - Use non-sparking tools
P243 - Take action to prevent static discharges
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling
P270 - Do not eat, drink or smoke when using this product
P271 - Use only outdoors or in a well-ventilated area
P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P310 - Immediately call a POISON CENTER or doctor
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Vapors may cause flash fire or explosion. Highly flammable.

Health Hazards

May cause respiratory irritation. May be harmful if swallowed. Causes skin irritation. Harmful if inhaled. May cause drowsiness or dizziness.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
tert-Butyl alcohol	75-65-0	90.0
Lithium tantalum tert-butoxide	21864-30-2	10.0

SECTION 4. FIRST AID MEASURES

General Advice

If symptoms persist, call a physician.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

Ingestion

Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects

Difficulty in breathing. Causes eye burns. Causes severe eye damage. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

Self-Protection of the First Aider

No special precautions required.

Notes to Physician

Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Flammable. Containers may explode when heated. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information. Do not allow material to contaminate ground water system. Do not flush into surface water or sanitary sewer system.

Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid ingestion and inhalation. Do not get in eyes, on skin, or on clothing. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. To

Lithium tantalum tert-butoxide, 10% w/v in tert-butanol

avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Take precautionary measures against static discharges.

Storage

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat, sparks and flame.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
tert-Butyl alcohol	-	TWA: 100 ppm TWA: 303 mg/m ³	TWA: 100 ppm	TWA: 100 ppm TWA: 303 mg/m ³

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
tert-Butyl alcohol	TWA: 100 ppm	(Vacated) TWA: 100 ppm (Vacated) TWA: 300 mg/m ³ (Vacated) STEL: 150 ppm (Vacated) STEL: 450 mg/m ³ TWA: 100 ppm TWA: 300 mg/m ³	IDLH: 1600 ppm TWA: 100 ppm TWA: 300 mg/m ³ STEL: 150 ppm STEL: 450 mg/m ³	STEL: 150 ppm 15 min STEL: 462 mg/m ³ 15 min TWA: 100 ppm 8 hr TWA: 308 mg/m ³ 8 hr	

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods

MDHS 91 Metals and metalloids in workplace air by X-ray fluorescence spectrometry MDHS 99 Metals in air by ICP-AES BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

Exposure Controls**Engineering Measures**

None under normal use conditions. Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Use explosion-proof electrical/ventilating/lighting equipment. .

Personal protective equipment**Eye Protection**

Goggles (European standard - EN 166)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber Viton (R)	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Lithium tantalum tert-butoxide, 10% w/v in tert-butanol

Skin and body protection	Long sleeved clothing
Respiratory Protection	No protective equipment is needed under normal use conditions.
Large scale/emergency use	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced Recommended Filter type: Particle filter
Small scale/Laboratory use	Maintain adequate ventilation Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
Hygiene Measures	Handle in accordance with good industrial hygiene and safety practice.
Environmental exposure controls	No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Light yellow	
Physical State	Liquid	
Odor	No information available	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	11 °C / 51.8 °F	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	23 hPa @ 20 °C	
Vapor Density	No data available	(Air = 1.0)
Specific Gravity / Density	No data available	
Bulk Density	Not applicable	Liquid
Water Solubility	Immiscible	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
tert-Butyl alcohol	0.317	
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	No data available	
Explosive Properties		Vapors may form explosive mixtures with air
Oxidizing Properties	No information available	

SECTION 10. STABILITY AND REACTIVITY

Stability	Moisture sensitive.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	No information available.

Lithium tantalum tert-butoxide, 10% w/v in tert-butanol

Conditions to Avoid Keep away from open flames, hot surfaces and sources of ignition.

Materials to avoid No information available.

Hazardous Decomposition Products Carbon monoxide (CO). Carbon dioxide (CO₂). Lithium oxide. Tantalum oxide.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Toxicology data for the components

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
tert-Butyl alcohol	>3100 mg/kg (Rat)	>2000 mg/kg (Rabbit)	>31 mg/L/4h (Rat)

(b) skin corrosion/irritation; Category 2

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Respiratory

No data available

Skin

No data available

Component	Test method	Test species	Study result
tert-Butyl alcohol 75-65-0 (90.0)	OECD Test Guideline 406 Skin sensitization	guinea pig	non-sensitising

(e) germ cell mutagenicity; No data available

Component	Test method	Test species	Study result
tert-Butyl alcohol 75-65-0 (90.0)	AMES test	in vitro	negative

(f) carcinogenicity; No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; Category 3

Results / Target organs

Respiratory system
Central nervous system (CNS)

(i) STOT-repeated exposure; No data available

Target Organs

No information available.

(j) aspiration hazard; No data available

Symptoms / effects, both acute and delayed Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting:
Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

SECTION 12. ECOLOGICAL INFORMATION

Lithium tantalum tert-butoxide, 10% w/v in tert-butanol

Ecotoxicity effects

May cause long-term adverse effects in the environment. Do not allow material to contaminate ground water system.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
tert-Butyl alcohol	LC50 >961 mg/L/96h (Pimephales promelas)	EC50 933 mg/L 48 h	EC50 1000 mg/L 72 h	EC50 > 10000 mg/L 17 h

Persistence and Degradability

Product contains heavy metals. Discharge into the environment must be avoided. Special pre-treatment is necessary

Persistence

May persist, based on information available.

Degradation in sewage treatment plant

Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential

May have some potential to bioaccumulate

Component	log Pow	Bioconcentration factor (BCF)
tert-Butyl alcohol	0.317	1.09 dimensionless

Mobility in soil

Spillage unlikely to penetrate soil Is not likely mobile in the environment due its low water solubility

Endocrine Disruptor Information

This product does not contain any known or suspected endocrine disruptors

Persistent Organic Pollutant

This product does not contain any known or suspected substance

Ozone Depletion Potential

This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS**Waste from Residues/Unused Products**

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging

Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

Other Information

Waste codes should be assigned by the user based on the application for which the product was used. Do not flush to sewer. Can be landfilled or incinerated, when in compliance with local regulations. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION**Road and Rail Transport**

UN-No	UN1120
Proper Shipping Name	BUTANOLS
Hazard Class	3
Packing Group	II

IMDG/IMO

UN-No	UN1120
Proper Shipping Name	BUTANOLS
Hazard Class	3
Packing Group	II

IATA

Lithium tantalum tert-butoxide, 10% w/v in tert-butanol

UN-No UN1120
 Proper Shipping Name BUTANOLS
 Hazard Class 3
 Packing Group II

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
tert-Butyl alcohol	X	X	X	X	200-889-7	X	X	X	X	X	X	KE-24895

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
 Revision Date 08-May-2024
 Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Lithium tantalum tert-butoxide, 10% w/v in tert-butanol

Key literature references and sources for data<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Physical hazards

On basis of test data

Health Hazards

Calculation method

Environmental hazards

Calculation method

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet