

ALFAA39463

## Barium tetracyanoplatinate(II) tetrahydrate

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
Product Description: 四氰基铂酸钡(II) 四水合物  
Barium tetracyanoplatinate(II) tetrahydrate

Cat No. : 39463  
CAS No 13755-32-3  
Molecular Formula BaPt(CN)<sub>4</sub>·4H<sub>2</sub>O

Supplier Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State  
Solid

Appearance  
Yellow

Odor  
Odorless

#### Emergency Overview

Toxic if swallowed. Very toxic to aquatic life with long lasting effects. Contact with acids liberates very toxic gas.

#### Classification of the substance or mixture

|                          |            |
|--------------------------|------------|
| Acute Oral Toxicity      | Category 3 |
| Acute aquatic toxicity   | Category 1 |
| Chronic aquatic toxicity | Category 1 |

#### Label Elements



Signal Word

Danger

Hazard Statements

# SAFETY DATA SHEET

## Barium tetracyanoplatinate(II) tetrahydrate

H301 - Toxic if swallowed  
H410 - Very toxic to aquatic life with long lasting effects

### Precautionary Statements

#### Prevention

P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product

#### Response

P301 + P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor  
P330 - Rinse mouth

#### Storage

P405 - Store locked up

#### Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

### Physical and Chemical Hazards

Contact with acids liberates very toxic gas.

#### Health Hazards

Toxic if swallowed.

#### Environmental hazards

Very toxic to aquatic life with long lasting effects.

This product does not contain any known or suspected endocrine disruptors.

## SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

| Component                                   | CAS No     | Weight % |
|---|------------|----------|
| Barium tetracyanoplatinate(II) tetrahydrate | 13755-32-3 | <=100    |

## SECTION 4. FIRST AID MEASURES

### General Advice

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

### Eye Contact

In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

### Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

### Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

### Ingestion

Do NOT induce vomiting. Call a physician or poison control center immediately.

### Most important symptoms and effects

None reasonably foreseeable.

### Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

### Notes to Physician

Treat symptomatically.

## SECTION 5. FIRE-FIGHTING MEASURES

# SAFETY DATA SHEET

## Barium tetracyanoplatinate(II) tetrahydrate

**Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Do not allow run-off from fire-fighting to enter drains or water courses.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

### SECTION 6. ACCIDENTAL RELEASE MEASURES

**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas.

**Environmental Precautions**

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

Refer to protective measures listed in Sections 8 and 13.

### SECTION 7. HANDLING AND STORAGE

**Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Avoid dust formation. Use only under a chemical fume hood. Do not breathe (dust, vapor, mist, gas). Do not ingest. If swallowed then seek immediate medical assistance.

**Storage**

Keep container tightly closed in a dry and well-ventilated place.

**Specific Use(s)**

Use in laboratories

### SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

**Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation

# SAFETY DATA SHEET

## Barium tetracyanoplatinate(II) tetrahydrate

or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

### Personal protective equipment

**Eye Protection** Wear safety glasses with side shields (or goggles) (European standard - EN 166)

**Hand Protection** Protective gloves

| Glove material | Breakthrough time | Glove thickness | EU standard | Glove comments        |
|----------------|-------------------|-----------------|-------------|-----------------------|
| Natural rubber | See manufacturers | -               | EN 374      | (minimum requirement) |
| Nitrile rubber | recommendations   |                 |             |                       |
| Neoprene       |                   |                 |             |                       |
| PVC            |                   |                 |             |                       |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.  
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particulates filter conforming to EN 143

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Particle filtering: EN149:2001  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

|                                   |                          |  |
|-----------------------------------|--------------------------|--|
| <b>Appearance</b>                 | Yellow                   |  |
| <b>Physical State</b>             | Solid                    |  |
| <b>Odor</b>                       | Odorless                 |  |
| <b>Odor Threshold</b>             | No data available        |  |
| <b>pH</b>                         | No information available |  |
| <b>Melting Point/Range</b>        | ~ 100 °C / 212 °F        |  |
| <b>Softening Point</b>            | No data available        |  |
| <b>Boiling Point/Range</b>        | No information available |  |
| <b>Flash Point</b>                | No information available | <b>Method -</b> No information available |
| <b>Evaporation Rate</b>           | Not applicable           | Solid                                    |
| <b>Flammability (solid,gas)</b>   | No information available |  |
| <b>Explosion Limits</b>           | No data available        |  |
| <b>Vapor Pressure</b>             | No data available        |  |
| <b>Vapor Density</b>              | Not applicable           | Solid                                    |
| <b>Specific Gravity / Density</b> | 3.05 g/cm3               | @ 20 °C                                  |

# SAFETY DATA SHEET

## Barium tetracyanoplatinate(II) tetrahydrate

|  |                          |       |
|--|--------------------------|-------|
| <b>Bulk Density</b>                            | No data available        |       |
| <b>Water Solubility</b>                        | No information available |       |
| <b>Solubility in other solvents</b>            | No information available |       |
| <b>Partition Coefficient (n-octanol/water)</b> |                          |       |
| <b>Autoignition Temperature</b>                | No data available        |       |
| <b>Decomposition Temperature</b>               | No data available        |       |
| <b>Viscosity</b>                               | Not applicable           | Solid |
| <b>Explosive Properties</b>                    | No information available |       |
| <b>Oxidizing Properties</b>                    | No information available |       |

|                          |  |
|--------------------------|--|
| <b>Molecular Formula</b> | BaPt(CN) <sub>4</sub> ·4H <sub>2</sub> O |
| <b>Molecular Weight</b>  | 508.56 (436.50anhy)                      |

### SECTION 10. STABILITY AND REACTIVITY

|                                 |                                 |
|---------------------------------|---------------------------------|
| <b>Stability</b>                | Stable under normal conditions. |
| <b>Hazardous Reactions</b>      | None under normal processing.   |
| <b>Hazardous Polymerization</b> | No information available.       |
| <b>Conditions to Avoid</b>      | None known.                     |
| <b>Materials to avoid</b>       | No information available.       |

**Hazardous Decomposition Products** None under normal use conditions.

### SECTION 11. TOXICOLOGICAL INFORMATION

#### Product Information

|   |   |
|---|---|
| <b>(a) acute toxicity;</b>                    |   |
| <b>(b) skin corrosion/irritation;</b>         | No data available   |
| <b>(c) serious eye damage/irritation;</b>     | No data available   |
| <b>(d) respiratory or skin sensitization;</b> |   |
| <b>Respiratory</b>                            | No data available   |
| <b>Skin</b>                                   | No data available   |
| <b>(e) germ cell mutagenicity;</b>            | No data available   |
| <b>(f) carcinogenicity;</b>                   | No data available   |
|   | There are no known carcinogenic chemicals in this product |
| <b>(g) reproductive toxicity;</b>             | No data available   |
| <b>(h) STOT-single exposure;</b>              | No data available   |
| <b>(i) STOT-repeated exposure;</b>            | No data available   |
| <b>Target Organs</b>                          | No information available.                                 |

# SAFETY DATA SHEET

## Barium tetracyanoplatinate(II) tetrahydrate

(j) aspiration hazard; Not applicable  
Solid

Symptoms / effects, both acute and delayed No information available

### SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects** Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

**Persistence and Degradability** No information available  
**Degradability** Not relevant for inorganic substances.  
**Degradation in sewage treatment plant** Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Bioaccumulative Potential** No information available

**Mobility in soil** No information available

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

### SECTION 13. DISPOSAL CONSIDERATIONS

**Waste from Residues/Unused Products** Should not be released into the environment. Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point.

**Other Information** Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not let this chemical enter the environment.

### SECTION 14. TRANSPORT INFORMATION

#### Road and Rail Transport

**UN-No** UN1564  
**Proper Shipping Name** Barium compound, n.o.s.  
**Technical Shipping Name** (Barium tetracyanoplatinate(II) tetrahydrate)  
**Hazard Class** 6.1  
**Packing Group** II

#### IMDG/IMO

**UN-No** UN1564  
**Proper Shipping Name** Barium compound, n.o.s.  
**Technical Shipping Name** (Barium tetracyanoplatinate(II) tetrahydrate)  
**Hazard Class** 6.1

# SAFETY DATA SHEET

## Barium tetracyanoplatinate(II) tetrahydrate

**Packing Group** II

### IATA

**UN-No** UN1564  
**Proper Shipping Name** Barium compound, n.o.s.  
**Technical Shipping Name** (Barium tetracyanoplatinate(II) tetrahydrate)  
**Hazard Class** 6.1  
**Packing Group** II

**Special Precautions for User** No special precautions required

## SECTION 15. REGULATORY INFORMATION

### International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

### National Regulations

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 06-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

### Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical incident response training.

### Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

# SAFETY DATA SHEET

## Barium tetracyanoplatinate(II) tetrahydrate

---

Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development  
**BCF** - Bioconcentration factor

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

### Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

### Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**