

ALFAA39561

Zinc 2-ethylhexanoate, ca 80% in mineral spirits

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 2-乙基己酸锌
 Zinc 2-ethylhexanoate, ca 80% in mineral spirits

Cat No. : 39561
Molecular Formula C16 H30 O4 Zn

Supplier Avocado Research Chemicals Ltd.
 (Part of Thermo Fisher Scientific)
 Shore Road, Heysham
 Lancashire, LA3 2XY,
 United Kingdom
 Office Tel: +44 (0) 1524 850506
 Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
 Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Liquid

Appearance
No information available

Odor
No information available

Emergency Overview

Flammable liquid and vapor. May be harmful if swallowed. May be fatal if swallowed and enters airways. Causes serious eye irritation. May cause genetic defects. May cause cancer. Suspected of damaging fertility or the unborn child. Causes damage to organs through prolonged or repeated exposure. Harmful to aquatic life with long lasting effects. Repeated exposure may cause skin dryness or cracking.

Classification of the substance or mixture

Flammable liquids.	Category 3
Aspiration Toxicity	Category 1
Acute Oral Toxicity	Category 5
Serious Eye Damage/Eye Irritation	Category 2
Germ Cell Mutagenicity	Category 1B
Carcinogenicity	Category 1B
Reproductive Toxicity	Category 2
Specific target organ toxicity - (repeated exposure)	Category 1
Chronic aquatic toxicity	Category 3

Label Elements

SAFETY DATA SHEET

Zinc 2-ethylhexanoate, ca 80% in mineral spirits

**Signal Word****Danger****Hazard Statements**

H226 - Flammable liquid and vapor
H303 - May be harmful if swallowed
H304 - May be fatal if swallowed and enters airways
H319 - Causes serious eye irritation
H340 - May cause genetic defects
H350 - May cause cancer
H372 - Causes damage to organs through prolonged or repeated exposure
H412 - Harmful to aquatic life with long lasting effects
H361 - Suspected of damaging fertility or the unborn child

Precautionary Statements**Prevention**

P201 - Obtain special instructions before use
P202 - Do not handle until all safety precautions have been read and understood
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
P233 - Keep container tightly closed
P240 - Ground and bond container and receiving equipment
P242 - Use non-sparking tools
P243 - Take action to prevent static discharges
P260 - Do not breathe dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling
P270 - Do not eat, drink or smoke when using this product
P280 - Wear eye protection/ face protection

Response

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P308 + P313 - IF exposed or concerned: Get medical advice/attention
P301 + P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor
P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell
P331 - Do NOT induce vomiting
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish

Storage

P403 + P235 - Store in a well-ventilated place. Keep cool

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Vapors may cause flash fire or explosion.

Health Hazards

May be harmful if swallowed. Aspiration hazard if swallowed - can enter lungs and cause damage. Causes serious eye irritation. May cause genetic defects. May cause cancer. Suspected of damaging fertility or the unborn child. Causes damage to organs through prolonged or repeated exposure.

Environmental hazards

Harmful to aquatic life with long lasting effects. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil. The product is insoluble and sinks in water.

Toxicity to Soil Dwelling Organisms. Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

SAFETY DATA SHEET

Zinc 2-ethylhexanoate, ca 80% in mineral spirits

Component	CAS No	Weight %
Zinc 2-ethylhexoate	136-53-8	80.00
Stoddard solvent	8052-41-3	20.00

SECTION 4. FIRST AID MEASURES

General Advice

If symptoms persist, call a physician.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur. Risk of serious damage to the lungs (by aspiration).

Ingestion

Clean mouth with water and drink afterwards plenty of water. Do NOT induce vomiting. Call a physician or poison control center immediately. If vomiting occurs naturally, have victim lean forward.

Most important symptoms and effects

Difficulty in breathing. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Carbon dioxide (CO₂). Powder. Foam. Water may be ineffective. Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Flammable. Containers may explode when heated. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions

Ensure adequate ventilation. Use personal protective equipment as required. Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions

Zinc 2-ethylhexanoate, ca 80% in mineral spirits

Should not be released into the environment. See Section 12 for additional Ecological Information. Avoid release to the environment. Collect spillage. Do not flush into surface water or sanitary sewer system.

Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. Take precautionary measures against static discharges.

Storage

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat, sparks and flame.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
Stoddard solvent	-	TWA: 100 ppm TWA: 525 mg/m ³		TWA: 100 ppm TWA: 525 mg/m ³

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Stoddard solvent	TWA: 100 ppm	(Vacated) TWA: 100 ppm (Vacated) TWA: 525 mg/m ³ TWA: 500 ppm TWA: 2900 mg/m ³	IDLH: 20000 mg/m ³ TWA: 350 mg/m ³ Ceiling: 1800 mg/m ³	-	

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

Exposure Controls**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Use explosion-proof electrical/ventilating/lighting equipment. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment**Eye Protection**

Goggles (European standard - EN 166)

Zinc 2-ethylhexanoate, ca 80% in mineral spirits

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Butyl rubber	480 minutes	0.3 mm	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection

Long sleeved clothing

Respiratory Protection

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use

In case of insufficient ventilation, wear suitable respiratory equipment

Recommended Filter type: Multi-purpose/ABEK conforming to EN14387

Small scale/Laboratory use

Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

When RPE is used a face piece Fit Test should be conducted

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls

Prevent product from entering drains.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance

Physical State

Liquid

Odor

No information available

Odor Threshold

No data available

pH

No information available

Melting Point/Range

No data available

Softening Point

No data available

Boiling Point/Range

No information available

Flash Point

No information available

Method - No information available

Evaporation Rate

No data available

Flammability (solid,gas)

Not applicable

Liquid

Explosion Limits

No data available

Vapor Pressure

23 hPa @ 20 °C

Vapor Density

No data available

(Air = 1.0)

Specific Gravity / Density

1.07 g/cm³

@ 20 °C

Bulk Density

Not applicable

Liquid

Water Solubility

Immiscible

Solubility in other solvents

No information available

Partition Coefficient (n-octanol/water)

Component

log Pow

Stoddard solvent

6.4

Autoignition Temperature

No data available

Decomposition Temperature

No data available

Viscosity

No data available

Explosive Properties

explosive air/vapour mixtures possible

Oxidizing Properties

No information available

SAFETY DATA SHEET

Zinc 2-ethylhexanoate, ca 80% in mineral spirits

Molecular Formula C16 H30 O4 Zn
Molecular Weight 351.79

SECTION 10. STABILITY AND REACTIVITY

Stability Stable under normal conditions.

Hazardous Reactions None under normal processing.

Hazardous Polymerization No information available.

Conditions to Avoid Keep away from open flames, hot surfaces and sources of ignition.

Materials to avoid Oxidizing agent.

Hazardous Decomposition Products Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;
Toxicology data for the components

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Zinc 2-ethylhexoate	LD50 = 3550 mg/kg (Rat) LD50 = 3700 mg/kg (Rat)	LD50 > 5000 mg/kg (Rabbit)	LC50 > 23.2 mg/L (Rat) 1 h
Stoddard solvent	5000 mg/kg (orl, rat)	LD50 > 3000 mg/kg (Rabbit)	LC50 > 5.5 mg/L (Rat) 4 h

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; Category 2

(d) respiratory or skin sensitization;
Respiratory No data available
Skin No data available

(e) germ cell mutagenicity; Category 1B

(f) carcinogenicity; Category 1B
The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	EU	UK	Germany	IARC
Stoddard solvent	Carc Cat. 1B			

(g) reproductive toxicity; Category 2

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; Category 1
Target Organs Central nervous system (CNS).

SAFETY DATA SHEET

Zinc 2-ethylhexanoate, ca 80% in mineral spirits

(j) aspiration hazard; Category 1

Symptoms / effects, both acute and delayed Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects

Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

Persistence and Degradability**Persistence**

Immiscible with water.

Degradation in sewage treatment plant

Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential

May have some potential to bioaccumulate

Component	log Pow	Bioconcentration factor (BCF)
Stoddard solvent	6.4	No data available

Mobility in soil

Spillage unlikely to penetrate soil The product is insoluble and sinks in water Is not likely mobile in the environment due its low water solubility

Endocrine Disruptor Information

This product does not contain any known or suspected endocrine disruptors

Persistent Organic Pollutant

This product does not contain any known or suspected substance

Ozone Depletion Potential

This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging

Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

Other Information

Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Can be landfilled or incinerated, when in compliance with local regulations. Do not let this chemical enter the environment. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport**UN-No**

UN1268

Proper Shipping Name

Petroleum distillates, n.o.s.

Technical Shipping Name

(Zinc 2-ethylhexanoate 80%, Mineral spirits)

Hazard Class

3

Packing Group

III

IMDG/IMO

SAFETY DATA SHEET**Zinc 2-ethylhexanoate, ca 80% in mineral spirits**

UN-No UN1268
Proper Shipping Name Petroleum distillates, n.o.s.
Technical Shipping Name (Zinc 2-ethylhexanoate 80%, Mineral spirits)
Hazard Class 3
Packing Group III

IATA

UN-No UN1268
Proper Shipping Name Petroleum distillates, n.o.s.
Technical Shipping Name (Zinc 2-ethylhexanoate 80%, Mineral spirits)
Hazard Class 3
Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Zinc 2-ethylhexanoate	-	-	X	X	205-251-1	X	X	X	X	X	X	KE-13763
Stoddard solvent	-	X	X	X	232-489-3	X	X	X	-		X	KE-32199

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Revision Date 09-May-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

SAFETY DATA SHEET

Zinc 2-ethylhexanoate, ca 80% in mineral spirits

LC50 - Lethal Concentration 50%
NOEC - No Observed Effect Concentration
PBT - Persistent, Bioaccumulative, Toxic

EC50 - Effective Concentration 50%
POW - Partition coefficient Octanol:Water
vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association
ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road
OECD - Organisation for Economic Co-operation and Development
BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code
MARPOL - International Convention for the Prevention of Pollution from Ships
ATE - Acute Toxicity Estimate
VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Physical hazards	On basis of test data
Health Hazards	Calculation method
Environmental hazards	Calculation method

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet