

ALFAA39602

## Tri-n-butyltin fluoride

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

**产品说明:**  
**Product Description:** 三正丁基氟化锡  
 Tri-n-butyltin fluoride

**Cat No. :** 39602  
**CAS No** 1983-10-4  
**Molecular Formula** [CH<sub>3</sub> (CH<sub>2</sub>)<sub>3</sub> ]<sub>3</sub> SnF

**Supplier** Avocado Research Chemicals Ltd.  
 (Part of Thermo Fisher Scientific)  
 Shore Road, Heysham  
 Lancashire, LA3 2XY,  
 United Kingdom  
 Office Tel: +44 (0) 1524 850506  
 Office Fax: +44 (0) 1524 850608

**Emergency Telephone Number** For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
 Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

**E-mail address** begel.sdsdesk@thermofisher.com

**Recommended Use** Laboratory chemicals.  
**Uses advised against** No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Solid

**Appearance**  
White

**Odor**  
pungent

#### Emergency Overview

Causes serious eye irritation. Causes damage to organs. May cause respiratory irritation. Causes damage to organs through prolonged or repeated exposure. Harmful to aquatic life. Very toxic to aquatic life with long lasting effects. Toxic if swallowed. Harmful in contact with skin. Causes skin irritation.

#### Classification of the substance or mixture

Acute Oral Toxicity	Category 3
Acute Dermal Toxicity	Category 4
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Specific target organ toxicity - (single exposure)	Category 1 Category 3
Specific target organ toxicity - (repeated exposure)	Category 1
Acute aquatic toxicity	Category 1 Category 3
Chronic aquatic toxicity	Category 1

#### Label Elements

**Signal Word****Danger****Hazard Statements**

H319 - Causes serious eye irritation  
H370 - Causes damage to organs  
H335 - May cause respiratory irritation  
H372 - Causes damage to organs through prolonged or repeated exposure  
H410 - Very toxic to aquatic life with long lasting effects  
H301 - Toxic if swallowed  
H312 - Harmful in contact with skin  
H315 - Causes skin irritation

**Precautionary Statements****Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P301 + P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor  
P302 + P352 - IF ON SKIN: Wash with plenty of soap and water  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P312 - Call a POISON CENTER or doctor if you feel unwell  
P330 - Rinse mouth  
P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P405 - Store locked up

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Causes serious eye irritation. Causes damage to organs. May cause respiratory irritation. Causes damage to organs through prolonged or repeated exposure. Toxic if swallowed. Harmful in contact with skin. Causes skin irritation.

**Environmental hazards**

Harmful to aquatic life. Very toxic to aquatic life with long lasting effects. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil. The product is insoluble and sinks in water.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Stannane, tributylfluoro-	1983-10-4	<=100

**Note**

Note 1: The concentration stated or, in the absence of such concentrations, the generic concentrations of this Regulation (Table 3.1) or the generic concentrations of Directive 1999/45/EC (Table 3.2), are the percentages by weight of the metallic element calculated with reference to the total weight of the mixture

**SECTION 4. FIRST AID MEASURES**

**General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**Eye Contact**

In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required.

**Ingestion**

Do NOT induce vomiting. Call a physician or poison control center immediately.

**Most important symptoms and effects**

None reasonably foreseeable.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Do not allow run-off from fire-fighting to enter drains or water courses.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas.

**Environmental Precautions**

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

Refer to protective measures listed in Sections 8 and 13.

## SECTION 7. HANDLING AND STORAGE

**Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Avoid dust formation. Use only under a chemical fume hood. Do not breathe (dust, vapor, mist, gas). Do not ingest. If swallowed then seek immediate medical assistance.

**Storage**

Keep container tightly closed in a dry and well-ventilated place.

**Specific Use(s)**

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
Stannane, tributylfluoro-	-	TWA: 0.1 mg/m <sup>3</sup>		STEL: 0.2 mg/m <sup>3</sup>

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Stannane, tributylfluoro-	TWA: 0.1 mg/m <sup>3</sup> STEL: 0.2 mg/m <sup>3</sup> Skin	(Vacated) TWA: 0.1 mg/m <sup>3</sup> Skin	IDLH: 25 mg/m <sup>3</sup> TWA: 0.1 mg/m <sup>3</sup>	STEL: 0.2 mg/m <sup>3</sup> 15 min TWA: 0.1 mg/m <sup>3</sup> 8 hr Skin	

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

**Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

**Exposure Controls****Engineering Measures**

Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment****Eye Protection**

Goggles (European standard - EN 166)

**Hand Protection**

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**SAFETY DATA SHEET****Tri-n-butyltin fluoride**

<b>Skin and body protection</b>	Long sleeved clothing
<b>Respiratory Protection</b>	When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly
<b>Large scale/emergency use</b>	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced <b>Recommended Filter type:</b> Particulates filter conforming to EN 143
<b>Small scale/Laboratory use</b>	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. <b>Recommended half mask:-</b> Particle filtering: EN149:2001 When RPE is used a face piece Fit Test should be conducted
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.
<b>Environmental exposure controls</b>	Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

<b>Appearance</b>	White	
<b>Physical State</b>	Solid	
<b>Odor</b>	pungent	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	248 - 252 °C / 478.4 - 485.6 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	No information available	
<b>Flash Point</b>	145 °C / 293 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	Not applicable	Solid
<b>Flammability (solid,gas)</b>	No information available	
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	Not applicable	Solid
<b>Specific Gravity / Density</b>	1.27 g/cm3	@ 20 °C
<b>Bulk Density</b>	No data available	
<b>Water Solubility</b>	Insoluble in water	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	Not applicable	Solid
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	[CH <sub>3</sub> (CH <sub>2</sub> ) <sub>3</sub> ] <sub>3</sub> SnF	
<b>Molecular Weight</b>	309.04	

**SECTION 10. STABILITY AND REACTIVITY**

<b>Stability</b>	Stable under normal conditions.
<b>Hazardous Reactions</b>	None under normal processing.

**Hazardous Polymerization** No information available.**Conditions to Avoid** None known.**Materials to avoid** No information available.**Hazardous Decomposition Products** None under normal use conditions.**SECTION 11. TOXICOLOGICAL INFORMATION****Product Information****(a) acute toxicity;**

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Stannane, tributylfluoro-			LC50 = 0.4 ppm ( Rat ) 4 h

**(b) skin corrosion/irritation;** Category 2**(c) serious eye damage/irritation;** Category 2**(d) respiratory or skin sensitization;**

Respiratory	No data available
Skin	No data available

**(e) germ cell mutagenicity;** No data available

**(f) carcinogenicity;** No data available

There are no known carcinogenic chemicals in this product

**(g) reproductive toxicity;** No data available**(h) STOT-single exposure;** No data available**(i) STOT-repeated exposure;** Category 1

Target Organs	Cardiovascular system, Blood.
---------------	-------------------------------

**(j) aspiration hazard;** Not applicable

Solid

**Symptoms / effects, both acute and delayed** No information available**SECTION 12. ECOLOGICAL INFORMATION**

**Ecotoxicity effects** Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

**Persistence and Degradability**

**SAFETY DATA SHEET****Tri-n-butyltin fluoride****Persistence  
Degradation in sewage  
treatment plant**

Insoluble in water.  
Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Bioaccumulative Potential**

May have some potential to bioaccumulate

**Mobility in soil**

Spillage unlikely to penetrate soil The product is insoluble and sinks in water Is not likely mobile in the environment due its low water solubility

**Endocrine Disruptor Information**

Component	EU - Endocrine Disruptors Candidate List	EU - Endocrine Disruptors - Evaluated Substances	Japan - Endocrine Disruptor Information
Stannane, tributylfluoro-	Group I Chemical	High Exposure Concern	

**Persistent Organic Pollutant**

This product does not contain any known or suspected substance

**Ozone Depletion Potential**

This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS****Waste from Residues/Unused  
Products**

Should not be released into the environment. Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging**

Dispose of this container to hazardous or special waste collection point.

**Other Information**

Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not let this chemical enter the environment.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

**UN-No** UN3146  
**Proper Shipping Name** Organotin compound, solid, n.o.s.  
**Technical Shipping Name** (Tri-n-butyltin fluoride)  
**Hazard Class** 6.1  
**Packing Group** III

**IMDG/IMO**

**UN-No** UN3146  
**Proper Shipping Name** Organotin compound, solid, n.o.s.  
**Technical Shipping Name** (Tri-n-butyltin fluoride)  
**Hazard Class** 6.1  
**Packing Group** III

**IATA**

**UN-No** UN3146  
**Proper Shipping Name** ORGANOTIN COMPOUND, SOLID, N.O.S.\*  
**Technical Shipping Name** (Tri-n-butyltin fluoride)  
**Hazard Class** 6.1  
**Packing Group** III

**Special Precautions for User**

No special precautions required

## Tri-n-butyltin fluoride

## SECTION 15. REGULATORY INFORMATION

## International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Stannane, tributylfluoro-	X	-	X	-	217-847-9	-	X	X	X	X	-	KE-34042

## Note

Note 1: The concentration stated or, in the absence of such concentrations, the generic concentrations of this Regulation (Table 3.1) or the generic concentrations of Directive 1999/45/EC (Table 3.2), are the percentages by weight of the metallic element calculated with reference to the total weight of the mixture

## National Regulations

Component	Toxic Chemical Substances Control Act
Stannane, tributylfluoro- 1983-10-4 ( <=100 )	Class IV (1 wt%)

## SECTION 16. OTHER INFORMATION

## Prepared By

Health, Safety and Environmental Department

## Revision Date

03-May-2024

## Revision Summary

New emergency telephone response service provider.

## Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical incident response training.

Legend

**CAS** - Chemical Abstracts Service

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**ENCS** - Japanese Existing and New Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**TWA** - Time Weighted Average

**ACGIH** - American Conference of Governmental Industrial Hygienists

**IARC** - International Agency for Research on Cancer

**DNEL** - Derived No Effect Level

**PNEC** - Predicted No Effect Concentration

**RPE** - Respiratory Protective Equipment

**LD50** - Lethal Dose 50%

**LC50** - Lethal Concentration 50%

**EC50** - Effective Concentration 50%

**NOEC** - No Observed Effect Concentration

**POW** - Partition coefficient Octanol:Water

**PBT** - Persistent, Bioaccumulative, Toxic

**vPvB** - very Persistent, very Bioaccumulative



**Tri-n-butyltin fluoride**

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**