

ALFAA42335

Dichloromethane-d2

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 氘代二氯甲烷-{ 2 } , 99.9%(同位素)
Dichloromethane-d2

Cat No. : 42335
CAS No 1665-00-5
Molecular Formula C Cl2 D2

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Liquid

Appearance
Colorless

Odor
sweet

Emergency Overview

Causes skin irritation. Causes serious eye irritation. May cause drowsiness and dizziness. Suspected of causing cancer.
Hygroscopic.

Classification of the substance or mixture

Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Carcinogenicity	Category 2
Specific target organ toxicity - (single exposure)	Category 3

Label Elements



Signal Word

Warning

Hazard Statements

H315 - Causes skin irritation
H319 - Causes serious eye irritation
H336 - May cause drowsiness or dizziness
H351 - Suspected of causing cancer

Precautionary Statements**Prevention**

P201 - Obtain special instructions before use
P202 - Do not handle until all safety precautions have been read and understood
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling
P271 - Use only outdoors or in a well-ventilated area
P280 - Wear eye protection/ face protection

Response

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P308 + P313 - IF exposed or concerned: Get medical advice/attention
P332 + P313 - If skin irritation occurs: Get medical advice/attention
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Hygroscopic.

Health Hazards

Causes skin irritation. Causes serious eye irritation. May cause drowsiness or dizziness. Suspected of causing cancer.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its volatility. The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

Contains a known or suspected endocrine disruptor. Contains a substance on the National Authorities Endocrine Disruptor Lists.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Dichloro(2H2)methane	1665-00-5	100
Methylene chloride	75-09-2	-

SECTION 4. FIRST AID MEASURES**General Advice**

If symptoms persist, call a physician.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

Ingestion

Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects

. Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

Self-Protection of the First Aider

Use personal protective equipment as required.

Notes to Physician

A patient adversely affected by exposure to this product should not be given adrenaline (epinephrine) or similar heart stimulant since these would increase the risk of cardiac arrhythmias. Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Water spray, carbon dioxide (CO₂), dry chemical, alcohol-resistant foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors. Keep product and empty container away from heat and sources of ignition.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Use personal protective equipment as required. Ensure adequate ventilation.

Environmental Precautions

Should not be released into the environment.

Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Ensure adequate ventilation. Avoid ingestion and inhalation.

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place. Store under an inert atmosphere. Protect from moisture.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters**

Dichloromethane-d2

Component	China	Taiwan	Thailand	Hong Kong
Methylene chloride	TWA: 200 mg/m ³	TWA: 50 ppm TWA: 174 mg/m ³	STEL: 125 ppm TWA: 25 ppm	TWA: 50 ppm TWA: 174 mg/m ³

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Methylene chloride	TWA: 50 ppm	(Vacated) TWA: 500 ppm (Vacated) STEL: 2000 ppm (Vacated) Ceiling: 1000 ppm TWA: 25 ppm STEL: 125 ppm	IDLH: 2300 ppm	STEL: 200 ppm 15 min STEL: 706 mg/m ³ 15 min TWA: 353 mg/m ³ 8 hr TWA: 100 ppm 8 hr Skin	TWA: 353 mg/m ³ (8h) TWA: 100 ppm (8h) STEL: 706 mg/m ³ (15min) STEL: 200 ppm (15min) Skin

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

Exposure Controls**Engineering Measures**

Use only under a chemical fume hood. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Viton (R)	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: low boiling organic solvent Type AX Brown conforming to EN371

Dichloromethane-d2

Small scale/Laboratory use

Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141

When RPE is used a face piece Fit Test should be conducted

Hygiene Measures

When using do not eat, drink or smoke. Provide regular cleaning of equipment, work area and clothing.

Environmental exposure controls

Do not allow material to contaminate ground water system.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Colorless	
Physical State	Liquid	
Odor	sweet	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	-97 °C / -142.6 °F	
Softening Point	No data available	
Boiling Point/Range	40 °C / 104 °F	@ 760 mmHg
Flash Point	No information available	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	Lower 13 Vol% Upper 22 Vol%	
Vapor Pressure	450 hPa @ 20 °C	
Vapor Density	No data available	(Air = 1.0)
Specific Gravity / Density	1.360	
Bulk Density	Not applicable	Liquid
Water Solubility	Insoluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
Methylene chloride	1.25	
Autoignition Temperature	556 °C / 1032.8 °F	
Decomposition Temperature	120 °C	
Viscosity	No data available	
Explosive Properties	No information available	
Oxidizing Properties	No information available	

Molecular Formula	C Cl2 D2
Molecular Weight	86.95

SECTION 10. STABILITY AND REACTIVITY

Stability	Hygroscopic.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	Hazardous polymerization does not occur.
Conditions to Avoid	Incompatible products. Excess heat. Exposure to moist air or water.
Materials to avoid	Strong oxidizing agents. Strong acids. Amines.

Hazardous Decomposition Products Carbon monoxide (CO). Carbon dioxide (CO₂). Phosgene. Hydrogen chloride gas.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Methylene chloride	> 2000 mg/kg (Rat)	> 2000 mg/kg (Rat)	53 mg/L (Rat) 6 h 76000 mg/m ³ (Rat) 4 h

(b) skin corrosion/irritation; Category 2

(c) serious eye damage/irritation; Category 2

(d) respiratory or skin sensitization;

Respiratory
SkinBased on available data, the classification criteria are not met
Based on available data, the classification criteria are not met

(e) germ cell mutagenicity; Based on available data, the classification criteria are not met

(f) carcinogenicity; Category 2

The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	EU	UK	Germany	IARC
Methylene chloride				Group 2A

(g) reproductive toxicity; Based on available data, the classification criteria are not met

(h) STOT-single exposure; Category 3

Results / Target organs

Central nervous system (CNS)

(i) STOT-repeated exposure; Based on available data, the classification criteria are not met

Target Organs

None known.

(j) aspiration hazard; Based on available data, the classification criteria are not met

Other Adverse Effects

Tumorigenic effects have been reported in experimental animals.

Symptoms / effects, both acute and delayed

Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects

This product contains the following substance(s) which are hazardous for the environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Dichloro(2H2)methane	Pimephales promelas: LC50:193 mg/L/96h	EC50: 140 mg/L/48h	EC50:>660 mg/L/96h	EC50: 1 mg/L/24 h EC50: 2.88 mg/L/15 min
Methylene chloride	Pimephales promelas: LC50:193 mg/L/96h	EC50: 140 mg/L/48h	EC50:>660 mg/L/96h	EC50: 1 mg/L/24 h EC50: 2.88 mg/L/15 min

Persistence and Degradability

Persistence

Persistence is unlikely, based on information available.

Bioaccumulative Potential Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Methylene chloride	1.25	6.4 - 40 dimensionless

Mobility in soil The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces. Will likely be mobile in the environment due to its volatility. Disperses rapidly in air.

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with federal, state and local regulations. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Do not reuse empty containers. Dispose of in accordance with local regulations. Dispose of this container to hazardous or special waste collection point.

Other Information Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No UN1593
Proper Shipping Name DICHLOROMETHANE
Hazard Class 6.1
Packing Group III

IMDG/IMO

UN-No UN1593
Proper Shipping Name DICHLOROMETHANE
Hazard Class 6.1
Packing Group III

IATA

UN-No UN1593
Proper Shipping Name DICHLOROMETHANE
Hazard Class 6.1
Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of	List of dangerous	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
-----------	------------------	-------------------	------	-------	--------	------	-----	-------	------	------	------	------

SAFETY DATA SHEET**Dichloromethane-d2**

	Hazardous Chemicals (2015 Edition)	goods GB 12268 - 2012										
Dichloro(2H2)methane	-	-	X	-	216-776-0	-	-	-	-	-	-	-
Methylene chloride	X	X	X	X	200-838-9	X	X	X	X	X	X	KE-23893

National Regulations

Component	Toxic Chemical Substances Control Act
Methylene chloride 75-09-2 (-)	Class IV (25 wt%)

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Creation Date 19-Aug-2010
Revision Date 26-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical incident response training.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet