

ALFAA43306

## 1-Ethoxy-2-propanol, 90+%, remainder 2-ethoxy-1-propanol

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
Product Description: 1-乙氧基-2-丙醇  
1-Ethoxy-2-propanol, 90+%, remainder 2-ethoxy-1-propanol

Cat No. : 43306  
Molecular Formula C5 H12 O2

Supplier Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Liquid

**Appearance**  
Colorless

**Odor**  
No information available

**Emergency Overview**  
Flammable liquid and vapor. May cause drowsiness and dizziness. May be harmful if swallowed.

#### Classification of the substance or mixture

Flammable liquids.	Category 3
Acute Oral Toxicity	Category 5
Specific target organ toxicity - (single exposure)	Category 3

#### Label Elements



Signal Word

Warning

Hazard Statements

## 1-Ethoxy-2-propanol, 90+%, remainder 2-ethoxy-1-propanol

H226 - Flammable liquid and vapor  
H336 - May cause drowsiness or dizziness  
H303 - May be harmful if swallowed

**Precautionary Statements****Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P240 - Ground and bond container and receiving equipment  
P242 - Use non-sparking tools  
P243 - Take action to prevent static discharges  
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
P270 - Do not eat, drink or smoke when using this product  
P271 - Use only outdoors or in a well-ventilated area  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower  
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P312 - Call a POISON CENTER or doctor if you feel unwell  
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Vapors may cause flash fire or explosion. Flammable liquid.

**Health Hazards**

May cause drowsiness or dizziness. May be harmful if swallowed.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Propylene glycol ethyl ether	1569-02-4	90.00
2-Ethoxypropanol	19089-47-5	10.00

**SECTION 4. FIRST AID MEASURES****General Advice**

If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water.

**Most important symptoms and effects**

Difficulty in breathing. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

## 1-Ethoxy-2-propanol, 90+%, remainder 2-ethoxy-1-propanol

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Carbon dioxide (CO<sub>2</sub>). Powder. Water spray. In case of major fire and large quantities: Evacuate area. Fight fire remotely due to the risk of explosion. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Flammable. Containers may explode when heated. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Remove all sources of ignition. Take precautionary measures against static discharges.

**Environmental Precautions**

Should not be released into the environment. See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. Take precautionary measures against static discharges.

**Storage**

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat, sparks and flame.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters**

## 1-Ethoxy-2-propanol, 90+%, remainder 2-ethoxy-1-propanol

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Propylene glycol ethyl ether	TWA: 50 ppm STEL: 200 ppm Skin			-	

**Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

**Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Use explosion-proof electrical/ventilating/lighting equipment. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Wear safety glasses with side shields (or goggles) (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber Neoprene Natural rubber PVC	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.  
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Organic gases and vapours filter Type A Brown conforming to EN14387

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

## 1-Ethoxy-2-propanol, 90+%, remainder 2-ethoxy-1-propanol

<b>Appearance</b>	Colorless	
<b>Physical State</b>	Liquid	
<b>Odor</b>	No information available	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	No data available	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	132 °C / 269.6 °F	
<b>Flash Point</b>	42 °C / 107.6 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	23 hPa @ 20 °C	
<b>Vapor Density</b>	No data available	(Air = 1.0)
<b>Specific Gravity / Density</b>	No data available	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	Miscible	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	No data available	
<b>Explosive Properties</b>		explosive air/vapour mixtures possible
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C5 H12 O2	
<b>Molecular Weight</b>	104.15	

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	Keep away from open flames, hot surfaces and sources of ignition.
<b>Materials to avoid</b>	Acids. Oxidizing agent.

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

(a) acute toxicity;  
Toxicology data for the components

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Propylene glycol ethyl ether	LD50 = 4400 mg/kg ( Rat )	LD50 = 8100 mg/kg ( Rabbit )	LC50 > 9.59 mg/L ( Rat ) 4 h
2-Ethoxypropanol	LD50 = 7110 mg/kg ( Rat )		

(b) skin corrosion/irritation; No data available

## 1-Ethoxy-2-propanol, 90+%, remainder 2-ethoxy-1-propanol

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;

Respiratory No data available

Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; Category 3

Results / Target organs Central nervous system (CNS)

(i) STOT-repeated exposure; No data available

Target Organs No information available.

(j) aspiration hazard; No data available

Symptoms / effects, both acute and delayed Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

## SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects .

Persistence and Degradability

Persistence Miscible with water, Persistence is unlikely, based on information available.

Bioaccumulative Potential

Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Propylene glycol ethyl ether		1 dimensionless

Mobility in soil

The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

Endocrine Disruptor Information

This product does not contain any known or suspected endocrine disruptors

Persistent Organic Pollutant

This product does not contain any known or suspected substance

Ozone Depletion Potential

This product does not contain any known or suspected substance

## SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

## 1-Ethoxy-2-propanol, 90+%, remainder 2-ethoxy-1-propanol

**Contaminated Packaging**

Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

**Other Information**

Waste codes should be assigned by the user based on the application for which the product was used. Do not flush to sewer. Can be landfilled or incinerated, when in compliance with local regulations.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

UN-No UN1987  
 Proper Shipping Name ALCOHOLS, N.O.S.  
 Technical Shipping Name (1-Ethoxy-2-propanol, 2-Ethoxy-1-propanol)  
 Hazard Class 3  
 Packing Group III

**IMDG/IMO**

UN-No UN1987  
 Proper Shipping Name ALCOHOLS, N.O.S.  
 Technical Shipping Name (1-Ethoxy-2-propanol, 2-Ethoxy-1-propanol)  
 Hazard Class 3  
 Packing Group III

**IATA**

UN-No UN1987  
 Proper Shipping Name ALCOHOLS, N.O.S.  
 Technical Shipping Name (1-Ethoxy-2-propanol, 2-Ethoxy-1-propanol)  
 Hazard Class 3  
 Packing Group III

**Special Precautions for User** No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Propylene glycol ethyl ether	X	-	X	X	216-374-5	-	X	X	X	X	X	KE-13477
2-Ethoxypropanol	-	-	X	X	242-806-7	-	-	-	X	X	X	-

**National Regulations****SECTION 16. OTHER INFORMATION**

## 1-Ethoxy-2-propanol, 90+%, remainder 2-ethoxy-1-propanol

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 09-Apr-2018  
**Revision Date** 08-May-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Physical hazards**

On basis of test data

**Health Hazards**

Calculation method

**Environmental hazards**

Calculation method

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**