

ALFAA44869

Sponge Nickel, A-7063, promoted with 1% Molybdenum

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: 海绵体镍, A-7063, 1%钼加强
Product Description: Sponge Nickel, A-7063, promoted with 1% Molybdenum

Cat No. : 44869

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Solid Suspension

Appearance
No information available

Odor
No information available

Emergency Overview

Suspected of causing cancer. May cause an allergic skin reaction. Causes damage to organs through prolonged or repeated exposure.

Classification of the substance or mixture

Pyrophoric solids.	Category 1
Self-heating substances/mixtures	Category 1
Skin Sensitization	Category 1
Carcinogenicity	Category 2
Specific target organ toxicity - (repeated exposure)	Category 1

Label Elements

Contains Nickel/Aluminium alloy



SAFETY DATA SHEET

Sponge Nickel, A-7063, promoted with 1% Molybdenum

Signal Word**Danger****Hazard Statements**

H250 - Catches fire spontaneously if exposed to air
H251 - Self-heating: may catch fire
H351 - Suspected of causing cancer
H317 - May cause an allergic skin reaction
H372 - Causes damage to organs through prolonged or repeated exposure

Precautionary Statements**Prevention**

P270 - Do not eat, drink or smoke when using this product
P272 - Contaminated work clothing should not be allowed out of the workplace
P280 - Wear protective gloves
P201 - Obtain special instructions before use
P202 - Do not handle until all safety precautions have been read and understood
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
P222 - Do not allow contact with air
P235 + P410 - Keep cool. Protect from sunlight
P260 - Do not breathe dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling

Response

P308 + P313 - IF exposed or concerned: Get medical advice/attention
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
P302 + P335 + P334 - IF ON SKIN: Brush off loose particles from skin. Immerse in cool water or wrap in wet bandages
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P407 - Maintain air gap between stacks/pallets
P420 - Store away from other materials

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

Suspected of causing cancer. May cause an allergic skin reaction. Causes damage to organs through prolonged or repeated exposure.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil.

Do not allow evaporation to dryness; Hydrogen gas. Toxicity to Soil Dwelling Organisms. This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Nickel	7440-02-0	92.4
Aluminum	7429-90-5	6.4
Molybdenum	7439-98-7	1
Iron	7439-89-6	0.1
Chromium	7440-47-3	0.1

Note

Water Slurry

SECTION 4. FIRST AID MEASURES**General Advice**

If symptoms persist, call a physician.

SAFETY DATA SHEET

Sponge Nickel, A-7063, promoted with 1% Molybdenum

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

Ingestion

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

Most important symptoms and effects

May cause allergic skin reaction. Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

approved class D extinguishers. Do not use water or foam.

Extinguishing media which must not be used for safety reasons

Water may be ineffective. Water.

Specific Hazards Arising from the Chemical

Pyrophoric: Spontaneously flammable in air.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation. No special precautions required. Do not dry up the product.

Environmental Precautions

Do not flush into surface water or sanitary sewer system. Should not be released into the environment. Do not allow material to contaminate ground water system. Collect spillage. See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal. Pick up and transfer to properly labelled containers.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE

Handling

Sponge Nickel, A-7063, promoted with 1% Molybdenum

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Avoid dust formation.

Storage

Keep in a dry place. Keep away from acids. Store under an inert atmosphere. Protect from sunlight and store in well-ventilated place. Keep wetted with water. Keep away from open flames, hot surfaces and sources of ignition.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
Nickel	TWA: 1 mg/m ³	TWA: 1 mg/m ³	TWA: 1 mg/m ³	TWA: 1.5 mg/m ³
Aluminum	TWA: 3 mg/m ³	-	TWA: 15 mg/m ³ TWA: 5 mg/m ³	TWA: 10 mg/m ³
Chromium	TWA: 0.05 mg/m ³	TWA: 1 mg/m ³		TWA: 0.5 mg/m ³

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Nickel	TWA: 1.5 mg/m ³	(Vacated) TWA: 1 mg/m ³ TWA: 1 mg/m ³	IDLH: 10 mg/m ³ TWA: 0.015 mg/m ³	STEL: 1.5 mg/m ³ 15 min TWA: 0.5 mg/m ³ 8 hr Skin	
Aluminum	TWA: 1 mg/m ³	(Vacated) TWA: 15 mg/m ³ (Vacated) TWA: 5 mg/m ³ TWA: 15 mg/m ³ TWA: 5 mg/m ³	TWA: 10 mg/m ³ TWA: 5 mg/m ³	STEL: 30 mg/m ³ 15 min STEL: 12 mg/m ³ 15 min TWA: 10 mg/m ³ 8 hr TWA: 4 mg/m ³ 8 hr	
Molybdenum	TWA: 10 mg/m ³ TWA: 3 mg/m ³	(Vacated) TWA: 10 mg/m ³	IDLH: 5000 mg/m ³	STEL: 20 mg/m ³ 15 min TWA: 10 mg/m ³ 8 hr	
Chromium	TWA: 0.5 mg/m ³	(Vacated) TWA: 1 mg/m ³ TWA: 1 mg/m ³	IDLH: 250 mg/m ³ TWA: 0.5 mg/m ³	STEL: 1.5 mg/m ³ 15 min TWA: 0.5 mg/m ³ 8 hr	TWA: 2 mg/m ³ (8hr)

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust MDHS42/2 Nickel and inorganic compounds of nickel in air (except nickel carbonyl) Laboratory method using flame atomic absorption spectrometry or electrothermal atomic absorption spectrometry MDHS 91 Metals and metalloids in workplace air by X-ray fluorescence spectrometry MDHS 99 Metals in air by ICP-AES

Exposure Controls**Engineering Measures**

None under normal use conditions.

Personal protective equipment**Eye Protection**

Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection

No special protective equipment required

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Disposable gloves	See manufacturers recommendations	-	EN 374	(minimum requirement)

SAFETY DATA SHEET

Sponge Nickel, A-7063, promoted with 1% Molybdenum

Skin and body protection	Long sleeved clothing
Respiratory Protection	No special protective equipment required.
Large scale/emergency use	In case of insufficient ventilation, wear suitable respiratory equipment Recommended Filter type: Particulates filter conforming to EN 143
Small scale/Laboratory use	No personal respiratory protective equipment normally required When RPE is used a face piece Fit Test should be conducted
Hygiene Measures	Handle in accordance with good industrial hygiene and safety practice.
Environmental exposure controls	Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance		
Physical State	Solid Suspension	
Odor	No information available	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	Insoluble in water	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	400 °C	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	

SECTION 10. STABILITY AND REACTIVITY

Stability	Air sensitive.
Hazardous Reactions	None under normal processing. Pyrophoric: Spontaneously flammable in air.
Hazardous Polymerization	No information available.
Conditions to Avoid	None known.
Materials to avoid	Acids. Strong bases. Oxidizing agent.

SAFETY DATA SHEET

Sponge Nickel, A-7063, promoted with 1% Molybdenum

Hazardous Decomposition Products Nickel oxides. Fumes of aluminum or aluminum oxide. Molybdenum oxides. Iron oxides. Chromium oxide.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;
Toxicology data for the components

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Nickel	LD50 > 9000 mg/kg (Rat)		LC50 > 10.2 mg/L (Rat) 1 h
Aluminum			LC50 > 0.888 mg/L (Rat) 4 h
Molybdenum		LD50 > 2000 mg/kg (Rat)	LC50 > 5.84 mg/L (Rat) 4 h
Iron	7500 mg/kg (Rat)		

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;

Respiratory

No data available

Skin

Category 1

May cause sensitization by skin contact

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; Category 2

The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	EU	UK	Germany	IARC
Nickel			Cat. 1	Group 2B

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; Category 1

Route of exposure

Inhalation

Target Organs

Lungs.

(j) aspiration hazard; Not applicable
Solid

Symptoms / effects, both acute and delayed Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects May cause long-term adverse effects in the environment. Do not allow material to

Sponge Nickel, A-7063, promoted with 1% Molybdenum

contaminate ground water system.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Nickel	LC50: > 100 mg/L, 96h (Brachydanio rerio) LC50: = 1.3 mg/L, 96h semi-static (Cyprinus carpio) LC50: = 10.4 mg/L, 96h static (Cyprinus carpio)	EC50 = 510 µg/L 96h	EC50 = 0.1 mg/L 72h EC50 = 0.18 mg/L 72h	

Persistence and Degradability

Persistence
Degradability
Degradation in sewage treatment plant

Product contains heavy metals. Discharge into the environment must be avoided. Special pre-treatment is necessary
Insoluble in water, May persist.
Not relevant for inorganic substances.
Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential

May have some potential to bioaccumulate; Product has a high potential to bioconcentrate

Component	log Pow	Bioconcentration factor (BCF)
Chromium		1.03 - 1.22

Mobility in soil

Spillage unlikely to penetrate soil Is not likely mobile in the environment due its low water solubility

Endocrine Disruptor Information
Persistent Organic Pollutant
Ozone Depletion Potential

This product does not contain any known or suspected endocrine disruptors
This product does not contain any known or suspected substance
This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS**Waste from Residues/Unused Products**

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging

Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

Other Information

Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Can be landfilled or incinerated, when in compliance with local regulations. Do not let this chemical enter the environment.

SECTION 14. TRANSPORT INFORMATION**Road and Rail Transport**

UN-No UN1378
Proper Shipping Name METAL CATALYST, WETTED
Hazard Class 4.2
Packing Group II

IMDG/IMO

UN-No UN1378
Proper Shipping Name METAL CATALYST, WETTED

SAFETY DATA SHEET**Sponge Nickel, A-7063, promoted with 1% Molybdenum**

Hazard Class 4.2
Packing Group II

IATA

UN-No UN1378
Proper Shipping Name METAL CATALYST, WETTED
Hazard Class 4.2
Packing Group II

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Nickel	-	-	X	X	231-111-4	X	X	X	X		X	KE-25818
Aluminum	X	X	X	X	231-072-3	X	X	X	X		X	KE-00881
Molybdenum	-	-	X	X	231-107-2	X	X	X	X		X	KE-25427
Iron	-	-	X	X	231-096-4	X	X	X	X		X	KE-21059
Chromium	-	-	X	X	231-157-5	X	X	X	X		X	KE-05970

Note Water Slurry

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Creation Date 18-May-2018
Revision Date 12-May-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

Sponge Nickel, A-7063, promoted with 1% Molybdenum

WEL - Workplace Exposure Limit**ACGIH** - American Conference of Governmental Industrial Hygienists**DNEL** - Derived No Effect Level**RPE** - Respiratory Protective Equipment**LC50** - Lethal Concentration 50%**NOEC** - No Observed Effect Concentration**PBT** - Persistent, Bioaccumulative, Toxic**TWA** - Time Weighted Average**IARC** - International Agency for Research on Cancer**PNEC** - Predicted No Effect Concentration**LD50** - Lethal Dose 50%**EC50** - Effective Concentration 50%**POW** - Partition coefficient Octanol:Water**vPvB** - very Persistent, very Bioaccumulative**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road**OECD** - Organisation for Economic Co-operation and Development**BCF** - Bioconcentration factor**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code**MARPOL** - International Convention for the Prevention of Pollution from Ships**ATE** - Acute Toxicity Estimate**VOC** - (Volatile Organic Compound)**Key literature references and sources for data**<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Physical hazards

On basis of test data

Health Hazards

Calculation method

Environmental hazards

Calculation method

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet