

ALFAA87676

Nickel Aluminum, Raney® type non-activated

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 镍铝
 Nickel Aluminum, Raney® type non-activated

Cat No. :
Molecular Formula 87676
 Ni:Al

Supplier Avocado Research Chemicals Ltd.
 (Part of Thermo Fisher Scientific)
 Shore Road, Heysham
 Lancashire, LA3 2XY,
 United Kingdom
 Office Tel: +44 (0) 1524 850506
 Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
 Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Solid

Appearance
Grey - Black

Odor
Odorless

Emergency Overview

Flammable solid. Suspected of causing cancer. In contact with water releases flammable gas. May cause an allergic skin reaction. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Causes damage to organs through prolonged or repeated exposure.

Classification of the substance or mixture

Flammable solids.	Category 2
Substances/mixtures which, in contact with water, emit flammable gases	Category 2
Respiratory Sensitization	Category 1
Skin Sensitization	Category 1
Carcinogenicity	Category 2
Specific target organ toxicity - (repeated exposure)	Category 1

Label Elements

SAFETY DATA SHEET

Nickel Aluminum, Raney® type non-activated

**Signal Word****Danger****Hazard Statements**

H228 - Flammable solid
H261 - In contact with water releases flammable gases
H351 - Suspected of causing cancer
H317 - May cause an allergic skin reaction
H334 - May cause allergy or asthma symptoms or breathing difficulties if inhaled
H372 - Causes damage to organs through prolonged or repeated exposure

Precautionary Statements**Prevention**

P201 - Obtain special instructions before use
P202 - Do not handle until all safety precautions have been read and understood
P231 + P232 - Handle and store contents under inert gas. Protect from moisture
P260 - Do not breathe dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling
P270 - Do not eat, drink or smoke when using this product
P272 - Contaminated work clothing should not be allowed out of the workplace
P280 - Wear protective gloves
P284 - In case of inadequate ventilation wear respiratory protection

Response

P304 + P341 - IF INHALED: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing
P308 + P313 - IF exposed or concerned: Get medical advice/attention
P342 + P311 - If experiencing respiratory symptoms: Call a POISON CENTER or doctor
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
P302 + P335 + P334 - IF ON SKIN: Brush off loose particles from skin. Immerse in cool water
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P402 + P404 - Store in a dry place. Store in a closed container

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Combustible material. In contact with water releases flammable gas. Water reactive.

Health Hazards

Suspected of causing cancer. May cause an allergic skin reaction. May cause allergy or asthma symptoms or breathing difficulties if inhaled. Causes damage to organs through prolonged or repeated exposure.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil.

Toxicity to Soil Dwelling Organisms. This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Nickel alloy, base , Ni,Al	12635-29-9	50.0
Nickel	7440-02-0	50.00

SECTION 4. FIRST AID MEASURES

SAFETY DATA SHEET

Nickel Aluminum, Raney® type non-activated

General Advice

If symptoms persist, call a physician.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

Ingestion

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

Most important symptoms and effects

May cause allergy or asthma symptoms or breathing difficulties if inhaled. May cause allergic skin reaction. Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

approved class D extinguishers. Do not use water or foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

Environmental Precautions

Do not flush into surface water or sanitary sewer system. Should not be released into the environment. Do not allow material to contaminate ground water system.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SAFETY DATA SHEET

Nickel Aluminum, Raney® type non-activated

SECTION 7. HANDLING AND STORAGE

Handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Avoid dust formation.

Storage

Keep container tightly closed in a dry and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

Component	China	Taiwan	Thailand	Hong Kong
Nickel alloy, base , Ni,Al	-	TWA: 1 mg/m ³	TWA: 1 mg/m ³	-
Nickel	TWA: 1 mg/m ³	TWA: 1 mg/m ³	TWA: 1 mg/m ³	TWA: 1.5 mg/m ³

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Nickel alloy, base , Ni,Al		(Vacated) TWA: 1 mg/m ³	IDLH: 10 mg/m ³ TWA: 0.015 mg/m ³	-	
Nickel	TWA: 1.5 mg/m ³	(Vacated) TWA: 1 mg/m ³ TWA: 1 mg/m ³	IDLH: 10 mg/m ³ TWA: 0.015 mg/m ³	STEL: 1.5 mg/m ³ 15 min TWA: 0.5 mg/m ³ 8 hr Skin	

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust MDHS42/2 Nickel and inorganic compounds of nickel in air (except nickel carbonyl) Laboratory method using flame atomic absorption spectrometry or electrothermal atomic absorption spectrometry

Exposure Controls

Engineering Measures

Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection

Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

SAFETY DATA SHEET

Nickel Aluminum, Raney® type non-activated

Skin and body protection	Long sleeved clothing
Respiratory Protection	When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly
Large scale/emergency use	In case of insufficient ventilation, wear suitable respiratory equipment Recommended Filter type: Particulates filter conforming to EN 143
Small scale/Laboratory use	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. When RPE is used a face piece Fit Test should be conducted
Hygiene Measures	Handle in accordance with good industrial hygiene and safety practice.
Environmental exposure controls	Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Grey - Black	
Physical State	Solid	
Odor	Odorless	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	23 hPa @ 20 °C	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	Insoluble in water	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	Ni:Al	

SECTION 10. STABILITY AND REACTIVITY

Stability	Water reactive.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	No information available.

SAFETY DATA SHEET

Nickel Aluminum, Raney® type non-activated

Conditions to Avoid None known.

Materials to avoid Acids. Oxidizing agent.

Hazardous Decomposition Products Nickel oxides. Fumes of aluminum or aluminum oxide. Hydrogen.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;
Toxicology data for the components

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Nickel	LD50 > 9000 mg/kg (Rat)		LC50 > 10.2 mg/L (Rat) 1 h

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;
 Respiratory Category 1
 Skin Category 1
 No information available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; Category 2
 The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	EU	UK	Germany	IARC
Nickel			Cat. 1	Group 2B

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; Category 1

Route of exposure Inhalation
 Target Organs Lungs.

(j) aspiration hazard; Not applicable
 Solid

Symptoms / effects, both acute and delayed Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects The product contains following substances which are hazardous for the environment. Contains a substance which is: Very toxic to aquatic organisms. May cause long-term adverse effects in the environment. Do not allow material to contaminate ground water

SAFETY DATA SHEET

Nickel Aluminum, Raney® type non-activated

system.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Nickel	LC50: > 100 mg/L, 96h (Brachydanio rerio) LC50: = 1.3 mg/L, 96h semi-static (Cyprinus carpio) LC50: = 10.4 mg/L, 96h static (Cyprinus carpio)	EC50 = 510 µg/L 96h	EC50 = 0.1 mg/L 72h EC50 = 0.18 mg/L 72h	

Persistence and Degradability

Persistence
Degradation in sewage treatment plant

Product contains heavy metals. Discharge into the environment must be avoided. Special pre-treatment is necessary
 Insoluble in water, May persist.
 Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential

May have some potential to bioaccumulate; Product has a high potential to bioconcentrate

Mobility in soil

Spillage unlikely to penetrate soil Is not likely mobile in the environment due its low water solubility

Endocrine Disruptor Information
Persistent Organic Pollutant
Ozone Depletion Potential

This product does not contain any known or suspected endocrine disruptors
 This product does not contain any known or suspected substance
 This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging

Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

Other Information

Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Can be landfilled or incinerated, when in compliance with local regulations.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No
Proper Shipping Name
Technical Shipping Name
Hazard Class
Packing Group

UN3208
 METALLIC SUBSTANCE, WATER-REACTIVE, N.O.S.
 (ALUMINIUM POWDER, Nickel powder)
 4.3
 II

IMDG/IMO

UN-No
Proper Shipping Name
Technical Shipping Name
Hazard Class
Packing Group

UN3208
 METALLIC SUBSTANCE, WATER-REACTIVE, N.O.S.
 (ALUMINIUM POWDER, Nickel powder)
 4.3
 II

SAFETY DATA SHEET

Nickel Aluminum, Raney® type non-activated

IATA

UN-No UN3208
Proper Shipping Name METALLIC SUBSTANCE, WATER-REACTIVE, N.O.S.*
Technical Shipping Name (ALUMINIUM POWDER, Nickel powder)
Hazard Class 4.3
Packing Group II

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION
International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Nickel alloy, base , Ni,Al	X	-	X	-	-	-	-	-	-		-	-
Nickel	-	-	X	X	231-111-4	X	X	X	X		X	KE-25818

National Regulations
SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Revision Date 09-May-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

SAFETY DATA SHEET

Nickel Aluminum, Raney® type non-activated

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Physical hazards

On basis of test data

Health Hazards

Calculation method

Environmental hazards

Calculation method

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet