

ALFAAA10534

p-Xylene

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: Product Description:	对二甲苯, 99% p-Xylene
Cat No. :	A10534
Synonyms	1,4-Dimethylbenzene
CAS No	106-42-3
Molecular Formula	C8 H10
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information US call: 001-800-227-6701 / Europe call: +32 14 57 52 11 Emergency Number US :001-201-796-7100 / Europe : +32 14 57 52 99 CHEMTREC Tel. No. US :001-800-424-9300 / Europe :001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State Liquid	Appearance Colorless	Odor aromatic
Emergency Overview Highly flammable liquid and vapor. May be harmful if swallowed. May be fatal if swallowed and enters airways. Harmful in contact with skin. Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. May cause respiratory irritation. Harmful to aquatic life with long lasting effects.		

Classification of the substance or mixture

Flammable liquids.	Category 3
Aspiration Toxicity	Category 1
Acute Oral Toxicity	Category 5
Acute Dermal Toxicity	Category 4
Acute Inhalation Toxicity - Vapors	Category 4
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Specific target organ toxicity - (single exposure)	Category 3
Chronic aquatic toxicity	Category 3

Label Elements

**Signal Word****Danger****Hazard Statements**

H226 - Flammable liquid and vapor
H303 - May be harmful if swallowed
H304 - May be fatal if swallowed and enters airways
H315 - Causes skin irritation
H319 - Causes serious eye irritation
H335 - May cause respiratory irritation
H412 - Harmful to aquatic life with long lasting effects
H312 + H332 - Harmful in contact with skin or if inhaled

Precautionary Statements**Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
P240 - Ground and bond container and receiving equipment
P241 - Use explosion-proof electrical/ ventilating/ lighting equipment
P242 - Use non-sparking tools
P243 - Take action to prevent static discharges
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling
P270 - Do not eat, drink or smoke when using this product
P271 - Use only outdoors or in a well-ventilated area
P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P301 + P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor
P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P312 - Call a POISON CENTER or doctor if you feel unwell
P331 - Do NOT induce vomiting
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Highly flammable. Vapors may cause flash fire or explosion.

Health Hazards

May be harmful if swallowed. Aspiration hazard if swallowed - can enter lungs and cause damage. Harmful in contact with skin. Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. May cause respiratory irritation.

Environmental hazards

Harmful to aquatic life with long lasting effects. . Is not likely mobile in the environment due its low water solubility. Will likely be mobile in the environment due to its volatility. Spillage unlikely to penetrate soil. The product is insoluble and floats on water. The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

Other Hazards

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

p-Xylene

Component	CAS No	Weight %
p-Xylene	106-42-3	>95

SECTION 4. FIRST AID MEASURES

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

Inhalation

Remove to fresh air. If breathing is difficult, give oxygen. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Immediate medical attention is required. Risk of serious damage to the lungs (by aspiration).

Ingestion

Aspiration hazard. Do NOT induce vomiting. Call a physician or poison control center immediately. If vomiting occurs naturally, have victim lean forward.

Most important symptoms and effects

Difficulty in breathing. . Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

CO₂, dry chemical, dry sand, alcohol-resistant foam. Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

Water may be ineffective.

Specific Hazards Arising from the Chemical

Flammable. Risk of ignition. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back. Containers may explode when heated. Thermal decomposition can lead to release of irritating gases and vapors. Keep product and empty container away from heat and sources of ignition.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions

Use personal protective equipment as required. Remove all sources of ignition. Take precautionary measures against static discharges. Avoid contact with skin, eyes or clothing.

Environmental Precautions

Avoid release to the environment. See Section 12 for additional Ecological Information. Do not flush into surface water or sanitary sewer system. Collect spillage.

p-Xylene

Methods for Containment and Clean Up

Remove all sources of ignition. Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Use only under a chemical fume hood. Use spark-proof tools and explosion-proof equipment. Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharges. Use only non-sparking tools.

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat, sparks and flame. Flammables area.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
p-Xylene	TWA: 50 mg/m ³ STEL: 100 mg/m ³	TWA: 100 ppm TWA: 434 mg/m ³		-

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
p-Xylene	TWA: 20 ppm		IDLH: 900 ppm TWA: 100 ppm TWA: 435 mg/m ³ STEL: 150 ppm STEL: 655 mg/m ³	STEL: 100 ppm 15 min STEL: 441 mg/m ³ 15 min TWA: 50 ppm 8 hr TWA: 220 mg/m ³ 8 hr Skin	TWA: 50 ppm (8h) TWA: 221 mg/m ³ (8h) STEL: 100 ppm (15min) STEL: 442 mg/m ³ (15min) Skin

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

Exposure Controls**Engineering Measures**

Use only under a chemical fume hood. Use explosion-proof electrical/ventilating/lighting equipment. Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment**Eye Protection**

Goggles (European standard - EN 166)

p-Xylene

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection

Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Recommended Filter type: Organic gases and vapours filter Type A Brown conforming to EN14387

Small scale/Laboratory use

Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141

When RPE is used a face piece Fit Test should be conducted

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls

Prevent product from entering drains. Do not allow material to contaminate ground water system.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance

Colorless

Physical State

Liquid

Odor

aromatic

Odor Threshold

No data available

pH

Not applicable

Melting Point/Range

13 °C / 55.4 °F

Softening Point

No data available

Boiling Point/Range

138 °C / 280.4 °F

Flash Point

25 °C / 77 °F

Method - No information available

Evaporation Rate

No data available

Flammability (solid,gas)

Not applicable

Liquid

Explosion Limits

Lower 1.1 Vol%

Upper 7 Vol%

Vapor Pressure

8 mbar @ 20 °C

Vapor Density

3.7 (Air = 1.0)

(Air = 1.0)

Specific Gravity / Density

0.866

Bulk Density

Not applicable

Liquid

Water Solubility

0.2 g/L (20°C)

practically insoluble

Solubility in other solvents

No information available

p-Xylene

Partition Coefficient (n-octanol/water)

Component	log Pow
p-Xylene	3.2
Autoignition Temperature	465 °C / 869 °F
Decomposition Temperature	No data available
Viscosity	0.648 mPa.s (20°C)

Explosive Properties explosive air/vapour mixtures possible
Oxidizing Properties No information available

Molecular Formula C8 H10
Molecular Weight 106.17

SECTION 10. STABILITY AND REACTIVITY

Stability Stable under normal conditions.

Hazardous Reactions None under normal processing.
Hazardous Polymerization Hazardous polymerization does not occur.

Conditions to Avoid Incompatible products. Excess heat. Keep away from open flames, hot surfaces and sources of ignition.

Materials to avoid Strong oxidizing agents. Strong acids. Strong bases.

Hazardous Decomposition Products Carbon monoxide (CO). Carbon dioxide (CO₂). Hydrocarbons. Aldehydes.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
p-Xylene	LD50 = 4029 mg/kg (Rat)	LD50 = 12126 mg/kg (Rabbit)	LC50 = 4740 ppm (Rat) 4 h

(b) skin corrosion/irritation; Category 2

(c) serious eye damage/irritation; Category 2

(d) respiratory or skin sensitization;

Respiratory No data available
Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity;

Reproductive Effects No data available
Experiments have shown reproductive toxicity effects on laboratory animals.
Developmental Effects Developmental effects have occurred in experimental animals.
Teratogenicity Teratogenic effects have occurred in experimental animals.

p-Xylene

(h) STOT-single exposure;	Category 3
Results / Target organs	Respiratory system
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	Category 1
Other Adverse Effects	See actual entry in RTECS for complete information
Symptoms / effects, both acute and delayed	Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Do not empty into drains. The product contains following substances which are hazardous for the environment. Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. Contains a substance which is: Toxic to aquatic organisms.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
p-Xylene	LC50: = 8.8 mg/L, 96h semi-static (Poecilia reticulata) LC50: = 2.6 mg/L, 96h static (Oncorhynchus mykiss) LC50: = 2.6 mg/L, 96h (Oncorhynchus mykiss) LC50: 7.2 - 9.9 mg/L, 96h static (Pimephales promelas)	EC50: 3.55 - 6.31 mg/L, 48h Static (Daphnia magna)	EC50: = 3.2 mg/L, 72h static (Pseudokirchneriella subcapitata)	EC50 = 5.7 mg/L 30 min

Persistence and Degradability Expected to be biodegradable
Persistence Insoluble in water, Persistence is unlikely, based on information available.
Degradation in sewage treatment plant Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential May have some potential to bioaccumulate

Component	log Pow	Bioconcentration factor (BCF)
p-Xylene	3.2	2.2 dimensionless

Mobility in soil Spillage unlikely to penetrate soil The product is insoluble and floats on water The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces Is not likely mobile in the environment due its low water solubility Will likely be mobile in the environment due to its volatility

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

p-Xylene

Contaminated Packaging

Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

Other Information

Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Can be landfilled or incinerated, when in compliance with local regulations. Do not let this chemical enter the environment. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION**Road and Rail Transport**

UN-No UN1307
 Proper Shipping Name XYLENES
 Hazard Class 3
 Packing Group III

IMDG/IMO

UN-No UN1307
 Proper Shipping Name XYLENES
 Hazard Class 3
 Packing Group III

IATA

UN-No UN1307
 Proper Shipping Name XYLENES
 Hazard Class 3
 Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
p-Xylene	X	X	X	X	203-396-5	X	X	X	X	X	X	KE-35430

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By
Creation Date

Health, Safety and Environmental Department
 24-Mar-2014

p-Xylene

Revision Date

07-Mar-2024

Revision Summary

New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend**CAS** - Chemical Abstracts Service**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances**PICCS** - Philippines Inventory of Chemicals and Chemical Substances**IECSC** - Chinese Inventory of Existing Chemical Substances**KECL** - Korean Existing and Evaluated Chemical Substances**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List**ENCS** - Japanese Existing and New Chemical Substances**AICS** - Australian Inventory of Chemical Substances**NZIoC** - New Zealand Inventory of Chemicals**WEL** - Workplace Exposure Limit**ACGIH** - American Conference of Governmental Industrial Hygienists**DNEL** - Derived No Effect Level**RPE** - Respiratory Protective Equipment**LC50** - Lethal Concentration 50%**NOEC** - No Observed Effect Concentration**PBT** - Persistent, Bioaccumulative, Toxic**TWA** - Time Weighted Average**IARC** - International Agency for Research on Cancer**PNEC** - Predicted No Effect Concentration**LD50** - Lethal Dose 50%**EC50** - Effective Concentration 50%**POW** - Partition coefficient Octanol:Water**vPvB** - very Persistent, very Bioaccumulative**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road**OECD** - Organisation for Economic Co-operation and Development**BCF** - Bioconcentration factor**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code**MARPOL** - International Convention for the Prevention of Pollution from Ships**ATE** - Acute Toxicity Estimate**VOC** - (Volatile Organic Compound)**Key literature references and sources for data**<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadviser - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet