

ALFAAA10914

## 4-Bromobenzonitrile

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

**产品说明:** 4-溴苯甲腈  
**Product Description:** 4-Bromobenzonitrile

**Cat No. :** A10914  
**Synonyms** p-Bromobenzonitrile.; Benzonitrile, 4-bromo-  
**CAS No** 623-00-7  
**Molecular Formula** C7 H4 Br N

**Supplier** Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

**Emergency Telephone Number** For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

**E-mail address** begel.sdsdesk@thermofisher.com

**Recommended Use** Laboratory chemicals.  
**Uses advised against** No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Solid

**Appearance**  
White

**Odor**  
No information available

#### Emergency Overview

Harmful if swallowed. Harmful in contact with skin. Causes serious eye irritation. Harmful to aquatic life with long lasting effects.

#### Classification of the substance or mixture

|                                   |            |
|-----------------------------------|------------|
| Acute Oral Toxicity               | Category 4 |
| Acute Dermal Toxicity             | Category 4 |
| Serious Eye Damage/Eye Irritation | Category 2 |
| Chronic aquatic toxicity          | Category 3 |

#### Label Elements



**Signal Word**

**Warning**

## 4-Bromobenzonitrile

**Hazard Statements**

H319 - Causes serious eye irritation

H412 - Harmful to aquatic life with long lasting effects

H302 + H312 - Harmful if swallowed or in contact with skin

**Precautionary Statements****Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling

P270 - Do not eat, drink or smoke when using this product

P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water

P330 - Rinse mouth

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P312 - Call a POISON CENTER or doctor if you feel unwell

P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 - Store in a well-ventilated place

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Harmful if swallowed. Harmful in contact with skin. Causes serious eye irritation.

**Environmental hazards**

Harmful to aquatic life with long lasting effects. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil.

Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

| Component           | CAS No   | Weight % |
|---------------------|----------|----------|
| 4-Bromobenzonitrile | 623-00-7 | <= 100   |

**SECTION 4. FIRST AID MEASURES****General Advice**

If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

**Most important symptoms and effects**

None reasonably foreseeable.

**Self-Protection of the First Aider**

## 4-Bromobenzonitrile

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray. Carbon dioxide (CO<sub>2</sub>). Dry chemical. Chemical foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

**Environmental Precautions**

Should not be released into the environment. Do not flush into surface water or sanitary sewer system.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Avoid dust formation.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

## 4-Bromobenzonitrile

## Exposure Controls

## Engineering Measures

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

## Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

| Glove material | Breakthrough time | Glove thickness | EU standard | Glove comments        |
|----------------|-------------------|-----------------|-------------|-----------------------|
| Nitrile rubber | See manufacturers | -               | EN 374      | (minimum requirement) |
| Neoprene       | recommendations   |                 |             |                       |
| Natural rubber |                   |                 |             |                       |
| PVC            |                   |                 |             |                       |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Long sleeved clothing

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.  
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particulates filter conforming to EN 143

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Particle filtering: EN149:2001  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** Prevent product from entering drains.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

|                                 |                                 |  |
|---------------------------------|---------------------------------|--|
| <b>Appearance</b>               | White                           |  |
| <b>Physical State</b>           | Solid                           |  |
| <b>Odor</b>                     | No information available        |  |
| <b>Odor Threshold</b>           | No data available               |  |
| <b>pH</b>                       | No information available        |  |
| <b>Melting Point/Range</b>      | 111 - 114 °C / 231.8 - 237.2 °F |  |
| <b>Softening Point</b>          | No data available               |  |
| <b>Boiling Point/Range</b>      | 235 - 237 °C / 455 - 458.6 °F   | @ 760 mmHg                               |
| <b>Flash Point</b>              | No information available        | <b>Method -</b> No information available |
| <b>Evaporation Rate</b>         | Not applicable                  | Solid                                    |
| <b>Flammability (solid,gas)</b> | No information available        |  |
| <b>Explosion Limits</b>         | No data available               |  |

## 4-Bromobenzonitrile

|   |                          |       |
|---|--------------------------|-------|
| Vapor Pressure                          | No data available        |       |
| Vapor Density                           | Not applicable           | Solid |
| Specific Gravity / Density              | No data available        |       |
| Bulk Density                            | No data available        |       |
| Water Solubility                        | 0,2 g/L @24°C            |       |
| Solubility in other solvents            | No information available |       |
| Partition Coefficient (n-octanol/water) |                          |       |
| Component                               | log Pow                  |       |
| 4-Bromobenzonitrile                     | 2.3                      |       |
| Autoignition Temperature                | No data available        |       |
| Decomposition Temperature               | No data available        |       |
| Viscosity                               | Not applicable           | Solid |
| Explosive Properties                    | No information available |       |
| Oxidizing Properties                    | No information available |       |
| Molecular Formula                       | C7 H4 Br N               |       |
| Molecular Weight                        | 182.02                   |       |

## SECTION 10. STABILITY AND REACTIVITY

|                          |  |
|--------------------------|--|
| Stability                | Stable under recommended storage conditions. |
| Hazardous Reactions      | None under normal processing.                |
| Hazardous Polymerization | No information available.                    |
| Conditions to Avoid      | Incompatible products.                       |
| Materials to avoid       | Strong oxidizing agents. Strong bases.       |

**Hazardous Decomposition Products** Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>). Hydrogen halides.

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

## (a) acute toxicity;

| Component           | LD50 Oral             | LD50 Dermal | LC50 Inhalation |
|---------------------|-----------------------|-------------|-----------------|
| 4-Bromobenzonitrile | >300-2000 mg/kg (rat) |             |                 |

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; Category 2

## (d) respiratory or skin sensitization;

|             |                   |
|-------------|-------------------|
| Respiratory | No data available |
| Skin        | No data available |

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

## 4-Bromobenzonitrile

|  |  |
|--|--|
| (h) STOT-single exposure;                  | No data available  |
| (i) STOT-repeated exposure;                | No data available  |
| Target Organs                              | No information available.                                      |
| (j) aspiration hazard;                     | Not applicable<br>Solid  |
| Other Adverse Effects                      | The toxicological properties have not been fully investigated. |
| Symptoms / effects, both acute and delayed | No information available                                       |

## SECTION 12. ECOLOGICAL INFORMATION

|                     |  |
|---------------------|--|
| Ecotoxicity effects | Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment. |
|---------------------|--|

| Component           | Freshwater Fish                         | Water Flea | Freshwater Algae | Microtox   |
|---------------------|---|------------|------------------|--|
| 4-Bromobenzonitrile | LC50: 19 mg/L/96 H<br>(Cyprinus carpio) |            |                  | EC50 = 8.13 mg/L 5 min<br>EC50 = 8.32 mg/L 15 min<br>EC50 = 8.71 mg/L 30 min |

|                                       |   |
|---------------------------------------|---|
| Persistence and Degradability         | Not readily biodegradable   |
| Persistence                           | Persistence is unlikely.  |
| Degradation in sewage treatment plant | Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants. |

|                           |                             |
|---------------------------|-----------------------------|
| Bioaccumulative Potential | Bioaccumulation is unlikely |
|---------------------------|-----------------------------|

| Component           | log Pow | Bioconcentration factor (BCF) |
|---------------------|---------|-------------------------------|
| 4-Bromobenzonitrile | 2.3     | No data available             |

|                  |  |
|------------------|--|
| Mobility in soil | Spillage unlikely to penetrate soil Is not likely mobile in the environment due its low water solubility |
|------------------|--|

|                                 |   |
|---------------------------------|---|
| Endocrine Disruptor Information | This product does not contain any known or suspected endocrine disruptors |
| Persistent Organic Pollutant    | This product does not contain any known or suspected substance            |
| Ozone Depletion Potential       | This product does not contain any known or suspected substance            |

## SECTION 13. DISPOSAL CONSIDERATIONS

|                                     |  |
|-------------------------------------|--|
| Waste from Residues/Unused Products | Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.                               |
| Contaminated Packaging              | Dispose of this container to hazardous or special waste collection point.  |
| Other Information                   | Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not let this chemical enter the environment. |

## 4-Bromobenzonitrile

## SECTION 14. TRANSPORT INFORMATION

Road and Rail TransportIMDG/IMO Not regulatedIATA Not regulatedSpecial Precautions for User No special precautions required

## SECTION 15. REGULATORY INFORMATION

**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

| Component           | The Inventory of Hazardous Chemicals (2015 Edition) | List of dangerous goods GB 12268 - 2012 | TCSI | IECSC | EINECS    | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL |
|---------------------|---|---|------|-------|-----------|------|-----|-------|------|------|------|------|
| 4-Bromobenzonitrile | -   | -                                       | X    | X     | 210-764-9 | -    | -   | X     | -    |      | -    | -    |

**National Regulations**

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 27-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

## 4-Bromobenzonitrile

**DNEL** - Derived No Effect Level  
**RPE** - Respiratory Protective Equipment  
**LC50** - Lethal Concentration 50%  
**NOEC** - No Observed Effect Concentration  
**PBT** - Persistent, Bioaccumulative, Toxic

**PNEC** - Predicted No Effect Concentration  
**LD50** - Lethal Dose 50%  
**EC50** - Effective Concentration 50%  
**POW** - Partition coefficient Octanol:Water  
**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association  
**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road  
**OECD** - Organisation for Economic Co-operation and Development  
**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code  
**MARPOL** - International Convention for the Prevention of Pollution from Ships  
**ATE** - Acute Toxicity Estimate  
**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**