

ALFAAA10979

## 4-Bromobenzylamine hydrochloride

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
Product Description: 4-溴苄胺 盐酸盐  
4-Bromobenzylamine hydrochloride

Cat No. : A10979  
CAS No 26177-44-6  
Molecular Formula C7 H8 Br N . H Cl

Supplier Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Powder Solid

**Appearance**  
Beige

**Odor**  
Odorless

#### Emergency Overview

Harmful if swallowed. Harmful in contact with skin. Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation.

#### Classification of the substance or mixture

Acute Oral Toxicity	Category 4
Acute Dermal Toxicity	Category 4
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Specific target organ toxicity - (single exposure)	Category 3

#### Label Elements



# SAFETY DATA SHEET

## 4-Bromobenzylamine hydrochloride

**Signal Word****Warning****Hazard Statements**

H315 - Causes skin irritation  
H319 - Causes serious eye irritation  
H335 - May cause respiratory irritation  
H302 + H312 - Harmful if swallowed or in contact with skin

**Precautionary Statements****Prevention**

P271 - Use only outdoors or in a well-ventilated area  
P280 - Wear protective gloves/protective clothing/eye protection/face protection  
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product

**Response**

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P330 - Rinse mouth  
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P312 - Call a POISON CENTER or doctor if you feel unwell  
P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Harmful if swallowed. Harmful in contact with skin. Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
4-Bromobenzylamine hydrochloride	26177-44-6	98

**SECTION 4. FIRST AID MEASURES****Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention.

**Inhalation**

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Get medical attention.

**Ingestion**

Clean mouth with water. Get medical attention.

**Most important symptoms and effects**

No information available.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray. Carbon dioxide (CO<sub>2</sub>). Dry chemical. Chemical foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation.

**Environmental Precautions**

See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal. Do not let this chemical enter the environment.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Avoid contact with skin and eyes. Do not breathe dust. Do not ingest. If swallowed then seek immediate medical assistance.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

# SAFETY DATA SHEET

## 4-Bromobenzylamine hydrochloride

### Exposure Controls

#### Engineering Measures

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

#### Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber Neoprene Natural rubber PVC	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.  
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particulates filter conforming to EN 143

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Particle filtering: EN149:2001  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

### SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Beige	
<b>Physical State</b>	Powder Solid	
<b>Odor</b>	Odorless	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	272 - 276 °C / 521.6 - 528.8 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	No information available	
<b>Flash Point</b>	No information available	<b>Method -</b> No information available
<b>Evaporation Rate</b>	Not applicable	Solid
<b>Flammability (solid,gas)</b>	No information available	

# SAFETY DATA SHEET

## 4-Bromobenzylamine hydrochloride

<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	Not applicable	Solid
<b>Specific Gravity / Density</b>	No data available	
<b>Bulk Density</b>	No data available	
<b>Water Solubility</b>	No information available	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	Not applicable	Solid
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C7 H8 Br N . H Cl	
<b>Molecular Weight</b>	222.52	

### SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions.
<b>Hazardous Reactions</b>	No information available.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	Incompatible products.
<b>Materials to avoid</b>	Strong oxidizing agents.
<b>Hazardous Decomposition Products</b>	Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ). Hydrogen halides. Hydrogen chloride gas.

### SECTION 11. TOXICOLOGICAL INFORMATION

#### Product Information

<b>(a) acute toxicity;</b>	
<b>(b) skin corrosion/irritation;</b>	Category 2
<b>(c) serious eye damage/irritation;</b>	Category 2
<b>(d) respiratory or skin sensitization;</b>	
Respiratory	No data available
Skin	No data available
<b>(e) germ cell mutagenicity;</b>	No data available
<b>(f) carcinogenicity;</b>	No data available
	There are no known carcinogenic chemicals in this product
<b>(g) reproductive toxicity;</b>	No data available

**SAFETY DATA SHEET**  
**4-Bromobenzylamine hydrochloride**

<b>(h) STOT-single exposure;</b>	Category 3
<b>Results / Target organs</b>	Respiratory system
<b>(i) STOT-repeated exposure;</b>	No data available
<b>Target Organs</b>	No information available.
<b>(j) aspiration hazard;</b>	Not applicable Solid
<b>Other Adverse Effects</b>	The toxicological properties have not been fully investigated.
<b>Symptoms / effects, both acute and delayed</b>	No information available

**SECTION 12. ECOLOGICAL INFORMATION**

<b>Ecotoxicity effects</b>	Do not empty into drains.
<b>Persistence and Degradability</b>	No information available
<b>Bioaccumulative Potential</b>	No information available
<b>Mobility in soil</b>	No information available
<b>Endocrine Disruptor Information</b>	This product does not contain any known or suspected endocrine disruptors
<b>Persistent Organic Pollutant</b>	This product does not contain any known or suspected substance
<b>Ozone Depletion Potential</b>	This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS**

<b>Waste from Residues/Unused Products</b>	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
<b>Contaminated Packaging</b>	Dispose of this container to hazardous or special waste collection point.
<b>Other Information</b>	Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

**SECTION 14. TRANSPORT INFORMATION**

<b><u>Road and Rail Transport</u></b>	Not Regulated
<b><u>IMDG/IMO</u></b>	Not regulated
<b><u>IATA</u></b>	Not regulated
<b>Special Precautions for User</b>	No special precautions required

## SECTION 15. REGULATORY INFORMATION

## International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
4-Bromobenzylamine hydrochloride	-	-	X	-	247-503-3	-	-	-	-		-	-

## National Regulations

## SECTION 16. OTHER INFORMATION

## Prepared By

## Revision Date

## Revision Summary

Health, Safety and Environmental Department

27-Apr-2024

New emergency telephone response service provider.

## Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

## Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

# SAFETY DATA SHEET

## 4-Bromobenzylamine hydrochloride

---

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

### Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**