

ALFAAA10997

## Benzylamine

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: Product Description:	苄胺 Benzylamine
Cat No. :	A10997
Synonyms	Benzenemethanamine
CAS No	100-46-9
Molecular Formula	C7 H9 N
Supplier	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
Emergency Telephone Number	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
E-mail address	begel.sdsdesk@thermofisher.com
Recommended Use	Laboratory chemicals.
Uses advised against	No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State Liquid	Appearance Clear	Odor Ammonia-like
<b>Emergency Overview</b> Causes severe skin burns and eye damage. Combustible liquid. Harmful if swallowed. Harmful in contact with skin.		

#### Classification of the substance or mixture

Flammable liquids.	Category 4
Acute Oral Toxicity	Category 4
Acute Dermal Toxicity	Category 4
Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1

#### Label Elements



**Signal Word****Danger****Hazard Statements**

H227 - Combustible liquid

H314 - Causes severe skin burns and eye damage

H302 + H312 - Harmful if swallowed or in contact with skin

**Precautionary Statements****Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking

P233 - Keep container tightly closed

P240 - Ground and bond container and receiving equipment

P243 - Take action to prevent static discharges

P261 - Avoid breathing dust/fume/gas/mist/vapors/spray

P264 - Wash face, hands and any exposed skin thoroughly after handling

P270 - Do not eat, drink or smoke when using this product

P271 - Use only outdoors or in a well-ventilated area

P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P310 - Immediately call a POISON CENTER or doctor

P374 - Fight fire with normal precautions from a reasonable distance

P330 - Rinse mouth

P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P235 - Store in a well-ventilated place. Keep cool

P404 - Store in a closed container

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Combustible material.

**Health Hazards**

Corrosive. Causes skin and eye burns. Causes serious eye damage. Harmful if swallowed. Harmful in contact with skin.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Benzenemethanamine	100-46-9	>95

**SECTION 4. FIRST AID MEASURES****General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

**Inhalation**

Remove to fresh air. Get medical attention. If not breathing, give artificial respiration.

**Ingestion**

Do NOT induce vomiting. Call a physician or poison control center immediately.

**Most important symptoms and effects**

Difficulty in breathing. Causes burns by all exposure routes. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

**Self-Protection of the First Aider**

Use personal protective equipment as required.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

CO<sub>2</sub>, dry chemical, dry sand, alcohol-resistant foam. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors. The product causes burns of eyes, skin and mucous membranes. Combustible material. Containers may explode when heated.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Use personal protective equipment as required. Ensure adequate ventilation. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas. Remove all sources of ignition. Take precautionary measures against static discharges. Avoid contact with skin, eyes or clothing.

**Environmental Precautions**

Should not be released into the environment. Do not flush into surface water or sanitary sewer system. See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Use only under a chemical fume hood. Wear personal protective equipment/face protection. Keep away from open flames, hot surfaces and sources of ignition. Avoid contact with skin, eyes or clothing. Avoid ingestion and inhalation. Avoid breathing dust/fume/gas/mist/vapors/spray.

**Storage**

## Benzylamine

Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat, sparks and flame. Flammables area. Corrosives area.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours

**Exposure Controls****Engineering Measures**

Use only under a chemical fume hood. Ensure that eyewash stations and safety showers are close to the workstation location. Use explosion-proof electrical/ventilating/lighting equipment. Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment****Eye Protection**

Goggles (European standard - EN 166)

**Hand Protection**

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection**

Long sleeved clothing

**Respiratory Protection**

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use**

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

**Recommended Filter type:** Particulates filter conforming to EN 143 Ammonia and organic ammonia derivatives filter Type K Green conforming to EN14387

**Small scale/Laboratory use**

Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141

When RPE is used a face piece Fit Test should be conducted

<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.
<b>Environmental exposure controls</b>	Prevent product from entering drains.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Clear	
<b>Physical State</b>	Liquid	
<b>Odor</b>	Ammonia-like	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	11.6	100 g/l aq. sol
<b>Melting Point/Range</b>	-30 °C / -22 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	182 - 185 °C / 359.6 - 365 °F	@ 760 mmHg
<b>Flash Point</b>	72 °C / 161.6 °F	<b>Method -</b> CC (closed cup)
<b>Evaporation Rate</b>	No information available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	<b>Lower</b> 0.9 vol% <b>Upper</b> 14 vol%	
<b>Vapor Pressure</b>	0.6 mbar @ 20 °C	
<b>Vapor Density</b>	3.70 (Air = 1.0)	(Air = 1.0)
<b>Specific Gravity / Density</b>	0.980	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	Soluble	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
Benzenemethanamine	1.09	
<b>Autoignition Temperature</b>	405 °C / 761 °F	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	1.82 mPa.s @ 20 °C	
<b>Explosive Properties</b>		explosive air/vapour mixtures possible
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C7 H9 N	
<b>Molecular Weight</b>	107.15	

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid</b>	Incompatible products. Excess heat. Keep away from open flames, hot surfaces and sources of ignition.
<b>Materials to avoid</b>	Strong oxidizing agents. Acids.

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>). Nitrogen oxides (NO<sub>x</sub>).

## SECTION 11. TOXICOLOGICAL INFORMATION

### Product Information

#### (a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
-----------	-----------	-------------	-----------------

**SAFETY DATA SHEET****Benzylamine**

Benzenemethanamine	552 mg/kg ( Rat )	1350 mg/kg ( Rat )	LC50 > 0.65 mg/L ( Rat ) 3 h
--------------------	-------------------	--------------------	------------------------------

(b) skin corrosion/irritation; Category 1 B

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Respiratory

Based on available data, the classification criteria are not met

Skin

Based on available data, the classification criteria are not met

(e) germ cell mutagenicity;

Based on available data, the classification criteria are not met

Not mutagenic in AMES Test

(f) carcinogenicity;

Based on available data, the classification criteria are not met

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity;

Based on available data, the classification criteria are not met

(h) STOT-single exposure;

Based on available data, the classification criteria are not met

(i) STOT-repeated exposure;

Based on available data, the classification criteria are not met

Target Organs

None known.

(j) aspiration hazard;

Based on available data, the classification criteria are not met

**Symptoms / effects, both acute and delayed**

Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

## SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects**

Contains a substance which is: Harmful to aquatic organisms. Do not empty into drains. Do not flush into surface water or sanitary sewer system. The product contains following substances which are hazardous for the environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Benzenemethanamine	Pimephales promelas: LC50: 102 mg/L/96h	EC50: 60 mg/L/48h		EC50 = 17.0 mg/L 15 min EC50 = 17.0 mg/L 30 min EC50 = 21.4 mg/L 5 min

**Persistence and Degradability**

Persistence

Readily biodegradable

Degradation in sewage treatment plant

Persistence is unlikely.

Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Bioaccumulative Potential**

Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
-----------	---------	-------------------------------

**SAFETY DATA SHEET****Benzylamine**

Benzenemethanamine	1.09	No data available
--------------------	------	-------------------

**Mobility in soil** The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS**

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point.

**Other Information** Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Large amounts will affect pH and harm aquatic organisms. Solutions with high pH-value must be neutralized before discharge.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

**UN-No** UN2735  
**Proper Shipping Name** AMINES, LIQUID, CORROSIVE, N.O.S.  
**Technical Shipping Name** Benzylamine  
**Hazard Class** 8  
**Packing Group** II

**IMDG/IMO**

**UN-No** UN2735  
**Proper Shipping Name** AMINES, LIQUID, CORROSIVE, N.O.S.  
**Technical Shipping Name** Benzylamine  
**Hazard Class** 8  
**Packing Group** II

**IATA**

**UN-No** UN2735  
**Proper Shipping Name** AMINES, LIQUID, CORROSIVE, N.O.S.  
**Technical Shipping Name** Benzylamine  
**Hazard Class** 8  
**Packing Group** II

**Special Precautions for User** No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous	List of dangerous goods GB	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL

**SAFETY DATA SHEET****Benzylamine**

	Chemicals (2015 Edition)	12268 - 2012										
Benzenemethanamine	X	-	X	X	202-854-1	X	X	X	X	X	X	KE-02568

**National Regulations****SECTION 16. OTHER INFORMATION**

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 12-Jun-2009  
**Revision Date** 22-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

# SAFETY DATA SHEET

Benzylamine

---

**End of Safety Data Sheet**