

ALFAAA12249

4-Chlorobutyryl chloride

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 4-氯丁酰氯, 98%
 4-Chlorobutyryl chloride

Cat No. : A12249
Synonyms 4-CBC
CAS No 4635-59-0
Molecular Formula C4 H6 Cl2 O

Supplier Avocado Research Chemicals Ltd.
 (Part of Thermo Fisher Scientific)
 Shore Road, Heysham
 Lancashire, LA3 2XY,
 United Kingdom
 Office Tel: +44 (0) 1524 850506
 Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
 Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
 Liquid

Appearance
 Clear

Odor
 Stench

Emergency Overview

Combustible liquid. May be corrosive to metals. Harmful if swallowed. Causes severe skin burns and eye damage. Fatal if inhaled.
 Contact with water liberates toxic gas. Moisture sensitive. Stench. Lachrymator (substance which increases the flow of tears).

Classification of the substance or mixture

Flammable liquids.	Category 4
Substances/mixtures corrosive to metal	Category 1
Acute Oral Toxicity	Category 4
Acute Inhalation Toxicity - Vapors	Category 2
Skin Corrosion/Irritation	Category 1 A
Serious Eye Damage/Eye Irritation	Category 1

Label Elements

**Signal Word****Danger****Hazard Statements**

H227 - Combustible liquid
H290 - May be corrosive to metals
H302 - Harmful if swallowed
H314 - Causes severe skin burns and eye damage
H330 - Fatal if inhaled

Precautionary Statements**Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
P234 - Keep only in original packaging
P264 - Wash face, hands and any exposed skin thoroughly after handling
P270 - Do not eat, drink or smoke when using this product
P271 - Use only outdoors or in a well-ventilated area
P280 - Wear protective gloves/protective clothing/eye protection/face protection
P284 - Wear respiratory protection

Response

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P310 - Immediately call a POISON CENTER or doctor
P330 - Rinse mouth
P331 - Do NOT induce vomiting
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
P390 - Absorb spillage to prevent material damage
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P402 - Store in a dry place
P403 + P233 - Store in a well-ventilated place. Keep container tightly closed
P406 - Store in corrosion resistant polypropylene container with a resistant liner
P405 - Store locked up

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Combustible material. May be corrosive to metals.

Health Hazards

Harmful if swallowed. Corrosive. Causes skin and eye burns. Fatal if inhaled. Lachrymator (substance which increases the flow of tears).

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. . Is not likely mobile in the environment. Reacts with water.

Other Hazards

Lachrymator (substance which increases the flow of tears)
Stench. Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Butanoyl chloride, 4-chloro-	4635-59-0	>95

SECTION 4. FIRST AID MEASURES**Eye Contact**

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

Inhalation

Remove to fresh air. Immediate medical attention is required. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. If not breathing, give artificial respiration.

Ingestion

Do NOT induce vomiting. Call a physician or poison control center immediately.

Most important symptoms and effects

Difficulty in breathing. Causes burns by all exposure routes. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Carbon dioxide (CO₂). Dry chemical. Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

Water.

Specific Hazards Arising from the Chemical

Combustible material. Contact with water liberates toxic gas. Water reactive. Containers may explode when heated.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid contact with skin, eyes or clothing. Keep people away from and upwind of spill/leak. Evacuate personnel to safe areas. Take precautionary measures against static discharges. Remove all sources of ignition.

Environmental Precautions

See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

4-Chlorobutyl chloride

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal. Wear self-contained breathing apparatus and protective suit. Provide adequate ventilation. Do not expose spill to water. Remove all sources of ignition.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Ensure adequate ventilation. Wear personal protective equipment/face protection. Do not allow contact with water because of violent reaction. Keep under nitrogen. Avoid contact with skin, eyes or clothing. Avoid breathing dust/fume/gas/mist/vapors/spray. Avoid ingestion and inhalation. Keep away from open flames, hot surfaces and sources of ignition.

Storage

Corrosives area. Keep away from heat, sparks and flame. Protect from direct sunlight. Protect from moisture. Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours

Exposure Controls**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Use explosion-proof electrical/ventilating/lighting equipment. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment**Eye Protection**

Goggles (European standard - EN 166)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Butyl rubber	recommendations			
Nitrile rubber				
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection

Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection

When workers are facing concentrations above the exposure limit they must use

4-Chlorobutryl chloride

appropriate certified respirators.

To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Recommended Filter type: Particulates filter conforming to EN 143 Acid gases filter Type E Yellow conforming to EN14387

Small scale/Laboratory use

Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141

When RPE is used a face piece Fit Test should be conducted

Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls

No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Clear	
Physical State	Liquid	
Odor	Stench	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	-47 °C / -52.6 °F	
Softening Point	No data available	
Boiling Point/Range	173 - 174 °C / 343.4 - 345.2 °F	@ 760 mmHg
Flash Point	85 °C / 185 °F	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	Lower 5.5 Vol% Upper 11.7 Vol%	
Vapor Pressure	4 hPa @ 20 °C	
Vapor Density	4.86	(Air = 1.0)
Specific Gravity / Density	1.250	
Bulk Density	Not applicable	Liquid
Water Solubility	Reacts with water	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	440 °C / 824 °F	
Decomposition Temperature	> 120°C	
Viscosity	No data available	
Explosive Properties		explosive air/vapour mixtures possible
Oxidizing Properties	No information available	
Molecular Formula	C4 H6 Cl2 O	
Molecular Weight	141	

SECTION 10. STABILITY AND REACTIVITY**Stability**

Moisture sensitive. Contact with water liberates toxic gas.

Hazardous Reactions

No information available.

Hazardous Polymerization

No information available.

4-Chlorobutryl chloride

Conditions to Avoid Exposure to light. Incompatible products. Exposure to moist air or water. Keep away from open flames, hot surfaces and sources of ignition.

Materials to avoid Water. Strong bases. Alcohols. Amines.

Hazardous Decomposition Products Carbon monoxide (CO). Carbon dioxide (CO₂). Phosgene. Hydrogen chloride gas.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Butanoyl chloride, 4-chloro-	1350 mg/L (Rat)		LC50 0.65 - 0.87 mg/L (Rat) 4 h

(b) skin corrosion/irritation; Category 1 A

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Respiratory
Skin

Based on available data, the classification criteria are not met
Based on available data, the classification criteria are not met

(e) germ cell mutagenicity;

Based on available data, the classification criteria are not met
Not mutagenic in AMES Test

(f) carcinogenicity;

Based on available data, the classification criteria are not met
There are no known carcinogenic chemicals in this product

(g) reproductive toxicity;

Based on available data, the classification criteria are not met

(h) STOT-single exposure;

Based on available data, the classification criteria are not met

(i) STOT-repeated exposure;

Target Organs

Based on available data, the classification criteria are not met
None known.

(j) aspiration hazard;

Based on available data, the classification criteria are not met

Other Adverse Effects

The toxicological properties have not been fully investigated.

Symptoms / effects, both acute and delayed

Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Reacts with water so no ecotoxicity data for the substance is available.

4-Chlorobutryl chloride

Persistence and Degradability	Readily biodegradable
Persistence	Persistence is unlikely, based on information available.
Degradability	Reacts with water.
Degradation in sewage treatment plant	Water reactive.
Bioaccumulative Potential	Product does not bioaccumulate due to reaction with water
Mobility in soil	Reacts with water Is not likely mobile in the environment

Endocrine Disruptor Information	This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant	This product does not contain any known or suspected substance
Ozone Depletion Potential	This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
Contaminated Packaging	Dispose of this container to hazardous or special waste collection point.
Other Information	Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No	UN2922
Proper Shipping Name	Corrosive liquid, toxic, n.o.s.
Technical Shipping Name	(4-CHLOROBUTYRYL CHLORIDE)
Hazard Class	8
Subsidiary Hazard Class	6.1
Packing Group	I

IMDG/IMO

UN-No	UN2922
Proper Shipping Name	Corrosive liquid, toxic, n.o.s.
Technical Shipping Name	(4-CHLOROBUTYRYL CHLORIDE)
Hazard Class	8
Subsidiary Hazard Class	6.1
Packing Group	I

IATA

UN-No	UN2922
Proper Shipping Name	Corrosive liquid, toxic, n.o.s.
Technical Shipping Name	(4-CHLOROBUTYRYL CHLORIDE)
Hazard Class	8
Subsidiary Hazard Class	6.1
Packing Group	I

4-Chlorobutyl chloride

Special Precautions for User No special precautions required**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Butanoyl chloride, 4-chloro-	-	-	X	X	225-059-1	X	-	X	X	X	X	-

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Creation Date 22-Sep-2009
Revision Date 22-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet