

ALFAAA12263

Pyridine-2,6-dicarboxylic acid

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 吡啶-2,6-二羧酸
Pyridine-2,6-dicarboxylic acid

Cat No. : A12263
Synonyms Dipicolinic acid
CAS No 499-83-2
Molecular Formula C7 H5 N O4

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Powder Solid

Appearance
White

Odor
Odorless

Emergency Overview

Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation. Moisture sensitive.

Classification of the substance or mixture

Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Specific target organ toxicity - (single exposure)	Category 3

Label Elements



Signal Word

Warning

Pyridine-2,6-dicarboxylic acid

Hazard Statements

H315 - Causes skin irritation
H319 - Causes serious eye irritation
H335 - May cause respiratory irritation

Precautionary Statements**Prevention**

P271 - Use only outdoors or in a well-ventilated area
P280 - Wear protective gloves/protective clothing/eye protection/face protection
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling

Response

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P332 + P313 - If skin irritation occurs: Get medical advice/attention
P337 + P313 - If eye irritation persists: Get medical advice/attention
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
2,6-Pyridinedicarboxylic acid	499-83-2	99

SECTION 4. FIRST AID MEASURES**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Get medical attention.

Inhalation

Remove to fresh air. Get medical attention. If not breathing, give artificial respiration.

Ingestion

Do NOT induce vomiting. Get medical attention.

Most important symptoms and effects

No information available.

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Water spray. Carbon dioxide (CO₂). Dry chemical. Chemical foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Avoid contact with skin and eyes. Avoid dust formation.

Environmental Precautions

See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Avoid dust formation. Do not let this chemical enter the environment.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Ensure adequate ventilation. Wear personal protective equipment/face protection. Avoid contact with skin and eyes. Avoid dust formation.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls

Pyridine-2,6-dicarboxylic acid

Engineering Measures

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Wear safety glasses with side shields (or goggles) Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers recommendations	-	EN 374	(minimum requirement)
Butyl rubber				
Nitrile rubber				
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Particulates filter conforming to EN 143

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	White	
Physical State	Powder Solid	
Odor	Odorless	
Odor Threshold	No data available	
pH	2	
Melting Point/Range	248 - 250 °C / 478.4 - 482 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	188 °C / 370.4 °F	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	

SAFETY DATA SHEET**Pyridine-2,6-dicarboxylic acid**

Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	5 g/l (20°C)	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
2,6-Pyridinedicarboxylic acid	0.3	
Autoignition Temperature	620 °C / 1148 °F	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	C7 H5 N O4	
Molecular Weight	167.12	

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions. Moisture sensitive.
Hazardous Reactions	No information available.
Hazardous Polymerization	Hazardous polymerization does not occur.
Conditions to Avoid	Incompatible products. Exposure to moist air or water.
Materials to avoid	Acids. Bases. Strong oxidizing agents.

Hazardous Decomposition Products Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information	No acute toxicity information is available for this product
(a) acute toxicity;	
(b) skin corrosion/irritation;	Category 2
(c) serious eye damage/irritation;	Category 2
(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available
	There are no known carcinogenic chemicals in this product
(g) reproductive toxicity;	No data available

(h) STOT-single exposure;	Category 3
Results / Target organs	Respiratory system
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	Not applicable Solid
Other Adverse Effects	The toxicological properties have not been fully investigated.
Symptoms / effects, both acute and delayed	No information available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Do not empty into drains.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
2,6-Pyridinedicarboxylic acid	LC50: = 322 mg/L, 96h flow-through (Pimephales promelas)			

Persistence and Degradability
Persistence Soluble in water, Persistence is unlikely, based on information available.

Bioaccumulative Potential Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
2,6-Pyridinedicarboxylic acid	0.3	No data available

Mobility in soil The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point.

Other Information Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Solutions with low pH-value must be neutralized before discharge.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport Not Regulated

IMDG/IMO Not regulated**IATA** Not regulated**Special Precautions for User** No special precautions required**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
2,6-Pyridinedicarboxylic acid	-	-	X	X	207-894-3	X	X	X	X	X	X	KE-29940

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Creation Date 29-Mar-2012
Revision Date 27-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend**CAS** - Chemical Abstracts Service**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances**PICCS** - Philippines Inventory of Chemicals and Chemical Substances**IECSC** - Chinese Inventory of Existing Chemical Substances**KECL** - Korean Existing and Evaluated Chemical Substances**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List**ENCS** - Japanese Existing and New Chemical Substances**AICS** - Australian Inventory of Chemical Substances**NZIoC** - New Zealand Inventory of Chemicals**WEL** - Workplace Exposure Limit**ACGIH** - American Conference of Governmental Industrial Hygienists**DNEL** - Derived No Effect Level**RPE** - Respiratory Protective Equipment**LC50** - Lethal Concentration 50%**TWA** - Time Weighted Average**IARC** - International Agency for Research on Cancer**PNEC** - Predicted No Effect Concentration**LD50** - Lethal Dose 50%**EC50** - Effective Concentration 50%

Pyridine-2,6-dicarboxylic acid**NOEC** - No Observed Effect Concentration**PBT** - Persistent, Bioaccumulative, Toxic**POW** - Partition coefficient Octanol:Water**vPvB** - very Persistent, very Bioaccumulative**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road**OECD** - Organisation for Economic Co-operation and Development**BCF** - Bioconcentration factor**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code**MARPOL** - International Convention for the Prevention of Pollution from Ships**ATE** - Acute Toxicity Estimate**VOC** - (Volatile Organic Compound)**Key literature references and sources for data**<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet