

ALFAAA12500

o-Xylylene dichloride

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

| | |
|-------------------------------|--|
| 产品说明: Product Description: | 邻亚二甲苯二氯 o-Xylylene dichloride |
| Cat No. : | A12500 |
| Synonyms | 1,2-Bis(chloromethyl)benzene |
| CAS No | 612-12-4 |
| Molecular Formula | C8 H8 Cl2 |
| Supplier | Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608 |
| Emergency Telephone Number | For information US call: 001-800-227-6701 / Europe call: +32 14 57 52 11 Emergency Number US :001-201-796-7100 / Europe : +32 14 57 52 99 CHEMTREC Tel. No. US :001-800-424-9300 / Europe :001-703-527-3887 |
| E-mail address | begel.sdsdesk@thermofisher.com |
| Recommended Use | Laboratory chemicals. |
| Uses advised against | No Information available |

SECTION 2. HAZARD IDENTIFICATION

| | | |
|--|---------------------|------------------|
| Physical State Solid | Appearance Beige | Odor Odorless |
| Emergency Overview Harmful if swallowed. Causes severe skin burns and eye damage. Fatal if inhaled. Very toxic to aquatic life with long lasting effects. Lachrymator (substance which increases the flow of tears). | | |

Classification of the substance or mixture

| | |
|---|--------------|
| Acute Oral Toxicity | Category 4 |
| Acute Inhalation Toxicity - Dusts and Mists | Category 2 |
| Skin Corrosion/Irritation | Category 1 B |
| Serious Eye Damage/Eye Irritation | Category 1 |
| Acute aquatic toxicity | Category 1 |
| Chronic aquatic toxicity | Category 1 |

Label Elements

**Signal Word****Danger****Hazard Statements**

H302 - Harmful if swallowed
H314 - Causes severe skin burns and eye damage
H330 - Fatal if inhaled
H410 - Very toxic to aquatic life with long lasting effects

Precautionary Statements**Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling
P271 - Use only outdoors or in a well-ventilated area
P270 - Do not eat, drink or smoke when using this product
P280 - Wear protective gloves/protective clothing/eye protection/face protection
P284 - Wear respiratory protection

Response

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P310 - Immediately call a POISON CENTER or doctor
P330 - Rinse mouth
P331 - Do NOT induce vomiting
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed
P405 - Store locked up

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

Harmful if swallowed. Corrosive. Causes skin and eye burns. Fatal if inhaled.

Environmental hazards

Very toxic to aquatic life with long lasting effects. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

Other Hazards

Lachrymator (substance which increases the flow of tears)
This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

| Component | CAS No | Weight % |
|---------------------------------|----------|----------|
| Benzene, 1,2-bis(chloromethyl)- | 612-12-4 | >95 |

SECTION 4. FIRST AID MEASURES**Eye Contact**

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Immediate medical attention is required.

Inhalation

Remove from exposure, lie down. Remove to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Immediate medical attention is required.

Ingestion

Do NOT induce vomiting. Call a physician immediately. Clean mouth with water.

Most important symptoms and effects

Causes burns by all exposure routes. . Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Carbon dioxide (CO₂). Dry chemical. Chemical foam. Do not use a solid water stream as it may scatter and spread fire.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Do not allow run-off from fire-fighting to enter drains or water courses.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation.

Environmental Precautions

Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. Prevent product from entering drains. Local authorities should be advised if significant spillages cannot be contained.

Methods for Containment and Clean Up

Wear self-contained breathing apparatus and protective suit. Sweep up and shovel into suitable containers for disposal. Do not let this chemical enter the environment.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Do not breathe dust. Do not get in eyes, on skin, or on clothing. Do not ingest. If swallowed then seek immediate medical

o-Xylylene dichloride

assistance. Handle product only in closed system or provide appropriate exhaust ventilation.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Corrosives area.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment**Eye Protection**

Goggles (European standard - EN 166)

Hand Protection

Protective gloves

| Glove material | Breakthrough time | Glove thickness | EU standard | Glove comments |
|----------------|-------------------|-----------------|-------------|-----------------------|
| Nitrile rubber | See manufacturers | - | EN 374 | (minimum requirement) |
| Neoprene | recommendations | | | |
| Natural rubber | | | | |
| PVC | | | | |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection

Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Particulates filter conforming to EN 143

Small scale/Laboratory use

Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Particle filtering: EN149:2001
When RPE is used a face piece Fit Test should be conducted

o-Xylylene dichloride

| | |
|--|---|
| Hygiene Measures | Handle in accordance with good industrial hygiene and safety practice. |
| Environmental exposure controls | Prevent product from entering drains. Do not allow material to contaminate ground water system. Local authorities should be advised if significant spillages cannot be contained. |

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

| | | |
|--|---------------------------------|--|
| Appearance | Beige | |
| Physical State | Solid | |
| Odor | Odorless | |
| Odor Threshold | No data available | |
| pH | No information available | |
| Melting Point/Range | 53 - 57 °C / 127.4 - 134.6 °F | |
| Softening Point | No data available | |
| Boiling Point/Range | 239 - 241 °C / 462.2 - 465.8 °F | @ 760 mmHg |
| Flash Point | 107 °C / 224.6 °F | Method - No information available |
| Evaporation Rate | Not applicable | Solid |
| Flammability (solid,gas) | No information available | |
| Explosion Limits | No data available | |
| Vapor Pressure | 0.07 hPa @ 20 °C | |
| Vapor Density | Not applicable | Solid |
| Specific Gravity / Density | No data available | |
| Bulk Density | No data available | |
| Water Solubility | hydrolysis | |
| Solubility in other solvents | No information available | |
| Partition Coefficient (n-octanol/water) | | |
| Autoignition Temperature | 450 °C / 842 °F | |
| Decomposition Temperature | No data available | |
| Viscosity | Not applicable | Solid |
| Explosive Properties | No information available | |
| Oxidizing Properties | No information available | |
| Molecular Formula | C8 H8 Cl2 | |
| Molecular Weight | 175.06 | |

SECTION 10. STABILITY AND REACTIVITY

| | |
|---------------------------------|---|
| Stability | Stable under normal conditions. |
| Hazardous Reactions | May react with metals and lead to the formation of flammable hydrogen gas. |
| Hazardous Polymerization | No information available. |
| Conditions to Avoid | Keep away from open flames, hot surfaces and sources of ignition. Excess heat. Incompatible products. Exposure to moisture. |
| Materials to avoid | Bases. Strong oxidizing agents. Alcohols. Amines. Metals. |

Hazardous Decomposition Products Carbon monoxide (CO). Carbon dioxide (CO₂). Phosgene. Hydrogen chloride gas.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

| Component | LD50 Oral | LD50 Dermal | LC50 Inhalation |
|---------------------------------|--------------------|-------------|--------------------|
| Benzene, 1,2-bis(chloromethyl)- | 2263 mg/kg (Rat) | | 0.25 mg/l/4H (rat) |

o-Xylylene dichloride

| | | | |
|--|-----------------|--|--|
| | 603 mg/kg (Rat) | | |
|--|-----------------|--|--|

(b) skin corrosion/irritation; Category 1 B

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Respiratory

No data available

Skin

No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available

Target Organs

No information available.

(j) aspiration hazard; Not applicable
Solid

Other Adverse Effects The toxicological properties have not been fully investigated. See actual entry in RTECS for complete information

Symptoms / effects, both acute and delayed Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

Persistence and Degradability

Persistence

Soluble in water, Persistence is unlikely, based on information available.

Degradation in sewage treatment plant

Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential Bioaccumulation is unlikely

Mobility in soil The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

o-Xylylene dichloride

| | |
|---------------------------------|---|
| Endocrine Disruptor Information | This product does not contain any known or suspected endocrine disruptors |
| Persistent Organic Pollutant | This product does not contain any known or suspected substance |
| Ozone Depletion Potential | This product does not contain any known or suspected substance |

SECTION 13. DISPOSAL CONSIDERATIONS

| | |
|-------------------------------------|---|
| Waste from Residues/Unused Products | Should not be released into the environment. Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations. |
| Contaminated Packaging | Dispose of this container to hazardous or special waste collection point. |
| Other Information | Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Large amounts will affect pH and harm aquatic organisms. Do not let this chemical enter the environment. |

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

| | |
|-------------------------|---|
| UN-No | UN2928 |
| Proper Shipping Name | Toxic solid, corrosive, organic, n.o.s. |
| Technical Shipping Name | Benzene, 1,2-bis(chloromethyl)- |
| Hazard Class | 6.1 |
| Subsidiary Hazard Class | 8 |
| Packing Group | II |

IMDG/IMO

| | |
|-------------------------|---|
| UN-No | UN2928 |
| Proper Shipping Name | Toxic solid, corrosive, organic, n.o.s. |
| Technical Shipping Name | Benzene, 1,2-bis(chloromethyl)- |
| Hazard Class | 6.1 |
| Subsidiary Hazard Class | 8 |
| Packing Group | II |

IATA

| | |
|-------------------------|---|
| UN-No | UN2928 |
| Proper Shipping Name | Toxic solid, corrosive, organic, n.o.s. |
| Technical Shipping Name | Benzene, 1,2-bis(chloromethyl)- |
| Hazard Class | 6.1 |
| Subsidiary Hazard Class | 8 |
| Packing Group | II |

| | |
|------------------------------|---------------------------------|
| Special Precautions for User | No special precautions required |
|------------------------------|---------------------------------|

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

| Component | The Inventory of Hazardous Chemicals (2015 Edition) | List of dangerous goods GB 12268 - 2012 | TCSI | IECSC | EINECS | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL |
|-----------|---|---|------|-------|-----------|------|-----|-------|------|------|------|------|
| Benzene, | - | - | X | - | 210-291-8 | X | - | X | X | X | - | - |

o-Xylylene dichloride

| | | | | | | | | | | | | |
|------------------------|--|--|--|--|--|--|--|--|--|--|--|--|
| 1,2-bis(chloromethyl)- | | | | | | | | | | | | |
|------------------------|--|--|--|--|--|--|--|--|--|--|--|--|

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Revision Date 22-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice
 Chemical incident response training.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet