

ALFAAA13030

## Methyl methacrylate

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
 Product Description: 甲基丙烯酸甲酯, 99%, 含氢醌稳定剂  
 Methyl methacrylate

Cat No. : A13030  
 Synonyms MMA  
 CAS No 80-62-6  
 Molecular Formula C5 H8 O2

Supplier Avocado Research Chemicals Ltd.  
 (Part of Thermo Fisher Scientific)  
 Shore Road, Heysham  
 Lancashire, LA3 2XY,  
 United Kingdom  
 Office Tel: +44 (0) 1524 850506  
 Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
 Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
 Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State  
 Liquid

Appearance  
 Colorless

Odor  
 Strong

#### Emergency Overview

Highly flammable liquid and vapor. Causes skin irritation. May cause an allergic skin reaction. May cause respiratory irritation.  
 Lachrymator (substance which increases the flow of tears).

#### Classification of the substance or mixture

Flammable liquids.	Category 2
Skin Corrosion/Irritation	Category 2
Skin Sensitization	Category 1
Specific target organ toxicity - (single exposure)	Category 3

#### Label Elements



**Signal Word****Danger****Hazard Statements**

H225 - Highly flammable liquid and vapor  
H315 - Causes skin irritation  
H317 - May cause an allergic skin reaction  
H335 - May cause respiratory irritation

**Precautionary Statements****Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P240 - Ground and bond container and receiving equipment  
P241 - Use explosion-proof electrical/ ventilating/ lighting equipment  
P242 - Use non-sparking tools  
P243 - Take action to prevent static discharges  
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P271 - Use only outdoors or in a well-ventilated area  
P272 - Contaminated work clothing should not be allowed out of the workplace  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower  
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P312 - Call a POISON CENTER or doctor if you feel unwell  
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish  
P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Vapors may cause flash fire or explosion. Highly flammable.

**Health Hazards**

Causes skin irritation. May cause an allergic skin reaction. May cause respiratory irritation. Lachrymator (substance which increases the flow of tears).

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. . Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

**Other Hazards**

Lachrymator (substance which increases the flow of tears)  
This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Methyl methacrylate	80-62-6	>95

**Note**

Stabiliser: Methylhydroquinone

**SECTION 4. FIRST AID MEASURES****Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. In the case of skin

## Methyl methacrylate

irritation or allergic reactions see a physician.

**Inhalation**

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Get medical attention.

**Ingestion**

Do NOT induce vomiting. Clean mouth with water. Get medical attention.

**Most important symptoms and effects**

May cause allergic skin reaction. Difficulty in breathing. Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing: Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Carbon dioxide (CO<sub>2</sub>). Foam. Dry chemical. Water mist may be used to cool closed containers. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

Water.

**Specific Hazards Arising from the Chemical**

Flammable. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back. Containers may explode when heated. Vapors may form explosive mixtures with air.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Remove all sources of ignition. Take precautionary measures against static discharges.

**Environmental Precautions**

Do not flush into surface water or sanitary sewer system. See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment. Do not let this chemical enter the environment.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Avoid contact with skin and eyes. Do not breathe mist/vapors/spray. Handle product only in closed system or provide appropriate exhaust ventilation. Use spark-proof tools and explosion-proof equipment. Use only non-sparking tools. Keep away from open

## Methyl methacrylate

flames, hot surfaces and sources of ignition. To avoid ignition of vapors by static electricity discharge, all metal parts of the equipment must be grounded. Take precautionary measures against static discharges.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep away from heat, sparks and flame. Refrigerator/flammables. Inhibitor levels should be maintained.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
Methyl methacrylate	TWA: 100 mg/m <sup>3</sup>	TWA: 100 ppm TWA: 410 mg/m <sup>3</sup>	TWA: 100 ppm	TWA: 50 ppm TWA: 205 mg/m <sup>3</sup> STEL: 100 ppm STEL: 410 mg/m <sup>3</sup>

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Methyl methacrylate	TWA: 50 ppm STEL: 100 ppm	(Vacated) TWA: 100 ppm (Vacated) TWA: 410 mg/m <sup>3</sup> TWA: 100 ppm TWA: 410 mg/m <sup>3</sup>	IDLH: 1000 ppm TWA: 100 ppm TWA: 410 mg/m <sup>3</sup>	STEL: 100 ppm 15 min STEL: 416 mg/m <sup>3</sup> 15 min TWA: 50 ppm 8 hr TWA: 208 mg/m <sup>3</sup> 8 hr	TWA: 50 ppm (8h) STEL: 100 ppm (15min)

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

**Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

**Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Use explosion-proof electrical/ventilating/lighting equipment. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment****Eye Protection**

Goggles (European standard - EN 166)

**Hand Protection**

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g.

## Methyl methacrylate

sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

<b>Skin and body protection</b>	Wear appropriate protective gloves and clothing to prevent skin exposure
<b>Respiratory Protection</b>	When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly
<b>Large scale/emergency use</b>	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced <b>Recommended Filter type:</b> Organic gases and vapours filter Type A Brown conforming to EN14387
<b>Small scale/Laboratory use</b>	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. <b>Recommended half mask:-</b> Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141 When RPE is used a face piece Fit Test should be conducted
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.
<b>Environmental exposure controls</b>	Prevent product from entering drains.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Colorless	
<b>Physical State</b>	Liquid	
<b>Odor</b>	Strong	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	-48 °C / -54.4 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	100 °C / 212 °F	@ 760 mmHg
<b>Flash Point</b>	8 °C / 46.4 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	<b>Lower</b> 2.1 <b>Upper</b> 12.5	
<b>Vapor Pressure</b>	40 mbar @ 20 °C	
<b>Vapor Density</b>	3.5 (Air = 1.0)	(Air = 1.0)
<b>Specific Gravity / Density</b>	0.930	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	15.9 g/L (20°C)	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
Methyl methacrylate	1.38	
<b>Autoignition Temperature</b>	430 °C / 806 °F	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	0.6 mPa s at 20 °C	
<b>Explosive Properties</b>		Vapors may form explosive mixtures with air
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C5 H8 O2	
<b>Molecular Weight</b>	100.12	

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions. Hazardous polymerization may occur upon depletion of inhibitor.
<b>Hazardous Reactions</b>	No information available.
<b>Hazardous Polymerization</b>	Hazardous polymerization may occur upon depletion of inhibitor.
<b>Conditions to Avoid</b>	Keep away from open flames, hot surfaces and sources of ignition. Excess heat. Exposure to light. Incompatible products.
<b>Materials to avoid</b>	Acids. Bases. Amines. Halogens. Peroxides. Reducing Agent.
<b>Hazardous Decomposition Products</b>	Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ).

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

## (a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Methyl methacrylate	LD50 8420 - 10000 mg/kg ( Rat )	LD50 5000 - 7500 mg/kg ( Rabbit )	LC50 = 29.8 mg/L ( Rat ) 4 h

## (b) skin corrosion/irritation;

Category 2

## (c) serious eye damage/irritation;

Based on available data, the classification criteria are not met

## (d) respiratory or skin sensitization;

Respiratory  
SkinBased on available data, the classification criteria are not met  
Category 1

May cause sensitization by skin contact

## (e) germ cell mutagenicity;

Based on available data, the classification criteria are not met  
Mutagenic effects have occurred in experimental animals

## (f) carcinogenicity;

Based on available data, the classification criteria are not met  
There are no known carcinogenic chemicals in this product(g) reproductive toxicity;  
Reproductive EffectsBased on available data, the classification criteria are not met  
Experiments have shown reproductive toxicity effects on laboratory animals.

## (h) STOT-single exposure;

Results / Target organs

Category 3

Respiratory system

## (i) STOT-repeated exposure;

Target Organs

Based on available data, the classification criteria are not met  
None known.

## (j) aspiration hazard;

Based on available data, the classification criteria are not met

**SAFETY DATA SHEET****Methyl methacrylate****Symptoms / effects, both acute and delayed**

Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing: Inhalation of high vapor concentrations may cause symptoms like headache, dizziness, tiredness, nausea and vomiting

**SECTION 12. ECOLOGICAL INFORMATION****Ecotoxicity effects**

Do not empty into drains. Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment. Contains a substance which is: Harmful to aquatic organisms.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Methyl methacrylate	LC50: 326.4 - 426.9 mg/L, 96h static (Poecilia reticulata) LC50: > 79 mg/L, 96h static (Oncorhynchus mykiss) LC50: > 79 mg/L, 96h flow-through (Oncorhynchus mykiss) LC50: 153.9 - 341.8 mg/L, 96h static (Lepomis macrochirus) LC50: 170 - 206 mg/L, 96h flow-through (Lepomis macrochirus) LC50: 125.5 - 190.7 mg/L, 96h static (Pimephales promelas) LC50: 243 - 275 mg/L, 96h flow-through (Pimephales promelas)	EC50: = 69 mg/L, 48h (Daphnia magna)	EC50: = 170 mg/L, 96h (Pseudokirchneriella subcapitata)	

**Persistence and Degradability**
**Persistence**  
**Degradation in sewage treatment plant**

Readily biodegradable  
Persistence is unlikely.  
Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Bioaccumulative Potential**

Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Methyl methacrylate	1.38	No data available

**Mobility in soil**

The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

**Endocrine Disruptor Information**  
**Persistent Organic Pollutant**  
**Ozone Depletion Potential**

This product does not contain any known or suspected endocrine disruptors  
This product does not contain any known or suspected substance  
This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS****Waste from Residues/Unused Products**

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging**

Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and

## Methyl methacrylate

empty container away from heat and sources of ignition.

## Other Information

Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Can be landfilled or incinerated, when in compliance with local regulations.

## SECTION 14. TRANSPORT INFORMATION

## Road and Rail Transport

UN-No UN1247  
Proper Shipping Name METHYL METHACRYLATE MONOMER, STABILIZED  
Hazard Class 3  
Packing Group II

## IMDG/IMO

UN-No UN1247  
Proper Shipping Name METHYL METHACRYLATE MONOMER, STABILIZED  
Hazard Class 3  
Packing Group II

## IATA

UN-No UN1247  
Proper Shipping Name METHYL METHACRYLATE MONOMER, STABILIZED  
Hazard Class 3  
Packing Group II

## Special Precautions for User

Inhibitors have been added to stabilize this product Inhibitor levels should be maintained  
Hazardous polymerization may occur upon depletion of inhibitor

## SECTION 15. REGULATORY INFORMATION

## International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Methyl methacrylate	X	X	X	X	201-297-1	X	X	X	X	X	X	KE-25050

Note Stabiliser: Methylhydroquinone

## National Regulations

## SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department  
Creation Date 13-Nov-2013  
Revision Date 12-May-2024



## Methyl methacrylate

## Revision Summary

New emergency telephone response service provider.

## Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

## Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

## Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**