

ALFAAA13681

Diethyl aminomalonate hydrochloride

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 氨基马来酸二乙酯盐酸盐
Diethyl aminomalonate hydrochloride

Cat No. : A13681
CAS No 13433-00-6
Molecular Formula C7 H13 N O4 . H Cl

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Solid

Appearance
Off-white

Odor
No information available

Emergency Overview

Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation. Moisture sensitive. Hygroscopic.

Classification of the substance or mixture

| | |
|--|------------|
| Skin Corrosion/Irritation | Category 2 |
| Serious Eye Damage/Eye Irritation | Category 2 |
| Specific target organ toxicity - (single exposure) | Category 3 |

Label Elements



Signal Word

Warning

Hazard Statements

SAFETY DATA SHEET

Diethyl aminomalonate hydrochloride

H315 - Causes skin irritation
H319 - Causes serious eye irritation
H335 - May cause respiratory irritation

Precautionary Statements

Prevention

P261 - Avoid breathing dust/fume/gas/mist/vapors/spray
P264 - Wash face, hands and any exposed skin thoroughly after handling
P271 - Use only outdoors or in a well-ventilated area
P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P312 - Call a POISON CENTER or doctor if you feel unwell
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Hygroscopic.

Health Hazards

Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

| Component | CAS No | Weight % |
|-------------------------------------|------------|----------|
| Diethyl aminomalonate hydrochloride | 13433-00-6 | >95 |

SECTION 4. FIRST AID MEASURES

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Get medical attention.

Inhalation

Remove to fresh air. If breathing is difficult, give oxygen. Get medical attention.

Ingestion

Do NOT induce vomiting. Get medical attention.

Most important symptoms and effects

No information available.

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

SAFETY DATA SHEET

Diethyl aminomalonate hydrochloride

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Water spray, carbon dioxide (CO₂), dry chemical, alcohol-resistant foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions

Ensure adequate ventilation. Use personal protective equipment as required. Avoid dust formation.

Environmental Precautions

Should not be released into the environment. See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Avoid dust formation.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE

Handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Avoid dust formation.

Storage

Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control Parameters

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls

Engineering Measures

Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in

SAFETY DATA SHEET

Diethyl aminomalonate hydrochloride

confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Wear safety glasses with side shields (or goggles) Goggles (European standard - EN 166)

Hand Protection Protective gloves

| Glove material | Breakthrough time | Glove thickness | EU standard | Glove comments |
|----------------|-------------------|-----------------|-------------|-----------------------|
| Nitrile rubber | See manufacturers | - | EN 374 | (minimum requirement) |
| Neoprene | recommendations | | | |
| Natural rubber | | | | |
| PVC | | | | |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection No protective equipment is needed under normal use conditions.

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Small scale/Laboratory use Maintain adequate ventilation

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

| | | |
|--|--------------------------|--|
| Appearance | Off-white | |
| Physical State | Solid | |
| Odor | No information available | |
| Odor Threshold | No data available | |
| pH | No information available | |
| Melting Point/Range | 166 °C / 330.8 °F | |
| Softening Point | No data available | |
| Boiling Point/Range | No information available | |
| Flash Point | No information available | Method - No information available |
| Evaporation Rate | Not applicable | Solid |
| Flammability (solid,gas) | No information available | |
| Explosion Limits | No data available | |
| Vapor Pressure | No data available | |
| Vapor Density | Not applicable | Solid |
| Specific Gravity / Density | No data available | |
| Bulk Density | No data available | |
| Water Solubility | Soluble | |
| Solubility in other solvents | No information available | |
| Partition Coefficient (n-octanol/water) | | |

SAFETY DATA SHEET

Diethyl aminomalonate hydrochloride

| | | |
|---------------------------|--------------------------|-------|
| Autoignition Temperature | No data available | |
| Decomposition Temperature | > 162°C | |
| Viscosity | Not applicable | Solid |
| Explosive Properties | No information available | |
| Oxidizing Properties | No information available | |

| | |
|-------------------|--------------------|
| Molecular Formula | C7 H13 N O4 . H Cl |
| Molecular Weight | 211.65 |

SECTION 10. STABILITY AND REACTIVITY

| | |
|----------------------------------|---|
| Stability | Moisture sensitive. Hygroscopic. |
| Hazardous Reactions | None under normal processing. |
| Hazardous Polymerization | No information available. |
| Conditions to Avoid | Incompatible products. Excess heat. Avoid dust formation. Exposure to moist air or water. |
| Materials to avoid | Strong oxidizing agents. Strong acids. Strong bases. |
| Hazardous Decomposition Products | Carbon monoxide (CO). Carbon dioxide (CO ₂). Nitrogen oxides (NO _x). Hydrogen chloride gas. |

SECTION 11. TOXICOLOGICAL INFORMATION

| | |
|--|---|
| Product Information | No acute toxicity information is available for this product |
| (a) acute toxicity; | |
| (b) skin corrosion/irritation; | Category 2 |
| (c) serious eye damage/irritation; | Category 2 |
| (d) respiratory or skin sensitization; | |
| Respiratory | No data available |
| Skin | No data available |
| (e) germ cell mutagenicity; | No data available |
| (f) carcinogenicity; | No data available |
| | There are no known carcinogenic chemicals in this product |
| (g) reproductive toxicity; | No data available |
| (h) STOT-single exposure; | Category 3 |
| Results / Target organs | Respiratory system |
| (i) STOT-repeated exposure; | No data available |
| Target Organs | No information available. |

SAFETY DATA SHEET

Diethyl aminomalonate hydrochloride

| | |
|--|--|
| (j) aspiration hazard; | Not applicable Solid |
| Other Adverse Effects | The toxicological properties have not been fully investigated. |
| Symptoms / effects, both acute and delayed | No information available |

SECTION 12. ECOLOGICAL INFORMATION

| | |
|--|---|
| Ecotoxicity effects | Do not empty into drains. |
| Persistence and Degradability Persistence | Soluble in water, Persistence is unlikely, based on information available. |
| Bioaccumulative Potential | Bioaccumulation is unlikely |
| Mobility in soil | The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils |
| Endocrine Disruptor Information Persistent Organic Pollutant Ozone Depletion Potential | This product does not contain any known or suspected endocrine disruptors This product does not contain any known or suspected substance This product does not contain any known or suspected substance |

SECTION 13. DISPOSAL CONSIDERATIONS

| | |
|-------------------------------------|--|
| Waste from Residues/Unused Products | Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations. |
| Contaminated Packaging | Dispose of this container to hazardous or special waste collection point. |
| Other Information | Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. |

SECTION 14. TRANSPORT INFORMATION

| | |
|--------------------------------|---------------------------------|
| <u>Road and Rail Transport</u> | Not Regulated |
| <u>IMDG/IMO</u> | Not regulated |
| <u>IATA</u> | Not regulated |
| Special Precautions for User | No special precautions required |

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

SAFETY DATA SHEET

Diethyl aminomalonate hydrochloride

| Component | The Inventory of Hazardous Chemicals (2015 Edition) | List of dangerous goods GB 12268 - 2012 | TCSI | IECSC | EINECS | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL |
|-------------------------------------|---|---|------|-------|-----------|------|-----|-------|------|------|------|------|
| Diethyl aminomalonate hydrochloride | - | - | X | X | 236-556-8 | - | - | X | X | X | - | - |

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Revision Date 26-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadviser - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the

SAFETY DATA SHEET

Diethyl aminomalonate hydrochloride

date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet