

ALFAAA13905

## Tiglic acid

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

|                               |  |
|-------------------------------|--|
| 产品说明:<br>Product Description: | 惕各酸<br>Tiglic acid   |
| Cat No. :                     | A13905   |
| Synonyms                      | Tiglic acid  |
| CAS No                        | 80-59-1  |
| Molecular Formula             | C5 H8 O2   |
| Supplier                      | Avocado Research Chemicals Ltd.<br>(Part of Thermo Fisher Scientific)<br>Shore Road, Heysham<br>Lancashire, LA3 2XY,<br>United Kingdom<br>Office Tel: +44 (0) 1524 850506<br>Office Fax: +44 (0) 1524 850608   |
| Emergency Telephone Number    | For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11<br>Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99<br><b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887 |
| E-mail address                | begel.sdsdesk@thermofisher.com   |
| Recommended Use               | Laboratory chemicals.  |
| Uses advised against          | No Information available   |

### SECTION 2. HAZARD IDENTIFICATION

|   |                     |                  |
|---|---------------------|------------------|
| Physical State<br>Powder Solid  | Appearance<br>Beige | Odor<br>Odorless |
| <b>Emergency Overview</b><br>Causes severe skin burns and eye damage. |                     |                  |

#### Classification of the substance or mixture

|                                   |              |
|-----------------------------------|--------------|
| Skin Corrosion/Irritation         | Category 1 C |
| Serious Eye Damage/Eye Irritation | Category 1   |

#### Label Elements



Signal Word

Danger

Hazard Statements

H314 - Causes severe skin burns and eye damage

**Precautionary Statements****Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling

P271 - Use only outdoors or in a well-ventilated area

P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P301 + P330 + P331 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower

P310 - Immediately call a POISON CENTER or doctor

P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Corrosive. Causes skin and eye burns.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

| Component   | CAS No  | Weight % |
|-------------|---------|----------|
| Tiglic acid | 80-59-1 | >95      |

**SECTION 4. FIRST AID MEASURES****General Advice**

Immediate medical attention is not required. Show this safety data sheet to the doctor in attendance. If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If symptoms persist, call a physician.

Immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes. Keep eye wide open while rinsing.

**Skin Contact**

Rinse immediately with plenty of water and seek medical advice. If symptoms persist, call a physician. Call a physician immediately. SPEEDY ACTION IS CRITICAL, GET MEDICAL AID IMMEDIATELY. If skin irritation persists, call a physician. Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.

**Inhalation**

Remove to fresh air. If symptoms persist, call a physician. Artificial respiration and/or oxygen may be necessary. Consult a physician if necessary. Immediate medical attention is not required. Move to fresh air in case of accidental inhalation of vapors.

**Ingestion**

Immediate medical attention is not required. Rinse mouth. Drink plenty of water. Do NOT induce vomiting. Clean mouth with water and drink afterwards plenty of water. Do not induce vomiting without medical advice. Never give anything by mouth to an unconscious person. Consult a physician if necessary.

**Most important symptoms and effects**

Causes burns by all exposure routes. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

**Self-Protection of the First Aider**

Use personal protective equipment as required.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray. Carbon dioxide (CO<sub>2</sub>). Dry chemical. Alcohol resistant foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Use personal protective equipment as required. Avoid contact with skin and eyes. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak.

**Environmental Precautions**

Prevent entry into waterways, sewers, basements or confined areas. Do not flush into surface water or sanitary sewer system. Prevent further leakage or spillage if safe to do so. Prevent product from entering drains. See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Ensure adequate ventilation. No information available. Pay attention to flashback.

**Storage**

Keep out of the reach of children. Keep in properly labeled containers. Keep refrigerated. Keep containers tightly closed in a dry, cool and well-ventilated place. Corrosives area.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**

**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

**Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ventilation systems. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Wear safety glasses with side shields (or goggles) Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

| Glove material | Breakthrough time                 | Glove thickness | EU standard | Glove comments        |
|----------------|-----------------------------------|-----------------|-------------|-----------------------|
| Natural rubber | See manufacturers recommendations | -               | EN 374      | (minimum requirement) |
| Butyl rubber   |                                   |                 |             |                       |
| Nitrile rubber |                                   |                 |             |                       |
| Neoprene       |                                   |                 |             |                       |
| PVC            |                                   |                 |             |                       |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Impervious gloves

**Respiratory Protection** No protective equipment is needed under normal use conditions.

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

**Small scale/Laboratory use** Maintain adequate ventilation

**Hygiene Measures** When using do not eat, drink or smoke. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Provide regular cleaning of equipment, work area and clothing.

**Environmental exposure controls** Do not allow material to contaminate ground water system.

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

**Appearance** Beige  
**Physical State** Powder Solid

**Odor** Odorless  
**Odor Threshold** No data available  
**pH** No information available

## SAFETY DATA SHEET

## Tiglic acid

|  |                             |  |
|--|-----------------------------|--|
| <b>Melting Point/Range</b>                     | 61 - 65 °C / 141.8 - 149 °F |  |
| <b>Softening Point</b>                         | No data available           |  |
| <b>Boiling Point/Range</b>                     | 198.4 °C / 389.1 °F         | @ 760 mmHg                               |
| <b>Flash Point</b>                             | 95 °C / 203 °F              | <b>Method -</b> No information available |
| <b>Evaporation Rate</b>                        | Not applicable              | Solid                                    |
| <b>Flammability (solid,gas)</b>                | No information available    |  |
| <b>Explosion Limits</b>                        | No data available           |  |
| <b>Vapor Pressure</b>                          | No data available           |  |
| <b>Vapor Density</b>                           | Not applicable              | Solid                                    |
| <b>Specific Gravity / Density</b>              | 0.960                       |  |
| <b>Bulk Density</b>                            | No data available           |  |
| <b>Water Solubility</b>                        | soluble in hot water        |  |
| <b>Solubility in other solvents</b>            | No information available    |  |
| <b>Partition Coefficient (n-octanol/water)</b> |                             |  |
| <b>Component</b>                               | <b>log Pow</b>              |  |
| Tiglic acid                                    | 1.4                         |  |
| <b>Autoignition Temperature</b>                | No data available           |  |
| <b>Decomposition Temperature</b>               | No data available           |  |
| <b>Viscosity</b>                               | Not applicable              | Solid                                    |
| <b>Explosive Properties</b>                    | No information available    |  |
| <b>Oxidizing Properties</b>                    | No information available    |  |
| <b>Molecular Formula</b>                       | C5 H8 O2                    |  |
| <b>Molecular Weight</b>                        | 100.12                      |  |

## SECTION 10. STABILITY AND REACTIVITY

|                                 |   |
|---------------------------------|---|
| <b>Stability</b>                | Stable under normal conditions.         |
| <b>Hazardous Reactions</b>      | No information available.               |
| <b>Hazardous Polymerization</b> | No information available.               |
| <b>Conditions to Avoid</b>      | Incompatible products.                  |
| <b>Materials to avoid</b>       | Bases. Reducing Agent. Oxidizing agent. |

**Hazardous Decomposition Products** Thermal decomposition can lead to release of irritating gases and vapors. Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

## (a) acute toxicity;

| Component   | LD50 Oral             | LD50 Dermal | LC50 Inhalation |
|-------------|-----------------------|-------------|-----------------|
| Tiglic acid | LD50 > 5 g/kg ( Rat ) |             |                 |

(b) skin corrosion/irritation; Category 1 C

(c) serious eye damage/irritation; Category 1

## (d) respiratory or skin sensitization;

|                    |                   |
|--------------------|-------------------|
| <b>Respiratory</b> | No data available |
| <b>Skin</b>        | No data available |

|                             |  |
|-----------------------------|--|
| (e) germ cell mutagenicity; | No data available  |
| (f) carcinogenicity;        | No data available<br>There are no known carcinogenic chemicals in this product |
| (g) reproductive toxicity;  | No data available  |
| (h) STOT-single exposure;   | No data available  |
| (i) STOT-repeated exposure; | No data available  |
| Target Organs               | No information available.  |
| (j) aspiration hazard;      | Not applicable<br>Solid  |

**Other Adverse Effects** The toxicological properties have not been fully investigated.

**Symptoms / effects, both acute and delayed** Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

## SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects** Do not empty into drains. .

**Persistence and Degradability**  
**Persistence** Persistence is unlikely.

**Bioaccumulative Potential** Bioaccumulation is unlikely

| Component   | log Pow | Bioconcentration factor (BCF) |
|-------------|---------|-------------------------------|
| Tiglic acid | 1.4     | No data available             |

**Mobility in soil** The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors  
**Persistent Organic Pollutant** This product does not contain any known or suspected substance  
**Ozone Depletion Potential** This product does not contain any known or suspected substance

## SECTION 13. DISPOSAL CONSIDERATIONS

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point.

**Other Information** Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms.

## SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No UN3261  
Proper Shipping Name Corrosive solid, acidic, organic, n.o.s.  
Technical Shipping Name Tiglic acid  
Hazard Class 8  
Packing Group III

IMDG/IMO

UN-No UN3261  
Proper Shipping Name Corrosive solid, acidic, organic, n.o.s.  
Technical Shipping Name Tiglic acid  
Hazard Class 8  
Packing Group III

IATA

UN-No UN3261  
Proper Shipping Name Corrosive solid, acidic, organic, n.o.s.  
Technical Shipping Name Tiglic acid  
Hazard Class 8  
Packing Group III

Special Precautions for User No special precautions required

## SECTION 15. REGULATORY INFORMATION

**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

| Component   | The Inventory of Hazardous Chemicals (2015 Edition) | List of dangerous goods GB 12268 - 2012 | TCSI | IECSC | EINECS    | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL     |
|-------------|---|---|------|-------|-----------|------|-----|-------|------|------|------|----------|
| Tiglic acid | -   | -                                       | X    | X     | 201-295-0 | X    | X   | X     | X    | X    | X    | KE-23594 |

**National Regulations**

## SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department  
Revision Date 25-Apr-2024  
Revision Summary New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.  
Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit

## Tiglic acid

and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**