

ALFAAA14056

2-Vinylpyridine

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 2-乙烯吡啶
 2-Vinylpyridine

Cat No. : A14056
Synonyms 2-Ethenylpyridine.
CAS No 100-69-6
Molecular Formula C7 H7 N

Supplier Avocado Research Chemicals Ltd.
 (Part of Thermo Fisher Scientific)
 Shore Road, Heysham
 Lancashire, LA3 2XY,
 United Kingdom
 Office Tel: +44 (0) 1524 850506
 Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
 Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Liquid

Appearance
Brown

Odor
pungent

Emergency Overview

Highly flammable liquid and vapor. Harmful if swallowed. Toxic in contact with skin. Causes severe skin burns and eye damage. May cause an allergic skin reaction. Toxic to aquatic life with long lasting effects. Corrosive to the respiratory tract. Lachrymator (substance which increases the flow of tears).

Classification of the substance or mixture

Flammable liquids.	Category 3
Acute Oral Toxicity	Category 4
Acute Dermal Toxicity	Category 3
Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1
Skin Sensitization	Category 1
Chronic aquatic toxicity	Category 2

Label Elements

2-Vinylpyridine



Signal Word

Danger

Hazard Statements

H226 - Flammable liquid and vapor
 H302 - Harmful if swallowed
 H311 - Toxic in contact with skin
 H314 - Causes severe skin burns and eye damage
 H317 - May cause an allergic skin reaction
 H411 - Toxic to aquatic life with long lasting effects

Precautionary Statements

Prevention

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
 P240 - Ground and bond container and receiving equipment
 P241 - Use explosion-proof electrical/ ventilating/ lighting equipment
 P242 - Use non-sparking tools
 P243 - Take action to prevent static discharges
 P264 - Wash face, hands and any exposed skin thoroughly after handling
 P270 - Do not eat, drink or smoke when using this product
 P271 - Use only outdoors or in a well-ventilated area
 P272 - Contaminated work clothing should not be allowed out of the workplace
 P280 - Wear protective gloves/protective clothing/eye protection/face protection
 P284 - Wear respiratory protection

Response

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
 P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
 P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 P310 - Immediately call a POISON CENTER or doctor
 P330 - Rinse mouth
 P331 - Do NOT induce vomiting
 P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish
 P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed
 P405 - Store locked up

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Highly flammable. Vapors may cause flash fire or explosion.

Health Hazards

Harmful if swallowed. Toxic in contact with skin. Corrosive. Causes skin and eye burns. May cause an allergic skin reaction.

Environmental hazards

Toxic to aquatic life with long lasting effects. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

Other Hazards

Lachrymator (substance which increases the flow of tears)
 This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
-----------	--------	----------

2-Vinylpyridine

Pyridine, 2-ethenyl-	100-69-6	>95
----------------------	----------	-----

SECTION 4. FIRST AID MEASURES

General Advice

Immediate medical attention is required. Show this safety data sheet to the doctor in attendance.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. Immediate medical attention is required.

Inhalation

If breathing is difficult, give oxygen. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Remove to fresh air. Immediate medical attention is required.

Ingestion

Do NOT induce vomiting. Call a physician or poison control center immediately.

Most important symptoms and effects

Difficulty in breathing. Causes burns by all exposure routes. May cause allergy or asthma symptoms or breathing difficulties if inhaled. May cause allergic skin reaction. . Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Water spray, carbon dioxide (CO2), dry chemical, alcohol-resistant foam. Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors. The product causes burns of eyes, skin and mucous membranes. Flammable. Containers may explode when heated. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions

Use personal protective equipment as required. Evacuate personnel to safe areas. Keep people away from and upwind of

2-Vinylpyridine

spill/leak. Ensure adequate ventilation. Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions

Do not flush into surface water or sanitary sewer system. See Section 12 for additional Ecological Information. Avoid release to the environment. Collect spillage.

Methods for Containment and Clean Up

Keep in suitable, closed containers for disposal. Soak up with inert absorbent material. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Do not breathe mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Wear personal protective equipment/face protection. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. Take precautionary measures against static discharges.

Storage

To maintain product quality: Store in freezer. Keep container tightly closed. Keep away from heat, sparks and flame.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

Exposure Controls**Engineering Measures**

Use explosion-proof electrical/ventilating/lighting equipment. Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment**Eye Protection**

Goggles (European standard - EN 166)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

2-Vinylpyridine

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection	Long sleeved clothing
Respiratory Protection	When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly
Large scale/emergency use	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced Recommended Filter type: Particulates filter conforming to EN 143 Ammonia and organic ammonia derivatives filter Type K Green conforming to EN14387
Small scale/Laboratory use	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141 When RPE is used a face piece Fit Test should be conducted
Hygiene Measures	Handle in accordance with good industrial hygiene and safety practice.
Environmental exposure controls	Prevent product from entering drains. Do not allow material to contaminate ground water system.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Brown	
Physical State	Liquid	
Odor	pungent	
Odor Threshold	No data available	
pH	8	100 g/L aq.sol
Melting Point/Range	-50 °C / -58 °F	
Softening Point	No data available	
Boiling Point/Range	159 °C / 318.2 °F	@ 760 mmHg
Flash Point	47 °C / 116.6 °F	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	1.9 mmHg @ 20 °C	
Vapor Density	3.64 (Air = 1.0)	(Air = 1.0)
Specific Gravity / Density	0.998	
Bulk Density	Not applicable	Liquid
Water Solubility	25 g/L (20°C)	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Component	log Pow	
Pyridine, 2-ethenyl-	1.54	
Autoignition Temperature	440 - °C / 824 - °F	
Decomposition Temperature	> 30°C	
Viscosity	1.2 cPs at 20 °C	
Explosive Properties		explosive air/vapour mixtures possible
Oxidizing Properties	No information available	
Molecular Formula	C7 H7 N	
Molecular Weight	105.14	

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under recommended storage conditions. Polymerization can occur.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	Hazardous polymerization does not occur.
Conditions to Avoid	Incompatible products. Excess heat. Keep away from open flames, hot surfaces and sources of ignition.
Materials to avoid	Strong oxidizing agents. Strong acids. Strong bases. Alkaline. Peroxides.
Hazardous Decomposition Products	Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO ₂). Hydrogen cyanide (hydrocyanic acid). Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Pyridine, 2-ethenyl-	336 mg/kg (Rat)	650 mg/kg (Rabbit)	9 mg/L/4h (Mouse)

(b) skin corrosion/irritation; Category 1 B

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Respiratory
Skin

Based on available data, the classification criteria are not met
Category 1

May cause sensitization by skin contact

(e) germ cell mutagenicity;

Based on available data, the classification criteria are not met

(f) carcinogenicity;

Based on available data, the classification criteria are not met
There are no known carcinogenic chemicals in this product

(g) reproductive toxicity;

Based on available data, the classification criteria are not met

(h) STOT-single exposure;

Based on available data, the classification criteria are not met

(i) STOT-repeated exposure;

Target Organs

Based on available data, the classification criteria are not met
None known.

(j) aspiration hazard;

Based on available data, the classification criteria are not met

Other Adverse Effects

The toxicological properties have not been fully investigated. See actual entry in RTECS for complete information

2-Vinylpyridine

Symptoms / effects, both acute and delayed Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of allergic reaction may include rash, itching, swelling, trouble breathing, tingling of the hands and feet, dizziness, lightheadedness, chest pain, muscle pain or flushing

SECTION 12. ECOLOGICAL INFORMATION**Ecotoxicity effects**

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Pyridine, 2-ethenyl-	LC50=648 mg/L 96h			

Persistence and Degradability**Persistence**

Soluble in water, Persistence is unlikely, based on information available.

Degradation in sewage treatment plant

Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Bioaccumulative Potential

Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Pyridine, 2-ethenyl-	1.54	No data available

Mobility in soil

The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

Endocrine Disruptor Information

This product does not contain any known or suspected endocrine disruptors

Persistent Organic Pollutant

This product does not contain any known or suspected substance

Ozone Depletion Potential

This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS**Waste from Residues/Unused Products**

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging

Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

Other Information

Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Can be landfilled or incinerated, when in compliance with local regulations. Do not empty into drains. Large amounts will affect pH and harm aquatic organisms. Do not let this chemical enter the environment.

SECTION 14. TRANSPORT INFORMATION**Road and Rail Transport**

UN-No	UN3073
Proper Shipping Name	VINYLPYRIDINES, STABILIZED
Hazard Class	6.1
Subsidiary Hazard Class	3, 8
Packing Group	II

2-Vinylpyridine

IMDG/IMO

UN-No UN3073
Proper Shipping Name VINYL PYRIDINES, STABILIZED
Hazard Class 6.1
Subsidiary Hazard Class 3, 8
Packing Group II

IATA

UN-No UN3073
Proper Shipping Name VINYL PYRIDINES, STABILIZED
Hazard Class 6.1
Subsidiary Hazard Class 3, 8
Packing Group II

Special Precautions for User Inhibitors have been added to stabilize this product Inhibitor levels should be maintained
 Hazardous polymerization may occur upon depletion of inhibitor

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Pyridine, 2-ethenyl-	X	-	X	X	202-879-8	X	-	X	X	X	X	KE-05-1351

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Creation Date 23-Mar-2012
Revision Date 07-Mar-2024
Revision Summary New emergency telephone response service provider.

Training Advice
 Chemical incident response training.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

2-Vinylpyridine

WEL - Workplace Exposure Limit**ACGIH** - American Conference of Governmental Industrial Hygienists**DNEL** - Derived No Effect Level**RPE** - Respiratory Protective Equipment**LC50** - Lethal Concentration 50%**NOEC** - No Observed Effect Concentration**PBT** - Persistent, Bioaccumulative, Toxic**TWA** - Time Weighted Average**IARC** - International Agency for Research on Cancer**PNEC** - Predicted No Effect Concentration**LD50** - Lethal Dose 50%**EC50** - Effective Concentration 50%**POW** - Partition coefficient Octanol:Water**vPvB** - very Persistent, very Bioaccumulative**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road**OECD** - Organisation for Economic Co-operation and Development**BCF** - Bioconcentration factor**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code**MARPOL** - International Convention for the Prevention of Pollution from Ships**ATE** - Acute Toxicity Estimate**VOC** - (Volatile Organic Compound)**Key literature references and sources for data**<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet