

ALFAAA14145

## 2-Decanone

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

<b>产品说明:</b> <b>Product Description:</b>	<b>2-癸酮, 97%</b> <b>2-Decanone</b>
<b>Cat No. :</b>	<b>A14145</b>
<b>Synonyms</b>	Methyl octyl ketone
<b>CAS No</b>	693-54-9
<b>Molecular Formula</b>	C10 H20 O
<b>Supplier</b>	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
<b>Emergency Telephone Number</b>	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
<b>E-mail address</b>	begel.sdsdesk@thermofisher.com
<b>Recommended Use</b> <b>Uses advised against</b>	Laboratory chemicals. No Information available

### SECTION 2. HAZARD IDENTIFICATION

<b>Physical State</b> Liquid	<b>Appearance</b> Light yellow	<b>Odor</b> Odorless
<b>Emergency Overview</b> Combustible liquid.		

#### Classification of the substance or mixture

Flammable liquids.	Category 4
--------------------	------------

#### Label Elements

None required

**Signal Word**                      **Warning**

**Hazard Statements**  
H227 - Combustible liquid

**Precautionary Statements**  
**Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish

**Storage**

P403 + P235 - Store in a well-ventilated place. Keep cool

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Combustible material.

**Health Hazards**

The product contains no substances which at their given concentration are considered to be hazardous to health.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
2-Decanone	693-54-9	98

**SECTION 4. FIRST AID MEASURES****Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

**Skin Contact**

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.

**Inhalation**

Remove from exposure, lie down. Remove to fresh air.

**Ingestion**

Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Drink plenty of water. If possible drink milk afterwards.

**Most important symptoms and effects**

Difficulty in breathing. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

**Self-Protection of the First Aider**

No special precautions required.

**Notes to Physician**

Treat symptomatically. Symptoms may be delayed.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray. Carbon dioxide (CO<sub>2</sub>). Dry chemical. Alcohol resistant foam. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Combustible material. Containers may explode when heated.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full

protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

## SECTION 6. ACCIDENTAL RELEASE MEASURES

### Personal Precautions

Remove all sources of ignition. Take precautionary measures against static discharges.

### Environmental Precautions

Do not flush into surface water or sanitary sewer system.

### Methods for Containment and Clean Up

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal. Sweep up and shovel into suitable containers for disposal. Remove all sources of ignition.

Refer to protective measures listed in Sections 8 and 13.

## SECTION 7. HANDLING AND STORAGE

### Handling

Avoid contact with skin and eyes. Avoid contact with skin and clothing. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Avoid breathing vapors or mists. Do not ingest. If swallowed then seek immediate medical assistance. Wash thoroughly after handling. Keep away from open flames, hot surfaces and sources of ignition.

### Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed. Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat, sparks and flame.

### Specific Use(s)

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control Parameters

### Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours

### Exposure Controls

### Engineering Measures

None under normal use conditions. Ensure adequate ventilation, especially in confined areas. .

### Personal protective equipment

**Eye Protection** Wear safety glasses with side shields (or goggles) (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Viton (R)	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger

of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

<b>Skin and body protection</b>	Long sleeved clothing
<b>Respiratory Protection</b>	No protective equipment is needed under normal use conditions.
<b>Large scale/emergency use</b>	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced <b>Recommended Filter type:</b> Particle filter
<b>Small scale/Laboratory use</b>	Maintain adequate ventilation <b>Recommended half mask:-</b> Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.
<b>Environmental exposure controls</b>	Prevent product from entering drains. Do not allow material to contaminate ground water system.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Light yellow	
<b>Physical State</b>	Liquid	
<b>Odor</b>	Odorless	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	3.5 °C / 38.3 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	211 °C / 411.8 °F	@ 760 mmHg
<b>Flash Point</b>	71 °C / 159.8 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	5.38	(Air = 1.0)
<b>Specific Gravity / Density</b>	0.820	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	No information available	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
2-Decanone	3.73	
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	No data available	
<b>Explosive Properties</b>		explosive air/vapour mixtures possible
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C10 H20 O	
<b>Molecular Weight</b>	156.27	

## SECTION 10. STABILITY AND REACTIVITY

## 2-Decanone

<b>Stability</b>	Stable under normal conditions.
<b>Hazardous Reactions</b>	No information available.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	Incompatible products. Keep away from open flames, hot surfaces and sources of ignition.
<b>Materials to avoid</b>	Oxidizing agent.
<b>Hazardous Decomposition Products</b>	Thermal decomposition can lead to release of irritating gases and vapors. Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ).

## SECTION 11. TOXICOLOGICAL INFORMATION

<b>Product Information</b>	No acute toxicity information is available for this product
<b>(a) acute toxicity;</b>	
<b>(b) skin corrosion/irritation;</b>	No data available
<b>(c) serious eye damage/irritation;</b>	No data available
<b>(d) respiratory or skin sensitization;</b>	
Respiratory	No data available
Skin	No data available
<b>(e) germ cell mutagenicity;</b>	No data available
<b>(f) carcinogenicity;</b>	No data available
	There are no known carcinogenic chemicals in this product
<b>(g) reproductive toxicity;</b>	No data available
<b>(h) STOT-single exposure;</b>	No data available
<b>(i) STOT-repeated exposure;</b>	No data available
Target Organs	No information available.
<b>(j) aspiration hazard;</b>	No data available
<b>Symptoms / effects, both acute and delayed</b>	Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

## SECTION 12. ECOLOGICAL INFORMATION

<b>Ecotoxicity effects</b>	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. The product contains following substances which are hazardous for the environment.
----------------------------	--

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
2-Decanone	LC50: 4 - 4.2 mg/L, 96h flow-through			EC50 = 6.1 mg/L 5 min

## SAFETY DATA SHEET

## 2-Decanone

	(Pimephales promelas)			
--	-----------------------	--	--	--

**Persistence and Degradability****Persistence****Degradation in sewage treatment plant**

No information available

Persistence is unlikely.

Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Bioaccumulative Potential**

Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
2-Decanone	3.73	No data available

**Mobility in soil**

No information available

**Endocrine Disruptor Information****Persistent Organic Pollutant****Ozone Depletion Potential**

This product does not contain any known or suspected endocrine disruptors

This product does not contain any known or suspected substance

This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS****Waste from Residues/Unused Products**

Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. Consult local, regional, and national hazardous waste regulations to ensure complete and accurate classification.

**Contaminated Packaging**

Empty remaining contents. Dispose of in accordance with local regulations. Do not re-use empty containers.

**Other Information**

Do not flush to sewer.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

Not Regulated

**IMDG/IMO**

Not regulated

**IATA**

Not regulated

**Special Precautions for User**

No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
2-Decanone	-	X	X	X	211-752-6	X	-	X	X	X	X	KE-09489

## National Regulations

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 27-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**