

ALFAAA14185

## 2-Phenyl-2-butenal,(E)+(Z)

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
Product Description: 2-苯基-2-丁烯醛  
2-Phenyl-2-butenal,(E)+(Z)

Cat No. : A14185  
CAS No 4411-89-6  
Molecular Formula C10 H10 O

Supplier Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Liquid

**Appearance**  
Colorless

**Odor**  
No information available

**Emergency Overview**  
Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation. Sensitivity to light.

#### Classification of the substance or mixture

Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Specific target organ toxicity - (single exposure)	Category 3

#### Label Elements



Signal Word

Warning

Hazard Statements

## 2-Phenyl-2-butenal,(E)+(Z)

H315 - Causes skin irritation  
H319 - Causes serious eye irritation  
H335 - May cause respiratory irritation

**Precautionary Statements****Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling  
P280 - Wear protective gloves/protective clothing/eye protection/face protection  
P261 - Avoid breathing dust/fume/gas/mist/vapors/spray  
P271 - Use only outdoors or in a well-ventilated area

**Response**

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing  
P302 + P352 - IF ON SKIN: Wash with plenty of soap and water  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P312 - Call a POISON CENTER or doctor if you feel unwell  
P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
Benzeneacetaldehyde, .alpha.-ethylidene-	4411-89-6	<=100

**SECTION 4. FIRST AID MEASURES****General Advice**

If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water.

**Most important symptoms and effects**

None reasonably foreseeable.

**Self-Protection of the First Aider**

No special precautions required.

## 2-Phenyl-2-butenal,(E)+(Z)

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required.

**Environmental Precautions**

Should not be released into the environment. See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid ingestion and inhalation. Do not get in eyes, on skin, or on clothing.

**Storage**

Protect from light.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Exposure Controls****Engineering Measures**

None under normal use conditions. Ensure that eyewash stations and safety showers are close to the workstation location. .

**Personal protective equipment****Eye Protection**

Goggles (European standard - EN 166)

## 2-Phenyl-2-butenal,(E)+(Z)

## Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

## Skin and body protection

Long sleeved clothing

## Respiratory Protection

No protective equipment is needed under normal use conditions.

## Large scale/emergency use

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

**Recommended Filter type:** Particle filter

## Small scale/Laboratory use

Maintain adequate ventilation

**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141

## Hygiene Measures

Handle in accordance with good industrial hygiene and safety practice.

## Environmental exposure controls

No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

## Appearance

Colorless

## Physical State

Liquid

## Odor

No information available

## Odor Threshold

No data available

## pH

No information available

## Melting Point/Range

No data available

## Softening Point

No data available

## Boiling Point/Range

No information available

## Flash Point

No information available

**Method -** No information available

## Evaporation Rate

No data available

## Flammability (solid,gas)

Not applicable

Liquid

## Explosion Limits

No data available

## Vapor Pressure

No data available

## Vapor Density

No data available

(Air = 1.0)

## Specific Gravity / Density

No data available

## Bulk Density

Not applicable

Liquid

## Water Solubility

No information available

## Solubility in other solvents

No information available

## Partition Coefficient (n-octanol/water)

## Autoignition Temperature

No data available

## Decomposition Temperature

No data available

## Viscosity

No data available

## Explosive Properties

No information available

## 2-Phenyl-2-butenal,(E)+(Z)

**Oxidizing Properties** No information available

**Molecular Formula** C10 H10 O  
**Molecular Weight** 146.19

**SECTION 10. STABILITY AND REACTIVITY**

**Stability** Light sensitive.

**Hazardous Reactions** None under normal processing.  
**Hazardous Polymerization** No information available.

**Conditions to Avoid** Exposure to light.

**Materials to avoid** No information available.

**Hazardous Decomposition Products** None under normal use conditions.

**SECTION 11. TOXICOLOGICAL INFORMATION****Product Information**

**(a) acute toxicity;**

**(b) skin corrosion/irritation;** Category 2

**(c) serious eye damage/irritation;** Category 2

**(d) respiratory or skin sensitization;**

**Respiratory** No data available  
**Skin** No data available

**(e) germ cell mutagenicity;** No data available

**(f) carcinogenicity;** No data available

There are no known carcinogenic chemicals in this product

**(g) reproductive toxicity;** No data available

**(h) STOT-single exposure;** Category 3

**Results / Target organs** Respiratory system

**(i) STOT-repeated exposure;** No data available

**Target Organs** No information available.

**(j) aspiration hazard;** No data available

**Symptoms / effects,both acute and delayed** No information available

## 2-Phenyl-2-butenal,(E)+(Z)

## SECTION 12. ECOLOGICAL INFORMATION

<b>Ecotoxicity effects</b>	Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.
<b>Persistence and Degradability</b>	No information available
<b>Bioaccumulative Potential</b>	No information available
<b>Mobility in soil</b>	No information available
<b>Endocrine Disruptor Information</b>	This product does not contain any known or suspected endocrine disruptors
<b>Persistent Organic Pollutant</b>	This product does not contain any known or suspected substance
<b>Ozone Depletion Potential</b>	This product does not contain any known or suspected substance

## SECTION 13. DISPOSAL CONSIDERATIONS

<b>Waste from Residues/Unused Products</b>	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
<b>Contaminated Packaging</b>	Dispose of this container to hazardous or special waste collection point.
<b>Other Information</b>	Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

## SECTION 14. TRANSPORT INFORMATION

**Road and Rail Transport** Not Regulated

**IMDG/IMO** Not regulated

**IATA** Not regulated

**Special Precautions for User** No special precautions required

## SECTION 15. REGULATORY INFORMATION

## International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Benzeneacetaldehyde, .alpha.-ethylidene-	-	-	X	X	224-567-0	X	X	X	-		X	-

## National Regulations

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 02-May-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

**Legend**

<b>CAS</b> - Chemical Abstracts Service	<b>TSCA</b> - United States Toxic Substances Control Act Section 8(b) Inventory
<b>EINECS/ELINCS</b> - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances	<b>DSL/NDSL</b> - Canadian Domestic Substances List/Non-Domestic Substances List
<b>PICCS</b> - Philippines Inventory of Chemicals and Chemical Substances	<b>ENCS</b> - Japanese Existing and New Chemical Substances
<b>IECSC</b> - Chinese Inventory of Existing Chemical Substances	<b>AICS</b> - Australian Inventory of Chemical Substances
<b>KECL</b> - Korean Existing and Evaluated Chemical Substances	<b>NZIoC</b> - New Zealand Inventory of Chemicals
<b>WEL</b> - Workplace Exposure Limit	<b>TWA</b> - Time Weighted Average
<b>ACGIH</b> - American Conference of Governmental Industrial Hygienists	<b>IARC</b> - International Agency for Research on Cancer
<b>DNEL</b> - Derived No Effect Level	<b>PNEC</b> - Predicted No Effect Concentration
<b>RPE</b> - Respiratory Protective Equipment	<b>LD50</b> - Lethal Dose 50%
<b>LC50</b> - Lethal Concentration 50%	<b>EC50</b> - Effective Concentration 50%
<b>NOEC</b> - No Observed Effect Concentration	<b>POW</b> - Partition coefficient Octanol:Water
<b>PBT</b> - Persistent, Bioaccumulative, Toxic	<b>vPvB</b> - very Persistent, very Bioaccumulative
<b>ICAO/IATA</b> - International Civil Aviation Organization/International Air Transport Association	<b>IMO/IMDG</b> - International Maritime Organization/International Maritime Dangerous Goods Code
<b>ADR</b> - European Agreement Concerning the International Carriage of Dangerous Goods by Road	<b>MARPOL</b> - International Convention for the Prevention of Pollution from Ships
<b>OECD</b> - Organisation for Economic Co-operation and Development	<b>ATE</b> - Acute Toxicity Estimate
<b>BCF</b> - Bioconcentration factor	<b>VOC</b> - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>  
Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**