

ALFAAA14756

## 2-Aminobenzamide

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

|                               |  |
|-------------------------------|--|
| 产品说明:<br>Product Description: | 2-氨基苯甲酰胺, 98+%<br>2-Aminobenzamide   |
| Cat No. :                     | A14756   |
| Synonyms                      | ATA; 2-Aminobenzamide  |
| CAS No                        | 88-68-6  |
| Molecular Formula             | C7 H8 N2 O   |
| Supplier                      | Avocado Research Chemicals Ltd.<br>(Part of Thermo Fisher Scientific)<br>Shore Road, Heysham<br>Lancashire, LA3 2XY,<br>United Kingdom<br>Office Tel: +44 (0) 1524 850506<br>Office Fax: +44 (0) 1524 850608   |
| Emergency Telephone Number    | For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11<br>Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99<br><b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887 |
| E-mail address                | begel.sdsdesk@thermofisher.com   |
| Recommended Use               | Laboratory chemicals.  |
| Uses advised against          | No Information available   |

### SECTION 2. HAZARD IDENTIFICATION

|  |                           |                                  |
|--|---------------------------|----------------------------------|
| Physical State<br>Powder Solid                       | Appearance<br>Light brown | Odor<br>No information available |
| Emergency Overview<br>Causes serious eye irritation. |                           |                                  |

#### Classification of the substance or mixture

|                                   |            |
|-----------------------------------|------------|
| Serious Eye Damage/Eye Irritation | Category 2 |
|-----------------------------------|------------|

#### Label Elements



Signal Word

Warning

#### Hazard Statements

H319 - Causes serious eye irritation

**Precautionary Statements****Prevention**

P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P310 - Immediately call a POISON CENTER or doctor

**Storage**

P403 - Store in a well-ventilated place

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

Causes serious eye irritation.

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

| Component           | CAS No  | Weight % |
|---------------------|---------|----------|
| Benzamide, 2-amino- | 88-68-6 | > 99     |

**SECTION 4. FIRST AID MEASURES****Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes.

**Inhalation**

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration.

**Ingestion**

Clean mouth with water. Get medical attention.

**Most important symptoms and effects**

Causes eye burns.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray. Carbon dioxide (CO<sub>2</sub>). Dry chemical. Chemical foam.

**Extinguishing media which must not be used for safety reasons**

## 2-Aminobenzamide

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation.

**Environmental Precautions**

See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Avoid contact with skin and eyes. Do not breathe dust.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

**Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment****Eye Protection**

Goggles (European standard - EN 166)

**Hand Protection**

Protective gloves

## 2-Aminobenzamide

| Glove material                                      | Breakthrough time                 | Glove thickness | EU standard | Glove comments        |
|---|-----------------------------------|-----------------|-------------|-----------------------|
| Nitrile rubber<br>Neoprene<br>Natural rubber<br>PVC | See manufacturers recommendations | -               | EN 374      | (minimum requirement) |

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** No protective equipment is needed under normal use conditions.

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

**Small scale/Laboratory use** Maintain adequate ventilation

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

|  |                                 |  |
|--|---------------------------------|--|
| <b>Appearance</b>                              | Light brown                     |  |
| <b>Physical State</b>                          | Powder Solid                    |  |
| <b>Odor</b>                                    | No information available        |  |
| <b>Odor Threshold</b>                          | No data available               |  |
| <b>pH</b>                                      | No information available        |  |
| <b>Melting Point/Range</b>                     | 111 - 114 °C / 231.8 - 237.2 °F |  |
| <b>Softening Point</b>                         | No data available               |  |
| <b>Boiling Point/Range</b>                     | 300 °C / 572 °F                 | @ 760 mmHg                               |
| <b>Flash Point</b>                             | 198 °C / 388.4 °F               | <b>Method -</b> No information available |
| <b>Evaporation Rate</b>                        | Not applicable                  | Solid                                    |
| <b>Flammability (solid,gas)</b>                | No information available        |  |
| <b>Explosion Limits</b>                        | No data available               |  |
| <b>Vapor Pressure</b>                          | No information available        |  |
| <b>Vapor Density</b>                           | Not applicable                  | Solid                                    |
| <b>Specific Gravity / Density</b>              | No data available               |  |
| <b>Bulk Density</b>                            | No data available               |  |
| <b>Water Solubility</b>                        | <5 g/l water (20°C)             |  |
| <b>Solubility in other solvents</b>            | No information available        |  |
| <b>Partition Coefficient (n-octanol/water)</b> |                                 |  |
| <b>Component</b>                               | <b>log Pow</b>                  |  |
| Benzamide, 2-amino-                            | 0.35                            |  |
| <b>Autoignition Temperature</b>                | 590 °C / 1094 °F                |  |
| <b>Decomposition Temperature</b>               | No data available               |  |
| <b>Viscosity</b>                               | Not applicable                  | Solid                                    |
| <b>Explosive Properties</b>                    | No information available        |  |
| <b>Oxidizing Properties</b>                    | No information available        |  |
| <b>Molecular Formula</b>                       | C7 H8 N2 O                      |  |
| <b>Molecular Weight</b>                        | 136.15                          |  |

## SECTION 10. STABILITY AND REACTIVITY

**Stability** Stable under normal conditions.

**Hazardous Reactions** No information available.

**Hazardous Polymerization** No information available.

**Conditions to Avoid** Incompatible products.

**Materials to avoid** Strong oxidizing agents.

**Hazardous Decomposition Products** Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

## SECTION 11. TOXICOLOGICAL INFORMATION

**Product Information** No acute toxicity information is available for this product

**(a) acute toxicity;**

| Component           | LD50 Oral | LD50 Dermal | LC50 Inhalation             |
|---------------------|-----------|-------------|-----------------------------|
| Benzamide, 2-amino- |           |             | LC50 > 5.4 mg/L ( Rat ) 4 h |

**(b) skin corrosion/irritation;** No data available

**(c) serious eye damage/irritation;** Category 2

**(d) respiratory or skin sensitization;**

**Respiratory** No data available  
**Skin** No data available

**(e) germ cell mutagenicity;** No data available

**(f) carcinogenicity;** No data available

There are no known carcinogenic chemicals in this product

**(g) reproductive toxicity;** No data available

**(h) STOT-single exposure;** No data available

**(i) STOT-repeated exposure;** No data available

**Target Organs** No information available.

**(j) aspiration hazard;** Not applicable  
Solid

**Other Adverse Effects** The toxicological properties have not been fully investigated.

**Symptoms / effects, both acute and delayed** No information available

## 2-Aminobenzamide

## SECTION 12. ECOLOGICAL INFORMATION

## Ecotoxicity effects

| Component           | Freshwater Fish  | Water Flea | Freshwater Algae | Microtox |
|---------------------|--|------------|------------------|----------|
| Benzamide, 2-amino- | LC50: 354 - 439 mg/L,<br>96h flow-through<br>(Pimephales promelas) |            |                  |          |

Persistence and Degradability  
Persistence

Expected to be biodegradable  
Persistence is unlikely.

## Bioaccumulative Potential

Bioaccumulation is unlikely

| Component           | log Pow | Bioconcentration factor (BCF) |
|---------------------|---------|-------------------------------|
| Benzamide, 2-amino- | 0.35    | No data available             |

## Mobility in soil

The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

Endocrine Disruptor Information  
Persistent Organic Pollutant  
Ozone Depletion Potential

This product does not contain any known or suspected endocrine disruptors  
This product does not contain any known or suspected substance  
This product does not contain any known or suspected substance

## SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused  
Products

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

## Contaminated Packaging

Dispose of this container to hazardous or special waste collection point.

## Other Information

Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

## SECTION 14. TRANSPORT INFORMATION

## Road and Rail Transport

Not Regulated

## IMDG/IMO

Not regulated

## IATA

Not regulated

## Special Precautions for User

No special precautions required

## SECTION 15. REGULATORY INFORMATION

## International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

| Component | The | List of | TCSI | IECSC | EINECS | TSCA | DSL | PICCS | ENCS | ISHL | AICS | KECL |
|-----------|-----|---------|------|-------|--------|------|-----|-------|------|------|------|------|
|-----------|-----|---------|------|-------|--------|------|-----|-------|------|------|------|------|

## 2-Aminobenzamide

|                     |   |                                 |   |   |           |   |   |   |   |   |   |             |
|---------------------|---|---------------------------------|---|---|-----------|---|---|---|---|---|---|-------------|
|                     | Inventory of Hazardous Chemicals (2015 Edition) | dangerous goods GB 12268 - 2012 |   |   |           |   |   |   |   |   |   |             |
| Benzamide, 2-amino- | -   | -                               | X | X | 201-851-2 | X | - | X | X | X | X | 2011-3-5344 |

## National Regulations

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Revision Date** 06-Mar-2024  
**Revision Summary** New emergency telephone response service provider.

## Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

## Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

## Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other

# **SAFETY DATA SHEET**

**2-Aminobenzamide**

---

materials or in any process, unless specified in the text

**End of Safety Data Sheet**