

ALFAAA15111

Mesityl oxide, 90+%, remainder 4-methyl-4-penten-2-one

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 氧化异亚丙基丙酮, 90+%, 残留物 4-methyl-4-penten-2-one
Mesityl oxide, 90+%, remainder 4-methyl-4-penten-2-one

Cat No. : A15111
Synonyms Isopropylidene-acetone; Isobutenyl methyl ketone; 4-Methyl-3-penten-2-one
CAS No 141-79-7
Molecular Formula C6H10O

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Liquid

Appearance
Clear

Odor
Odorless

Emergency Overview

Flammable liquid and vapor. Harmful if swallowed. Harmful in contact with skin. Harmful if inhaled.

Classification of the substance or mixture

Flammable liquids.	Category 3
Acute Oral Toxicity	Category 4
Acute Dermal Toxicity	Category 4
Acute Inhalation Toxicity - Vapors	Category 4

Label Elements



SAFETY DATA SHEET

Mesityl oxide, 90+%, remainder 4-methyl-4-penten-2-one

Signal Word**Warning****Hazard Statements**

H226 - Flammable liquid and vapor

H302 + H312 + H332 - Harmful if swallowed, in contact with skin or if inhaled

Precautionary Statements**Prevention**

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking

P233 - Keep container tightly closed

P240 - Ground and bond container and receiving equipment

P242 - Use non-sparking tools

P243 - Take action to prevent static discharges

P261 - Avoid breathing dust/fume/gas/mist/vapors/spray

P264 - Wash face, hands and any exposed skin thoroughly after handling

P270 - Do not eat, drink or smoke when using this product

P271 - Use only outdoors or in a well-ventilated area

P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P312 - Call a POISON CENTER or doctor if you feel unwell

P330 - Rinse mouth

P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish

P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P235 - Store in a well-ventilated place. Keep cool

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

Vapors may cause flash fire or explosion. Flammable liquid.

Health Hazards

Harmful if swallowed. Harmful in contact with skin. Harmful if inhaled.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Will likely be mobile in the environment due to its volatility. Spillage unlikely to penetrate soil. The product is insoluble and floats on water. The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces.

Toxicity to Soil Dwelling Organisms. Toxic to terrestrial vertebrates. This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Mesityl oxide	141-79-7	> 90
4-Penten-2-one, 4-methyl-	3744-02-3	<10

SECTION 4. FIRST AID MEASURES**General Advice**

If symptoms persist, call a physician.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

SAFETY DATA SHEET

Mesityl oxide, 90+%, remainder 4-methyl-4-penten-2-one

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

Ingestion

Clean mouth with water and drink afterwards plenty of water.

Most important symptoms and effects

Difficulty in breathing. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Flammable. Containers may explode when heated. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal Precautions

Ensure adequate ventilation. Use personal protective equipment as required. Remove all sources of ignition. Take precautionary measures against static discharges.

Environmental Precautions

Should not be released into the environment.

Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE

Handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. Take precautionary measures against static discharges.

Storage

Keep container tightly closed in a dry and well-ventilated place. Keep away from heat, sparks and flame.

Mesityl oxide, 90+%, remainder 4-methyl-4-penten-2-one

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters**

Component	China	Taiwan	Thailand	Hong Kong
Mesityl oxide	TWA: 60 mg/m ³ STEL: 100 mg/m ³	TWA: 15 ppm TWA: 60 mg/m ³		-

Component	ACGIH TLV	OSHA PEL	NIOSH	The United Kingdom	European Union
Mesityl oxide	TWA: 15 ppm STEL: 25 ppm	(Vacated) TWA: 15 ppm (Vacated) TWA: 60 mg/m ³ (Vacated) STEL: 25 ppm (Vacated) STEL: 100 mg/m ³ TWA: 25 ppm TWA: 100 mg/m ³	IDLH: 1400 ppm TWA: 10 ppm TWA: 40 mg/m ³	-	

Legend

ACGIH - American Conference of Governmental Industrial Hygienists

OSHA - Occupational Safety and Health Administration

NIOSH: NIOSH - National Institute for Occupational Safety and Health

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

Exposure Controls**Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Use explosion-proof electrical/ventilating/lighting equipment. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment**Eye Protection**

Wear safety glasses with side shields (or goggles) (European standard - EN 166)

Hand Protection

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Viton (R)	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.

(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection

Long sleeved clothing

Respiratory Protection

When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

Mesityl oxide, 90+%, remainder 4-methyl-4-penten-2-one

	To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly
Large scale/emergency use	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced Recommended Filter type: Organic gases and vapours filter Type A Brown conforming to EN14387
Small scale/Laboratory use	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141 When RPE is used a face piece Fit Test should be conducted
Hygiene Measures	Handle in accordance with good industrial hygiene and safety practice.
Environmental exposure controls	No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Clear	
Physical State	Liquid	
Odor	Odorless	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	-53 °C / -63.4 °F	
Softening Point	No data available	
Boiling Point/Range	129 °C / 264.2 °F	@ 760 mmHg
Flash Point	28 °C / 82.4 °F	Method - No information available
Evaporation Rate	No information available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	10.53 mbar @ 20 °C	
Vapor Density	No information available	(Air = 1.0)
Specific Gravity / Density	0.854	
Bulk Density	Not applicable	Liquid
Water Solubility	Insoluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	340 °C / 644 °F	
Decomposition Temperature	No data available	
Viscosity	No data available	
Explosive Properties		explosive air/vapour mixtures possible
Oxidizing Properties	No information available	
Molecular Formula	C6H10O	
Molecular Weight	98.14	

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	No information available.
Conditions to Avoid	Keep away from open flames, hot surfaces and sources of ignition.

SAFETY DATA SHEET

Mesityl oxide, 90+%, remainder 4-methyl-4-penten-2-one

Materials to avoid Oxidizing agent.

Hazardous Decomposition Products Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Mesityl oxide	LD50 = 655 mg/kg (Rat)	LD50 = 5151 mg/kg (Rabbit)	LC50 = 1130 ppm (Rat) 4 h

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

(d) respiratory or skin sensitization;

Respiratory No data available
Skin No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available

There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available

Target Organs No information available.

(j) aspiration hazard; No data available

Symptoms / effects, both acute and delayed Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Mesityl oxide	LC50: = 72.93 mg/L, 96h static (Danio rerio)			

Persistence and Degradability

Persistence Insoluble in water, Persistence is unlikely, based on information available.

SAFETY DATA SHEET

Mesityl oxide, 90+%, remainder 4-methyl-4-penten-2-one

Bioaccumulative Potential	May have some potential to bioaccumulate
Mobility in soil	Spillage unlikely to penetrate soil The product is insoluble and floats on water The product contains volatile organic compounds (VOC) which will evaporate easily from all surfaces Is not likely mobile in the environment due its low water solubility Will likely be mobile in the environment due to its volatility
Endocrine Disruptor Information	This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant	This product does not contain any known or suspected substance
Ozone Depletion Potential	This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
Contaminated Packaging	Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.
Other Information	Waste codes should be assigned by the user based on the application for which the product was used. Do not flush to sewer. Can be landfilled or incinerated, when in compliance with local regulations.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No	UN1229
Proper Shipping Name	MESITYL OXIDE
Hazard Class	3
Packing Group	III

IMDG/IMO

UN-No	UN1229
Proper Shipping Name	MESITYL OXIDE
Hazard Class	3
Packing Group	III

IATA

UN-No	UN1229
Proper Shipping Name	MESITYL OXIDE
Hazard Class	3
Packing Group	III

Special Precautions for User	No special precautions required
-------------------------------------	---------------------------------

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

SAFETY DATA SHEET

Mesityl oxide, 90+%, remainder 4-methyl-4-penten-2-one

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Mesityl oxide	X	X	X	X	205-502-5	X	X	X	X	X	X	KE-24767
4-Penten-2-one, 4-methyl-	-	-		-	-	-	X	-	-		-	-

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Revision Date 12-May-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Chemical incident response training.

Fire prevention and fighting, identifying hazards and risks, static electricity, explosive atmospheres posed by vapours and dusts.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

SAFETY DATA SHEET**Mesityl oxide, 90+%, remainder 4-methyl-4-penten-2-one**

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet