

ALFAAA15670

3-Phenoxybenzyl chloride

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 3-苯氧基苄基氯
3-Phenoxybenzyl chloride

Cat No. : A15670
CAS No 53874-66-1
Molecular Formula C13 H11 Cl O

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Liquid

Appearance
Yellow

Odor
No information available

Emergency Overview

Harmful if swallowed. Causes severe skin burns and eye damage. Lachrymator (substance which increases the flow of tears).

Classification of the substance or mixture

Acute Oral Toxicity	Category 4
Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1

Label Elements



Signal Word

Danger

Hazard Statements

3-Phenoxybenzyl chloride

H302 - Harmful if swallowed

H314 - Causes severe skin burns and eye damage

Precautionary Statements**Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling

P270 - Do not eat, drink or smoke when using this product

P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P310 - Immediately call a POISON CENTER or doctor

P330 - Rinse mouth

P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 - Store in a well-ventilated place

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

Harmful if swallowed. Corrosive. Causes skin and eye burns. Lachrymator (substance which increases the flow of tears).

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

Other Hazards

Lachrymator (substance which increases the flow of tears)

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
1-(Chloromethyl)-3-phenoxybenzene	53874-66-1	98

SECTION 4. FIRST AID MEASURES**Eye Contact**

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Skin Contact

Immediate medical attention is required. Wash off immediately with plenty of water for at least 15 minutes.

Inhalation

Remove to fresh air. Get medical attention. If not breathing, give artificial respiration.

Ingestion

Do NOT induce vomiting. Get medical attention.

Most important symptoms and effects

Causes burns by all exposure routes. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Carbon dioxide (CO₂). Dry chemical. Chemical foam.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation.

Environmental Precautions

See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Handle product only in closed system or provide appropriate exhaust ventilation. Ensure adequate ventilation. Wear personal protective equipment/face protection. Avoid contact with skin, eyes or clothing. Avoid breathing dust/fume/gas/mist/vapors/spray.

Storage

Keep in a dry place. Keep container tightly closed. Corrosives area. Keep refrigerated. Keep containers tightly closed in a dry, cool and well-ventilated place.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters****Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the

3-Phenoxybenzyl chloride

introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves.
(Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Organic gases and vapours filter Type A Brown conforming to EN14387

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141
When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	Yellow	
Physical State	Liquid	
Odor	No information available	
Odor Threshold	No data available	
pH	No information available	
Melting Point/Range	No data available	
Softening Point	No data available	
Boiling Point/Range	141 - 142 °C / 285.8 - 287.6 °F	@ 5 mmHg
Flash Point	No information available	Method - No information available
Evaporation Rate	No data available	
Flammability (solid,gas)	Not applicable	Liquid
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	No data available	(Air = 1.0)

SAFETY DATA SHEET**3-Phenoxybenzyl chloride**

Specific Gravity / Density	No data available	
Bulk Density	Not applicable	Liquid
Water Solubility	No information available	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	No data available	
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	C13 H11 Cl O	
Molecular Weight	218.69	

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions.
Hazardous Reactions	No information available.
Hazardous Polymerization	No information available.
Conditions to Avoid	Incompatible products.
Materials to avoid	Bases. Strong oxidizing agents. Alcohols. Amines. Metals.

Hazardous Decomposition Products Carbon monoxide (CO). Carbon dioxide (CO₂). Hydrogen chloride gas.

SECTION 11. TOXICOLOGICAL INFORMATION**Product Information****(a) acute toxicity;**

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
1-(Chloromethyl)-3-phenoxybenzene	LD50 = 1224 mg/kg (Rat)		

(b) skin corrosion/irritation; Category 1 B

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Respiratory	No data available
Skin	No data available

(e) germ cell mutagenicity; No data available

(f) carcinogenicity; No data available
There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

3-Phenoxybenzyl chloride

(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	No data available
Other Adverse Effects	The toxicological properties have not been fully investigated.
Symptoms / effects, both acute and delayed	Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects	Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.
Persistence and Degradability	No information available
Bioaccumulative Potential	No information available
Mobility in soil	No information available
Endocrine Disruptor Information	This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant	This product does not contain any known or suspected substance
Ozone Depletion Potential	This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
Contaminated Packaging	Dispose of this container to hazardous or special waste collection point.
Other Information	Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms.

SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No	UN3265
Proper Shipping Name	CORROSIVE LIQUID, ACIDIC, ORGANIC, N.O.S.
Technical Shipping Name	3-Phenoxybenzyl chloride
Hazard Class	8
Packing Group	III

IMDG/IMO

UN-No	UN3265
Proper Shipping Name	CORROSIVE LIQUID, ACIDIC, ORGANIC, N.O.S.
Technical Shipping Name	3-Phenoxybenzyl chloride

3-Phenoxybenzyl chloride

Hazard Class 8
Packing Group III

IATA

UN-No UN3265
Proper Shipping Name CORROSIVE LIQUID, ACIDIC, ORGANIC, N.O.S.
Technical Shipping Name 3-Phenoxybenzyl chloride
Hazard Class 8
Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION

International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
1-(Chloromethyl)-3-phenoxybenzene	-	-	X	-	258-831-1	-	-	-	-	X	-	-

National Regulations

SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department
Creation Date 22-Sep-2009
Revision Date 25-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

3-Phenoxybenzyl chloride

RPE - Respiratory Protective Equipment
LC50 - Lethal Concentration 50%
NOEC - No Observed Effect Concentration
PBT - Persistent, Bioaccumulative, Toxic

LD50 - Lethal Dose 50%
EC50 - Effective Concentration 50%
POW - Partition coefficient Octanol:Water
vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet