

ALFAAA16265

## Hexanal

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

**产品说明:**  
**Product Description:** 己醛, 98%  
 Hexanal

**Cat No. :** A16265  
**Synonyms** Caproaldehyde; Hexaldehyde  
**CAS No** 66-25-1  
**Molecular Formula** C6 H12 O

**Supplier** Avocado Research Chemicals Ltd.  
 (Part of Thermo Fisher Scientific)  
 Shore Road, Heysham  
 Lancashire, LA3 2XY,  
 United Kingdom  
 Office Tel: +44 (0) 1524 850506  
 Office Fax: +44 (0) 1524 850608

**Emergency Telephone Number** For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
 Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

**E-mail address** begel.sdsdesk@thermofisher.com

**Recommended Use** Laboratory chemicals.  
**Uses advised against** No Information available

### SECTION 2. HAZARD IDENTIFICATION

Physical State	Appearance	Odor
Liquid	Clear	pungent
<b>Emergency Overview</b> Flammable liquid and vapor. Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation. May be harmful if swallowed.		

#### Classification of the substance or mixture

Flammable liquids.	Category 3
Acute Oral Toxicity	Category 5
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2A
Specific target organ toxicity - (single exposure)	Category 3

#### Label Elements

## Hexanal



## Signal Word

## Warning

## Hazard Statements

H226 - Flammable liquid and vapor  
H315 - Causes skin irritation  
H319 - Causes serious eye irritation  
H335 - May cause respiratory irritation  
H303 - May be harmful if swallowed

## Precautionary Statements

## Prevention

P241 - Use explosion-proof electrical/ ventilating/ lighting equipment  
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking  
P233 - Keep container tightly closed  
P240 - Ground and bond container and receiving equipment  
P242 - Use non-sparking tools  
P243 - Take action to prevent static discharges  
P264 - Wash face, hands and any exposed skin thoroughly after handling  
P270 - Do not eat, drink or smoke when using this product  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

## Response

P332 + P313 - If skin irritation occurs: Get medical advice/attention  
P337 + P313 - If eye irritation persists: Get medical advice/attention  
P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish  
P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell  
P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower  
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing  
P362 + P364 - Take off contaminated clothing and wash it before reuse

## Storage

P403 + P235 - Store in a well-ventilated place. Keep cool

## Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

## Physical and Chemical Hazards

Vapors may cause flash fire or explosion. Flammable liquid.

## Health Hazards

Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation. May be harmful if swallowed.

## Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

This product does not contain any known or suspected endocrine disruptors.

## SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
Hexaldehyde	66-25-1	<=100
2H-1-Benzopyran-6-ol, 3,4-dihydro-2,5,7,8-tetramethyl-2-(4,8,12-trimethyltridecyl)-, [2R-[2R*(4R*,8R*)]]-	59-02-9	0.05

## SECTION 4. FIRST AID MEASURES

**General Advice**

If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water.

**Most important symptoms and effects**

. Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Carbon dioxide (CO<sub>2</sub>). Dry chemical. Chemical foam. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Flammable. Vapors may travel to source of ignition and flash back. Containers may explode when heated. Vapors may form explosive mixtures with air.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Ensure adequate ventilation. Use personal protective equipment as required. Remove all sources of ignition. Take precautionary measures against static discharges.

**Environmental Precautions**

Should not be released into the environment. Do not flush into surface water or sanitary sewer system.

**Methods for Containment and Clean Up**

Keep in suitable, closed containers for disposal. Soak up with inert absorbent material. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

## Hexanal

## SECTION 7. HANDLING AND STORAGE

**Handling**

Ensure adequate ventilation. Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Avoid ingestion and inhalation. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. Take precautionary measures against static discharges.

**Storage**

Flammables area. Keep away from heat, sparks and flame. Keep containers tightly closed in a dry, cool and well-ventilated place. Containers should be dated when opened and tested periodically for the presence of peroxides.

**Specific Use(s)**

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

**Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

**Exposure Controls****Engineering Measures**

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Use explosion-proof electrical/ventilating/lighting equipment. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment**

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

**Small scale/Laboratory use** Maintain adequate ventilation

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** Prevent product from entering drains.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Clear	
<b>Physical State</b>	Liquid	
<b>Odor</b>	pungent	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	4-5	4.8 g/l aq. sol
<b>Melting Point/Range</b>	-56 °C / -68.8 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	130 - 131 °C / 266 - 267.8 °F	@ 760 mmHg
<b>Flash Point</b>	32 °C / 89.6 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	10.5 mmHg @ 20 °C	
<b>Vapor Density</b>	3.45 (Air = 1.0)	(Air = 1.0)
<b>Specific Gravity / Density</b>	0.815	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	No information available	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
Hexaldehyde	2.3	
<b>Autoignition Temperature</b>	220 °C / 428 °F	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	0.69 mPa s at 20 °C	
<b>Explosive Properties</b>		explosive air/vapour mixtures possible
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C6 H12 O	
<b>Molecular Weight</b>	100.16	

## SECTION 10. STABILITY AND REACTIVITY

<b>Stability</b>	Stable under normal conditions. May form explosive peroxides on prolonged storage.
<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	No information available.
<b>Conditions to Avoid</b>	Keep away from open flames, hot surfaces and sources of ignition. Exposure to air. Incompatible products.
<b>Materials to avoid</b>	Strong bases. Strong oxidizing agents. Ammonia. Amines.
<b>Hazardous Decomposition Products</b>	Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ).

## SECTION 11. TOXICOLOGICAL INFORMATION

**Product Information** The toxicological properties have not been fully investigated

**(a) acute toxicity;**

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
Hexaldehyde	LD50 = 4890 mg/kg ( Rat )	LD50 > 8100 mg/kg ( Rabbit )	
2H-1-Benzopyran-6-ol, 3,4-dihydro-2,5,7,8-tetramethyl-2-(4,8,12-trimethyltridecyl)-, [2R-[2R*(4R*,8R*)]]-	LD50 > 7000 mg/kg ( Rat )	LD50 > 5000 mg/kg ( Rabbit )	

**(b) skin corrosion/irritation;** Category 2

**(c) serious eye damage/irritation;** Category 2

**(d) respiratory or skin sensitization;**

**Respiratory** No data available  
**Skin** No data available

**(e) germ cell mutagenicity;** No data available

**(f) carcinogenicity;** No data available

There are no known carcinogenic chemicals in this product

**(g) reproductive toxicity;** No data available

**(h) STOT-single exposure;** No data available

**(i) STOT-repeated exposure;** No data available

**Target Organs** No information available.

**(j) aspiration hazard;** No data available

**Symptoms / effects, both acute and delayed** Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

## SECTION 12. ECOLOGICAL INFORMATION

**Ecotoxicity effects**

Contains a substance which is: Harmful to aquatic organisms. Do not empty into drains. Do not flush into surface water or sanitary sewer system. Do not allow material to contaminate ground water system. The product contains following substances which are hazardous for the environment.

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
Hexaldehyde	LC50: 12 - 16.5 mg/L, 96h flow-through (Pimephales promelas)			

**Persistence and Degradability**

**Persistence** Persistence is unlikely.  
**Degradation in sewage treatment plant** Contains substances known to be hazardous to the environment or not degradable in waste water treatment plants.

## Hexanal

**Bioaccumulative Potential** Bioaccumulation is unlikely

Component	log Pow	Bioconcentration factor (BCF)
Hexaldehyde	2.3	No data available

**Mobility in soil** The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors

**Persistent Organic Pollutant** This product does not contain any known or suspected substance

**Ozone Depletion Potential** This product does not contain any known or suspected substance

**SECTION 13. DISPOSAL CONSIDERATIONS**

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

**Other Information** Do not flush to sewer. Waste codes should be assigned by the user based on the application for which the product was used. Can be landfilled or incinerated, when in compliance with local regulations.

**SECTION 14. TRANSPORT INFORMATION****Road and Rail Transport**

**UN-No** UN1207  
**Proper Shipping Name** HEXALDEHYDE  
**Hazard Class** 3  
**Packing Group** III

**IMDG/IMO**

**UN-No** UN1207  
**Proper Shipping Name** HEXALDEHYDE  
**Hazard Class** 3  
**Packing Group** III

**IATA**

**UN-No** UN1207  
**Proper Shipping Name** HEXALDEHYDE  
**Hazard Class** 3  
**Packing Group** III

**Special Precautions for User** No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

## Hexanal

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
Hexaldehyde	X	X	X	X	200-624-5	X	X	X	X	X	X	KE-18623
2H-1-Benzopyran-6-ol, 3,4-dihydro-2,5,7,8-tetra-methyl-2-(4,8,12-trimethyltridecyl)-, [2R-[2R*(4R*,8R*)]]-	-	-	X	X	200-412-2	X	X	X	X	X	X	KE-10750

## National Regulations

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 10-May-2010  
**Revision Date** 16-May-2024  
**Revision Summary** New emergency telephone response service provider.

## Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

## Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS



**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**