

ALFAAA16865

3,3-Dimethylacrylic acid

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:
Product Description: 3,3-二甲基丙烯酸
3,3-Dimethylacrylic acid

Cat No. : A16865
CAS No 541-47-9
Molecular Formula C5 H8 O2

Supplier Avocado Research Chemicals Ltd.
(Part of Thermo Fisher Scientific)
Shore Road, Heysham
Lancashire, LA3 2XY,
United Kingdom
Office Tel: +44 (0) 1524 850506
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
Solid

Appearance
No information available

Odor
No information available

Emergency Overview
May be harmful in contact with skin. Causes severe skin burns and eye damage.

Classification of the substance or mixture

Acute Dermal Toxicity	Category 5
Skin Corrosion/Irritation	Category 1 C
Serious Eye Damage/Eye Irritation	Category 1

Label Elements



Signal Word

Danger

Hazard Statements

3,3-Dimethylacrylic acid

H313 - May be harmful in contact with skin
H314 - Causes severe skin burns and eye damage

Precautionary Statements**Prevention**

P264 - Wash face, hands and any exposed skin thoroughly after handling
P271 - Use only outdoors or in a well-ventilated area
P280 - Wear protective gloves/protective clothing/eye protection/face protection

Response

P301 + P330 + P331 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting
P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower
P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P310 - Immediately call a POISON CENTER or doctor
P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

May be harmful in contact with skin. Corrosive. Causes skin and eye burns.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil. The product evaporates slowly.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
.beta., .beta.-Dimethacrylic acid	541-47-9	>95

SECTION 4. FIRST AID MEASURES**General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required. Keep eye wide open while rinsing.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Call a physician immediately.

Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Call a physician or poison control center immediately. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device.

Ingestion

Immediate medical attention is required. Do NOT induce vomiting. Drink plenty of water. Never give anything by mouth to an unconscious person.

Most important symptoms and effects

Causes burns by all exposure routes. Ingestion causes severe swelling, severe damage to the delicate tissue and danger of

3,3-Dimethylacrylic acid

perforation: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

CO₂, dry chemical, dry sand, alcohol-resistant foam. Water mist may be used to cool closed containers.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

The product causes burns of eyes, skin and mucous membranes. Combustible material. Containers may explode when heated.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Use personal protective equipment as required. Evacuate personnel to safe areas. Avoid contact with skin, eyes or clothing. Remove all sources of ignition. Take precautionary measures against static discharges. Refer to protective measures listed in Sections 7 and 8

Environmental Precautions

Should not be released into the environment. Do not allow material to contaminate ground water system. See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal. Avoid dust formation. Remove all sources of ignition.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe dust. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition.

Storage

Keep out of the reach of children. Keep containers tightly closed in a dry, cool and well-ventilated place. Corrosives area. Keep away from heat, sparks and flame.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

3,3-Dimethylacrylic acid

Control Parameters

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust MDHS70 General methods for sampling airborne gases and vapours

Exposure Controls

Engineering Measures

Use only under a chemical fume hood. Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Butyl rubber	recommendations			
Nitrile rubber				
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Long sleeved clothing

Respiratory Protection No protective equipment is needed under normal use conditions.

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

Small scale/Laboratory use Maintain adequate ventilation

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance

Physical State Solid

Odor No information available

Odor Threshold No data available

pH No information available

SAFETY DATA SHEET**3,3-Dimethylacrylic acid**

Melting Point/Range	68.5 - 69.5 °C / 155.3 - 157.1 °F	
Softening Point	No data available	
Boiling Point/Range	194 - 195 °C / 381.2 - 383 °F	
Flash Point	93 °C / 199.4 °F	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	practically insoluble	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	465 °C / 869 °F	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties		explosive air/vapour mixtures possible
Oxidizing Properties	No information available	
Molecular Formula	C5 H8 O2	
Molecular Weight	100.12	

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	No information available.
Conditions to Avoid	Incompatible products. Excess heat. Avoid dust formation. Keep away from open flames, hot surfaces and sources of ignition.
Materials to avoid	Bases. Reducing Agent. Oxidizing agent.

Hazardous Decomposition Products Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 11. TOXICOLOGICAL INFORMATION**Product Information****(a) acute toxicity;**

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
.beta., .beta.-Dimethacrylic acid	LD50 = 3560 mg/kg (Rat)		

(b) skin corrosion/irritation; Category 1 C

(c) serious eye damage/irritation; Category 1

(d) respiratory or skin sensitization;

Respiratory	No data available
Skin	No data available

(e) germ cell mutagenicity; No data available

3,3-Dimethylacrylic acid

(f) carcinogenicity; No data available
There are no known carcinogenic chemicals in this product

(g) reproductive toxicity; No data available

(h) STOT-single exposure; No data available

(i) STOT-repeated exposure; No data available

Target Organs No information available.

(j) aspiration hazard; Not applicable
Solid

Other Adverse Effects The toxicological properties have not been fully investigated.

Symptoms / effects, both acute and delayed Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects Do not empty into drains. .

Persistence and Degradability
Persistence Insoluble in water, May persist, based on information available.

Bioaccumulative Potential May have some potential to bioaccumulate

Mobility in soil Spillage unlikely to penetrate soil The product evaporates slowly Is not likely mobile in the environment due its low water solubility Spillage unlikely to penetrate soil

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors
Persistent Organic Pollutant This product does not contain any known or suspected substance
Ozone Depletion Potential This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

Contaminated Packaging Dispose of this container to hazardous or special waste collection point.

Other Information Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains. Do not flush to sewer. Large amounts will affect pH and harm aquatic organisms.

SECTION 14. TRANSPORT INFORMATION

SAFETY DATA SHEET

3,3-Dimethylacrylic acid

Road and Rail Transport

UN-No UN3261
Proper Shipping Name Corrosive solid, acidic, organic, n.o.s.
Technical Shipping Name .beta., .beta.-Dimethacrylic acid
Hazard Class 8
Packing Group III

IMDG/IMO

UN-No UN3261
Proper Shipping Name Corrosive solid, acidic, organic, n.o.s.
Technical Shipping Name .beta., .beta.-Dimethacrylic acid
Hazard Class 8
Packing Group III

IATA

UN-No UN3261
Proper Shipping Name Corrosive solid, acidic, organic, n.o.s.
Technical Shipping Name .beta., .beta.-Dimethacrylic acid
Hazard Class 8
Packing Group III

Special Precautions for User No special precautions required

SECTION 15. REGULATORY INFORMATION**International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
.beta., .beta.-Dimethacrylic acid	-	-	X	X	208-782-7	X	X	X	X	X	X	KE-23593

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Creation Date 11-Apr-2011
Revision Date 25-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.
Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

3,3-Dimethylacrylic acid

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

CAS - Chemical Abstracts Service

EINECS/ELINCS - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

IECSC - Chinese Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

ENCS - Japanese Existing and New Chemical Substances

AICS - Australian Inventory of Chemical Substances

NZIoC - New Zealand Inventory of Chemicals

WEL - Workplace Exposure Limit

ACGIH - American Conference of Governmental Industrial Hygienists

DNEL - Derived No Effect Level

RPE - Respiratory Protective Equipment

LC50 - Lethal Concentration 50%

NOEC - No Observed Effect Concentration

PBT - Persistent, Bioaccumulative, Toxic

TWA - Time Weighted Average

IARC - International Agency for Research on Cancer

PNEC - Predicted No Effect Concentration

LD50 - Lethal Dose 50%

EC50 - Effective Concentration 50%

POW - Partition coefficient Octanol:Water

vPvB - very Persistent, very Bioaccumulative

ICAO/IATA - International Civil Aviation Organization/International Air Transport Association

ADR - European Agreement Concerning the International Carriage of Dangerous Goods by Road

OECD - Organisation for Economic Co-operation and Development

BCF - Bioconcentration factor

IMO/IMDG - International Maritime Organization/International Maritime Dangerous Goods Code

MARPOL - International Convention for the Prevention of Pollution from Ships

ATE - Acute Toxicity Estimate

VOC - (Volatile Organic Compound)

Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet