

ALFAAA17714

## 3-(Methacryloyloxy)propyltrimethoxysilane

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

<b>产品说明:</b> <b>Product Description:</b>	<b>3-(异丁烯酰氧)丙基三甲氧基硅烷</b> <b>3-(Methacryloyloxy)propyltrimethoxysilane</b>
<b>Cat No. :</b>	<b>A17714</b>
<b>Synonyms</b>	1-Propanol, 3-(trimethoxysilyl)-, methacryl; 3-Methacryloxypropyltrimethoxysilane; MEMO
<b>CAS No</b>	2530-85-0
<b>Molecular Formula</b>	C <sub>10</sub> H <sub>20</sub> O <sub>5</sub> Si
<b>Supplier</b>	Avocado Research Chemicals Ltd. (Part of Thermo Fisher Scientific) Shore Road, Heysham Lancashire, LA3 2XY, United Kingdom Office Tel: +44 (0) 1524 850506 Office Fax: +44 (0) 1524 850608
<b>Emergency Telephone Number</b>	For information <b>US</b> call: 001-800-227-6701 / <b>Europe</b> call: +32 14 57 52 11 Emergency Number <b>US</b> :001-201-796-7100 / <b>Europe</b> : +32 14 57 52 99 <b>CHEMTREC</b> Tel. No. <b>US</b> :001-800-424-9300 / <b>Europe</b> :001-703-527-3887
<b>E-mail address</b>	begel.sdsdesk@thermofisher.com
<b>Recommended Use</b> <b>Uses advised against</b>	Laboratory chemicals. No Information available

### SECTION 2. HAZARD IDENTIFICATION

<b>Physical State</b> Liquid	<b>Appearance</b> Off-white	<b>Odor</b> Slight
<b>Emergency Overview</b> Moisture sensitive.		

#### Classification of the substance or mixture

Based on available data, the classification criteria are not met

#### Label Elements

None required

#### **Physical and Chemical Hazards**

None identified.

#### **Health Hazards**

The product contains no substances which at their given concentration are considered to be hazardous to health.

#### **Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants. Is not likely mobile in the environment due its low water solubility. Spillage unlikely to penetrate soil. The product is insoluble and sinks in

# SAFETY DATA SHEET

## 3-(Methacryloyloxy)propyltrimethoxysilane

water. The product evaporates slowly.

This product does not contain any known or suspected endocrine disruptors.

### SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
2-Propenoic acid, 2-methyl-, 3-(trimethoxysilyl)propyl ester	2530-85-0	>95

### SECTION 4. FIRST AID MEASURES

#### General Advice

If symptoms persist, call a physician.

#### Eye Contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

#### Skin Contact

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

#### Inhalation

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

#### Ingestion

Clean mouth with water and drink afterwards plenty of water.

#### Most important symptoms and effects

None reasonably foreseeable.

#### Self-Protection of the First Aider

No special precautions required.

#### Notes to Physician

Treat symptomatically.

### SECTION 5. FIRE-FIGHTING MEASURES

#### Suitable Extinguishing Media

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam.

#### Extinguishing media which must not be used for safety reasons

No information available.

#### Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

#### Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

### SECTION 6. ACCIDENTAL RELEASE MEASURES

#### Personal Precautions

Ensure adequate ventilation. Use personal protective equipment as required.

#### Environmental Precautions

# SAFETY DATA SHEET

## 3-(Methacryloyloxy)propyltrimethoxysilane

Should not be released into the environment.

### Methods for Containment and Clean Up

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

## SECTION 7. HANDLING AND STORAGE

### Handling

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid ingestion and inhalation. Do not get in eyes, on skin, or on clothing.

### Storage

Keep containers tightly closed in a dry, cool and well-ventilated place.

### Specific Use(s)

Use in laboratories

## SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control Parameters

### Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours

### Exposure Controls

### Engineering Measures

Ensure that eyewash stations and safety showers are close to the workstation location. Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

### Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

## 3-(Methacryloyloxy)propyltrimethoxysilane

To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use**

Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced

**Recommended Filter type:** Organic gases and vapours filter Type A Brown conforming to EN14387

**Small scale/Laboratory use**

Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

**Recommended half mask:-** Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141

When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures**

Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls**

No information available.

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

<b>Appearance</b>	Off-white	
<b>Physical State</b>	Liquid	
<b>Odor</b>	Slight	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	No data available	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	253 °C / 487.4 °F	@ 1017 hPa
<b>Flash Point</b>	100 °C / 212 °F	<b>Method -</b> CC (closed cup)
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	<b>Lower</b> 0.90 <b>Upper</b> 5.40	
<b>Vapor Pressure</b>	2.3 Pa	
<b>Vapor Density</b>	8.6	(Air = 1.0)
<b>Specific Gravity / Density</b>	1.040	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	Insoluble	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Component</b>	<b>log Pow</b>	
2-Propenoic acid, 2-methyl-, 3-(trimethoxysilyl)propyl ester	2.1	
<b>Autoignition Temperature</b>	275 °C / 527 °F	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	No data available	
<b>Explosive Properties</b>	No information available	
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C10H20O5Si	
<b>Molecular Weight</b>	248.35	
<b>Refractive index</b>	1.4310	

**SECTION 10. STABILITY AND REACTIVITY****Stability**

Moisture sensitive.

## 3-(Methacryloyloxy)propyltrimethoxysilane

<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid</b>	Incompatible products. Excess heat.
<b>Materials to avoid</b>	Strong oxidizing agents.

**Hazardous Decomposition Products** Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

## SECTION 11. TOXICOLOGICAL INFORMATION

## Product Information

## (a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
2-Propenoic acid, 2-methyl-, 3-(trimethoxysilyl)propyl ester	LD50: > 2000 mg/kg bw (Rat)	LD50: > 2000 mg/kg bw (Rat)	LC50: > 2280 mg/m <sup>3</sup> (Rat)

## (b) skin corrosion/irritation;

## Test method

## Test species

## Observational endpoint

Based on available data, the classification criteria are not met  
OECD 404  
rabbit  
No skin irritation

## (c) serious eye damage/irritation;

## Test method

## Test species

## Observation end point

Based on available data, the classification criteria are not met  
OECD 405  
rabbit  
No eye irritation

## (d) respiratory or skin sensitization;

## Respiratory

## Skin

No data available  
Based on available data, the classification criteria are not met

Component	Test method	Test species	Study result
2-Propenoic acid, 2-methyl-, 3-(trimethoxysilyl)propyl ester 2530-85-0 ( >95 )	OECD Test Guideline 429 Local Lymph Node Assay	mouse	non-sensitising

## (e) germ cell mutagenicity;

Based on available data, the classification criteria are not met

## (f) carcinogenicity;

No data available

There are no known carcinogenic chemicals in this product

## (g) reproductive toxicity;

No data available

## (h) STOT-single exposure;

No data available

## (i) STOT-repeated exposure;

No data available

## Target Organs

No information available.

## (j) aspiration hazard;

No data available

## Other Adverse Effects

The toxicological properties have not been fully investigated.

**Symptoms / effects, both acute and** No information available

# SAFETY DATA SHEET

## 3-(Methacryloyloxy)propyltrimethoxysilane

delayed

### SECTION 12. ECOLOGICAL INFORMATION

#### Ecotoxicity effects

Component	Freshwater Fish	Water Flea	Freshwater Algae	Microtox
2-Propenoic acid, 2-methyl-, 3-(trimethoxysilyl)propyl ester	LC50: > 100 mg/L, 96h (Brachydanio rerio)	EC50: > 100 mg/L, 48h (Daphnia magna)	EC50: > 100 mg/L, 72h (Scenedesmus subspicatus)	EC50: > 1000 mg/L, 3h

#### Persistence and Degradability Persistence

Insoluble in water, May persist, based on information available.

#### Bioaccumulative Potential

May have some potential to bioaccumulate

Component	log Pow	Bioconcentration factor (BCF)
2-Propenoic acid, 2-methyl-, 3-(trimethoxysilyl)propyl ester	2.1	No data available

#### Mobility in soil

Spillage unlikely to penetrate soil The product is insoluble and sinks in water The product evaporates slowly Is not likely mobile in the environment due its low water solubility  
Spillage unlikely to penetrate soil

#### Endocrine Disruptor Information Persistent Organic Pollutant Ozone Depletion Potential

This product does not contain any known or suspected endocrine disruptors  
This product does not contain any known or suspected substance  
This product does not contain any known or suspected substance

### SECTION 13. DISPOSAL CONSIDERATIONS

#### Waste from Residues/Unused Products

Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

#### Contaminated Packaging

Dispose of this container to hazardous or special waste collection point.

#### Other Information

Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

### SECTION 14. TRANSPORT INFORMATION

#### Road and Rail Transport

Not Regulated

#### IMDG/IMO

Not regulated

#### IATA

Not regulated

#### Special Precautions for User

No special precautions required

### SECTION 15. REGULATORY INFORMATION

#### International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan

# SAFETY DATA SHEET

## 3-(Methacryloyloxy)propyltrimethoxysilane

(ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
2-Propenoic acid, 2-methyl-, 3-(trimethoxysilyl)propyl ester	-	-	X	X	219-785-8	X	X	X	X	X	X	KE-23175

### National Regulations

## SECTION 16. OTHER INFORMATION

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 28-Feb-2011  
**Revision Date** 27-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

### Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

### Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

### Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

# SAFETY DATA SHEET

## 3-(Methacryloyloxy)propyltrimethoxysilane

---

### Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**