

ALFAAA18932

## Isobutyl isothiocyanate

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明:  
Product Description: 异硫氰酸异丁酯  
Isobutyl isothiocyanate

Cat No. : A18932  
CAS No 591-82-2  
Molecular Formula C5 H9 N S

Supplier Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.  
Uses advised against No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Liquid

**Appearance**  
Colorless to yellow

**Odor**  
No information available

#### Emergency Overview

Flammable liquid and vapor. Harmful if swallowed. Harmful in contact with skin. Causes severe skin burns and eye damage.  
Harmful if inhaled. Moisture sensitive. Lachrymator (substance which increases the flow of tears).

#### Classification of the substance or mixture

Flammable liquids.	Category 3
Acute Oral Toxicity	Category 4
Acute Dermal Toxicity	Category 4
Acute Inhalation Toxicity - Vapors	Category 4
Skin Corrosion/Irritation	Category 1 B
Serious Eye Damage/Eye Irritation	Category 1

#### Label Elements



**Signal Word****Danger****Hazard Statements**

H226 - Flammable liquid and vapor

H314 - Causes severe skin burns and eye damage

H302 + H312 + H332 - Harmful if swallowed, in contact with skin or if inhaled

**Precautionary Statements****Prevention**

P240 - Ground and bond container and receiving equipment

P241 - Use explosion-proof electrical/ ventilating/ lighting equipment

P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking

P242 - Use non-sparking tools

P243 - Take action to prevent static discharges

P264 - Wash face, hands and any exposed skin thoroughly after handling

P270 - Do not eat, drink or smoke when using this product

P271 - Use only outdoors or in a well-ventilated area

P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P303 + P361 + P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P310 - Immediately call a POISON CENTER or doctor

P330 - Rinse mouth

P331 - Do NOT induce vomiting

P370 + P378 - In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish

P362 + P364 - Take off contaminated clothing and wash it before reuse

**Storage**

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

Flammable liquid. Vapors may cause flash fire or explosion.

**Health Hazards**

Harmful if swallowed. Harmful in contact with skin. Corrosive. Causes skin and eye burns. Harmful if inhaled. Lachrymator (substance which increases the flow of tears).

**Environmental hazards**

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

**Other Hazards**

Lachrymator (substance which increases the flow of tears)

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
2-Methylpropyl isothiocyanate	591-82-2	100

**SECTION 4. FIRST AID MEASURES**



**General Advice**

Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Immediate medical attention is required.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Call a physician immediately.

**Inhalation**

If not breathing, give artificial respiration. Remove from exposure, lie down. Do not use mouth-to-mouth method if victim ingested or inhaled the substance; give artificial respiration with the aid of a pocket mask equipped with a one-way valve or other proper respiratory medical device. Call a physician immediately.

**Ingestion**

Do NOT induce vomiting. Clean mouth with water. Never give anything by mouth to an unconscious person. Call a physician immediately.

**Most important symptoms and effects**

Causes burns by all exposure routes. Difficulty in breathing. Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

CO<sub>2</sub>, dry chemical, dry sand, alcohol-resistant foam. Water mist may be used to cool closed containers.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

The product causes burns of eyes, skin and mucous membranes. Thermal decomposition can lead to release of irritating gases and vapors. Flammable. Containers may explode when heated. Vapors may form explosive mixtures with air. Vapors may travel to source of ignition and flash back.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Use personal protective equipment as required. Ensure adequate ventilation. Evacuate personnel to safe areas. Keep people away from and upwind of spill/leak. Remove all sources of ignition. Take precautionary measures against static discharges.

**Environmental Precautions**

Should not be released into the environment. See Section 12 for additional Ecological Information.



## Isobutyl isothiocyanate

**Methods for Containment and Clean Up**

Soak up with inert absorbent material. Keep in suitable, closed containers for disposal. Remove all sources of ignition. Use spark-proof tools and explosion-proof equipment.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Wear personal protective equipment/face protection. Do not get in eyes, on skin, or on clothing. Use only under a chemical fume hood. Do not breathe mist/vapors/spray. Do not ingest. If swallowed then seek immediate medical assistance. Keep away from open flames, hot surfaces and sources of ignition. Use only non-sparking tools. Take precautionary measures against static discharges.

**Storage**

Keep containers tightly closed in a dry, cool and well-ventilated place. Flammables area. Keep away from heat, sparks and flame. Corrosives area.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS70 General methods for sampling airborne gases and vapours MDHS 88 Volatile organic compounds in air. Laboratory method using diffusive samplers, solvent desorption and gas chromatography MDHS 96 Volatile organic compounds in air - Laboratory method using pumped solid sorbent tubes, solvent desorption and gas chromatography

**Exposure Controls****Engineering Measures**

Use only under a chemical fume hood. Ensure that eyewash stations and safety showers are close to the workstation location. Use explosion-proof electrical/ventilating/lighting equipment. Ensure adequate ventilation, especially in confined areas. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

**Personal protective equipment****Eye Protection**

Goggles (European standard - EN 166)

**Hand Protection**

Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Natural rubber	See manufacturers	-	EN 374	(minimum requirement)
Nitrile rubber	recommendations			
Neoprene				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.



**SAFETY DATA SHEET****Isobutyl isothiocyanate**

<b>Skin and body protection</b>	Long sleeved clothing
<b>Respiratory Protection</b>	When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly
<b>Large scale/emergency use</b>	Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced <b>Recommended Filter type:</b> Organic gases and vapours filter Type A Brown conforming to EN14387
<b>Small scale/Laboratory use</b>	Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced. <b>Recommended half mask:-</b> Valve filtering: EN405; or; Half mask: EN140; plus filter, EN 141 When RPE is used a face piece Fit Test should be conducted
<b>Hygiene Measures</b>	Handle in accordance with good industrial hygiene and safety practice.
<b>Environmental exposure controls</b>	No information available.

**SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES**

<b>Appearance</b>	Colorless to yellow	
<b>Physical State</b>	Liquid	
<b>Odor</b>	No information available	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	No data available	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	160 - 162 °C / 320 - 323.6 °F	@ 760 mmHg
<b>Flash Point</b>	24 °C / 75.2 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	No data available	
<b>Flammability (solid,gas)</b>	Not applicable	Liquid
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No data available	
<b>Vapor Density</b>	No data available	(Air = 1.0)
<b>Specific Gravity / Density</b>	0.940	
<b>Bulk Density</b>	Not applicable	Liquid
<b>Water Solubility</b>	No information available	
<b>Solubility in other solvents</b>	No information available	
<b>Partition Coefficient (n-octanol/water)</b>		
<b>Autoignition Temperature</b>	No data available	
<b>Decomposition Temperature</b>	No data available	
<b>Viscosity</b>	No data available	
<b>Explosive Properties</b>		explosive air/vapour mixtures possible
<b>Oxidizing Properties</b>	No information available	
<b>Molecular Formula</b>	C5 H9 N S	
<b>Molecular Weight</b>	115.2	

**SECTION 10. STABILITY AND REACTIVITY**

<b>Stability</b>	Stable under normal conditions. Moisture sensitive.
------------------	---



<b>Hazardous Reactions</b>	None under normal processing.
<b>Hazardous Polymerization</b>	Hazardous polymerization does not occur.
<b>Conditions to Avoid</b>	Incompatible products. Excess heat. Keep away from open flames, hot surfaces and sources of ignition. Exposure to moist air or water.
<b>Materials to avoid</b>	Strong oxidizing agents. Strong acids. Strong bases. Water.
<b>Hazardous Decomposition Products</b>	Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ). Nitrogen oxides (NO <sub>x</sub> ). Sulfur oxides.

**SECTION 11. TOXICOLOGICAL INFORMATION****Product Information**

<b>(a) acute toxicity;</b>	
<b>(b) skin corrosion/irritation;</b>	Category 1 B
<b>(c) serious eye damage/irritation;</b>	Category 1
<b>(d) respiratory or skin sensitization;</b>	
Respiratory	No data available
Skin	No data available
	No information available
<b>(e) germ cell mutagenicity;</b>	No data available
<b>(f) carcinogenicity;</b>	No data available
	There are no known carcinogenic chemicals in this product
<b>(g) reproductive toxicity;</b>	No data available
<b>(h) STOT-single exposure;</b>	No data available
<b>(i) STOT-repeated exposure;</b>	No data available
Target Organs	No information available.
<b>(j) aspiration hazard;</b>	No data available

<b>Symptoms / effects, both acute and delayed</b>	Product is a corrosive material. Use of gastric lavage or emesis is contraindicated. Possible perforation of stomach or esophagus should be investigated: Ingestion causes severe swelling, severe damage to the delicate tissue and danger of perforation: Symptoms of overexposure may be headache, dizziness, tiredness, nausea and vomiting
---	---

**SECTION 12. ECOLOGICAL INFORMATION**

<b>Ecotoxicity effects</b>	Do not empty into drains.
<b>Persistence and Degradability</b>	No information available



**Bioaccumulative Potential** No information available

**Mobility in soil** No information available

**Endocrine Disruptor Information** This product does not contain any known or suspected endocrine disruptors

**Persistent Organic Pollutant** This product does not contain any known or suspected substance

**Ozone Depletion Potential** This product does not contain any known or suspected substance

### SECTION 13. DISPOSAL CONSIDERATIONS

**Waste from Residues/Unused Products** Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.

**Contaminated Packaging** Dispose of this container to hazardous or special waste collection point. Empty containers retain product residue, (liquid and/or vapor), and can be dangerous. Keep product and empty container away from heat and sources of ignition.

**Other Information** Waste codes should be assigned by the user based on the application for which the product was used. Do not flush to sewer. Can be landfilled or incinerated, when in compliance with local regulations. Do not empty into drains. Large amounts will affect pH and harm aquatic organisms.

### SECTION 14. TRANSPORT INFORMATION

#### Road and Rail Transport

**UN-No** UN3286  
**Proper Shipping Name** Flammable liquid, toxic, corrosive, n.o.s.  
**Technical Shipping Name** (Isobutyl isothiocyanate)  
**Hazard Class** 3  
**Subsidiary Hazard Class** 6.1, 8  
**Packing Group** II

#### IMDG/IMO

**UN-No** UN3286  
**Proper Shipping Name** Flammable liquid, toxic, corrosive, n.o.s.  
**Technical Shipping Name** (Isobutyl isothiocyanate)  
**Hazard Class** 3  
**Subsidiary Hazard Class** 6.1, 8  
**Packing Group** II

#### IATA

**UN-No** UN3286  
**Proper Shipping Name** Flammable liquid, toxic, corrosive, n.o.s.  
**Technical Shipping Name** (Isobutyl isothiocyanate)  
**Hazard Class** 3  
**Subsidiary Hazard Class** 6.1, 8  
**Packing Group** II

**Special Precautions for User** No special precautions required

### SECTION 15. REGULATORY INFORMATION



## Isobutyl isothiocyanate

## International Inventories

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
2-Methylpropyl isothiocyanate	-	-	X	-	209-733-2	-	-	-	-	-	-	-

## National Regulations

## SECTION 16. OTHER INFORMATION

Prepared By Health, Safety and Environmental Department  
 Creation Date 11-Nov-2009  
 Revision Date 27-Apr-2024  
 Revision Summary New emergency telephone response service provider.

## Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**RPE** - Respiratory Protective Equipment

**LC50** - Lethal Concentration 50%

**NOEC** - No Observed Effect Concentration

**PBT** - Persistent, Bioaccumulative, Toxic

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

**LD50** - Lethal Dose 50%

**EC50** - Effective Concentration 50%

**POW** - Partition coefficient Octanol:Water

**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

## Key literature references and sources for data

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS



**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**