

ALFAAA19152

## 4-Nitroanisole

### SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

**产品说明:** 硝基苯甲醚, 97%  
**Product Description:** 4-Nitroanisole

**Cat No. :** A19152  
**Synonyms** 1-Methoxy-4-nitrobenzene  
**CAS No** 100-17-4  
**Molecular Formula** C7 H7 N O3

**Supplier** Avocado Research Chemicals Ltd.  
(Part of Thermo Fisher Scientific)  
Shore Road, Heysham  
Lancashire, LA3 2XY,  
United Kingdom  
Office Tel: +44 (0) 1524 850506  
Office Fax: +44 (0) 1524 850608

**Emergency Telephone Number** For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11  
Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99  
**CHEMTREC** Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

**E-mail address** begel.sdsdesk@thermofisher.com

**Recommended Use** Laboratory chemicals.  
**Uses advised against** No Information available

### SECTION 2. HAZARD IDENTIFICATION

**Physical State**  
Solid

**Appearance**  
Green

**Odor**  
No information available

#### Emergency Overview

Harmful to aquatic life with long lasting effects. May be harmful if swallowed. Suspected of causing genetic defects.

#### Classification of the substance or mixture

Acute Oral Toxicity	Category 5
Germ Cell Mutagenicity	Category 2
Chronic aquatic toxicity	Category 3

#### Label Elements



Signal Word

Warning

## 4-Nitroanisole

**Hazard Statements**

H412 - Harmful to aquatic life with long lasting effects  
H303 - May be harmful if swallowed  
H341 - Suspected of causing genetic defects

**Precautionary Statements****Prevention**

P201 - Obtain special instructions before use  
P202 - Do not handle until all safety precautions have been read and understood  
P270 - Do not eat, drink or smoke when using this product  
P280 - Wear protective gloves/protective clothing/eye protection/face protection

**Response**

P301 + P312 - IF SWALLOWED: Call a POISON CENTER or doctor if you feel unwell  
P308 + P313 - IF exposed or concerned: Get medical advice/attention

**Storage**

P403 - Store in a well-ventilated place

**Disposal**

P501 - Dispose of contents/ container to an approved waste disposal plant

**Physical and Chemical Hazards**

None identified.

**Health Hazards**

May be harmful if swallowed. Suspected of causing genetic defects.

**Environmental hazards**

Harmful to aquatic life with long lasting effects. Will likely be mobile in the environment due to its water solubility. The product is water soluble, and may spread in water systems.

No information available

This product does not contain any known or suspected endocrine disruptors.

**SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS**

Component	CAS No	Weight %
4-Nitroanisole	100-17-4	99

**SECTION 4. FIRST AID MEASURES****General Advice**

If symptoms persist, call a physician.

**Eye Contact**

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.

**Skin Contact**

Wash off immediately with plenty of water for at least 15 minutes. If skin irritation persists, call a physician.

**Inhalation**

Remove to fresh air. If not breathing, give artificial respiration. Get medical attention if symptoms occur.

**Ingestion**

Clean mouth with water and drink afterwards plenty of water. Get medical attention if symptoms occur.

**Most important symptoms and effects**

None reasonably foreseeable.

**Self-Protection of the First Aider**

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

**Notes to Physician**

## 4-Nitroanisole

Treat symptomatically.

**SECTION 5. FIRE-FIGHTING MEASURES****Suitable Extinguishing Media**

Water spray, carbon dioxide (CO<sub>2</sub>), dry chemical, alcohol-resistant foam.

**Extinguishing media which must not be used for safety reasons**

No information available.

**Specific Hazards Arising from the Chemical**

Thermal decomposition can lead to release of irritating gases and vapors. Keep product and empty container away from heat and sources of ignition.

**Protective Equipment and Precautions for Firefighters**

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

**SECTION 6. ACCIDENTAL RELEASE MEASURES****Personal Precautions**

Use personal protective equipment as required. Ensure adequate ventilation. Avoid dust formation.

**Environmental Precautions**

Should not be released into the environment. See Section 12 for additional Ecological Information.

**Methods for Containment and Clean Up**

Sweep up and shovel into suitable containers for disposal. Keep in suitable, closed containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

**SECTION 7. HANDLING AND STORAGE****Handling**

Wear personal protective equipment/face protection. Ensure adequate ventilation. Avoid dust formation. Avoid ingestion and inhalation. Do not get in eyes, on skin, or on clothing.

**Storage**

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

**Specific Use(s)**

Use in laboratories

**SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION****Control Parameters****Monitoring methods**

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

**Exposure Controls****Engineering Measures**

## 4-Nitroanisole

Ensure adequate ventilation, especially in confined areas. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

## Personal protective equipment

**Eye Protection** Goggles (European standard - EN 166)

**Hand Protection** Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber	See manufacturers	-	EN 374	(minimum requirement)
Neoprene	recommendations			
Natural rubber				
PVC				

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatibility, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

**Skin and body protection** Wear appropriate protective gloves and clothing to prevent skin exposure

**Respiratory Protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators. To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

**Large scale/emergency use** Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced  
**Recommended Filter type:** Particulates filter conforming to EN 143

**Small scale/Laboratory use** Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.  
**Recommended half mask:-** Particle filtering: EN149:2001  
When RPE is used a face piece Fit Test should be conducted

**Hygiene Measures** Handle in accordance with good industrial hygiene and safety practice.

**Environmental exposure controls** No information available.

## SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Appearance</b>	Green	
<b>Physical State</b>	Solid	
<b>Odor</b>	No information available	
<b>Odor Threshold</b>	No data available	
<b>pH</b>	No information available	
<b>Melting Point/Range</b>	51 - 53 °C / 123.8 - 127.4 °F	
<b>Softening Point</b>	No data available	
<b>Boiling Point/Range</b>	260 °C / 500 °F	
<b>Flash Point</b>	130 °C / 266 °F	<b>Method -</b> No information available
<b>Evaporation Rate</b>	Not applicable	Solid
<b>Flammability (solid,gas)</b>	No information available	
<b>Explosion Limits</b>	No data available	
<b>Vapor Pressure</b>	No information available	
<b>Vapor Density</b>	Not applicable	Solid

## 4-Nitroanisole

Specific Gravity / Density	1.230	
Bulk Density	No data available	
Water Solubility	0.468 g/l (20°C)	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	458 °C / 856.4 °F	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	C7 H7 N O3	
Molecular Weight	153.14	

## SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions.
Hazardous Reactions	None under normal processing.
Hazardous Polymerization	No information available.
Conditions to Avoid	Avoid dust formation. Incompatible products. Excess heat.
Materials to avoid	Strong oxidizing agents. Strong bases.

**Hazardous Decomposition Products** Nitrogen oxides (NOx). Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

## SECTION 11. TOXICOLOGICAL INFORMATION

**Product Information** No acute toxicity information is available for this product

## (a) acute toxicity;

Component	LD50 Oral	LD50 Dermal	LC50 Inhalation
4-Nitroanisole	LD50 = 2300 mg/kg ( Rat )		

(b) skin corrosion/irritation; No data available

(c) serious eye damage/irritation; No data available

## (d) respiratory or skin sensitization;

Respiratory	No data available
Skin	No data available

(e) germ cell mutagenicity; Category 2  
Ames test:: positive

(f) carcinogenicity; No data available  
The table below indicates whether each agency has listed any ingredient as a carcinogen

Component	EU	UK	Germany	IARC
4-Nitroanisole				Group 2B

(g) reproductive toxicity; No data available

## 4-Nitroanisole

(h) STOT-single exposure;	No data available
(i) STOT-repeated exposure;	No data available
Target Organs	None known.
(j) aspiration hazard;	Not applicable Solid
Other Adverse Effects	The toxicological properties have not been fully investigated.
Symptoms / effects, both acute and delayed	No information available

## SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects	.
Persistence and Degradability Persistence	Soluble in water, Persistence is unlikely, based on information available.
Bioaccumulative Potential	Bioaccumulation is unlikely
Mobility in soil	The product is water soluble, and may spread in water systems Will likely be mobile in the environment due to its water solubility Highly mobile in soils
Endocrine Disruptor Information Persistent Organic Pollutant Ozone Depletion Potential	This product does not contain any known or suspected endocrine disruptors This product does not contain any known or suspected substance This product does not contain any known or suspected substance

## SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
Contaminated Packaging	Dispose of this container to hazardous or special waste collection point.
Other Information	Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

## SECTION 14. TRANSPORT INFORMATION

Road and Rail Transport

UN-No	UN3458
Proper Shipping Name	NITROANISOLES, SOLID
Hazard Class	6.1
Packing Group	III

IMDG/IMO

**SAFETY DATA SHEET****4-Nitroanisole**

**UN-No** UN3458  
**Proper Shipping Name** NITROANISOLES, SOLID  
**Hazard Class** 6.1  
**Packing Group** III

**IATA**

**UN-No** UN3458  
**Proper Shipping Name** NITROANISOLES, SOLID  
**Hazard Class** 6.1  
**Packing Group** III

**Special Precautions for User** No special precautions required

**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDSL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
4-Nitroanisole	X	-	X	X	202-825-3	X	-	X	X	X	X	KE-23338

**National Regulations****SECTION 16. OTHER INFORMATION**

**Prepared By** Health, Safety and Environmental Department  
**Creation Date** 03-Dec-2014  
**Revision Date** 27-Apr-2024  
**Revision Summary** New emergency telephone response service provider.

**Training Advice**

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

**Legend**

**CAS** - Chemical Abstracts Service

**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances

**PICCS** - Philippines Inventory of Chemicals and Chemical Substances

**IECSC** - Chinese Inventory of Existing Chemical Substances

**KECL** - Korean Existing and Evaluated Chemical Substances

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory

**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**ENCS** - Japanese Existing and New Chemical Substances

**AICS** - Australian Inventory of Chemical Substances

**NZIoC** - New Zealand Inventory of Chemicals

**WEL** - Workplace Exposure Limit

**ACGIH** - American Conference of Governmental Industrial Hygienists

**DNEL** - Derived No Effect Level

**TWA** - Time Weighted Average

**IARC** - International Agency for Research on Cancer

**PNEC** - Predicted No Effect Concentration

## 4-Nitroanisole

**RPE** - Respiratory Protective Equipment  
**LC50** - Lethal Concentration 50%  
**NOEC** - No Observed Effect Concentration  
**PBT** - Persistent, Bioaccumulative, Toxic

**LD50** - Lethal Dose 50%  
**EC50** - Effective Concentration 50%  
**POW** - Partition coefficient Octanol:Water  
**vPvB** - very Persistent, very Bioaccumulative

**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association

**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road

**OECD** - Organisation for Economic Co-operation and Development

**BCF** - Bioconcentration factor

**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code

**MARPOL** - International Convention for the Prevention of Pollution from Ships

**ATE** - Acute Toxicity Estimate

**VOC** - (Volatile Organic Compound)

**Key literature references and sources for data**

<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**