

ALFAAB20111

4,5-Diphenyl-2-mercaptooxazole

SECTION 1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

产品说明: 4,5-二苯基-2-巯基噁唑
 Product Description: 4,5-Diphenyl-2-mercaptooxazole

Cat No. : B20111
 CAS No 6670-13-9
 Molecular Formula C15 H11 N O S

Supplier Avocado Research Chemicals Ltd.
 (Part of Thermo Fisher Scientific)
 Shore Road, Heysham
 Lancashire, LA3 2XY,
 United Kingdom
 Office Tel: +44 (0) 1524 850506
 Office Fax: +44 (0) 1524 850608

Emergency Telephone Number For information **US** call: 001-800-227-6701 / **Europe** call: +32 14 57 52 11
 Emergency Number **US**:001-201-796-7100 / **Europe**: +32 14 57 52 99
CHEMTREC Tel. No. **US**:001-800-424-9300 / **Europe**:001-703-527-3887

E-mail address begel.sdsdesk@thermofisher.com

Recommended Use Laboratory chemicals.
 Uses advised against No Information available

SECTION 2. HAZARD IDENTIFICATION

Physical State
 Powder Solid

Appearance
 Light yellow

Odor
 Rotten-egg like

Emergency Overview

Harmful if swallowed. Harmful in contact with skin. Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. May cause respiratory irritation.

Classification of the substance or mixture

Acute Oral Toxicity	Category 4
Acute Dermal Toxicity	Category 4
Acute Inhalation Toxicity - Dusts and Mists	Category 4
Skin Corrosion/Irritation	Category 2
Serious Eye Damage/Eye Irritation	Category 2
Specific target organ toxicity - (single exposure)	Category 3

Label Elements



Signal Word**Warning****Hazard Statements**

H315 - Causes skin irritation

H319 - Causes serious eye irritation

H335 - May cause respiratory irritation

H302 + H312 + H332 - Harmful if swallowed, in contact with skin or if inhaled

Precautionary Statements**Prevention**

P261 - Avoid breathing dust/fume/gas/mist/vapors/spray

P264 - Wash face, hands and any exposed skin thoroughly after handling

P271 - Use only outdoors or in a well-ventilated area

P280 - Wear protective gloves/protective clothing/eye protection/face protection

P270 - Do not eat, drink or smoke when using this product

Response

P304 + P340 - IF INHALED: Remove person to fresh air and keep comfortable for breathing

P302 + P352 - IF ON SKIN: Wash with plenty of soap and water

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P312 - Call a POISON CENTER or doctor if you feel unwell

P330 - Rinse mouth

P362 + P364 - Take off contaminated clothing and wash it before reuse

Storage

P403 + P233 - Store in a well-ventilated place. Keep container tightly closed

Disposal

P501 - Dispose of contents/ container to an approved waste disposal plant

Physical and Chemical Hazards

None identified.

Health Hazards

Harmful if swallowed. Harmful in contact with skin. Causes skin irritation. Causes serious eye irritation. Harmful if inhaled. May cause respiratory irritation.

Environmental hazards

Contains no substances known to be hazardous to the environment or not degradable in waste water treatment plants.

This product does not contain any known or suspected endocrine disruptors.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS No	Weight %
4,5-Diphenyl-4-oxazoline-2-thione	6670-13-9	98

SECTION 4. FIRST AID MEASURES**Eye Contact**

Immediate medical attention is required. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes.

Skin Contact

Wash off immediately with soap and plenty of water while removing all contaminated clothes and shoes. Get medical attention. Take off contaminated clothing and shoes immediately.

Inhalation

Remove from exposure, lie down. Remove to fresh air. If not breathing, give artificial respiration. Immediate medical attention is required.

Ingestion

Never give anything by mouth to an unconscious person. Drink plenty of water. Call a physician immediately. If possible drink milk afterwards.

Most important symptoms and effects

No information available.

Self-Protection of the First Aider

Ensure that medical personnel are aware of the material(s) involved, take precautions to protect themselves and prevent spread of contamination.

Notes to Physician

Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Extinguishing media which must not be used for safety reasons

No information available.

Specific Hazards Arising from the Chemical

Thermal decomposition can lead to release of irritating gases and vapors.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear. Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 6. ACCIDENTAL RELEASE MEASURES**Personal Precautions**

Ensure adequate ventilation.

Environmental Precautions

See Section 12 for additional Ecological Information.

Methods for Containment and Clean Up

Sweep up and shovel into suitable containers for disposal.

Refer to protective measures listed in Sections 8 and 13.

SECTION 7. HANDLING AND STORAGE**Handling**

Avoid contact with skin and eyes. Avoid contact with skin and clothing. Remove and wash contaminated clothing and gloves, including the inside, before re-use. Avoid breathing vapors or mists. Do not ingest. If swallowed then seek immediate medical assistance. Wash thoroughly after handling.

Storage

Keep in a dry, cool and well-ventilated place. Keep container tightly closed.

Specific Use(s)

Use in laboratories

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION**Control Parameters**

4,5-Diphenyl-2-mercaptooxazole

Monitoring methods

BS EN 14042:2003 Title Identifier: Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents. MDHS14/3 General methods for sampling and gravimetric analysis of respirable and inhalable dust

Exposure Controls**Engineering Measures**

Ventilation systems. Ensure that eyewash stations and safety showers are close to the workstation location. Wherever possible, engineering control measures such as the isolation or enclosure of the process, the introduction of process or equipment changes to minimise release or contact, and the use of properly designed ventilation systems, should be adopted to control hazardous materials at source.

Personal protective equipment

Eye Protection Goggles (European standard - EN 166)

Hand Protection Protective gloves

Glove material	Breakthrough time	Glove thickness	EU standard	Glove comments
Nitrile rubber Neoprene Natural rubber PVC	See manufacturers recommendations	-	EN 374	(minimum requirement)

Inspect gloves before use.

Please observe the instructions regarding permeability and breakthrough time which are provided by the supplier of the gloves. (Refer to manufacturer/supplier for information)

Ensure gloves are suitable for the task: Chemical compatability, Dexterity, Operational conditions, User susceptibility, e.g. sensitisation effects, also take into consideration the specific local conditions under which the product is used, such as the danger of cuts, abrasion.

Remove gloves with care avoiding skin contamination.

Skin and body protection Wear appropriate protective gloves and clothing to prevent skin exposure

Respiratory Protection When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.
To protect the wearer, respiratory protective equipment must be the correct fit and be used and maintained properly

Large scale/emergency use Use a NIOSH/MSHA or European Standard EN 136 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced
Recommended Filter type: Particulates filter conforming to EN 143

Small scale/Laboratory use Use a NIOSH/MSHA or European Standard EN 149:2001 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
Recommended half mask:- Particle filtering: EN149:2001
When RPE is used a face piece Fit Test should be conducted

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

Environmental exposure controls No information available.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance Light yellow
Physical State Powder Solid

Odor Rotten-egg like
Odor Threshold No data available
pH No information available

4,5-Diphenyl-2-mercaptooxazole

Melting Point/Range	256 - 260 °C / 492.8 - 500 °F	
Softening Point	No data available	
Boiling Point/Range	No information available	
Flash Point	No information available	Method - No information available
Evaporation Rate	Not applicable	Solid
Flammability (solid,gas)	No information available	
Explosion Limits	No data available	
Vapor Pressure	No data available	
Vapor Density	Not applicable	Solid
Specific Gravity / Density	No data available	
Bulk Density	No data available	
Water Solubility	No information available	
Solubility in other solvents	No information available	
Partition Coefficient (n-octanol/water)		
Autoignition Temperature	No data available	
Decomposition Temperature	No data available	
Viscosity	Not applicable	Solid
Explosive Properties	No information available	
Oxidizing Properties	No information available	
Molecular Formula	C15 H11 N O S	
Molecular Weight	253.32	

SECTION 10. STABILITY AND REACTIVITY

Stability	Stable under normal conditions.
Hazardous Reactions	No information available.
Hazardous Polymerization	No information available.
Conditions to Avoid	None known.
Materials to avoid	Oxidizing agent.

Hazardous Decomposition Products Thermal decomposition can lead to release of irritating gases and vapors.

SECTION 11. TOXICOLOGICAL INFORMATION

Product Information

(a) acute toxicity;	
(b) skin corrosion/irritation;	Category 2
(c) serious eye damage/irritation;	Category 2
(d) respiratory or skin sensitization;	
Respiratory	No data available
Skin	No data available
(e) germ cell mutagenicity;	No data available
(f) carcinogenicity;	No data available
	There are no known carcinogenic chemicals in this product

SAFETY DATA SHEET
4,5-Diphenyl-2-mercaptooxazole

(g) reproductive toxicity;	No data available
(h) STOT-single exposure;	Category 3
Results / Target organs	Respiratory system
(i) STOT-repeated exposure;	No data available
Target Organs	No information available.
(j) aspiration hazard;	Not applicable Solid
Symptoms / effects, both acute and delayed	No information available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity effects	Contains no substances known to be hazardous to the environment or that are not degradable in waste water treatment plants.
Persistence and Degradability	No information available
Bioaccumulative Potential	No information available
Mobility in soil	No information available
Endocrine Disruptor Information Persistent Organic Pollutant Ozone Depletion Potential	This product does not contain any known or suspected endocrine disruptors This product does not contain any known or suspected substance This product does not contain any known or suspected substance

SECTION 13. DISPOSAL CONSIDERATIONS

Waste from Residues/Unused Products	Waste is classified as hazardous. Dispose of in accordance with the European Directives on waste and hazardous waste. Dispose of in accordance with local regulations.
Contaminated Packaging	Dispose of this container to hazardous or special waste collection point.
Other Information	Waste codes should be assigned by the user based on the application for which the product was used. Do not empty into drains.

SECTION 14. TRANSPORT INFORMATION

<u>Road and Rail Transport</u>	Not Regulated
<u>IMDG/IMO</u>	Not regulated

4,5-Diphenyl-2-mercaptooxazole

IATA Not regulated**Special Precautions for User** No special precautions required**SECTION 15. REGULATORY INFORMATION****International Inventories**

X = listed, China (IECSC), Europe (EINECS/ELINCS/NLP), U.S.A. (TSCA), Canada (DSL/NDL), Philippines (PICCS), Japan (ENCS), Japan (ISHL), Australia (AICS), Korea (KECL).

Component	The Inventory of Hazardous Chemicals (2015 Edition)	List of dangerous goods GB 12268 - 2012	TCSI	IECSC	EINECS	TSCA	DSL	PICCS	ENCS	ISHL	AICS	KECL
4,5-Diphenyl-4-oxazolone-2-thione	-	-	X	-	229-707-4	-	-	-	-		-	-

National Regulations**SECTION 16. OTHER INFORMATION**

Prepared By Health, Safety and Environmental Department
Revision Date 27-Apr-2024
Revision Summary New emergency telephone response service provider.

Training Advice

Chemical hazard awareness training, incorporating labelling, Safety Data Sheets (SDS), Personal Protective Equipment (PPE) and hygiene.

Use of personal protective equipment, covering appropriate selection, compatibility, breakthrough thresholds, care, maintenance, fit and standards.

First aid for chemical exposure, including the use of eye wash and safety showers.

Legend**CAS** - Chemical Abstracts Service**EINECS/ELINCS** - European Inventory of Existing Commercial Chemical Substances/EU List of Notified Chemical Substances**PICCS** - Philippines Inventory of Chemicals and Chemical Substances**IECSC** - Chinese Inventory of Existing Chemical Substances**KECL** - Korean Existing and Evaluated Chemical Substances**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory**DSL/NDL** - Canadian Domestic Substances List/Non-Domestic Substances List**ENCS** - Japanese Existing and New Chemical Substances**AICS** - Australian Inventory of Chemical Substances**NZIoC** - New Zealand Inventory of Chemicals**WEL** - Workplace Exposure Limit**ACGIH** - American Conference of Governmental Industrial Hygienists**DNEL** - Derived No Effect Level**RPE** - Respiratory Protective Equipment**LC50** - Lethal Concentration 50%**NOEC** - No Observed Effect Concentration**PBT** - Persistent, Bioaccumulative, Toxic**TWA** - Time Weighted Average**IARC** - International Agency for Research on Cancer**PNEC** - Predicted No Effect Concentration**LD50** - Lethal Dose 50%**EC50** - Effective Concentration 50%**POW** - Partition coefficient Octanol:Water**vPvB** - very Persistent, very Bioaccumulative**ICAO/IATA** - International Civil Aviation Organization/International Air Transport Association**ADR** - European Agreement Concerning the International Carriage of Dangerous Goods by Road**OECD** - Organisation for Economic Co-operation and Development**IMO/IMDG** - International Maritime Organization/International Maritime Dangerous Goods Code**MARPOL** - International Convention for the Prevention of Pollution from Ships**ATE** - Acute Toxicity Estimate

4,5-Diphenyl-2-mercaptooxazole

BCF - Bioconcentration factor**VOC** - (Volatile Organic Compound)**Key literature references and sources for data**<https://echa.europa.eu/information-on-chemicals>

Suppliers safety data sheet, Chemadvisor - LOLI, Merck index, RTECS

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet